

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333647-927

Luminaire Tested: **S125RDIW-S375D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333647-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3255.5 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	24	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	1.4
10°-20°	127.4	3.9
20°-30°	184.7	5.7
30°-40°	210.5	6.5
40°-50°	205.2	6.3
50°-60°	172.7	5.3
60°-70°	121.1	3.7
70°-80°	62.2	1.9
80°-90°	17.4	0.5
90°-100°	50.6	1.6
100°-110°	149.5	4.6
110°-120°	253.2	7.8
120°-130°	333.2	10.2
130°-140°	373.3	11.5
140°-150°	365.9	11.2
150°-160°	307.3	9.4
160°-170°	204.3	6.3
170°-180°	71.5	2.2
0°-30°	357.7	11.0
0°-40°	568.2	17.5
0°-60°	946.1	29.1
0°-90°	1146.8	35.2
90°-120°	453.2	13.9
90°-150°	1525.6	46.9
90°-180°	2109.0	64.8
0°-180°	3255.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	5	9	12	14	3
95°	38	40	45	49	50	41
105°	134	137	140	144	146	143
115°	254	256	257	256	256	251
125°	370	373	374	373	372	331
135°	481	484	485	485	483	371
145°	583	585	587	587	585	364
155°	667	667	668	670	667	307
165°	725	724	724	726	723	204
175°	754	752	752	755	751	72
180°	756	756	756	756	756	



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.9	6.6	6.3	6.1	5.9	5.8	5.9	6.0	6.2	6.3	6.4
90°	0.6	1.7	2.7	3.7	4.8	5.8	6.7	7.6	8.5	9.4	10.1
92.5°	14.3	15.0	15.7	16.4	17.2	18.1	19.3	20.4	21.5	22.6	23.4
95°	38.3	38.5	38.7	39.0	39.3	40.1	41.4	42.7	44.0	45.3	46.2
97.5°	63.5	63.6	63.7	63.8	63.9	64.9	66.7	68.5	70.3	72.1	73.0
100°	82.3	82.3	82.3	82.3	82.3	83.2	84.8	86.6	88.2	90.0	91.2
102.5°	102.6	103.1	103.6	104.1	104.6	105.4	106.2	107.1	107.9	108.8	110.1
105°	134.1	134.8	135.4	136.0	136.7	137.4	138.2	138.9	139.7	140.5	141.3
107.5°	168.9	169.5	170.2	170.9	171.5	172.1	172.8	173.3	174.0	174.5	174.9
110°	192.9	193.5	194.2	194.9	195.5	196.0	196.4	196.8	197.2	197.6	198.0



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.4	217.7	218.0	218.4	218.7	219.1	219.6	220.1	220.6	221.1	221.3
115°	253.5	254.0	254.5	255.0	255.6	256.0	256.2	256.4	256.7	257.0	256.8
117.5°	289.7	289.9	290.2	290.4	290.7	290.9	291.1	291.4	291.6	291.8	291.9
120°	312.3	312.9	313.5	314.3	314.9	315.3	315.4	315.5	315.7	315.8	315.8
122.5°	336.8	337.0	337.2	337.5	337.7	337.9	338.3	338.7	339.0	339.3	339.2
125°	369.9	370.7	371.5	372.2	373.0	373.5	373.6	373.8	373.9	374.0	373.8
127.5°	405.2	405.6	406.1	406.5	406.9	407.3	407.4	407.6	407.7	407.9	407.7
130°	426.4	427.0	427.7	428.3	429.0	429.4	429.7	429.9	430.2	430.5	430.3
132.5°	447.5	448.6	449.6	450.8	451.8	452.3	452.3	452.2	452.2	452.1	452.0
135°	481.0	481.8	482.6	483.4	484.2	484.7	484.7	484.9	485.1	485.1	485.1
137.5°	512.5	513.3	514.0	514.8	515.6	516.1	516.4	516.7	517.0	517.3	517.5
140°	532.8	533.5	534.1	534.7	535.4	535.9	536.3	536.7	537.1	537.5	537.7
142.5°	553.0	553.6	554.1	554.7	555.2	555.7	556.3	556.7	557.2	557.7	557.9
145°	582.8	583.3	583.8	584.3	584.9	585.3	585.7	586.1	586.5	586.9	586.9
147.5°	610.3	610.6	610.9	611.2	611.5	611.7	612.0	612.4	612.7	613.0	613.3
150°	628.7	628.5	628.4	628.3	628.1	628.4	628.8	629.4	629.9	630.4	630.4
152.5°	643.7	643.9	644.0	644.3	644.4	644.6	644.8	645.1	645.2	645.5	645.8
155°	666.9	666.9	666.9	666.9	666.9	666.9	667.1	667.2	667.3	667.5	668.0
157.5°	687.6	687.3	687.0	686.7	686.4	686.3	686.5	686.6	686.7	686.9	687.4
160°	699.8	699.4	699.0	698.6	698.2	698.1	698.2	698.4	698.5	698.6	699.2
162.5°	710.7	710.3	710.0	709.8	709.5	709.3	709.4	709.4	709.4	709.5	710.1
165°	725.1	724.8	724.6	724.3	724.1	724.0	724.1	724.2	724.4	724.5	725.0
167.5°	737.4	736.8	736.3	735.8	735.2	735.0	735.0	735.0	735.0	735.0	735.8
170°	743.9	743.4	742.8	742.4	741.8	741.6	741.6	741.6	741.6	741.6	742.4
172.5°	748.6	748.1	747.6	747.0	746.6	746.2	746.2	746.2	746.2	746.2	747.0
175°	753.9	753.4	752.9	752.3	751.8	751.5	751.5	751.5	751.5	751.5	752.3
177.5°	756.6	756.2	755.7	755.3	754.9	754.7	754.6	754.5	754.4	754.2	754.9
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	6.6	6.7	6.8	6.9	6.9	6.9	6.9	6.9
90°	10.7	11.4	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	24.3	25.2	26.1	26.6	26.9	27.2	27.5	27.7
95°	47.1	48.0	49.0	49.5	49.8	50.1	50.3	50.5
97.5°	73.8	74.7	75.6	76.0	76.2	76.4	76.5	76.7
100°	92.3	93.5	94.7	95.4	95.7	95.9	96.2	96.4
102.5°	111.4	112.6	113.9	114.7	115.1	115.5	115.8	116.2
105°	142.1	142.9	143.7	144.3	144.7	145.0	145.4	145.8
107.5°	175.3	175.7	176.1	176.3	176.3	176.3	176.2	176.2
110°	198.4	198.8	199.2	199.3	199.2	199.0	198.9	198.8



TEST NUMBER: P333647-927

CATALOG NUMBER: S125RDIW-S375D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.5	221.7	221.8	221.8	221.6	221.3	221.1	220.9
115°	256.7	256.6	256.4	256.4	256.2	256.1	256.0	255.8
117.5°	292.0	292.1	292.2	292.0	291.5	291.0	290.4	289.9
120°	315.8	315.8	315.8	315.5	315.1	314.5	313.9	313.5
122.5°	339.1	339.0	338.9	338.7	338.2	337.8	337.4	337.0
125°	373.5	373.2	373.0	372.8	372.6	372.5	372.4	372.2
127.5°	407.7	407.5	407.3	407.2	406.9	406.6	406.4	406.2
130°	430.2	430.1	429.9	429.8	429.5	429.2	429.0	428.7
132.5°	451.9	451.7	451.6	451.3	451.0	450.6	450.3	449.9
135°	485.1	485.1	485.1	484.9	484.3	483.9	483.3	482.8
137.5°	517.6	517.8	517.9	517.6	517.0	516.3	515.7	515.0
140°	538.1	538.3	538.5	538.4	537.7	537.0	536.4	535.8
142.5°	558.0	558.2	558.3	558.1	557.5	556.8	556.1	555.5
145°	586.9	586.9	586.9	586.7	586.3	585.9	585.5	585.1
147.5°	613.6	613.9	614.3	613.9	613.1	612.2	611.3	610.5
150°	630.4	630.4	630.4	630.3	630.0	629.8	629.5	629.2
152.5°	646.1	646.4	646.7	646.7	646.2	645.7	645.2	644.8
155°	668.5	669.0	669.6	669.5	668.8	668.2	667.5	666.9
157.5°	687.9	688.4	689.0	688.8	687.9	687.1	686.2	685.3
160°	699.7	700.2	700.7	700.7	700.0	699.3	698.7	698.1
162.5°	710.7	711.3	711.9	711.9	711.1	710.3	709.6	708.8
165°	725.6	726.1	726.6	726.4	725.7	724.9	724.1	723.3
167.5°	736.6	737.4	738.1	738.1	737.3	736.5	735.7	734.8
170°	743.1	743.9	744.7	744.7	743.7	742.8	741.9	741.0
172.5°	747.8	748.6	749.4	749.4	748.6	747.7	746.9	746.2
175°	753.1	753.9	754.7	754.6	753.7	752.8	751.9	751.0
177.5°	755.5	756.1	756.8	756.7	756.0	755.3	754.6	753.8
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7

(END OF REPORT)