

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333049-840

Luminaire Tested: **S124RDIW-S575D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333049-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7793.5 lumens
Efficiency: N/A
Efficacy: 144.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	66	61	56	53	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	1.2
10°-20°	268.8	3.4
20°-30°	388.2	5.0
30°-40°	440.0	5.6
40°-50°	424.9	5.5
50°-60°	353.4	4.5
60°-70°	244.0	3.1
70°-80°	123.7	1.6
80°-90°	36.8	0.5
90°-100°	59.9	0.8
100°-110°	381.9	4.9
110°-120°	730.6	9.4
120°-130°	927.4	11.9
130°-140°	992.3	12.7
140°-150°	927.9	11.9
150°-160°	748.3	9.6
160°-170°	482.6	6.2
170°-180°	166.3	2.1
0°-30°	753.5	9.7
0°-40°	1193.5	15.3
0°-60°	1971.8	25.3
0°-90°	2376.2	30.5
90°-120°	1172.4	15.0
90°-150°	4020.0	51.6
90°-180°	5417.0	69.5
0°-180°	7793.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	4	18	29	36	39	5
95°	72	30	29	36	38	93
105°	394	402	409	417	373	413
115°	736	740	739	741	741	724
125°	1035	1040	1037	1041	1043	924
135°	1284	1283	1288	1290	1293	989
145°	1480	1484	1484	1485	1488	925
155°	1623	1624	1620	1625	1622	748
165°	1712	1706	1706	1715	1704	484
175°	1751	1744	1745	1755	1741	167
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	15.2	14.7	14.3	13.8	13.3	13.2	13.6	13.9	14.2	14.5	14.7
90°	3.9	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6
92.5°	16.5	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5
95°	72.0	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6
97.5°	153.0	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7
100°	214.8	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7
102.5°	284.0	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3
105°	394.3	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3
107.5°	496.7	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8
110°	565.8	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	632.9	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6
115°	736.1	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3
117.5°	829.1	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2
120°	892.0	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6
122.5°	950.7	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0
125°	1034.8	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2
127.5°	1114.4	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6
130°	1165.8	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3
132.5°	1212.9	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5
135°	1283.6	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2
137.5°	1346.3	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2
140°	1387.2	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2
142.5°	1423.8	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8
145°	1480.2	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4
147.5°	1524.9	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2
150°	1557.4	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4
152.5°	1584.7	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0
155°	1623.0	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4
157.5°	1655.2	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4
160°	1674.0	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5
162.5°	1690.7	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2
165°	1712.0	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8
167.5°	1728.8	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7
170°	1738.2	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9
172.5°	1744.4	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2
175°	1751.3	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4
177.5°	1754.4	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	14.9	15.1	15.5	15.7	15.9	16.2	16.4	16.7
90°	32.3	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	31.3	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	32.3	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	34.9	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	47.8	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	171.0	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	413.9	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	512.1	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	578.9	579.4	580.0	580.7	581.6	582.5	583.3	584.2



TEST NUMBER: P333049-840

CATALOG NUMBER: S124RDIW-S575D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	643.4	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	739.9	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	837.0	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.3	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1039.2	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.5	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.5	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1220.8	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1288.8	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1353.8	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1394.1	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1431.4	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.6	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.5	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.4	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1622.7	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1688.0	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1710.1	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1726.3	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1736.3	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1742.5	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1750.0	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1752.9	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)