

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333663-927

Luminaire Tested: **S125RDIW-S610D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333663-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D470U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3171.1 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	89	89	89		76	76	76		65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73		67	66	64		58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61		60	57	54		51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52		53	49	46		45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44		47	43	39		41	38	35	31
5	70	59	51	45	66	55	48	42	49	43	38		43	38	34		37	33	30	27
6	65	53	45	39	61	50	42	37	44	38	34		39	34	30		33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30		35	30	27		31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27		32	28	24		28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24		30	25	22		26	22	20	18
10	49	37	29	25	46	35	28	24	31	25	22		28	23	20		24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	2.4
10°-20°	209.4	6.6
20°-30°	303.7	9.6
30°-40°	346.1	10.9
40°-50°	337.4	10.6
50°-60°	284.0	9.0
60°-70°	199.1	6.3
70°-80°	102.3	3.2
80°-90°	26.9	0.8
90°-100°	30.9	1.0
100°-110°	91.2	2.9
110°-120°	154.6	4.9
120°-130°	203.4	6.4
130°-140°	227.9	7.2
140°-150°	223.4	7.0
150°-160°	187.6	5.9
160°-170°	124.7	3.9
170°-180°	43.6	1.4
0°-30°	588.0	18.5
0°-40°	934.1	29.5
0°-60°	1555.4	49.0
0°-90°	1883.7	59.4
90°-120°	276.7	8.7
90°-150°	931.5	29.4
90°-180°	1287.0	40.6
0°-180°	3171.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	0	3	6	8	9	3
95°	23	24	28	30	31	25
105°	82	84	86	88	89	87
115°	155	156	157	157	156	153
125°	226	228	228	228	227	202
135°	294	296	296	296	295	226
145°	356	357	358	358	357	222
155°	407	407	408	409	407	187
165°	443	442	442	444	442	125
175°	460	459	459	461	458	44
180°	461	461	461	461	461	



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.5	9.9	9.3	8.6	8.3	8.4	8.4	8.4	8.4	8.5
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.8	6.2
92.5°	8.7	9.1	9.6	10.1	10.5	11.0	11.7	12.4	13.1	13.8	14.3
95°	23.4	23.5	23.7	23.8	24.0	24.5	25.3	26.1	26.9	27.6	28.2
97.5°	38.7	38.8	38.9	39.0	39.1	39.6	40.7	41.8	42.9	44.0	44.5
100°	50.3	50.3	50.3	50.3	50.3	50.8	51.8	52.8	53.9	54.9	55.7
102.5°	62.6	62.9	63.3	63.6	63.9	64.3	64.9	65.4	65.9	66.4	67.2
105°	81.8	82.2	82.6	83.0	83.5	83.9	84.4	84.8	85.3	85.8	86.3
107.5°	103.1	103.5	103.9	104.3	104.7	105.1	105.4	105.8	106.2	106.5	106.8
110°	117.8	118.2	118.6	119.0	119.4	119.7	119.9	120.2	120.4	120.6	120.9



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.7	132.9	133.1	133.3	133.6	133.8	134.1	134.4	134.7	135.0	135.1
115°	154.7	155.0	155.4	155.7	156.1	156.3	156.5	156.6	156.8	156.9	156.9
117.5°	176.9	177.0	177.1	177.3	177.4	177.6	177.8	177.8	178.0	178.2	178.2
120°	190.7	191.1	191.5	191.9	192.3	192.5	192.6	192.7	192.7	192.8	192.8
122.5°	205.6	205.7	205.9	206.0	206.1	206.4	206.5	206.8	207.0	207.2	207.1
125°	225.9	226.3	226.8	227.3	227.8	228.1	228.1	228.2	228.3	228.4	228.2
127.5°	247.4	247.6	248.0	248.2	248.5	248.7	248.7	248.8	248.9	249.1	249.0
130°	260.3	260.7	261.1	261.5	261.9	262.2	262.4	262.5	262.7	262.8	262.8
132.5°	273.2	273.9	274.6	275.2	275.8	276.2	276.2	276.1	276.1	276.0	275.9
135°	293.7	294.2	294.7	295.2	295.6	295.9	296.0	296.0	296.1	296.2	296.2
137.5°	312.9	313.4	313.9	314.3	314.8	315.1	315.3	315.4	315.6	315.8	315.9
140°	325.3	325.7	326.1	326.5	326.9	327.3	327.5	327.7	328.0	328.2	328.4
142.5°	337.6	337.9	338.3	338.7	339.0	339.3	339.6	339.9	340.2	340.6	340.6
145°	355.8	356.2	356.5	356.8	357.1	357.4	357.6	357.8	358.1	358.3	358.3
147.5°	372.6	372.8	373.0	373.1	373.4	373.5	373.7	373.9	374.1	374.3	374.5
150°	383.8	383.7	383.7	383.6	383.5	383.7	384.0	384.3	384.6	384.9	384.9
152.5°	393.0	393.2	393.2	393.3	393.5	393.6	393.7	393.9	394.0	394.1	394.3
155°	407.2	407.2	407.2	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.8
157.5°	419.8	419.6	419.5	419.3	419.1	419.1	419.1	419.2	419.3	419.4	419.7
160°	427.3	427.1	426.7	426.5	426.3	426.2	426.3	426.4	426.4	426.5	426.9
162.5°	433.9	433.7	433.6	433.3	433.2	433.1	433.1	433.1	433.2	433.2	433.6
165°	442.7	442.5	442.4	442.2	442.0	442.0	442.1	442.2	442.3	442.4	442.7
167.5°	450.2	449.9	449.6	449.2	448.9	448.8	448.8	448.8	448.8	448.8	449.2
170°	454.2	453.8	453.5	453.2	452.9	452.7	452.7	452.7	452.7	452.7	453.2
172.5°	457.1	456.8	456.5	456.1	455.8	455.7	455.7	455.7	455.7	455.7	456.1
175°	460.3	459.9	459.6	459.3	459.0	458.8	458.8	458.8	458.8	458.8	459.3
177.5°	461.9	461.7	461.4	461.2	460.9	460.7	460.7	460.7	460.6	460.5	460.9
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	8.6	8.6	8.7	8.7	8.6	8.6	8.6	8.5
90°	6.6	7.0	7.4	7.7	7.9	8.2	8.4	8.6
92.5°	14.8	15.4	15.9	16.2	16.4	16.6	16.8	17.0
95°	28.8	29.3	29.9	30.3	30.4	30.6	30.7	30.9
97.5°	45.1	45.6	46.1	46.4	46.5	46.7	46.7	46.8
100°	56.4	57.1	57.8	58.2	58.4	58.5	58.7	58.9
102.5°	68.0	68.8	69.6	70.0	70.3	70.5	70.7	71.0
105°	86.7	87.2	87.7	88.1	88.3	88.6	88.8	89.0
107.5°	107.0	107.3	107.5	107.7	107.7	107.6	107.6	107.6
110°	121.1	121.4	121.6	121.7	121.6	121.5	121.4	121.4



TEST NUMBER: P333663-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.2	135.3	135.5	135.5	135.3	135.1	135.0	134.8
115°	156.8	156.7	156.6	156.5	156.5	156.4	156.3	156.2
117.5°	178.3	178.3	178.4	178.3	178.0	177.7	177.3	177.0
120°	192.8	192.8	192.8	192.7	192.3	192.0	191.7	191.4
122.5°	207.1	207.0	206.9	206.8	206.5	206.3	206.0	205.7
125°	228.1	227.9	227.8	227.6	227.5	227.4	227.4	227.3
127.5°	248.9	248.8	248.7	248.6	248.4	248.3	248.1	248.0
130°	262.7	262.6	262.5	262.4	262.2	262.1	261.9	261.7
132.5°	275.8	275.8	275.7	275.6	275.4	275.1	274.9	274.6
135°	296.2	296.2	296.2	296.0	295.7	295.4	295.1	294.8
137.5°	316.0	316.1	316.2	316.1	315.7	315.3	314.8	314.4
140°	328.5	328.7	328.8	328.7	328.3	327.9	327.5	327.1
142.5°	340.7	340.8	340.9	340.7	340.3	339.9	339.5	339.1
145°	358.3	358.3	358.3	358.2	358.0	357.7	357.5	357.3
147.5°	374.6	374.9	375.0	374.9	374.3	373.8	373.2	372.7
150°	384.9	384.9	384.9	384.8	384.7	384.5	384.4	384.2
152.5°	394.5	394.7	394.8	394.8	394.5	394.3	394.0	393.6
155°	408.1	408.4	408.8	408.8	408.4	408.0	407.6	407.2
157.5°	420.0	420.3	420.6	420.6	420.0	419.5	419.0	418.4
160°	427.2	427.5	427.9	427.8	427.4	427.0	426.6	426.2
162.5°	434.0	434.3	434.7	434.7	434.2	433.7	433.2	432.8
165°	443.0	443.3	443.6	443.5	443.1	442.6	442.1	441.6
167.5°	449.7	450.2	450.7	450.7	450.1	449.6	449.2	448.7
170°	453.7	454.2	454.7	454.6	454.1	453.5	453.0	452.4
172.5°	456.6	457.1	457.6	457.6	457.0	456.5	456.1	455.6
175°	459.8	460.3	460.8	460.7	460.2	459.6	459.1	458.5
177.5°	461.3	461.7	462.1	462.0	461.6	461.1	460.7	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)