

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333691-927

Luminaire Tested: **S125RDIW-S850D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333691-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1050U927-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5453.9 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.4	1.9
10°-20°	286.2	5.2
20°-30°	415.1	7.6
30°-40°	473.1	8.7
40°-50°	461.1	8.5
50°-60°	388.2	7.1
60°-70°	272.1	5.0
70°-80°	139.9	2.6
80°-90°	37.6	0.7
90°-100°	69.1	1.3
100°-110°	204.0	3.7
110°-120°	345.5	6.3
120°-130°	454.7	8.3
130°-140°	509.6	9.3
140°-150°	499.4	9.2
150°-160°	419.5	7.7
160°-170°	278.8	5.1
170°-180°	97.6	1.8
0°-30°	803.8	14.7
0°-40°	1276.8	23.4
0°-60°	2126.1	39.0
0°-90°	2575.7	47.2
90°-120°	618.6	11.3
90°-150°	2082.3	38.2
90°-180°	2878.0	52.8
0°-180°	5453.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	7	13	17	19	5
95°	52	54	62	67	69	56
105°	183	187	192	196	199	195
115°	346	349	351	350	349	342
125°	505	509	510	509	508	452
135°	657	661	662	662	659	506
145°	795	799	801	801	799	497
155°	910	910	911	914	910	419
165°	990	988	989	992	987	279
175°	1029	1026	1026	1030	1025	98
180°	1031	1031	1031	1031	1031	



TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.3	14.6	13.8	13.1	12.4	12.0	12.1	12.2	12.4	12.4	12.6
90°	0.8	2.2	3.6	5.1	6.5	7.8	9.1	10.4	11.6	12.8	13.7
92.5°	19.4	20.4	21.4	22.4	23.4	24.7	26.2	27.7	29.3	30.8	32.0
95°	52.2	52.5	52.9	53.2	53.6	54.7	56.5	58.2	60.0	61.8	63.1
97.5°	86.7	86.8	87.0	87.1	87.3	88.6	91.0	93.5	95.9	98.4	99.6
100°	112.4	112.4	112.4	112.4	112.4	113.5	115.8	118.2	120.5	122.8	124.5
102.5°	140.0	140.7	141.4	142.1	142.8	143.8	145.0	146.2	147.3	148.5	150.3
105°	183.0	183.9	184.8	185.7	186.6	187.6	188.6	189.7	190.8	191.9	192.9
107.5°	230.5	231.4	232.3	233.2	234.1	235.0	235.8	236.6	237.4	238.2	238.8
110°	263.2	264.2	265.1	265.9	266.9	267.6	268.1	268.6	269.2	269.7	270.2



TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	296.7	297.1	297.6	298.1	298.5	299.1	299.8	300.5	301.1	301.8	302.1
115°	345.9	346.7	347.4	348.1	348.8	349.4	349.7	350.1	350.4	350.8	350.6
117.5°	395.4	395.7	396.0	396.3	396.7	397.0	397.4	397.7	398.0	398.3	398.5
120°	426.2	427.1	428.0	428.9	429.8	430.3	430.5	430.7	430.9	431.0	431.0
122.5°	459.6	459.9	460.3	460.6	460.9	461.3	461.8	462.2	462.7	463.2	463.0
125°	504.9	506.0	507.0	508.1	509.1	509.8	510.0	510.2	510.3	510.5	510.2
127.5°	553.0	553.7	554.3	554.8	555.5	555.9	556.1	556.3	556.5	556.7	556.6
130°	581.9	582.8	583.8	584.6	585.5	586.1	586.5	586.8	587.2	587.6	587.4
132.5°	610.9	612.3	613.8	615.2	616.7	617.4	617.3	617.3	617.2	617.1	617.0
135°	656.6	657.7	658.7	659.8	660.9	661.5	661.7	661.9	662.0	662.2	662.2
137.5°	699.7	700.7	701.7	702.7	703.8	704.5	704.9	705.3	705.7	706.1	706.2
140°	727.2	728.1	729.0	729.9	730.8	731.5	732.1	732.6	733.1	733.6	734.0
142.5°	754.9	755.6	756.4	757.1	757.9	758.6	759.2	759.9	760.6	761.3	761.4
145°	795.4	796.1	796.9	797.6	798.3	798.9	799.5	800.0	800.6	801.1	801.1
147.5°	833.1	833.5	833.9	834.2	834.6	835.0	835.4	835.8	836.3	836.7	837.2
150°	858.1	857.9	857.7	857.5	857.4	857.6	858.3	859.0	859.8	860.5	860.5
152.5°	878.6	878.8	879.1	879.4	879.6	879.9	880.2	880.4	880.7	881.1	881.5
155°	910.2	910.2	910.2	910.2	910.2	910.3	910.5	910.7	910.9	911.1	911.8
157.5°	938.5	938.1	937.7	937.3	936.9	936.8	937.0	937.2	937.4	937.5	938.3
160°	955.2	954.7	954.1	953.6	953.1	952.9	953.1	953.2	953.4	953.6	954.3
162.5°	969.9	969.6	969.2	968.8	968.4	968.2	968.3	968.3	968.4	968.4	969.2
165°	989.8	989.4	989.0	988.6	988.2	988.2	988.4	988.6	988.7	988.9	989.6
167.5°	1006.4	1005.7	1005.0	1004.2	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.2
170°	1015.4	1014.7	1014.0	1013.3	1012.6	1012.2	1012.2	1012.2	1012.2	1012.2	1013.3
172.5°	1021.8	1021.1	1020.4	1019.7	1019.0	1018.6	1018.6	1018.6	1018.6	1018.6	1019.7
175°	1029.0	1028.3	1027.6	1026.9	1026.2	1025.8	1025.8	1025.8	1025.8	1025.8	1026.9
177.5°	1032.8	1032.1	1031.6	1031.0	1030.5	1030.1	1029.9	1029.8	1029.7	1029.5	1030.4
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4



TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	12.8	13.0	13.2	13.2	13.2	13.2	13.1	13.1
90°	14.7	15.5	16.4	17.1	17.7	18.2	18.7	19.3
92.5°	33.2	34.4	35.6	36.3	36.7	37.1	37.5	37.9
95°	64.3	65.5	66.8	67.6	68.0	68.3	68.7	69.0
97.5°	100.8	102.0	103.1	103.8	104.0	104.3	104.5	104.6
100°	126.0	127.6	129.2	130.2	130.6	130.9	131.3	131.7
102.5°	152.0	153.8	155.5	156.6	157.1	157.6	158.1	158.6
105°	194.0	195.0	196.1	196.9	197.5	198.0	198.5	199.1
107.5°	239.3	239.9	240.3	240.7	240.6	240.6	240.5	240.5
110°	270.8	271.3	271.9	272.0	271.9	271.6	271.5	271.3





TEST NUMBER: P333691-927

CATALOG NUMBER: S125RDIW-S850D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.3	302.5	302.8	302.8	302.5	302.1	301.8	301.5
115°	350.4	350.2	350.1	349.9	349.7	349.5	349.4	349.2
117.5°	398.5	398.7	398.9	398.5	397.8	397.1	396.4	395.7
120°	431.0	431.0	431.0	430.7	430.0	429.3	428.6	427.9
122.5°	462.9	462.7	462.6	462.2	461.7	461.1	460.5	459.9
125°	509.8	509.5	509.1	508.8	508.7	508.4	508.3	508.1
127.5°	556.3	556.2	556.0	555.8	555.4	555.1	554.7	554.4
130°	587.2	587.0	586.8	586.6	586.2	585.9	585.5	585.2
132.5°	616.7	616.6	616.4	616.1	615.5	615.1	614.6	614.0
135°	662.2	662.2	662.2	661.9	661.2	660.4	659.7	659.0
137.5°	706.5	706.7	706.9	706.5	705.7	704.8	703.9	703.0
140°	734.4	734.7	735.1	734.8	734.0	733.0	732.1	731.3
142.5°	761.7	761.9	762.2	761.8	760.9	760.0	759.1	758.2
145°	801.1	801.1	801.1	800.8	800.3	799.7	799.2	798.7
147.5°	837.6	838.0	838.4	838.0	836.9	835.6	834.4	833.2
150°	860.5	860.5	860.5	860.3	859.9	859.6	859.2	858.9
152.5°	881.9	882.3	882.7	882.6	882.0	881.4	880.7	880.0
155°	912.5	913.2	913.9	913.8	912.9	912.0	911.2	910.2
157.5°	939.0	939.7	940.4	940.2	939.0	937.8	936.6	935.5
160°	955.1	955.8	956.5	956.3	955.5	954.6	953.7	952.8
162.5°	970.1	970.9	971.8	971.7	970.7	969.6	968.6	967.6
165°	990.3	991.0	991.7	991.6	990.5	989.4	988.4	987.3
167.5°	1005.4	1006.4	1007.5	1007.5	1006.4	1005.3	1004.2	1003.1
170°	1014.3	1015.4	1016.4	1016.4	1015.1	1013.9	1012.6	1011.4
172.5°	1020.7	1021.8	1022.9	1022.9	1021.8	1020.6	1019.5	1018.4
175°	1027.9	1029.0	1030.2	1030.0	1028.8	1027.5	1026.3	1025.0
177.5°	1031.3	1032.1	1032.9	1032.8	1031.9	1030.9	1029.9	1028.9
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4

(END OF REPORT)