

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333063-840

Luminaire Tested: **S124RDIW-S795D1050U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333063-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1050U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7605.2 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.7
10°-20°	389.6	5.1
20°-30°	609.4	8.0
30°-40°	677.4	8.9
40°-50°	601.0	7.9
50°-60°	468.4	6.2
60°-70°	306.6	4.0
70°-80°	150.8	2.0
80°-90°	41.2	0.5
90°-100°	46.8	0.6
100°-110°	298.3	3.9
110°-120°	570.7	7.5
120°-130°	724.4	9.5
130°-140°	775.1	10.2
140°-150°	724.8	9.5
150°-160°	584.5	7.7
160°-170°	377.0	5.0
170°-180°	129.9	1.7
0°-30°	1128.1	14.8
0°-40°	1805.6	23.7
0°-60°	2875.0	37.8
0°-90°	3373.6	44.4
90°-120°	915.8	12.0
90°-150°	3140.1	41.3
90°-180°	4232.0	55.6
0°-180°	7605.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	31	3	31	3	31	14
95°	30	56	30	56	30	24
105°	292	308	292	308	292	254
115°	579	575	579	575	579	573
125°	814	808	814	808	814	725
135°	1010	1003	1010	1003	1010	777
145°	1162	1156	1162	1156	1162	726
155°	1267	1268	1267	1268	1267	584
165°	1331	1337	1331	1337	1331	376
175°	1360	1368	1360	1368	1360	129
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	15.6	15.0	15.5	15.3	15.7	15.0	15.2	15.8	14.6	14.8	14.4
90°	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2	23.8	22.5	20.7
92.5°	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4	23.0	21.7	19.9
95°	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2	23.8	22.5	22.3
97.5°	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3	27.2	27.0	52.4
100°	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3	41.2	45.0	76.4
102.5°	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5	175.2	216.9	221.0
105°	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4	321.2	319.2	318.1
107.5°	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0	399.0	398.0	396.5
110°	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1	451.7	451.2	449.9



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6	502.7	502.8	502.1
115°	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9	577.5	577.0	577.3
117.5°	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8	653.9	654.0	653.5
120°	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8	700.0
122.5°	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1	746.8	746.5	746.2
125°	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7	811.0	810.3	810.8
127.5°	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0	876.2	876.3	875.1
130°	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1	914.9	914.7	914.0
132.5°	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6	953.4	953.2	952.3
135°	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7	1006.2	1005.8	1004.9
137.5°	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5	1057.0	1056.5	1055.5
140°	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0	1088.3	1087.6	1087.2
142.5°	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1	1117.6	1117.1	1116.8
145°	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7	1159.5	1159.2	1159.2
147.5°	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3	1196.1	1195.9	1196.1
150°	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6	1219.6	1219.6	1219.8
152.5°	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0	1239.6	1239.3	1239.7
155°	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5	1266.6	1265.7	1266.4
157.5°	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8	1289.6
160°	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5	1303.7
162.5°	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5	1317.2	1315.8	1316.1
165°	1331.1	1333.2	1335.2	1337.3	1339.3	1339.5	1337.7	1335.8	1334.0	1332.2	1332.2
167.5°	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5	1346.5	1344.4	1344.6
170°	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2	1354.4	1352.6	1352.4
172.5°	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2	1359.4	1357.6	1357.4
175°	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0	1364.9	1362.9	1362.6
177.5°	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3	1367.8	1366.3	1365.9
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	14.0	13.3	13.8	13.3	13.3	14.5	15.2	15.2	14.4	13.6	12.8
90°	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0	5.6	8.1	10.6
92.5°	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9	13.0	13.1	13.3
95°	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2	48.6	40.8	33.1
97.5°	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5	124.3	129.2	134.0
100°	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8	171.9	176.0	180.1
102.5°	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9	224.8	227.8	230.9
105°	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0	309.3	310.7	312.0
107.5°	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0	388.7	389.3	390.0
110°	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0	442.7	443.3	444.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4	495.6	496.9	498.1
115°	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0	575.7	576.4	577.0
117.5°	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6	648.5	649.4	650.4
120°	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8	697.7	698.6	699.5
122.5°	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7	743.2	743.7	744.3
125°	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3	809.2	810.1	811.0
127.5°	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5	870.7	871.0	871.2
130°	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6	910.9	911.1	911.3
132.5°	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5	947.9	948.3	948.7
135°	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7	1002.5	1002.3	1002.0
137.5°	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6	1051.7	1051.8	1051.9
140°	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6	1084.0	1084.5	1084.9
142.5°	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2	1113.0	1113.8	1114.7
145°	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2	1156.9	1157.5	1158.2
147.5°	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1	1192.4	1193.8	1195.0
150°	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6	1217.5	1218.4	1219.3
152.5°	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8	1238.6	1239.3	1240.0
155°	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7	1268.0	1268.2	1268.4
157.5°	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9	1292.7	1292.6	1292.4
160°	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6	1307.0	1306.3	1305.6
162.5°	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7	1319.9	1319.0	1318.1
165°	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3	1336.2	1335.0	1333.8
167.5°	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4	1349.2	1348.1	1346.9
170°	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8	1356.3	1355.0	1353.6
172.5°	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6	1361.3	1359.9	1358.6
175°	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0	1366.7	1365.2	1363.9
177.5°	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4	1369.2	1367.9	1366.7
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	13.3	13.3	13.7	13.2	14.0	14.3	14.2	14.5	15.2	14.6	14.8
90°	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2	26.6	28.0	28.9
92.5°	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4	25.8	27.2	27.9
95°	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2	26.6	28.0	28.8
97.5°	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3	27.5	27.6	27.8
100°	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3	33.4	29.6	27.8
102.5°	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5	91.8	50.1	29.3
105°	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4	325.4	327.4	324.4
107.5°	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0	401.0	402.0	402.9
110°	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1	452.6	453.0	453.6



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6	502.5	502.4	502.8
115°	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9	578.5	578.9	579.2
117.5°	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8	653.8	653.7	653.6
120°	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7	701.3	701.7	701.7
122.5°	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1	747.3	747.6	747.5
125°	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7	812.4	813.0	813.5
127.5°	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0	875.9	875.7	875.6
130°	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1	915.4	915.6	915.7
132.5°	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6	953.9	954.1	954.1
135°	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7	1007.1	1007.6	1008.0
137.5°	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5	1058.0	1058.5	1058.7
140°	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0	1089.6	1090.4	1090.9
142.5°	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1	1118.6	1119.1	1119.3
145°	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7	1159.9	1160.1	1160.5
147.5°	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3	1196.4	1196.6	1196.8
150°	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6	1219.6	1219.6	1219.7
152.5°	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0	1240.3	1240.7	1240.8
155°	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5	1268.4	1269.3	1269.4
157.5°	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5
160°	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0
162.5°	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5	1319.9	1321.2	1321.2
165°	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8	1337.7	1339.5	1339.3
167.5°	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5	1350.5	1352.4	1352.3
170°	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2	1358.1	1359.9	1359.7
172.5°	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2	1363.0	1364.8	1364.5
175°	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0	1369.0	1371.1	1370.7
177.5°	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3	1370.7	1372.2	1371.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	15.8	15.5	15.0	15.6	15.0	15.5	15.8	14.8	14.6	15.2	14.5
90°	29.3	29.8	30.2	30.7	30.2	29.8	29.3	28.9	28.0	26.6	25.2
92.5°	28.0	28.1	28.2	28.3	28.2	28.1	28.0	27.9	27.2	25.8	24.4
95°	29.0	29.2	29.5	29.7	29.5	29.2	29.0	28.8	28.0	26.6	25.2
97.5°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	27.6	27.5	27.3
100°	28.0	28.2	28.4	28.7	28.4	28.2	28.0	27.8	29.6	33.4	37.3
102.5°	29.3	29.4	29.4	29.5	29.4	29.4	29.3	29.3	50.1	91.8	133.5
105°	316.2	308.0	299.8	291.6	299.8	308.0	316.2	324.4	327.4	325.4	323.4
107.5°	403.8	404.7	405.6	406.4	405.6	404.7	403.8	402.9	402.0	401.0	400.0
110°	454.3	454.9	455.7	456.4	455.7	454.9	454.3	453.6	453.0	452.6	452.1



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.7	504.5	505.4	506.2	505.4	504.5	503.7	502.8	502.4	502.5	502.6
115°	579.2	579.2	579.2	579.2	579.2	579.2	579.2	579.2	578.9	578.5	577.9
117.5°	653.5	653.4	653.3	653.2	653.3	653.4	653.5	653.6	653.7	653.8	653.8
120°	701.3	700.7	700.3	699.8	700.3	700.7	701.3	701.7	701.7	701.3	700.7
122.5°	747.1	746.6	746.2	745.7	746.2	746.6	747.1	747.5	747.6	747.3	747.1
125°	813.7	814.0	814.3	814.5	814.3	814.0	813.7	813.5	813.0	812.4	811.7
127.5°	875.4	875.1	874.9	874.8	874.9	875.1	875.4	875.6	875.7	875.9	876.0
130°	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.7	915.6	915.4	915.1
132.5°	953.9	953.7	953.6	953.4	953.6	953.7	953.9	954.1	954.1	953.9	953.6
135°	1008.6	1009.0	1009.5	1009.9	1009.5	1009.0	1008.6	1008.0	1007.6	1007.1	1006.7
137.5°	1058.5	1058.4	1058.3	1058.1	1058.3	1058.4	1058.5	1058.7	1058.5	1058.0	1057.5
140°	1091.1	1091.3	1091.5	1091.8	1091.5	1091.3	1091.1	1090.9	1090.4	1089.6	1089.0
142.5°	1119.4	1119.4	1119.5	1119.5	1119.5	1119.4	1119.4	1119.3	1119.1	1118.6	1118.1
145°	1160.9	1161.4	1161.8	1162.4	1161.8	1161.4	1160.9	1160.5	1160.1	1159.9	1159.7
147.5°	1197.1	1197.3	1197.5	1197.7	1197.5	1197.3	1197.1	1196.8	1196.6	1196.4	1196.3
150°	1219.9	1220.2	1220.4	1220.6	1220.4	1220.2	1219.9	1219.7	1219.6	1219.6	1219.6
152.5°	1240.7	1240.5	1240.4	1240.3	1240.4	1240.5	1240.7	1240.8	1240.7	1240.3	1240.0
155°	1268.7	1268.1	1267.4	1266.7	1267.4	1268.1	1268.7	1269.4	1269.3	1268.4	1267.5
157.5°	1292.3	1291.1	1290.0	1288.8	1290.0	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1
160°	1307.6	1306.3	1304.8	1303.5	1304.8	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3
162.5°	1319.6	1318.1	1316.6	1314.9	1316.6	1318.1	1319.6	1321.2	1321.2	1319.9	1318.5
165°	1337.3	1335.2	1333.2	1331.1	1333.2	1335.2	1337.3	1339.3	1339.5	1337.7	1335.8
167.5°	1350.1	1347.8	1345.5	1343.2	1345.5	1347.8	1350.1	1352.3	1352.4	1350.5	1348.5
170°	1357.4	1355.1	1352.8	1350.6	1352.8	1355.1	1357.4	1359.7	1359.9	1358.1	1356.2
172.5°	1362.0	1359.6	1357.2	1354.6	1357.2	1359.6	1362.0	1364.5	1364.8	1363.0	1361.2
175°	1368.0	1365.2	1362.5	1359.8	1362.5	1365.2	1368.0	1370.7	1371.1	1369.0	1367.0
177.5°	1369.6	1367.5	1365.2	1363.1	1365.2	1367.5	1369.6	1371.8	1372.2	1370.7	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	14.2	14.3	14.0	13.2	13.7	13.3	13.3	12.8	13.6	14.4	15.2
90°	23.8	22.5	20.7	18.9	17.1	15.2	13.0	10.6	8.1	5.6	3.0
92.5°	23.0	21.7	19.9	18.1	16.3	14.4	13.4	13.3	13.1	13.0	12.9
95°	23.8	22.5	22.3	22.0	21.8	21.6	25.3	33.1	40.8	48.6	56.2
97.5°	27.2	27.0	52.4	77.8	103.1	128.6	138.8	134.0	129.2	124.3	119.5
100°	41.2	45.0	76.4	107.8	139.2	170.6	184.2	180.1	176.0	171.9	167.8
102.5°	175.2	216.9	221.0	225.1	229.2	233.3	233.8	230.9	227.8	224.8	221.9
105°	321.2	319.2	318.1	317.0	315.8	314.7	313.5	312.0	310.7	309.3	308.0
107.5°	399.0	398.0	396.5	395.0	393.3	391.8	390.7	390.0	389.3	388.7	388.0
110°	451.7	451.2	449.9	448.5	447.2	445.8	444.7	444.0	443.3	442.7	442.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	502.7	502.8	502.1	501.5	500.9	500.3	499.3	498.1	496.9	495.6	494.4
115°	577.5	577.0	577.3	577.5	577.7	577.9	577.7	577.0	576.4	575.7	575.0
117.5°	653.9	654.0	653.5	653.0	652.5	652.0	651.3	650.4	649.4	648.5	647.6
120°	700.3	699.8	700.0	700.3	700.5	700.7	700.4	699.5	698.6	697.7	696.8
122.5°	746.8	746.5	746.2	745.9	745.6	745.3	744.8	744.3	743.7	743.2	742.7
125°	811.0	810.3	810.8	811.2	811.7	812.1	811.9	811.0	810.1	809.2	808.3
127.5°	876.2	876.3	875.1	874.1	873.1	872.0	871.4	871.2	871.0	870.7	870.5
130°	914.9	914.7	914.0	913.3	912.7	912.0	911.5	911.3	911.1	910.9	910.6
132.5°	953.4	953.2	952.3	951.5	950.6	949.8	949.1	948.7	948.3	947.9	947.5
135°	1006.2	1005.8	1004.9	1004.0	1003.1	1002.2	1001.8	1002.0	1002.3	1002.5	1002.7
137.5°	1057.0	1056.5	1055.5	1054.5	1053.5	1052.5	1052.0	1051.9	1051.8	1051.7	1051.6
140°	1088.3	1087.6	1087.2	1086.7	1086.3	1085.8	1085.4	1084.9	1084.5	1084.0	1083.6
142.5°	1117.6	1117.1	1116.8	1116.5	1116.3	1116.0	1115.5	1114.7	1113.8	1113.0	1112.2
145°	1159.5	1159.2	1159.2	1159.2	1159.2	1159.2	1158.9	1158.2	1157.5	1156.9	1156.2
147.5°	1196.1	1195.9	1196.1	1196.4	1196.6	1196.8	1196.3	1195.0	1193.8	1192.4	1191.1
150°	1219.6	1219.6	1219.8	1220.1	1220.3	1220.5	1220.2	1219.3	1218.4	1217.5	1216.6
152.5°	1239.6	1239.3	1239.7	1240.1	1240.5	1240.9	1240.7	1240.0	1239.3	1238.6	1237.8
155°	1266.6	1265.7	1266.4	1267.1	1267.7	1268.4	1268.6	1268.4	1268.2	1268.0	1267.7
157.5°	1290.0	1288.8	1289.6	1290.3	1291.1	1291.9	1292.3	1292.4	1292.6	1292.7	1292.9
160°	1304.8	1303.5	1303.7	1303.9	1304.2	1304.4	1304.8	1305.6	1306.3	1307.0	1307.6
162.5°	1317.2	1315.8	1316.1	1316.3	1316.5	1316.7	1317.3	1318.1	1319.0	1319.9	1320.7
165°	1334.0	1332.2	1332.2	1332.2	1332.2	1332.2	1332.7	1333.8	1335.0	1336.2	1337.3
167.5°	1346.5	1344.4	1344.6	1344.7	1344.8	1345.0	1345.6	1346.9	1348.1	1349.2	1350.4
170°	1354.4	1352.6	1352.4	1352.2	1351.9	1351.7	1352.3	1353.6	1355.0	1356.3	1357.8
172.5°	1359.4	1357.6	1357.4	1357.1	1356.9	1356.7	1357.2	1358.6	1359.9	1361.3	1362.6
175°	1364.9	1362.9	1362.6	1362.4	1362.2	1362.0	1362.5	1363.9	1365.2	1366.7	1368.0
177.5°	1367.8	1366.3	1365.9	1365.6	1365.2	1364.9	1365.3	1366.7	1367.9	1369.2	1370.4
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	15.2	14.5	13.3	13.3	13.8	13.3	14.0	14.4	14.8	14.6	15.8
90°	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8	25.2
92.5°	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0	24.4
95°	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8	25.2
97.5°	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2	27.3
100°	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2	37.3
102.5°	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2	133.5
105°	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2	323.4
107.5°	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0	400.0
110°	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7	452.1



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7	502.6
115°	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5	577.9
117.5°	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9	653.8
120°	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3	700.7
122.5°	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8	747.1
125°	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0	811.7
127.5°	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2	876.0
130°	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9	915.1
132.5°	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4	953.6
135°	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2	1006.7
137.5°	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0	1057.5
140°	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3	1089.0
142.5°	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6	1118.1
145°	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5	1159.7
147.5°	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1	1196.3
150°	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6	1219.6
152.5°	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6	1240.0
155°	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6	1267.5
157.5°	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0	1291.1
160°	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8	1306.3
162.5°	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2	1318.5
165°	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0	1335.8
167.5°	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5	1348.5
170°	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4	1356.2
172.5°	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4	1361.2
175°	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9	1367.0
177.5°	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8	1369.3
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	15.2	15.0	15.7	15.3	15.5	15.0	15.6
90°	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.6	453.0	453.6	454.3	454.9	455.7	456.4



TEST NUMBER: P333063-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)