

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333065-840

Luminaire Tested: **S124RDIW-S795D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333065-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1050U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7476.7 lumens  
Efficiency: N/A  
Efficacy: 142.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11326	11326	11326
5°	11351	11212	11281
10°	11280	11077	11077
15°	11150	10845	10764
20°	10972	10539	10345
25°	10745	10180	9922
30°	10523	9803	9392
35°	10279	9411	8861
40°	9985	8965	8286
45°	9712	8524	7702
50°	9403	8013	7082
55°	9071	7484	6410
60°	8707	6902	5724
65°	8373	6178	5049
70°	7886	5375	4286
75°	7271	4457	3484
80°	6341	3394	3199
85°	5372	3084	2881



TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	1.8
10°-20°	367.5	4.9
20°-30°	530.6	7.1
30°-40°	601.5	8.0
40°-50°	580.8	7.8
50°-60°	483.0	6.5
60°-70°	333.5	4.5
70°-80°	169.1	2.3
80°-90°	47.3	0.6
90°-100°	46.8	0.6
100°-110°	298.3	4.0
110°-120°	570.7	7.6
120°-130°	724.4	9.7
130°-140°	775.1	10.4
140°-150°	724.8	9.7
150°-160°	584.5	7.8
160°-170°	377.0	5.0
170°-180°	129.9	1.7
0°-30°	1029.9	13.8
0°-40°	1631.4	21.8
0°-60°	2695.2	36.0
0°-90°	3245.1	43.4
90°-120°	915.8	12.2
90°-150°	3140.1	42.0
90°-180°	4232.0	56.6
0°-180°	7476.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1401	1396	1384	1394	1392	133
15°	1334	1324	1298	1295	1288	376
25°	1206	1186	1143	1125	1114	556
35°	1043	1008	955	919	899	651
45°	851	810	747	696	675	656
55°	644	600	532	478	455	576
65°	438	391	323	279	264	433
75°	233	193	143	119	112	246
85°	58	38	33	31	31	65
90°	3	14	22	28	31	5
95°	56	23	22	28	30	72
105°	308	314	319	326	292	322
115°	575	578	577	579	579	566
125°	808	812	810	813	814	721
135°	1003	1002	1006	1008	1010	772
145°	1156	1159	1159	1160	1162	722
155°	1268	1268	1266	1269	1267	584
165°	1337	1332	1332	1339	1331	378
175°	1368	1362	1363	1371	1360	130
180°	1368	1368	1368	1368	1368	



TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1406.3	1405.5	1404.7	1404.0	1403.2	1401.8	1399.7	1397.7	1395.5	1393.4	1395.5
5°	1400.7	1399.8	1398.8	1397.9	1396.8	1395.0	1392.1	1389.3	1386.3	1383.5	1385.9
7.5°	1388.1	1387.0	1386.0	1385.0	1384.0	1381.7	1378.0	1374.2	1370.5	1366.8	1368.3
10°	1376.0	1374.8	1373.6	1372.4	1371.2	1368.5	1364.2	1359.9	1355.6	1351.3	1352.2
12.5°	1360.5	1359.2	1357.8	1356.3	1355.0	1351.8	1346.8	1341.6	1336.6	1331.5	1332.1
15°	1334.1	1332.0	1329.8	1327.7	1325.5	1321.5	1315.5	1309.5	1303.5	1297.6	1297.1
17.5°	1302.1	1299.0	1295.9	1292.8	1289.7	1284.5	1277.4	1270.2	1263.0	1255.9	1254.6
20°	1277.2	1274.0	1271.0	1267.9	1264.8	1259.2	1251.0	1242.9	1234.8	1226.7	1224.8
22.5°	1249.7	1246.2	1242.7	1239.2	1235.8	1229.6	1220.9	1212.2	1203.6	1194.9	1192.0
25°	1206.3	1201.9	1197.7	1193.4	1189.1	1182.0	1172.3	1162.5	1152.7	1142.9	1138.8
27.5°	1160.7	1155.4	1149.9	1144.6	1139.1	1131.3	1120.7	1110.3	1099.8	1089.4	1084.4
30°	1128.9	1123.0	1117.0	1111.1	1105.1	1096.5	1085.3	1074.1	1062.8	1051.6	1045.6
32.5°	1095.4	1088.7	1082.0	1075.2	1068.5	1059.3	1047.7	1036.1	1024.5	1012.9	1006.0
35°	1043.0	1035.4	1027.7	1020.1	1012.5	1002.7	990.8	978.8	966.8	954.9	946.8
37.5°	986.9	979.1	971.2	963.3	955.4	944.9	931.7	918.5	905.2	892.0	882.9
40°	947.5	939.6	931.7	923.8	915.9	905.1	891.5	878.0	864.3	850.7	840.7
42.5°	909.6	901.3	893.1	884.8	876.6	865.4	851.2	837.0	822.8	808.6	798.4
45°	850.7	841.9	833.0	824.3	815.4	803.9	789.5	775.2	760.8	746.6	734.9
47.5°	789.9	780.8	771.7	762.5	753.5	741.4	726.6	711.7	696.8	681.9	669.7
50°	748.7	739.4	730.0	720.7	711.4	699.1	683.9	668.6	653.3	638.0	626.1
52.5°	706.6	697.5	688.3	679.2	670.1	657.7	642.1	626.4	610.8	595.1	583.0
55°	644.5	634.9	625.4	615.8	606.3	593.8	578.2	562.7	547.2	531.7	519.3
57.5°	583.1	573.1	563.2	553.3	543.3	530.7	515.4	500.2	484.9	469.6	457.1
60°	539.3	529.7	520.2	510.6	501.0	488.7	473.3	458.1	442.8	427.5	415.1
62.5°	499.7	489.8	479.9	469.9	460.0	447.2	431.5	415.9	400.2	384.6	373.0
65°	438.3	428.0	417.7	407.5	397.2	384.5	369.1	353.9	338.6	323.4	313.1
67.5°	374.5	364.7	354.8	345.0	335.1	323.2	308.9	294.8	280.5	266.4	257.5
70°	334.1	324.1	314.0	304.0	294.0	282.2	268.5	254.9	241.4	227.7	219.8
72.5°	291.1	282.1	273.0	263.9	254.8	243.9	231.1	218.1	205.3	192.5	185.7
75°	233.1	224.3	215.4	206.6	197.7	187.7	176.5	165.3	154.1	142.9	137.3
77.5°	174.2	166.7	159.3	151.8	144.2	135.9	126.9	117.9	108.8	99.7	96.4
80°	136.4	129.5	122.6	115.6	108.8	101.7	94.5	87.4	80.2	73.0	72.3
82.5°	103.8	97.5	91.1	84.7	78.4	73.1	69.1	64.9	60.8	56.8	56.1
85°	58.0	53.2	48.5	43.7	38.9	36.2	35.4	34.7	34.0	33.3	32.8
87.5°	20.4	19.4	18.3	17.3	16.3	15.9	16.1	16.2	16.4	16.6	16.7
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	12.9	13.0	13.1	13.3	13.4	14.4	16.3	18.1	19.9	21.7	23.0
95°	56.2	48.6	40.8	33.1	25.3	21.6	21.8	22.0	22.3	22.5	23.8
97.5°	119.5	124.3	129.2	134.0	138.8	128.6	103.1	77.8	52.4	27.0	27.2
100°	167.8	171.9	176.0	180.1	184.2	170.6	139.2	107.8	76.4	45.0	41.2
102.5°	221.9	224.8	227.8	230.9	233.8	233.3	229.2	225.1	221.0	216.9	175.2
105°	308.0	309.3	310.7	312.0	313.5	314.7	315.8	317.0	318.1	319.2	321.2
107.5°	388.0	388.7	389.3	390.0	390.7	391.8	393.3	395.0	396.5	398.0	399.0
110°	442.0	442.7	443.3	444.0	444.7	445.8	447.2	448.5	449.9	451.2	451.7



TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	494.4	495.6	496.9	498.1	499.3	500.3	500.9	501.5	502.1	502.8	502.7
115°	575.0	575.7	576.4	577.0	577.7	577.9	577.7	577.5	577.3	577.0	577.5
117.5°	647.6	648.5	649.4	650.4	651.3	652.0	652.5	653.0	653.5	654.0	653.9
120°	696.8	697.7	698.6	699.5	700.4	700.7	700.5	700.3	700.0	699.8	700.3
122.5°	742.7	743.2	743.7	744.3	744.8	745.3	745.6	745.9	746.2	746.5	746.8
125°	808.3	809.2	810.1	811.0	811.9	812.1	811.7	811.2	810.8	810.3	811.0
127.5°	870.5	870.7	871.0	871.2	871.4	872.0	873.1	874.1	875.1	876.3	876.2
130°	910.6	910.9	911.1	911.3	911.5	912.0	912.7	913.3	914.0	914.7	914.9
132.5°	947.5	947.9	948.3	948.7	949.1	949.8	950.6	951.5	952.3	953.2	953.4
135°	1002.7	1002.5	1002.3	1002.0	1001.8	1002.2	1003.1	1004.0	1004.9	1005.8	1006.2
137.5°	1051.6	1051.7	1051.8	1051.9	1052.0	1052.5	1053.5	1054.5	1055.5	1056.5	1057.0
140°	1083.6	1084.0	1084.5	1084.9	1085.4	1085.8	1086.3	1086.7	1087.2	1087.6	1088.3
142.5°	1112.2	1113.0	1113.8	1114.7	1115.5	1116.0	1116.3	1116.5	1116.8	1117.1	1117.6
145°	1156.2	1156.9	1157.5	1158.2	1158.9	1159.2	1159.2	1159.2	1159.2	1159.2	1159.5
147.5°	1191.1	1192.4	1193.8	1195.0	1196.3	1196.8	1196.6	1196.4	1196.1	1195.9	1196.1
150°	1216.6	1217.5	1218.4	1219.3	1220.2	1220.5	1220.3	1220.1	1219.8	1219.6	1219.6
152.5°	1237.8	1238.6	1239.3	1240.0	1240.7	1240.9	1240.5	1240.1	1239.7	1239.3	1239.6
155°	1267.7	1268.0	1268.2	1268.4	1268.6	1268.4	1267.7	1267.1	1266.4	1265.7	1266.6
157.5°	1292.9	1292.7	1292.6	1292.4	1292.3	1291.9	1291.1	1290.3	1289.6	1288.8	1290.0
160°	1307.6	1307.0	1306.3	1305.6	1304.8	1304.4	1304.2	1303.9	1303.7	1303.5	1304.8
162.5°	1320.7	1319.9	1319.0	1318.1	1317.3	1316.7	1316.5	1316.3	1316.1	1315.8	1317.2
165°	1337.3	1336.2	1335.0	1333.8	1332.7	1332.2	1332.2	1332.2	1332.2	1332.2	1334.0
167.5°	1350.4	1349.2	1348.1	1346.9	1345.6	1345.0	1344.8	1344.7	1344.6	1344.4	1346.5
170°	1357.8	1356.3	1355.0	1353.6	1352.3	1351.7	1351.9	1352.2	1352.4	1352.6	1354.4
172.5°	1362.6	1361.3	1359.9	1358.6	1357.2	1356.7	1356.9	1357.1	1357.4	1357.6	1359.4
175°	1368.0	1366.7	1365.2	1363.9	1362.5	1362.0	1362.2	1362.4	1362.6	1362.9	1364.9
177.5°	1370.4	1369.2	1367.9	1366.7	1365.3	1364.9	1365.2	1365.6	1365.9	1366.3	1367.8
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0



TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1397.7	1399.7	1401.8	1402.8	1402.6	1402.4	1402.2	1402.0
5°	1388.3	1390.7	1393.1	1394.0	1393.5	1393.1	1392.6	1392.1
7.5°	1369.8	1371.4	1372.9	1373.2	1372.5	1371.7	1371.0	1370.2
10°	1353.2	1354.1	1355.1	1355.1	1354.1	1353.2	1352.2	1351.3
12.5°	1332.7	1333.2	1333.8	1333.4	1332.1	1330.8	1329.4	1328.1
15°	1296.7	1296.2	1295.7	1294.6	1292.9	1291.2	1289.6	1287.9
17.5°	1253.2	1251.9	1250.5	1248.6	1246.1	1243.5	1241.0	1238.5
20°	1222.8	1220.9	1219.0	1216.6	1213.5	1210.3	1207.2	1204.2
22.5°	1189.2	1186.3	1183.5	1180.7	1178.2	1175.7	1173.2	1170.6
25°	1134.8	1130.7	1126.7	1123.5	1121.1	1118.7	1116.3	1113.9
27.5°	1079.3	1074.4	1069.3	1065.1	1061.7	1058.2	1054.8	1051.4
30°	1039.7	1033.7	1027.7	1022.8	1019.1	1015.2	1011.4	1007.5
32.5°	999.1	992.2	985.2	980.0	976.3	972.7	969.1	965.4
35°	938.7	930.6	922.5	916.3	912.0	907.7	903.3	899.1
37.5°	873.8	864.7	855.7	849.0	844.8	840.4	836.2	831.8
40°	830.7	820.6	810.6	803.4	799.2	794.9	790.6	786.3
42.5°	788.2	778.0	767.8	760.4	755.9	751.4	747.0	742.5
45°	723.2	711.4	699.7	691.8	687.4	683.2	678.8	674.6
47.5°	657.6	645.5	633.4	624.9	620.3	615.5	610.8	606.0
50°	614.2	602.3	590.3	582.1	577.5	573.0	568.5	563.9
52.5°	570.9	558.8	546.5	538.2	533.4	528.7	524.0	519.3
55°	506.9	494.4	482.1	473.6	469.1	464.5	460.0	455.4
57.5°	444.4	431.8	419.2	411.2	407.8	404.3	400.9	397.5
60°	402.7	390.3	377.9	369.7	366.0	362.1	358.3	354.5
62.5°	361.6	350.2	338.7	331.4	328.4	325.4	322.2	319.2
65°	302.8	292.6	282.3	275.7	272.9	269.9	267.1	264.3
67.5°	248.7	239.9	231.1	225.1	222.0	218.7	215.6	212.5
70°	212.0	204.1	196.2	191.1	188.7	186.3	183.9	181.6
72.5°	179.0	172.3	165.5	161.1	159.0	156.7	154.5	152.3
75°	131.9	126.4	120.9	117.4	116.0	114.6	113.1	111.7
77.5°	93.3	90.1	86.8	85.0	84.6	84.2	83.8	83.3
80°	71.6	70.9	70.2	69.7	69.5	69.2	69.0	68.8
82.5°	55.6	55.1	54.6	54.2	54.0	53.7	53.5	53.3
85°	32.3	31.9	31.4	31.1	31.1	31.1	31.1	31.1
87.5°	16.7	16.8	16.9	17.1	17.4	17.6	17.9	18.2
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	24.4	25.8	27.2	27.9	28.0	28.1	28.2	28.3
95°	25.2	26.6	28.0	28.8	29.0	29.2	29.5	29.7
97.5°	27.3	27.5	27.6	27.8	28.0	28.2	28.4	28.7
100°	37.3	33.4	29.6	27.8	28.0	28.2	28.4	28.7
102.5°	133.5	91.8	50.1	29.3	29.3	29.4	29.4	29.5
105°	323.4	325.4	327.4	324.4	316.2	308.0	299.8	291.6
107.5°	400.0	401.0	402.0	402.9	403.8	404.7	405.6	406.4
110°	452.1	452.6	453.0	453.6	454.3	454.9	455.7	456.4





TEST NUMBER: P333065-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	502.6	502.5	502.4	502.8	503.7	504.5	505.4	506.2
115°	577.9	578.5	578.9	579.2	579.2	579.2	579.2	579.2
117.5°	653.8	653.8	653.7	653.6	653.5	653.4	653.3	653.2
120°	700.7	701.3	701.7	701.7	701.3	700.7	700.3	699.8
122.5°	747.1	747.3	747.6	747.5	747.1	746.6	746.2	745.7
125°	811.7	812.4	813.0	813.5	813.7	814.0	814.3	814.5
127.5°	876.0	875.9	875.7	875.6	875.4	875.1	874.9	874.8
130°	915.1	915.4	915.6	915.7	915.7	915.7	915.7	915.7
132.5°	953.6	953.9	954.1	954.1	953.9	953.7	953.6	953.4
135°	1006.7	1007.1	1007.6	1008.0	1008.6	1009.0	1009.5	1009.9
137.5°	1057.5	1058.0	1058.5	1058.7	1058.5	1058.4	1058.3	1058.1
140°	1089.0	1089.6	1090.4	1090.9	1091.1	1091.3	1091.5	1091.8
142.5°	1118.1	1118.6	1119.1	1119.3	1119.4	1119.4	1119.5	1119.5
145°	1159.7	1159.9	1160.1	1160.5	1160.9	1161.4	1161.8	1162.4
147.5°	1196.3	1196.4	1196.6	1196.8	1197.1	1197.3	1197.5	1197.7
150°	1219.6	1219.6	1219.6	1219.7	1219.9	1220.2	1220.4	1220.6
152.5°	1240.0	1240.3	1240.7	1240.8	1240.7	1240.5	1240.4	1240.3
155°	1267.5	1268.4	1269.3	1269.4	1268.7	1268.1	1267.4	1266.7
157.5°	1291.1	1292.3	1293.5	1293.5	1292.3	1291.1	1290.0	1288.8
160°	1306.3	1307.6	1309.0	1309.0	1307.6	1306.3	1304.8	1303.5
162.5°	1318.5	1319.9	1321.2	1321.2	1319.6	1318.1	1316.6	1314.9
165°	1335.8	1337.7	1339.5	1339.3	1337.3	1335.2	1333.2	1331.1
167.5°	1348.5	1350.5	1352.4	1352.3	1350.1	1347.8	1345.5	1343.2
170°	1356.2	1358.1	1359.9	1359.7	1357.4	1355.1	1352.8	1350.6
172.5°	1361.2	1363.0	1364.8	1364.5	1362.0	1359.6	1357.2	1354.6
175°	1367.0	1369.0	1371.1	1370.7	1368.0	1365.2	1362.5	1359.8
177.5°	1369.3	1370.7	1372.2	1371.8	1369.6	1367.5	1365.2	1363.1
180°	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0	1368.0

(END OF REPORT)