

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333067-840

Luminaire Tested: **S124RDIW-S795D1340U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333067-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8791.9 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	19				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				
9	49	38	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.5
10°-20°	389.6	4.4
20°-30°	609.4	6.9
30°-40°	677.4	7.7
40°-50°	601.0	6.8
50°-60°	468.4	5.3
60°-70°	306.6	3.5
70°-80°	150.8	1.7
80°-90°	42.3	0.5
90°-100°	59.9	0.7
100°-110°	381.9	4.3
110°-120°	730.6	8.3
120°-130°	927.4	10.5
130°-140°	992.3	11.3
140°-150°	927.9	10.6
150°-160°	748.3	8.5
160°-170°	482.6	5.5
170°-180°	166.3	1.9
0°-30°	1128.1	12.8
0°-40°	1805.6	20.5
0°-60°	2875.0	32.7
0°-90°	3374.7	38.4
90°-120°	1172.4	13.3
90°-150°	4020.0	45.7
90°-180°	5417.0	61.6
0°-180°	8791.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	39	4	39	4	39	18
95°	38	72	38	72	38	30
105°	373	394	373	394	373	326
115°	741	736	741	736	741	734
125°	1043	1035	1043	1035	1043	929
135°	1293	1284	1293	1284	1293	995
145°	1488	1480	1488	1480	1488	930
155°	1622	1623	1622	1623	1622	748
165°	1704	1712	1704	1712	1704	481
175°	1741	1751	1741	1751	1741	166
180°	1751	1751	1751	1751	1751	



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	17.3	16.8	17.1	17.0	17.3	16.7	16.7	17.2	16.0	16.1	15.7
90°	39.3	38.7	38.2	37.6	37.0	35.9	34.0	32.3	30.6	28.8	26.5
92.5°	36.2	36.1	36.0	35.9	35.6	34.7	33.0	31.3	29.5	27.8	25.4
95°	38.0	37.7	37.4	37.1	36.9	35.9	34.0	32.3	30.6	28.8	28.5
97.5°	36.7	36.4	36.1	35.9	35.5	35.2	35.1	34.9	34.7	34.5	67.1
100°	36.7	36.4	36.1	35.9	35.5	37.9	42.8	47.8	52.7	57.7	97.8
102.5°	37.8	37.7	37.6	37.6	37.5	64.1	117.5	171.0	224.3	277.7	283.0
105°	373.3	383.7	394.3	404.8	415.3	419.2	416.6	413.9	411.3	408.7	407.2
107.5°	520.3	519.2	518.1	516.9	515.8	514.6	513.4	512.1	510.8	509.6	507.6
110°	584.2	583.3	582.5	581.6	580.7	580.0	579.4	578.9	578.2	577.6	575.9



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	648.1	647.0	645.9	644.8	643.7	643.2	643.3	643.4	643.6	643.7	642.9
115°	741.3	741.3	741.3	741.3	741.3	741.0	740.5	739.9	739.3	738.7	739.0
117.5°	836.2	836.4	836.5	836.6	836.7	836.8	836.9	837.0	837.2	837.3	836.6
120°	896.0	896.6	897.1	897.7	898.3	898.3	897.7	897.1	896.6	896.0	896.3
122.5°	954.6	955.2	955.7	956.3	956.9	957.0	956.7	956.3	956.0	955.6	955.2
125°	1042.7	1042.4	1042.1	1041.8	1041.5	1040.9	1040.1	1039.2	1038.2	1037.4	1037.9
127.5°	1119.9	1120.1	1120.3	1120.6	1120.8	1121.1	1121.3	1121.5	1121.6	1121.8	1120.4
130°	1172.4	1172.4	1172.4	1172.4	1172.4	1172.2	1171.8	1171.5	1171.3	1171.0	1170.1
132.5°	1220.5	1220.7	1221.0	1221.2	1221.4	1221.4	1221.1	1220.8	1220.5	1220.2	1219.1
135°	1292.8	1292.2	1291.6	1291.1	1290.5	1289.9	1289.3	1288.8	1288.2	1287.6	1286.5
137.5°	1354.6	1354.8	1355.0	1355.1	1355.3	1355.1	1354.4	1353.8	1353.2	1352.5	1351.3
140°	1397.7	1397.4	1397.0	1396.7	1396.4	1395.8	1395.0	1394.1	1393.2	1392.4	1391.8
142.5°	1433.2	1433.2	1433.1	1433.1	1433.0	1432.7	1432.0	1431.4	1430.8	1430.1	1429.8
145°	1488.0	1487.4	1486.8	1486.2	1485.7	1485.2	1484.9	1484.6	1484.4	1484.1	1484.1
147.5°	1533.3	1533.0	1532.8	1532.5	1532.2	1531.9	1531.7	1531.5	1531.2	1531.0	1531.3
150°	1562.7	1562.4	1562.1	1561.8	1561.5	1561.4	1561.4	1561.4	1561.4	1561.4	1561.7
152.5°	1587.8	1588.0	1588.1	1588.3	1588.5	1588.3	1587.9	1587.4	1587.0	1586.5	1587.0
155°	1621.6	1622.4	1623.4	1624.3	1625.1	1625.0	1623.8	1622.7	1621.4	1620.3	1621.1
157.5°	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9	1650.9
160°	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8	1669.0
162.5°	1683.4	1685.4	1687.4	1689.4	1691.3	1691.4	1689.7	1688.0	1686.2	1684.5	1684.8
165°	1704.1	1706.8	1709.4	1712.0	1714.5	1714.8	1712.4	1710.1	1707.8	1705.5	1705.5
167.5°	1719.6	1722.5	1725.4	1728.3	1731.2	1731.4	1728.8	1726.3	1723.7	1721.1	1721.3
170°	1729.0	1731.9	1734.8	1737.8	1740.6	1740.9	1738.6	1736.3	1733.9	1731.6	1731.3
172.5°	1734.2	1737.4	1740.5	1743.6	1746.9	1747.3	1744.9	1742.5	1740.2	1737.9	1737.6
175°	1740.8	1744.2	1747.8	1751.3	1754.7	1755.2	1752.6	1750.0	1747.4	1744.7	1744.4
177.5°	1744.9	1747.8	1750.6	1753.3	1756.2	1756.7	1754.7	1752.9	1751.0	1749.2	1748.7
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	15.1	14.2	14.6	14.1	13.8	14.9	15.7	15.3	14.7	14.1	13.4
90°	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9	7.2	10.3	13.5
92.5°	23.1	20.8	18.5	17.2	17.1	16.9	16.7	16.5	16.7	16.9	17.1
95°	28.3	28.0	27.7	32.4	42.3	52.2	62.1	72.0	62.1	52.2	42.3
97.5°	99.6	132.0	164.5	177.6	171.5	165.3	159.2	153.0	159.2	165.3	171.5
100°	137.9	178.1	218.3	235.8	230.6	225.3	220.0	214.8	220.0	225.3	230.6
102.5°	288.2	293.4	298.6	299.3	295.5	291.6	287.8	284.0	287.8	291.6	295.5
105°	405.8	404.3	402.8	401.2	399.5	397.8	396.0	394.3	396.0	397.8	399.5
107.5°	505.5	503.6	501.6	500.2	499.3	498.5	497.6	496.7	497.6	498.5	499.3
110°	574.1	572.4	570.7	569.4	568.5	567.6	566.7	565.8	566.7	567.6	568.5



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	642.1	641.3	640.4	639.2	637.6	636.1	634.5	632.9	634.5	636.1	637.6
115°	739.3	739.6	739.9	739.6	738.7	737.9	737.0	736.1	737.0	737.9	738.7
117.5°	836.0	835.4	834.7	833.7	832.6	831.4	830.3	829.1	830.3	831.4	832.6
120°	896.6	896.9	897.1	896.7	895.5	894.3	893.1	892.0	893.1	894.3	895.5
122.5°	954.8	954.4	954.0	953.5	952.8	952.1	951.4	950.7	951.4	952.1	952.8
125°	1038.5	1039.2	1039.8	1039.5	1038.2	1037.1	1035.9	1034.8	1035.9	1037.1	1038.2
127.5°	1119.0	1117.7	1116.4	1115.6	1115.3	1115.0	1114.7	1114.4	1114.7	1115.0	1115.3
130°	1169.2	1168.4	1167.5	1166.9	1166.6	1166.4	1166.1	1165.8	1166.1	1166.4	1166.6
132.5°	1218.0	1217.0	1215.9	1215.0	1214.5	1214.0	1213.5	1212.9	1213.5	1214.0	1214.5
135°	1285.3	1284.0	1282.9	1282.5	1282.8	1283.0	1283.3	1283.6	1283.3	1283.0	1282.8
137.5°	1350.0	1348.7	1347.5	1346.8	1346.7	1346.5	1346.4	1346.3	1346.4	1346.5	1346.7
140°	1391.2	1390.6	1390.1	1389.5	1388.9	1388.3	1387.8	1387.2	1387.8	1388.3	1388.9
142.5°	1429.4	1429.1	1428.7	1428.1	1426.9	1425.9	1424.8	1423.8	1424.8	1425.9	1426.9
145°	1484.1	1484.1	1484.1	1483.6	1482.8	1481.9	1481.0	1480.2	1481.0	1481.9	1482.8
147.5°	1531.6	1531.9	1532.2	1531.5	1529.8	1528.2	1526.5	1524.9	1526.5	1528.2	1529.8
150°	1562.0	1562.3	1562.5	1562.1	1560.9	1559.7	1558.6	1557.4	1558.6	1559.7	1560.9
152.5°	1587.5	1588.1	1588.6	1588.4	1587.4	1586.5	1585.6	1584.7	1585.6	1586.5	1587.4
155°	1622.0	1623.0	1623.8	1624.1	1623.8	1623.5	1623.2	1623.0	1623.2	1623.5	1623.8
157.5°	1651.8	1652.8	1653.9	1654.5	1654.6	1654.8	1655.0	1655.2	1655.0	1654.8	1654.6
160°	1669.3	1669.6	1669.9	1670.5	1671.3	1672.2	1673.1	1674.0	1673.1	1672.2	1671.3
162.5°	1685.1	1685.4	1685.7	1686.4	1687.5	1688.6	1689.6	1690.7	1689.6	1688.6	1687.5
165°	1705.5	1705.5	1705.5	1706.2	1707.6	1709.1	1710.5	1712.0	1710.5	1709.1	1707.6
167.5°	1721.5	1721.7	1721.8	1722.7	1724.2	1725.8	1727.3	1728.8	1727.3	1725.8	1724.2
170°	1731.0	1730.7	1730.5	1731.2	1732.9	1734.6	1736.5	1738.2	1736.5	1734.6	1732.9
172.5°	1737.4	1737.1	1736.8	1737.5	1739.2	1741.0	1742.7	1744.4	1742.7	1741.0	1739.2
175°	1744.1	1743.8	1743.5	1744.2	1746.1	1747.8	1749.5	1751.3	1749.5	1747.8	1746.1
177.5°	1748.3	1747.8	1747.3	1747.9	1749.5	1751.1	1752.8	1754.4	1752.8	1751.1	1749.5
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	14.1	14.2	14.6	14.2	15.1	15.7	15.6	16.0	16.7	16.2	16.5
90°	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3	34.0	35.9	37.0
92.5°	17.2	18.5	20.8	23.1	25.4	27.8	29.5	31.3	33.0	34.7	35.6
95°	32.4	27.7	28.0	28.3	28.5	28.8	30.6	32.3	34.0	35.9	36.9
97.5°	177.6	164.5	132.0	99.6	67.1	34.5	34.7	34.9	35.1	35.2	35.5
100°	235.8	218.3	178.1	137.9	97.8	57.7	52.7	47.8	42.8	37.9	35.5
102.5°	299.3	298.6	293.4	288.2	283.0	277.7	224.3	171.0	117.5	64.1	37.5
105°	401.2	402.8	404.3	405.8	407.2	408.7	411.3	413.9	416.6	419.2	415.3
107.5°	500.2	501.6	503.6	505.5	507.6	509.6	510.8	512.1	513.4	514.6	515.8
110°	569.4	570.7	572.4	574.1	575.9	577.6	578.2	578.9	579.4	580.0	580.7



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	639.2	640.4	641.3	642.1	642.9	643.7	643.6	643.4	643.3	643.2	643.7
115°	739.6	739.9	739.6	739.3	739.0	738.7	739.3	739.9	740.5	741.0	741.3
117.5°	833.7	834.7	835.4	836.0	836.6	837.3	837.2	837.0	836.9	836.8	836.7
120°	896.7	897.1	896.9	896.6	896.3	896.0	896.6	897.1	897.7	898.3	898.3
122.5°	953.5	954.0	954.4	954.8	955.2	955.6	956.0	956.3	956.7	957.0	956.9
125°	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2	1039.2	1040.1	1040.9	1041.5
127.5°	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6	1121.5	1121.3	1121.1	1120.8
130°	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3	1171.5	1171.8	1172.2	1172.4
132.5°	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5	1220.8	1221.1	1221.4	1221.4
135°	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2	1288.8	1289.3	1289.9	1290.5
137.5°	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2	1353.8	1354.4	1355.1	1355.3
140°	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2	1394.1	1395.0	1395.8	1396.4
142.5°	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8	1431.4	1432.0	1432.7	1433.0
145°	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4	1484.6	1484.9	1485.2	1485.7
147.5°	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2	1531.5	1531.7	1531.9	1532.2
150°	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4	1561.4	1561.4	1561.4	1561.5
152.5°	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0	1587.4	1587.9	1588.3	1588.5
155°	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4	1622.7	1623.8	1625.0	1625.1
157.5°	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0
160°	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8
162.5°	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2	1688.0	1689.7	1691.4	1691.3
165°	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8	1710.1	1712.4	1714.8	1714.5
167.5°	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7	1726.3	1728.8	1731.4	1731.2
170°	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9	1736.3	1738.6	1740.9	1740.6
172.5°	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2	1742.5	1744.9	1747.3	1746.9
175°	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4	1750.0	1752.6	1755.2	1754.7
177.5°	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0	1752.9	1754.7	1756.7	1756.2
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	17.4	17.1	16.8	17.3	16.8	17.1	17.4	16.5	16.2	16.7	16.0
90°	37.6	38.2	38.7	39.3	38.7	38.2	37.6	37.0	35.9	34.0	32.3
92.5°	35.9	36.0	36.1	36.2	36.1	36.0	35.9	35.6	34.7	33.0	31.3
95°	37.1	37.4	37.7	38.0	37.7	37.4	37.1	36.9	35.9	34.0	32.3
97.5°	35.9	36.1	36.4	36.7	36.4	36.1	35.9	35.5	35.2	35.1	34.9
100°	35.9	36.1	36.4	36.7	36.4	36.1	35.9	35.5	37.9	42.8	47.8
102.5°	37.6	37.6	37.7	37.8	37.7	37.6	37.6	37.5	64.1	117.5	171.0
105°	404.8	394.3	383.7	373.3	383.7	394.3	404.8	415.3	419.2	416.6	413.9
107.5°	516.9	518.1	519.2	520.3	519.2	518.1	516.9	515.8	514.6	513.4	512.1
110°	581.6	582.5	583.3	584.2	583.3	582.5	581.6	580.7	580.0	579.4	578.9



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	644.8	645.9	647.0	648.1	647.0	645.9	644.8	643.7	643.2	643.3	643.4
115°	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.3	741.0	740.5	739.9
117.5°	836.6	836.5	836.4	836.2	836.4	836.5	836.6	836.7	836.8	836.9	837.0
120°	897.7	897.1	896.6	896.0	896.6	897.1	897.7	898.3	898.3	897.7	897.1
122.5°	956.3	955.7	955.2	954.6	955.2	955.7	956.3	956.9	957.0	956.7	956.3
125°	1041.8	1042.1	1042.4	1042.7	1042.4	1042.1	1041.8	1041.5	1040.9	1040.1	1039.2
127.5°	1120.6	1120.3	1120.1	1119.9	1120.1	1120.3	1120.6	1120.8	1121.1	1121.3	1121.5
130°	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.4	1172.2	1171.8	1171.5
132.5°	1221.2	1221.0	1220.7	1220.5	1220.7	1221.0	1221.2	1221.4	1221.4	1221.1	1220.8
135°	1291.1	1291.6	1292.2	1292.8	1292.2	1291.6	1291.1	1290.5	1289.9	1289.3	1288.8
137.5°	1355.1	1355.0	1354.8	1354.6	1354.8	1355.0	1355.1	1355.3	1355.1	1354.4	1353.8
140°	1396.7	1397.0	1397.4	1397.7	1397.4	1397.0	1396.7	1396.4	1395.8	1395.0	1394.1
142.5°	1433.1	1433.1	1433.2	1433.2	1433.2	1433.1	1433.1	1433.0	1432.7	1432.0	1431.4
145°	1486.2	1486.8	1487.4	1488.0	1487.4	1486.8	1486.2	1485.7	1485.2	1484.9	1484.6
147.5°	1532.5	1532.8	1533.0	1533.3	1533.0	1532.8	1532.5	1532.2	1531.9	1531.7	1531.5
150°	1561.8	1562.1	1562.4	1562.7	1562.4	1562.1	1561.8	1561.5	1561.4	1561.4	1561.4
152.5°	1588.3	1588.1	1588.0	1587.8	1588.0	1588.1	1588.3	1588.5	1588.3	1587.9	1587.4
155°	1624.3	1623.4	1622.4	1621.6	1622.4	1623.4	1624.3	1625.1	1625.0	1623.8	1622.7
157.5°	1654.5	1652.9	1651.4	1649.9	1651.4	1652.9	1654.5	1656.0	1656.0	1654.5	1652.9
160°	1674.0	1672.2	1670.5	1668.8	1670.5	1672.2	1674.0	1675.8	1675.8	1674.0	1672.2
162.5°	1689.4	1687.4	1685.4	1683.4	1685.4	1687.4	1689.4	1691.3	1691.4	1689.7	1688.0
165°	1712.0	1709.4	1706.8	1704.1	1706.8	1709.4	1712.0	1714.5	1714.8	1712.4	1710.1
167.5°	1728.3	1725.4	1722.5	1719.6	1722.5	1725.4	1728.3	1731.2	1731.4	1728.8	1726.3
170°	1737.8	1734.8	1731.9	1729.0	1731.9	1734.8	1737.8	1740.6	1740.9	1738.6	1736.3
172.5°	1743.6	1740.5	1737.4	1734.2	1737.4	1740.5	1743.6	1746.9	1747.3	1744.9	1742.5
175°	1751.3	1747.8	1744.2	1740.8	1744.2	1747.8	1751.3	1754.7	1755.2	1752.6	1750.0
177.5°	1753.3	1750.6	1747.8	1744.9	1747.8	1750.6	1753.3	1756.2	1756.7	1754.7	1752.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	15.6	15.7	15.1	14.2	14.6	14.2	14.1	13.4	14.1	14.7	15.3
90°	30.6	28.8	26.5	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9
92.5°	29.5	27.8	25.4	23.1	20.8	18.5	17.2	17.1	16.9	16.7	16.5
95°	30.6	28.8	28.5	28.3	28.0	27.7	32.4	42.3	52.2	62.1	72.0
97.5°	34.7	34.5	67.1	99.6	132.0	164.5	177.6	171.5	165.3	159.2	153.0
100°	52.7	57.7	97.8	137.9	178.1	218.3	235.8	230.6	225.3	220.0	214.8
102.5°	224.3	277.7	283.0	288.2	293.4	298.6	299.3	295.5	291.6	287.8	284.0
105°	411.3	408.7	407.2	405.8	404.3	402.8	401.2	399.5	397.8	396.0	394.3
107.5°	510.8	509.6	507.6	505.5	503.6	501.6	500.2	499.3	498.5	497.6	496.7
110°	578.2	577.6	575.9	574.1	572.4	570.7	569.4	568.5	567.6	566.7	565.8



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	643.6	643.7	642.9	642.1	641.3	640.4	639.2	637.6	636.1	634.5	632.9
115°	739.3	738.7	739.0	739.3	739.6	739.9	739.6	738.7	737.9	737.0	736.1
117.5°	837.2	837.3	836.6	836.0	835.4	834.7	833.7	832.6	831.4	830.3	829.1
120°	896.6	896.0	896.3	896.6	896.9	897.1	896.7	895.5	894.3	893.1	892.0
122.5°	956.0	955.6	955.2	954.8	954.4	954.0	953.5	952.8	952.1	951.4	950.7
125°	1038.2	1037.4	1037.9	1038.5	1039.2	1039.8	1039.5	1038.2	1037.1	1035.9	1034.8
127.5°	1121.6	1121.8	1120.4	1119.0	1117.7	1116.4	1115.6	1115.3	1115.0	1114.7	1114.4
130°	1171.3	1171.0	1170.1	1169.2	1168.4	1167.5	1166.9	1166.6	1166.4	1166.1	1165.8
132.5°	1220.5	1220.2	1219.1	1218.0	1217.0	1215.9	1215.0	1214.5	1214.0	1213.5	1212.9
135°	1288.2	1287.6	1286.5	1285.3	1284.0	1282.9	1282.5	1282.8	1283.0	1283.3	1283.6
137.5°	1353.2	1352.5	1351.3	1350.0	1348.7	1347.5	1346.8	1346.7	1346.5	1346.4	1346.3
140°	1393.2	1392.4	1391.8	1391.2	1390.6	1390.1	1389.5	1388.9	1388.3	1387.8	1387.2
142.5°	1430.8	1430.1	1429.8	1429.4	1429.1	1428.7	1428.1	1426.9	1425.9	1424.8	1423.8
145°	1484.4	1484.1	1484.1	1484.1	1484.1	1484.1	1483.6	1482.8	1481.9	1481.0	1480.2
147.5°	1531.2	1531.0	1531.3	1531.6	1531.9	1532.2	1531.5	1529.8	1528.2	1526.5	1524.9
150°	1561.4	1561.4	1561.7	1562.0	1562.3	1562.5	1562.1	1560.9	1559.7	1558.6	1557.4
152.5°	1587.0	1586.5	1587.0	1587.5	1588.1	1588.6	1588.4	1587.4	1586.5	1585.6	1584.7
155°	1621.4	1620.3	1621.1	1622.0	1623.0	1623.8	1624.1	1623.8	1623.5	1623.2	1623.0
157.5°	1651.4	1649.9	1650.9	1651.8	1652.8	1653.9	1654.5	1654.6	1654.8	1655.0	1655.2
160°	1670.5	1668.8	1669.0	1669.3	1669.6	1669.9	1670.5	1671.3	1672.2	1673.1	1674.0
162.5°	1686.2	1684.5	1684.8	1685.1	1685.4	1685.7	1686.4	1687.5	1688.6	1689.6	1690.7
165°	1707.8	1705.5	1705.5	1705.5	1705.5	1705.5	1706.2	1707.6	1709.1	1710.5	1712.0
167.5°	1723.7	1721.1	1721.3	1721.5	1721.7	1721.8	1722.7	1724.2	1725.8	1727.3	1728.8
170°	1733.9	1731.6	1731.3	1731.0	1730.7	1730.5	1731.2	1732.9	1734.6	1736.5	1738.2
172.5°	1740.2	1737.9	1737.6	1737.4	1737.1	1736.8	1737.5	1739.2	1741.0	1742.7	1744.4
175°	1747.4	1744.7	1744.4	1744.1	1743.8	1743.5	1744.2	1746.1	1747.8	1749.5	1751.3
177.5°	1751.0	1749.2	1748.7	1748.3	1747.8	1747.3	1747.9	1749.5	1751.1	1752.8	1754.4
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	15.7	14.9	13.8	14.1	14.6	14.2	15.1	15.7	16.1	16.0	17.2
90°	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3
92.5°	16.7	16.9	17.1	17.2	18.5	20.8	23.1	25.4	27.8	29.5	31.3
95°	62.1	52.2	42.3	32.4	27.7	28.0	28.3	28.5	28.8	30.6	32.3
97.5°	159.2	165.3	171.5	177.6	164.5	132.0	99.6	67.1	34.5	34.7	34.9
100°	220.0	225.3	230.6	235.8	218.3	178.1	137.9	97.8	57.7	52.7	47.8
102.5°	287.8	291.6	295.5	299.3	298.6	293.4	288.2	283.0	277.7	224.3	171.0
105°	396.0	397.8	399.5	401.2	402.8	404.3	405.8	407.2	408.7	411.3	413.9
107.5°	497.6	498.5	499.3	500.2	501.6	503.6	505.5	507.6	509.6	510.8	512.1
110°	566.7	567.6	568.5	569.4	570.7	572.4	574.1	575.9	577.6	578.2	578.9



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	634.5	636.1	637.6	639.2	640.4	641.3	642.1	642.9	643.7	643.6	643.4
115°	737.0	737.9	738.7	739.6	739.9	739.6	739.3	739.0	738.7	739.3	739.9
117.5°	830.3	831.4	832.6	833.7	834.7	835.4	836.0	836.6	837.3	837.2	837.0
120°	893.1	894.3	895.5	896.7	897.1	896.9	896.6	896.3	896.0	896.6	897.1
122.5°	951.4	952.1	952.8	953.5	954.0	954.4	954.8	955.2	955.6	956.0	956.3
125°	1035.9	1037.1	1038.2	1039.5	1039.8	1039.2	1038.5	1037.9	1037.4	1038.2	1039.2
127.5°	1114.7	1115.0	1115.3	1115.6	1116.4	1117.7	1119.0	1120.4	1121.8	1121.6	1121.5
130°	1166.1	1166.4	1166.6	1166.9	1167.5	1168.4	1169.2	1170.1	1171.0	1171.3	1171.5
132.5°	1213.5	1214.0	1214.5	1215.0	1215.9	1217.0	1218.0	1219.1	1220.2	1220.5	1220.8
135°	1283.3	1283.0	1282.8	1282.5	1282.9	1284.0	1285.3	1286.5	1287.6	1288.2	1288.8
137.5°	1346.4	1346.5	1346.7	1346.8	1347.5	1348.7	1350.0	1351.3	1352.5	1353.2	1353.8
140°	1387.8	1388.3	1388.9	1389.5	1390.1	1390.6	1391.2	1391.8	1392.4	1393.2	1394.1
142.5°	1424.8	1425.9	1426.9	1428.1	1428.7	1429.1	1429.4	1429.8	1430.1	1430.8	1431.4
145°	1481.0	1481.9	1482.8	1483.6	1484.1	1484.1	1484.1	1484.1	1484.1	1484.4	1484.6
147.5°	1526.5	1528.2	1529.8	1531.5	1532.2	1531.9	1531.6	1531.3	1531.0	1531.2	1531.5
150°	1558.6	1559.7	1560.9	1562.1	1562.5	1562.3	1562.0	1561.7	1561.4	1561.4	1561.4
152.5°	1585.6	1586.5	1587.4	1588.4	1588.6	1588.1	1587.5	1587.0	1586.5	1587.0	1587.4
155°	1623.2	1623.5	1623.8	1624.1	1623.8	1623.0	1622.0	1621.1	1620.3	1621.4	1622.7
157.5°	1655.0	1654.8	1654.6	1654.5	1653.9	1652.8	1651.8	1650.9	1649.9	1651.4	1652.9
160°	1673.1	1672.2	1671.3	1670.5	1669.9	1669.6	1669.3	1669.0	1668.8	1670.5	1672.2
162.5°	1689.6	1688.6	1687.5	1686.4	1685.7	1685.4	1685.1	1684.8	1684.5	1686.2	1688.0
165°	1710.5	1709.1	1707.6	1706.2	1705.5	1705.5	1705.5	1705.5	1705.5	1707.8	1710.1
167.5°	1727.3	1725.8	1724.2	1722.7	1721.8	1721.7	1721.5	1721.3	1721.1	1723.7	1726.3
170°	1736.5	1734.6	1732.9	1731.2	1730.5	1730.7	1731.0	1731.3	1731.6	1733.9	1736.3
172.5°	1742.7	1741.0	1739.2	1737.5	1736.8	1737.1	1737.4	1737.6	1737.9	1740.2	1742.5
175°	1749.5	1747.8	1746.1	1744.2	1743.5	1743.8	1744.1	1744.4	1744.7	1747.4	1750.0
177.5°	1752.8	1751.1	1749.5	1747.9	1747.3	1747.8	1748.3	1748.7	1749.2	1751.0	1752.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	16.7	16.7	17.3	17.0	17.1	16.8	17.3
90°	34.0	35.9	37.0	37.6	38.2	38.7	39.3
92.5°	33.0	34.7	35.6	35.9	36.0	36.1	36.2
95°	34.0	35.9	36.9	37.1	37.4	37.7	38.0
97.5°	35.1	35.2	35.5	35.9	36.1	36.4	36.7
100°	42.8	37.9	35.5	35.9	36.1	36.4	36.7
102.5°	117.5	64.1	37.5	37.6	37.6	37.7	37.8
105°	416.6	419.2	415.3	404.8	394.3	383.7	373.3
107.5°	513.4	514.6	515.8	516.9	518.1	519.2	520.3
110°	579.4	580.0	580.7	581.6	582.5	583.3	584.2



TEST NUMBER: P333067-840

CATALOG NUMBER: S124RDIW-S795D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	643.3	643.2	643.7	644.8	645.9	647.0	648.1
115°	740.5	741.0	741.3	741.3	741.3	741.3	741.3
117.5°	836.9	836.8	836.7	836.6	836.5	836.4	836.2
120°	897.7	898.3	898.3	897.7	897.1	896.6	896.0
122.5°	956.7	957.0	956.9	956.3	955.7	955.2	954.6
125°	1040.1	1040.9	1041.5	1041.8	1042.1	1042.4	1042.7
127.5°	1121.3	1121.1	1120.8	1120.6	1120.3	1120.1	1119.9
130°	1171.8	1172.2	1172.4	1172.4	1172.4	1172.4	1172.4
132.5°	1221.1	1221.4	1221.4	1221.2	1221.0	1220.7	1220.5
135°	1289.3	1289.9	1290.5	1291.1	1291.6	1292.2	1292.8
137.5°	1354.4	1355.1	1355.3	1355.1	1355.0	1354.8	1354.6
140°	1395.0	1395.8	1396.4	1396.7	1397.0	1397.4	1397.7
142.5°	1432.0	1432.7	1433.0	1433.1	1433.1	1433.2	1433.2
145°	1484.9	1485.2	1485.7	1486.2	1486.8	1487.4	1488.0
147.5°	1531.7	1531.9	1532.2	1532.5	1532.8	1533.0	1533.3
150°	1561.4	1561.4	1561.5	1561.8	1562.1	1562.4	1562.7
152.5°	1587.9	1588.3	1588.5	1588.3	1588.1	1588.0	1587.8
155°	1623.8	1625.0	1625.1	1624.3	1623.4	1622.4	1621.6
157.5°	1654.5	1656.0	1656.0	1654.5	1652.9	1651.4	1649.9
160°	1674.0	1675.8	1675.8	1674.0	1672.2	1670.5	1668.8
162.5°	1689.7	1691.4	1691.3	1689.4	1687.4	1685.4	1683.4
165°	1712.4	1714.8	1714.5	1712.0	1709.4	1706.8	1704.1
167.5°	1728.8	1731.4	1731.2	1728.3	1725.4	1722.5	1719.6
170°	1738.6	1740.9	1740.6	1737.8	1734.8	1731.9	1729.0
172.5°	1744.9	1747.3	1746.9	1743.6	1740.5	1737.4	1734.2
175°	1752.6	1755.2	1754.7	1751.3	1747.8	1744.2	1740.8
177.5°	1754.7	1756.7	1756.2	1753.3	1750.6	1747.8	1744.9
180°	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3	1751.3

(END OF REPORT)