

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333454-830

Luminaire Tested: **S125DIW-S1090D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333454-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10111.1 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36																				
2	88	80	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30																				
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26																				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19																				
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17																				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.4
10°-20°	429.6	4.2
20°-30°	697.6	6.9
30°-40°	850.9	8.4
40°-50°	774.1	7.7
50°-60°	616.6	6.1
60°-70°	429.5	4.2
70°-80°	229.0	2.3
80°-90°	61.8	0.6
90°-100°	69.6	0.7
100°-110°	428.7	4.2
110°-120°	777.5	7.7
120°-130°	997.8	9.9
130°-140°	1073.2	10.6
140°-150°	1007.4	10.0
150°-160°	814.9	8.1
160°-170°	527.0	5.2
170°-180°	181.8	1.8
0°-30°	1271.5	12.6
0°-40°	2122.4	21.0
0°-60°	3513.1	34.7
0°-90°	4233.4	41.9
90°-120°	1275.7	12.6
90°-150°	4354.1	43.1
90°-180°	5878.0	58.1
0°-180°	10111.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	34	1	34	1	34	16
95°	30	81	30	81	30	25
105°	421	417	421	417	421	381
115°	778	783	778	783	778	772
125°	1114	1114	1114	1114	1114	991
135°	1383	1389	1383	1389	1383	1068
145°	1606	1610	1606	1610	1606	1003
155°	1761	1774	1761	1774	1761	812
165°	1862	1872	1862	1872	1862	525
175°	1906	1914	1906	1914	1906	181
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	19.0	19.9	20.2	20.0	20.3	20.1	21.8	21.5	22.7	23.8	25.4
90°	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8	24.3	22.7	20.5
92.5°	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8	24.3	22.7	20.7
95°	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8	24.3	22.7	34.7
97.5°	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0	60.9	69.8	93.5
100°	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9	199.9	246.9	245.6
102.5°	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2	306.1	315.0	314.2
105°	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4	535.3	535.2	534.6
110°	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2	609.2	610.1	609.4



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3	681.6	682.8	682.4
115°	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2	790.4	791.7	791.5
117.5°	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3	895.9	897.6	896.4
120°	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1	962.8	963.4	962.4
122.5°	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8	1027.5	1028.1	1027.7
125°	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2	1122.5	1123.7	1123.7
127.5°	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5	1208.2	1208.9	1209.1
130°	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8	1264.7	1265.6	1265.3
132.5°	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4	1316.5	1316.7	1317.4
135°	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5	1394.1	1394.8	1395.3
137.5°	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4	1465.3	1465.1	1465.7
140°	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5	1508.9	1508.3	1508.5
142.5°	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7	1552.7	1552.6	1552.1
145°	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9	1613.5	1613.3	1613.3
147.5°	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2	1665.8	1665.5	1665.1
150°	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6	1699.0	1698.4	1697.7
152.5°	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2	1728.5	1727.9	1727.3
155°	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8	1768.9	1767.9	1767.3
157.5°	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4	1802.4	1801.4	1801.3
160°	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3	1823.1	1821.8	1821.5
162.5°	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5	1841.7	1839.9	1839.7
165°	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1	1866.2	1864.3	1864.1
167.5°	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8	1884.5	1882.3	1882.0
170°	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4	1893.9	1891.3	1891.0
172.5°	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8	1901.6	1899.3	1898.8
175°	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9	1909.5	1907.0	1906.7
177.5°	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3	1913.5	1911.8	1911.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	26.0	24.6	22.1	20.1	17.1	15.1	14.0	14.0	13.0	13.0	14.0
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9	20.1	18.3	16.6
95°	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9	79.9	79.0	78.0
97.5°	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8	170.5	172.2	174.0
100°	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0	237.9	238.8	239.8
102.5°	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2	307.4	308.6	309.8
105°	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2	418.4	419.7	420.9
107.5°	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
110°	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7	678.4	679.2	680.0
115°	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3	784.8	786.4	788.0
117.5°	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5	892.4	892.3	892.3
120°	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5	960.3	960.0	959.6
122.5°	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8	1021.9	1023.1	1024.4
125°	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8	1116.0	1118.2	1120.4
127.5°	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6	1204.2	1205.8	1207.4
130°	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1	1258.7	1260.3	1261.9
132.5°	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5	1313.4	1315.2	1317.1
135°	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0	1390.9	1392.9	1394.8
137.5°	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3	1461.9	1463.6	1465.2
140°	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8	1507.5	1508.1	1508.7
142.5°	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8	1549.2	1549.5	1549.9
145°	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4	1611.0	1611.7	1612.3
147.5°	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3	1664.2	1664.1	1664.0
150°	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1697.7	1697.1	1696.5
152.5°	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3	1729.9	1728.5	1727.1
155°	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6	1771.7	1769.8	1767.9
157.5°	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2	1805.1	1803.9	1802.8
160°	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9	1827.0	1825.1	1823.3
162.5°	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1	1845.2	1843.3	1841.4
165°	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5	1869.6	1867.6	1865.8
167.5°	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6	1887.7	1885.7	1883.8
170°	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9	1897.6	1895.5	1893.2
172.5°	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7	1904.5	1902.2	1900.1
175°	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0	1912.1	1910.3	1908.4
177.5°	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4	1915.9	1914.4	1912.9
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	15.0	16.5	16.5	17.4	17.8	19.3	19.1	21.5	22.8	24.1	23.8
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8	27.4	29.0	30.3
92.5°	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8	27.4	29.0	30.0
95°	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8	27.4	29.0	29.8
97.5°	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0	43.2	34.2	29.8
100°	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9	105.9	59.0	34.9
102.5°	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2	288.3	279.5	264.3
105°	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.6
107.5°	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4	535.4	535.5	535.0
110°	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2	607.3	606.3	606.1



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3	679.2	678.0	677.1
115°	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2	788.0	786.6	785.1
117.5°	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3	892.7	891.0	889.8
120°	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1	961.5	960.9	959.8
122.5°	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8	1026.2	1025.6	1024.4
125°	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2	1119.9	1118.7	1117.6
127.5°	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5	1206.8	1206.1	1204.6
130°	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8	1262.8	1261.9	1260.6
132.5°	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4	1316.2	1316.0	1315.0
135°	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5	1392.9	1392.2	1390.9
137.5°	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4	1465.5	1465.7	1464.9
140°	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5	1510.1	1510.8	1510.1
142.5°	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7	1552.9	1553.0	1552.2
145°	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9	1614.2	1614.5	1613.7
147.5°	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2	1666.6	1667.0	1666.0
150°	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6	1700.3	1700.9	1700.0
152.5°	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2	1729.8	1730.4	1729.6
155°	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8	1770.8	1771.7	1770.8
157.5°	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4	1804.4	1805.4	1804.7
160°	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3	1825.6	1826.8	1826.3
162.5°	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5	1845.3	1847.0	1846.5
165°	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1	1870.1	1872.0	1871.6
167.5°	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8	1889.0	1891.3	1891.0
170°	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4	1898.9	1901.4	1901.3
172.5°	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8	1906.1	1908.4	1908.1
175°	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9	1914.5	1917.0	1916.8
177.5°	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3	1917.0	1918.8	1918.7
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	25.1	24.8	25.0	26.1	25.0	24.8	25.1	23.8	24.1	22.8	21.5
90°	31.2	32.1	33.1	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8
92.5°	30.4	30.9	31.4	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8
95°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8
97.5°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0
100°	33.6	32.3	31.1	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9
102.5°	242.8	221.4	199.9	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2
105°	422.4	422.1	421.7	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8
107.5°	534.0	533.1	532.2	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4
110°	606.3	606.6	607.0	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	676.7	676.3	675.8	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3
115°	783.3	781.3	779.4	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2
117.5°	889.0	888.2	887.3	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3
120°	958.2	956.6	955.1	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1
122.5°	1022.6	1020.7	1018.9	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8
125°	1116.6	1115.7	1114.7	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2
127.5°	1202.2	1200.0	1197.6	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5
130°	1259.0	1257.4	1255.8	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8
132.5°	1313.5	1311.9	1310.3	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4
135°	1389.0	1387.1	1385.3	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5
137.5°	1463.2	1461.6	1459.9	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4
140°	1508.3	1506.4	1504.5	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5
142.5°	1550.2	1548.3	1546.4	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7
145°	1611.8	1610.0	1608.1	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9
147.5°	1663.8	1661.5	1659.3	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2
150°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6
152.5°	1727.3	1725.0	1722.8	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2
155°	1768.4	1765.9	1763.3	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8
157.5°	1802.1	1799.6	1797.1	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4
160°	1823.7	1821.2	1818.6	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3
162.5°	1843.8	1841.0	1838.2	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5
165°	1869.2	1866.6	1864.1	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1
167.5°	1888.2	1885.4	1882.5	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8
170°	1898.5	1895.6	1892.7	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4
172.5°	1905.3	1902.4	1899.6	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8
175°	1914.0	1911.2	1908.4	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9
177.5°	1916.7	1914.7	1912.6	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	19.1	19.3	17.8	17.4	16.5	16.5	15.0	14.0	13.0	13.0	14.0
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	24.3	22.7	20.7	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9
95°	24.3	22.7	34.7	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9
97.5°	60.9	69.8	93.5	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8
100°	199.9	246.9	245.6	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0
102.5°	306.1	315.0	314.2	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2
105°	422.8	422.8	422.8	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2
107.5°	535.3	535.2	534.6	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3
110°	609.2	610.1	609.4	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	681.6	682.8	682.4	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7
115°	790.4	791.7	791.5	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3
117.5°	895.9	897.6	896.4	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5
120°	962.8	963.4	962.4	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5
122.5°	1027.5	1028.1	1027.7	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8
125°	1122.5	1123.7	1123.7	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8
127.5°	1208.2	1208.9	1209.1	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6
130°	1264.7	1265.6	1265.3	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1
132.5°	1316.5	1316.7	1317.4	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5
135°	1394.1	1394.8	1395.3	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0
137.5°	1465.3	1465.1	1465.7	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3
140°	1508.9	1508.3	1508.5	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8
142.5°	1552.7	1552.6	1552.1	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8
145°	1613.5	1613.3	1613.3	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4
147.5°	1665.8	1665.5	1665.1	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3
150°	1699.0	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1695.8	1696.5	1697.1	1697.7
152.5°	1728.5	1727.9	1727.3	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3
155°	1768.9	1767.9	1767.3	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6
157.5°	1802.4	1801.4	1801.3	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2
160°	1823.1	1821.8	1821.5	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9
162.5°	1841.7	1839.9	1839.7	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1
165°	1866.2	1864.3	1864.1	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5
167.5°	1884.5	1882.3	1882.0	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6
170°	1893.9	1891.3	1891.0	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9
172.5°	1901.6	1899.3	1898.8	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7
175°	1909.5	1907.0	1906.7	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0
177.5°	1913.5	1911.8	1911.5	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	14.0	15.1	17.1	20.1	22.1	24.6	26.0	25.4	23.8	22.7	21.5
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8
92.5°	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8
95°	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8
97.5°	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0
100°	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9
102.5°	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2
105°	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4
110°	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3
115°	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2
117.5°	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3
120°	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1
122.5°	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8
125°	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2
127.5°	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5
130°	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8
132.5°	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4
135°	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5
137.5°	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4
140°	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5
142.5°	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7
145°	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9
147.5°	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2
150°	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6
152.5°	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2
155°	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8
157.5°	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4
160°	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3
162.5°	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5
165°	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1
167.5°	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8
170°	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4
172.5°	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8
175°	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9
177.5°	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	21.8	20.1	20.3	20.0	20.2	19.9	19.0
90°	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333454-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)