

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333455-830

Luminaire Tested: **S125DIW-S1090D1560U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333455-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9330.5 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33				
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28	24				
5	68	56	48	43	62	52	45	40	44	39	35	36	32	29	29	27	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	32	53	42	35	30	36	30	27	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.5
10°-20°	429.6	4.6
20°-30°	697.6	7.5
30°-40°	850.9	9.1
40°-50°	774.1	8.3
50°-60°	616.6	6.6
60°-70°	429.5	4.6
70°-80°	229.0	2.5
80°-90°	61.8	0.7
90°-100°	122.3	1.3
100°-110°	361.3	3.9
110°-120°	611.9	6.6
120°-130°	805.3	8.6
130°-140°	902.4	9.7
140°-150°	884.4	9.5
150°-160°	742.8	8.0
160°-170°	493.8	5.3
170°-180°	172.8	1.9
0°-30°	1271.5	13.6
0°-40°	2122.4	22.7
0°-60°	3513.1	37.7
0°-90°	4233.4	45.4
90°-120°	1095.5	11.7
90°-150°	3687.7	39.5
90°-180°	5097.0	54.6
0°-180°	9330.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	34	1	34	1	34	21
95°	122	92	122	92	122	124
105°	352	324	352	324	352	373
115°	618	613	618	613	618	612
125°	900	894	900	894	900	803
135°	1167	1163	1167	1163	1167	900
145°	1414	1409	1414	1409	1414	883
155°	1612	1612	1612	1612	1612	742
165°	1748	1753	1748	1753	1748	493
175°	1815	1822	1815	1822	1815	172
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	19.0	19.9	20.2	20.0	20.4	20.1	21.8	21.5	22.7	23.8	25.4
90°	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9	24.3	22.7	20.5
92.5°	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7	56.6	54.6	51.8
95°	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9	111.7	109.4	106.3
97.5°	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4	176.3	174.3	169.9
100°	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2	220.4	217.4	213.4
102.5°	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2	266.1	263.0	260.9
105°	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6	341.7	339.8	337.8
107.5°	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8	422.8	421.9	420.5
110°	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6	478.5	477.6	476.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4	534.9	534.5	533.3
115°	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6	620.9	621.2	620.6
117.5°	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9	705.6	705.4	704.7
120°	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4	763.4	763.4	763.0
122.5°	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7	819.9	820.2	819.4
125°	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9	903.4	904.1	903.8
127.5°	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3	985.6	986.0	985.6
130°	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9	1040.2	1040.6	1039.9
132.5°	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2	1092.5	1092.9	1093.0
135°	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7	1172.7	1172.7	1172.4
137.5°	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1	1250.8	1250.4	1249.6
140°	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5	1299.9	1299.3	1298.4
142.5°	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9	1348.5	1348.1	1347.0
145°	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6	1418.6	1418.6	1417.7
147.5°	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3	1482.5	1481.8	1481.0
150°	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9	1523.9	1523.9	1522.6
152.5°	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8	1561.0	1560.3	1559.7
155°	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9	1614.7	1613.4	1613.1
157.5°	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8	1661.6	1660.3	1660.0
160°	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3	1690.0	1688.8	1688.5
162.5°	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0	1716.5	1714.9	1714.9
165°	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8	1752.6	1751.3	1751.0
167.5°	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4	1778.5	1776.6	1776.6
170°	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3	1794.4	1792.5	1792.5
172.5°	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7	1805.8	1803.9	1803.9
175°	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5	1818.5	1816.7	1816.7
177.5°	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3	1824.8	1823.3	1823.4
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	26.0	24.6	22.1	20.1	17.1	15.1	14.0	14.0	13.0	13.0	14.0
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4	36.2	38.0	39.7
95°	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4	93.0	93.7	94.3
97.5°	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5	153.7	154.0	154.3
100°	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0
102.5°	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9	249.2	250.4	251.7
105°	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1	325.6	327.3	328.9
107.5°	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2	409.8	411.4	413.0
110°	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3	467.9	469.4	471.0



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4	526.2	527.1	527.8
115°	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7	614.0	615.2	616.4
117.5°	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2	700.8	701.3	701.9
120°	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8	756.4	758.0	759.6
122.5°	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0	814.5	815.1	815.7
125°	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1	896.0	898.0	899.8
127.5°	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4	980.5	981.6	982.6
130°	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6	1032.2	1033.8	1035.3
132.5°	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8	1084.4	1086.9	1089.6
135°	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8	1164.7	1166.6	1168.5
137.5°	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0	1240.9	1242.6	1244.4
140°	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9	1289.5	1291.0	1292.6
142.5°	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8	1338.1	1339.4	1340.8
145°	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7	1409.9	1411.3	1412.5
147.5°	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3	1475.9	1476.6	1477.3
150°	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6	1519.3	1519.0	1518.6
152.5°	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9	1556.4	1556.9	1557.3
155°	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0	1661.3	1660.7	1659.9
160°	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6	1690.6	1689.7	1688.8
162.5°	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8	1717.0	1716.4	1715.7
165°	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8	1752.1	1751.4	1750.9
167.5°	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3	1781.0	1779.8	1778.5
170°	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2	1797.0	1795.6	1794.4
172.5°	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6	1808.4	1807.0	1805.8
175°	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4	1821.1	1819.9	1818.5
177.5°	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9	1827.9	1826.9	1825.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	15.0	16.5	16.5	17.4	17.8	19.3	19.1	21.5	22.8	24.1	23.8
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9	27.5	29.0	30.3
92.5°	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7	60.8	63.0	64.3
95°	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9	116.1	118.3	119.7
97.5°	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4	180.5	182.6	183.9
100°	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2	226.0	228.8	230.6
102.5°	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2	272.3	275.3	277.4
105°	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6	345.4	347.3	348.7
107.5°	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8	424.7	425.7	426.1
110°	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6	480.5	481.5	481.7



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4	535.8	536.2	536.2
115°	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6	620.3	619.9	619.6
117.5°	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9	706.2	706.3	705.9
120°	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4	763.4	763.4	762.7
122.5°	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7	819.4	819.2	818.6
125°	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9	902.2	901.5	901.1
127.5°	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3	985.1	984.7	984.2
130°	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9	1039.6	1039.2	1038.8
132.5°	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2	1091.9	1091.6	1091.0
135°	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7	1172.7	1172.7	1172.1
137.5°	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1	1251.5	1251.9	1251.3
140°	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5	1301.2	1301.7	1301.3
142.5°	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9	1349.2	1349.7	1349.1
145°	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6	1418.6	1418.6	1418.1
147.5°	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3	1484.0	1484.8	1484.1
150°	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9	1523.9	1523.9	1523.5
152.5°	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8	1562.5	1563.3	1563.1
155°	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9	1617.2	1618.4	1618.3
157.5°	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8	1664.2	1665.4	1665.0
160°	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3	1692.5	1693.8	1693.7
162.5°	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0	1719.5	1721.0	1720.8
165°	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8	1755.1	1756.3	1756.1
167.5°	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4	1782.3	1784.1	1784.1
170°	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3	1798.2	1800.1	1800.0
172.5°	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7	1809.6	1811.5	1811.5
175°	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5	1822.4	1824.3	1824.1
177.5°	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3	1827.8	1829.3	1829.2
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	25.1	24.8	25.0	26.2	25.0	24.8	25.1	23.8	24.1	22.8	21.5
90°	31.3	32.2	33.2	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9
92.5°	65.0	65.7	66.4	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7
95°	120.4	121.0	121.6	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9
97.5°	184.3	184.6	185.0	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4
100°	231.2	231.9	232.5	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2
102.5°	278.2	279.1	280.0	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2
105°	349.7	350.6	351.6	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6
107.5°	426.0	426.0	425.9	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8
110°	481.5	481.1	480.8	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	535.6	535.1	534.5	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4
115°	619.3	619.0	618.7	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6
117.5°	704.6	703.3	702.1	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9
120°	761.5	760.2	758.9	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4
122.5°	817.6	816.5	815.5	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7
125°	900.8	900.4	900.1	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9
127.5°	983.5	983.0	982.3	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3
130°	1038.2	1037.6	1036.9	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9
132.5°	1090.1	1089.2	1088.4	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2
135°	1170.8	1169.6	1168.3	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7
137.5°	1249.7	1248.1	1246.5	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1
140°	1299.8	1298.2	1296.6	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5
142.5°	1347.5	1346.0	1344.3	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9
145°	1417.2	1416.3	1415.3	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6
147.5°	1482.0	1479.8	1477.7	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3
150°	1522.9	1522.3	1521.6	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9
152.5°	1562.0	1560.9	1559.7	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8
155°	1616.7	1615.1	1613.5	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9
157.5°	1662.8	1660.8	1658.7	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8
160°	1692.1	1690.5	1688.9	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3
162.5°	1719.0	1717.1	1715.3	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0
165°	1754.2	1752.3	1750.4	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8
167.5°	1782.2	1780.3	1778.3	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4
170°	1797.7	1795.5	1793.3	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3
172.5°	1809.5	1807.5	1805.5	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7
175°	1821.9	1819.7	1817.5	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5
177.5°	1827.4	1825.6	1823.8	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	19.1	19.3	17.8	17.4	16.5	16.5	15.0	14.0	13.0	13.0	14.0
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	56.6	54.6	51.8	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4
95°	111.7	109.4	106.3	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4
97.5°	176.3	174.3	169.9	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5
100°	220.4	217.4	213.4	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0
102.5°	266.1	263.0	260.9	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9
105°	341.7	339.8	337.8	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1
107.5°	422.8	421.9	420.5	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2
110°	478.5	477.6	476.6	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.9	534.5	533.3	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4
115°	620.9	621.2	620.6	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7
117.5°	705.6	705.4	704.7	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2
120°	763.4	763.4	763.0	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8
122.5°	819.9	820.2	819.4	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0
125°	903.4	904.1	903.8	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1
127.5°	985.6	986.0	985.6	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4
130°	1040.2	1040.6	1039.9	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6
132.5°	1092.5	1092.9	1093.0	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8
135°	1172.7	1172.7	1172.4	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8
137.5°	1250.8	1250.4	1249.6	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0
140°	1299.9	1299.3	1298.4	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9
142.5°	1348.5	1348.1	1347.0	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8
145°	1418.6	1418.6	1417.7	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7
147.5°	1482.5	1481.8	1481.0	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3
150°	1523.9	1523.9	1522.6	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6
152.5°	1561.0	1560.3	1559.7	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9
155°	1614.7	1613.4	1613.1	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1661.6	1660.3	1660.0	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0
160°	1690.0	1688.8	1688.5	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6
162.5°	1716.5	1714.9	1714.9	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8
165°	1752.6	1751.3	1751.0	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8
167.5°	1778.5	1776.6	1776.6	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3
170°	1794.4	1792.5	1792.5	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2
172.5°	1805.8	1803.9	1803.9	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6
175°	1818.5	1816.7	1816.7	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4
177.5°	1824.8	1823.3	1823.4	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	14.0	15.1	17.1	20.1	22.1	24.6	26.0	25.4	23.8	22.7	21.5
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9
92.5°	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7
95°	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9
97.5°	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4
100°	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2
102.5°	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2
105°	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6
107.5°	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8
110°	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4
115°	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6
117.5°	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9
120°	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4
122.5°	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7
125°	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9
127.5°	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3
130°	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9
132.5°	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2
135°	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7
137.5°	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1
140°	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5
142.5°	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9
145°	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6
147.5°	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3
150°	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9
152.5°	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8
155°	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9
157.5°	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8
160°	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3
162.5°	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0
165°	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8
167.5°	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4
170°	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3
172.5°	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7
175°	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5
177.5°	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	21.8	20.1	20.4	20.0	20.2	19.9	19.0
90°	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333455-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)