

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333459-830

Luminaire Tested: **S125DIW-S1090D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333459-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1560U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9286.2 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.6	1.6
10°-20°	428.4	4.6
20°-30°	632.5	6.8
30°-40°	738.0	7.9
40°-50°	741.2	8.0
50°-60°	650.7	7.0
60°-70°	484.8	5.2
70°-80°	277.2	3.0
80°-90°	84.6	0.9
90°-100°	122.3	1.3
100°-110°	361.3	3.9
110°-120°	611.9	6.6
120°-130°	805.3	8.7
130°-140°	902.4	9.7
140°-150°	884.4	9.5
150°-160°	742.8	8.0
160°-170°	493.8	5.3
170°-180°	172.8	1.9
0°-30°	1212.5	13.1
0°-40°	1950.5	21.0
0°-60°	3342.4	36.0
0°-90°	4189.1	45.1
90°-120°	1095.5	11.8
90°-150°	3687.7	39.7
90°-180°	5097.0	54.9
0°-180°	9286.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	13	23	30	34	9
95°	92	96	109	119	122	99
105°	324	331	340	348	352	346
115°	613	618	621	620	618	606
125°	894	902	904	901	900	800
135°	1163	1171	1173	1172	1167	896
145°	1409	1414	1419	1418	1414	880
155°	1612	1612	1613	1618	1612	742
165°	1753	1750	1751	1756	1748	494
175°	1822	1817	1817	1824	1815	173
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.8	28.3	28.7	29.3	29.8	30.2	30.3	30.5	30.8	31.0	31.3
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	34.4	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6
95°	92.4	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7
97.5°	153.5	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3
100°	199.0	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4
102.5°	247.9	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1
105°	324.1	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7
107.5°	408.2	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8
110°	466.3	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5



TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9
115°	612.7	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9
117.5°	700.2	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6
120°	754.8	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4
122.5°	814.0	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9
125°	894.1	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4
127.5°	979.4	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6
130°	1030.6	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2
132.5°	1081.8	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5
135°	1162.8	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7
137.5°	1239.0	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8
140°	1287.9	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9
142.5°	1336.8	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5
145°	1408.7	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6
147.5°	1475.3	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5
150°	1519.6	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9
152.5°	1555.9	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0
155°	1612.0	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7
157.5°	1662.0	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6
160°	1691.6	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0
162.5°	1717.8	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5
165°	1752.8	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6
167.5°	1782.3	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5
170°	1798.2	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4
172.5°	1809.6	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8
175°	1822.4	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5
177.5°	1828.9	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	31.7	32.0	32.2	32.3	32.0	31.8	31.5	31.3
90°	25.9	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	58.7	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	113.9	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	178.4	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	223.2	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	269.2	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	343.6	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	423.8	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	479.6	480.5	481.5	481.7	481.5	481.1	480.8	480.5





TEST NUMBER: P333459-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	535.4	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.6	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	705.9	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.7	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.9	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.3	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.9	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1092.2	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.1	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1300.5	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1348.9	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1483.3	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1561.8	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1615.9	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1662.8	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1691.3	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1718.0	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1753.8	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1780.4	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1796.3	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1807.7	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1820.5	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1826.3	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)