

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332834-940

Luminaire Tested: **S124DIW-S1020D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332834-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8777.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	1.7
10°-20°	408.3	4.7
20°-30°	600.9	6.8
30°-40°	698.6	8.0
40°-50°	698.6	8.0
50°-60°	611.1	7.0
60°-70°	453.8	5.2
70°-80°	257.8	2.9
80°-90°	79.6	0.9
90°-100°	114.7	1.3
100°-110°	339.7	3.9
110°-120°	576.5	6.6
120°-130°	760.2	8.7
130°-140°	853.8	9.7
140°-150°	839.0	9.6
150°-160°	705.6	8.0
160°-170°	469.5	5.3
170°-180°	164.4	1.9
0°-30°	1154.1	13.1
0°-40°	1852.6	21.1
0°-60°	3162.3	36.0
0°-90°	3953.6	45.0
90°-120°	1030.9	11.7
90°-150°	3483.9	39.7
90°-180°	4823.0	55.0
0°-180°	8777.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	4	19	30	37	40	9
95°	81	93	102	106	106	90
105°	313	315	320	324	328	332
115°	586	586	584	582	581	578
125°	854	854	852	850	847	761
135°	1101	1109	1109	1106	1102	852
145°	1338	1343	1344	1343	1339	837
155°	1533	1533	1531	1536	1531	705
165°	1669	1665	1662	1669	1665	470
175°	1736	1729	1728	1736	1728	165
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	26.5	26.9	27.3	27.7	28.2	28.5	28.8	29.1	29.3	29.6	30.0
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	28.8	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3
95°	80.7	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1
97.5°	140.9	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6
100°	188.2	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3
102.5°	237.7	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7
105°	313.3	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9
107.5°	392.6	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8
110°	446.4	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.3	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3
115°	586.2	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3
117.5°	665.3	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4
120°	718.0	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8
122.5°	772.8	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1
125°	853.8	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9
127.5°	927.2	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4
130°	978.8	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3
132.5°	1031.5	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9
135°	1101.2	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7
137.5°	1177.1	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1
140°	1227.6	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9
142.5°	1273.8	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4
145°	1337.8	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1401.3	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4
150°	1440.0	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1476.6	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6
155°	1532.8	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7
157.5°	1580.1	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3
160°	1608.1	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3
162.5°	1633.9	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7
165°	1668.6	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7
167.5°	1695.2	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7
170°	1710.3	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6
172.5°	1721.0	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7
175°	1735.8	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8
177.5°	1740.6	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	30.3	30.7	31.0	31.3	31.4	31.5	31.7	31.7
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	55.4	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.0	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	163.8	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	206.9	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	252.5	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	321.8	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	396.7	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	446.6	445.9	445.3	445.5	446.4	447.3	448.2	449.1



TEST NUMBER: P332834-940

CATALOG NUMBER: S124DIW-S1020D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.2	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.9	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	662.5	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	716.3	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	771.1	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	851.2	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.9	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.7	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1032.2	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1108.0	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1181.4	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.7	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.3	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1344.0	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.2	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1482.3	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1579.2	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1607.2	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1632.3	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1665.4	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1693.4	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1708.5	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1719.8	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1738.7	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)