

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333489-830

Luminaire Tested: **S125DIW-S1270D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333489-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9934.6 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.1	1.8
10°-20°	494.7	5.0
20°-30°	730.5	7.4
30°-40°	852.4	8.6
40°-50°	856.1	8.6
50°-60°	751.5	7.6
60°-70°	559.9	5.6
70°-80°	320.2	3.2
80°-90°	97.1	1.0
90°-100°	122.3	1.2
100°-110°	361.3	3.6
110°-120°	611.9	6.2
120°-130°	805.3	8.1
130°-140°	902.4	9.1
140°-150°	884.4	8.9
150°-160°	742.8	7.5
160°-170°	493.8	5.0
170°-180°	172.8	1.7
0°-30°	1400.3	14.1
0°-40°	2252.7	22.7
0°-60°	3860.3	38.9
0°-90°	4837.5	48.7
90°-120°	1095.5	11.0
90°-150°	3687.7	37.1
90°-180°	5097.0	51.3
0°-180°	9934.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	13	23	30	34	9
95°	92	96	109	119	122	99
105°	324	331	340	348	352	346
115°	613	618	621	620	618	606
125°	894	902	904	901	900	800
135°	1163	1171	1173	1172	1167	896
145°	1409	1414	1419	1418	1414	880
155°	1612	1612	1613	1618	1612	742
165°	1753	1750	1751	1756	1748	494
175°	1822	1817	1817	1824	1815	173
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	32.0	32.5	33.1	33.6	34.0	34.4	34.6	34.8	35.0	35.2	35.4
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	34.4	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6
95°	92.4	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7
97.5°	153.5	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3
100°	199.0	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4
102.5°	247.9	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1
105°	324.1	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7
107.5°	408.2	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8
110°	466.3	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9
115°	612.7	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9
117.5°	700.2	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6
120°	754.8	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4
122.5°	814.0	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9
125°	894.1	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4
127.5°	979.4	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6
130°	1030.6	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2
132.5°	1081.8	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5
135°	1162.8	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7
137.5°	1239.0	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8
140°	1287.9	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9
142.5°	1336.8	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5
145°	1408.7	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6
147.5°	1475.3	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5
150°	1519.6	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9
152.5°	1555.9	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0
155°	1612.0	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7
157.5°	1662.0	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6
160°	1691.6	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0
162.5°	1717.8	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5
165°	1752.8	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6
167.5°	1782.3	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5
170°	1798.2	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4
172.5°	1809.6	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8
175°	1822.4	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5
177.5°	1828.9	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	35.7	36.1	36.4	36.4	36.0	35.7	35.3	35.1
90°	25.9	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	58.7	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	113.9	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	178.4	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	223.2	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	269.2	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	343.6	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	423.8	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	479.6	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333489-830

CATALOG NUMBER: S125DIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	535.4	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.6	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	705.9	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.7	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.9	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.3	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.9	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1092.2	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.1	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1300.5	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1348.9	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1483.3	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1561.8	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1615.9	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1662.8	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1691.3	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1718.0	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1753.8	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1780.4	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1796.3	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1807.7	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1820.5	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1826.3	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)