

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332815-940

Luminaire Tested: **S124DIW-S1020D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332815-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6688.4 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	2.2
10°-20°	408.3	6.1
20°-30°	600.9	9.0
30°-40°	698.6	10.4
40°-50°	698.6	10.4
50°-60°	611.1	9.1
60°-70°	453.8	6.8
70°-80°	257.8	3.9
80°-90°	77.0	1.2
90°-100°	30.3	0.5
100°-110°	193.0	2.9
110°-120°	369.2	5.5
120°-130°	468.7	7.0
130°-140°	501.4	7.5
140°-150°	468.9	7.0
150°-160°	378.1	5.7
160°-170°	243.9	3.6
170°-180°	84.1	1.3
0°-30°	1154.1	17.3
0°-40°	1852.6	27.7
0°-60°	3162.3	47.3
0°-90°	3951.0	59.1
90°-120°	592.4	8.9
90°-150°	2031.4	30.4
90°-180°	2737.0	40.9
0°-180°	6688.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	2	9	14	18	20	5
95°	36	15	14	18	19	47
105°	199	203	206	211	189	208
115°	372	374	373	375	375	366
125°	523	525	524	526	527	467
135°	649	648	651	652	653	500
145°	748	750	750	751	752	467
155°	820	821	819	821	820	378
165°	865	862	862	866	861	244
175°	885	881	882	887	880	84
180°	885	885	885	885	885	



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	26.0	26.1	26.2	26.4	26.5	26.5	26.6	26.6	26.6	26.6	26.8
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	8.4	8.5	8.6	8.6	8.6	9.4	10.5	11.7	12.8	14.0	14.9
95°	36.4	31.4	26.4	21.4	16.4	14.0	14.1	14.3	14.4	14.5	15.4
97.5°	77.3	80.4	83.6	86.7	89.8	83.1	66.7	50.3	33.9	17.5	17.6
100°	108.5	111.2	113.9	116.5	119.1	110.3	90.1	69.7	49.4	29.2	26.7
102.5°	143.5	145.4	147.4	149.4	151.2	150.9	148.3	145.6	142.9	140.4	113.3
105°	199.2	200.1	201.0	201.9	202.8	203.6	204.3	205.0	205.8	206.5	207.9
107.5°	251.0	251.5	251.9	252.4	252.8	253.5	254.5	255.5	256.5	257.4	258.2
110°	286.0	286.4	286.9	287.3	287.7	288.4	289.3	290.2	291.1	291.9	292.2



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	319.9	320.7	321.5	322.2	323.0	323.6	324.0	324.4	324.9	325.3	325.2
115°	372.0	372.5	372.9	373.3	373.7	373.9	373.7	373.6	373.4	373.3	373.6
117.5°	419.0	419.5	420.2	420.7	421.3	421.8	422.1	422.4	422.8	423.1	423.0
120°	450.8	451.4	451.9	452.5	453.1	453.3	453.2	453.1	452.9	452.7	453.1
122.5°	480.5	480.7	481.1	481.4	481.8	482.1	482.3	482.5	482.7	483.0	483.1
125°	522.9	523.5	524.1	524.7	525.2	525.4	525.1	524.9	524.5	524.2	524.7
127.5°	563.1	563.3	563.5	563.6	563.7	564.2	564.8	565.5	566.1	566.9	566.8
130°	589.1	589.2	589.4	589.5	589.7	590.0	590.4	590.8	591.3	591.7	591.9
132.5°	613.0	613.2	613.5	613.7	613.9	614.4	614.9	615.5	616.1	616.6	616.8
135°	648.6	648.5	648.4	648.2	648.1	648.3	648.9	649.4	650.1	650.7	650.9
137.5°	680.3	680.4	680.5	680.5	680.6	680.9	681.5	682.2	682.9	683.5	683.8
140°	701.0	701.2	701.5	701.9	702.1	702.4	702.8	703.0	703.3	703.6	704.0
142.5°	719.5	720.1	720.6	721.0	721.6	721.9	722.1	722.3	722.5	722.6	723.0
145°	748.0	748.4	748.9	749.3	749.8	749.9	749.9	749.9	749.9	749.9	750.1
147.5°	770.6	771.4	772.2	773.0	773.9	774.2	774.1	773.9	773.7	773.6	773.7
150°	787.0	787.6	788.2	788.8	789.3	789.6	789.4	789.3	789.2	789.0	789.0
152.5°	800.8	801.2	801.7	802.2	802.6	802.7	802.5	802.3	802.0	801.7	801.9
155°	820.1	820.3	820.4	820.6	820.7	820.6	820.1	819.7	819.2	818.8	819.4
157.5°	836.4	836.3	836.2	836.2	836.1	835.7	835.3	834.7	834.2	833.7	834.5
160°	845.9	845.4	845.1	844.6	844.2	843.8	843.7	843.6	843.4	843.3	844.2
162.5°	854.3	853.8	853.3	852.7	852.1	851.8	851.7	851.5	851.3	851.2	852.1
165°	865.1	864.3	863.6	862.9	862.2	861.8	861.8	861.8	861.8	861.8	863.0
167.5°	873.6	872.8	872.1	871.3	870.5	870.1	870.0	870.0	869.9	869.8	871.0
170°	878.3	877.4	876.6	875.7	874.9	874.4	874.6	874.8	874.9	875.0	876.2
172.5°	881.5	880.7	879.8	878.9	878.0	877.6	877.8	877.9	878.1	878.2	879.4
175°	884.9	884.0	883.2	882.3	881.5	881.1	881.2	881.4	881.5	881.6	883.0
177.5°	886.5	885.7	884.9	884.0	883.2	883.0	883.2	883.4	883.7	883.9	884.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	26.9	27.1	27.3	27.4	27.5	27.6	27.6	27.6
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	15.8	16.7	17.6	18.0	18.1	18.2	18.2	18.3
95°	16.3	17.2	18.1	18.6	18.7	18.9	19.1	19.2
97.5°	17.7	17.7	17.8	17.9	18.1	18.3	18.4	18.5
100°	24.2	21.6	19.1	17.9	18.1	18.3	18.4	18.5
102.5°	86.4	59.4	32.5	18.9	19.0	19.0	19.0	19.1
105°	209.2	210.4	211.8	209.8	204.6	199.2	193.9	188.7
107.5°	258.8	259.4	260.1	260.6	261.3	261.8	262.3	262.9
110°	292.5	292.7	293.1	293.5	293.9	294.4	294.8	295.2



TEST NUMBER: P332815-940

CATALOG NUMBER: S124DIW-S1020D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	325.1	325.1	325.0	325.3	325.8	326.4	327.0	327.5
115°	373.9	374.2	374.5	374.6	374.6	374.6	374.6	374.6
117.5°	422.9	422.9	422.8	422.8	422.8	422.7	422.6	422.6
120°	453.3	453.6	453.9	453.9	453.6	453.3	453.1	452.7
122.5°	483.3	483.5	483.7	483.6	483.3	483.0	482.7	482.4
125°	525.1	525.6	526.0	526.3	526.5	526.6	526.7	526.9
127.5°	566.7	566.6	566.5	566.4	566.3	566.1	566.1	566.0
130°	592.0	592.2	592.4	592.4	592.4	592.4	592.4	592.4
132.5°	616.9	617.1	617.2	617.2	617.2	617.0	616.9	616.8
135°	651.2	651.6	651.8	652.1	652.4	652.7	653.0	653.3
137.5°	684.1	684.5	684.7	684.9	684.8	684.7	684.7	684.6
140°	704.5	704.9	705.3	705.7	705.8	706.0	706.1	706.2
142.5°	723.4	723.6	724.0	724.2	724.2	724.2	724.2	724.2
145°	750.2	750.4	750.6	750.7	751.0	751.4	751.6	751.9
147.5°	773.8	774.0	774.1	774.3	774.4	774.5	774.7	774.8
150°	789.0	789.0	789.0	789.1	789.3	789.3	789.5	789.6
152.5°	802.2	802.4	802.6	802.7	802.6	802.5	802.5	802.4
155°	819.9	820.6	821.1	821.2	820.7	820.3	819.8	819.5
157.5°	835.3	836.1	836.8	836.8	836.1	835.3	834.5	833.7
160°	845.1	845.9	846.8	846.8	845.9	845.1	844.2	843.3
162.5°	853.0	853.8	854.7	854.7	853.7	852.7	851.7	850.7
165°	864.2	865.3	866.5	866.5	865.1	863.8	862.5	861.1
167.5°	872.4	873.6	874.9	874.9	873.3	871.9	870.4	869.0
170°	877.4	878.6	879.8	879.6	878.2	876.6	875.2	873.7
172.5°	880.6	881.7	882.9	882.7	881.1	879.6	878.0	876.4
175°	884.3	885.6	887.0	886.7	884.9	883.2	881.5	879.7
177.5°	885.8	886.7	887.7	887.4	886.0	884.6	883.2	881.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9

(END OF REPORT)