

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332854-940

Luminaire Tested: **S124DIW-S1195D1340U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332854-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8894.8 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45				45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38				38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	42	39	37	33				33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28				28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25				25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22				22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19				19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17				17
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18	16				16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13875	13875	13875	13875
5°	16339	13910	12277	13910
10°	19563	13849	11053	13849
15°	23147	13709	10151	13709
20°	25775	13566	9346	13566
25°	26191	13356	8790	13356
30°	22287	13154	8614	13154
35°	17134	12827	8615	12827
40°	13355	12440	8778	12440
45°	11136	11860	8926	11860
50°	9800	11150	9229	11150
55°	8978	10301	9600	10301
60°	8414	9541	10046	9541
65°	7834	8692	10418	8692
70°	7159	7848	10655	7848
75°	6394	6906	10524	6906
80°	5360	5658	10195	5658
85°	3955	4085	9763	4085



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.4	1.9
10°-20°	516.1	5.8
20°-30°	818.4	9.2
30°-40°	910.7	10.2
40°-50°	829.0	9.3
50°-60°	677.5	7.6
60°-70°	483.6	5.4
70°-80°	266.3	3.0
80°-90°	77.2	0.9
90°-100°	98.6	1.1
100°-110°	292.2	3.3
110°-120°	495.9	5.6
120°-130°	653.9	7.4
130°-140°	734.3	8.3
140°-150°	721.6	8.1
150°-160°	606.9	6.8
160°-170°	403.8	4.5
170°-180°	141.4	1.6
0°-30°	1501.9	16.9
0°-40°	2412.6	27.1
0°-60°	3919.1	44.1
0°-90°	4746.3	53.4
90°-120°	886.7	10.0
90°-150°	2996.4	33.7
90°-180°	4149.0	46.6
0°-180°	8894.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1719	1719	1719	1719	1719	
5°	2016	1716	1515	1716	2016	205
15°	2770	1640	1215	1640	2770	782
25°	2940	1499	987	1499	2940	1296
35°	1739	1302	874	1302	1739	1104
45°	975	1039	782	1039	975	768
55°	638	732	682	732	638	576
65°	410	455	545	455	410	406
75°	205	221	337	221	205	218
85°	43	44	105	44	43	53
90°	35	4	35	4	35	19
95°	91	69	91	69	91	95
105°	282	270	282	270	282	297
115°	500	504	500	504	500	494
125°	728	734	728	734	728	650
135°	948	947	948	947	948	732
145°	1152	1151	1152	1151	1152	721
155°	1317	1318	1317	1318	1317	606
165°	1432	1435	1432	1435	1432	403
175°	1486	1493	1486	1493	1486	141
180°	1495	1495	1495	1495	1495	



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1829.2	1828.5	1822.9	1821.8	1817.8	1812.7	1811.5	1802.4	1784.1	1775.6	1773.3
5°	2016.2	2030.5	2012.0	2008.4	2006.3	1982.8	1970.7	1956.4	1923.7	1904.5	1889.5
7.5°	2239.5	2241.2	2233.1	2226.6	2208.5	2188.0	2157.2	2124.5	2085.4	2044.9	2014.3
10°	2386.5	2392.2	2382.9	2381.5	2345.2	2322.4	2276.8	2238.4	2194.2	2145.1	2100.2
12.5°	2541.4	2533.4	2528.7	2498.2	2491.5	2450.0	2397.0	2357.4	2289.4	2232.8	2173.2
15°	2769.5	2753.9	2743.9	2701.9	2681.2	2623.5	2567.3	2523.9	2434.9	2350.2	2286.1
17.5°	2903.3	2919.0	2895.9	2878.7	2825.3	2784.9	2727.4	2636.3	2566.6	2461.4	2380.5
20°	3000.2	3001.6	2988.7	2971.0	2929.0	2877.7	2815.0	2715.3	2632.1	2527.5	2416.4
22.5°	3026.4	3026.6	3021.2	3004.6	2972.8	2931.2	2868.0	2784.9	2684.0	2570.2	2459.1
25°	2940.3	2937.5	2943.9	2962.4	2950.3	2937.5	2901.2	2839.3	2745.3	2624.9	2505.4
27.5°	2620.8	2640.4	2676.6	2722.2	2766.1	2799.5	2809.0	2796.2	2738.0	2639.1	2513.7
30°	2390.8	2414.9	2442.0	2487.5	2575.9	2626.4	2681.9	2723.9	2700.5	2621.5	2504.6
32.5°	2137.9	2143.9	2184.0	2235.8	2316.7	2414.0	2502.0	2587.2	2615.6	2574.1	2476.7
35°	1738.6	1748.6	1792.0	1843.3	1942.2	2061.1	2193.5	2311.7	2409.2	2448.4	2398.5
37.5°	1418.8	1447.4	1478.0	1533.1	1620.2	1727.3	1864.9	2017.9	2163.2	2260.6	2277.1
40°	1267.3	1285.0	1307.2	1349.2	1423.2	1528.6	1646.7	1821.9	1976.4	2115.9	2161.5
42.5°	1147.6	1158.1	1171.6	1209.6	1266.0	1370.8	1478.7	1632.8	1787.9	1954.7	2031.0
45°	975.4	986.1	1008.8	1030.9	1073.6	1146.2	1246.6	1373.3	1529.3	1690.1	1831.1
47.5°	851.0	857.7	871.3	894.9	931.2	979.1	1060.8	1166.6	1311.2	1467.3	1617.6
50°	780.3	786.0	796.7	818.1	845.8	888.5	955.5	1054.4	1167.6	1324.9	1472.3
52.5°	724.5	726.7	734.6	749.1	771.2	807.1	862.0	943.9	1049.1	1189.4	1336.2
55°	637.9	640.8	647.9	658.5	677.8	700.5	742.5	803.8	895.6	1017.4	1144.8
57.5°	566.7	568.7	574.7	578.8	594.6	613.1	645.4	689.2	758.8	862.0	975.8
60°	521.1	519.7	526.8	530.4	541.1	556.8	581.7	623.7	684.2	767.5	872.2
62.5°	476.7	474.7	480.7	485.4	491.5	504.9	525.3	558.2	607.3	682.6	773.0
65°	410.1	407.2	410.8	416.5	422.2	429.3	444.3	473.4	512.6	566.7	635.8
67.5°	343.1	346.2	346.7	349.6	352.8	362.6	372.7	393.4	421.1	464.3	522.9
70°	303.3	304.0	306.8	306.8	309.0	317.5	326.1	338.1	365.2	405.1	452.8
72.5°	263.4	266.4	265.3	267.5	269.1	274.8	281.1	292.6	315.7	345.3	385.6
75°	205.0	207.1	207.1	207.9	210.0	212.1	217.1	225.7	242.1	264.1	291.9
77.5°	149.5	149.8	150.8	153.4	153.4	156.8	160.5	167.3	175.4	190.6	207.5
80°	115.3	116.7	116.0	117.4	117.4	120.3	121.7	130.3	133.8	143.8	157.3
82.5°	84.6	86.0	85.9	87.8	89.0	89.5	91.6	95.0	98.5	107.4	112.9
85°	42.7	44.1	42.7	44.1	46.3	47.0	49.1	49.8	52.7	54.8	59.8
87.5°	19.4	21.0	21.0	21.4	22.5	22.8	23.1	22.2	24.2	24.4	26.3
90°	34.7	34.2	33.7	33.2	32.6	31.6	30.1	28.5	27.0	25.4	23.4
92.5°	51.4	51.0	50.7	50.4	50.1	49.5	48.6	47.6	46.7	45.8	44.3
95°	91.4	91.4	91.4	91.4	91.4	91.0	90.2	89.4	88.6	87.9	86.1
97.5°	143.2	143.2	143.2	143.2	143.2	142.7	141.8	140.9	139.9	139.0	136.9
100°	179.2	179.2	179.2	179.2	179.2	179.0	178.5	178.0	177.5	176.9	174.6
102.5°	220.0	219.7	219.5	219.4	219.1	218.6	217.9	217.2	216.5	215.8	213.7
105°	282.1	281.4	280.6	279.8	279.1	278.3	277.6	276.8	276.0	275.3	274.2
107.5°	342.8	342.9	342.9	343.0	343.0	342.7	341.9	341.2	340.5	339.7	339.7
110°	386.3	385.5	384.7	384.0	383.2	383.1	383.5	384.1	384.6	385.1	385.4



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.7	430.5	430.3	430.2	430.1	430.0	430.2	430.3	430.3	430.4	430.9
115°	499.6	499.8	500.1	500.3	500.6	500.9	501.1	501.4	501.7	501.9	502.4
117.5°	565.3	565.8	566.3	566.8	567.3	568.0	568.9	569.8	570.6	571.5	571.9
120°	615.2	614.7	614.2	613.7	613.1	613.6	614.8	616.2	617.4	618.7	619.5
122.5°	656.8	657.8	658.7	659.6	660.6	661.5	662.4	663.2	664.1	664.9	665.3
125°	728.5	729.1	729.6	730.1	730.6	731.1	731.6	732.2	732.6	733.2	733.4
127.5°	795.0	795.3	795.8	796.2	796.6	797.0	797.5	798.1	798.6	799.1	799.5
130°	838.4	839.5	840.4	841.5	842.6	843.3	843.8	844.4	844.8	845.3	845.3
132.5°	884.7	885.1	885.5	885.9	886.4	886.8	887.3	887.8	888.3	888.9	889.0
135°	948.2	949.0	949.9	950.6	951.4	952.0	952.5	953.1	953.6	954.0	954.0
137.5°	1015.1	1014.9	1014.9	1014.7	1014.5	1014.8	1015.5	1016.1	1016.7	1017.4	1017.0
140°	1055.9	1056.1	1056.3	1056.6	1056.9	1057.1	1057.4	1057.7	1057.9	1058.1	1058.1
142.5°	1096.5	1096.6	1096.6	1096.7	1096.7	1096.8	1096.9	1096.9	1097.0	1097.0	1097.3
145°	1151.8	1152.6	1153.3	1154.1	1154.9	1155.4	1155.7	1155.9	1156.2	1156.5	1156.2
147.5°	1207.8	1208.1	1208.3	1208.5	1208.8	1209.1	1209.2	1209.4	1209.7	1209.9	1210.1
150°	1242.1	1242.2	1242.5	1242.8	1243.0	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1
152.5°	1273.5	1274.2	1274.8	1275.5	1276.1	1276.2	1275.6	1275.0	1274.3	1273.7	1273.5
155°	1317.2	1318.2	1319.3	1320.3	1321.3	1321.3	1320.3	1319.3	1318.2	1317.2	1317.4
157.5°	1356.3	1357.2	1358.0	1358.9	1359.8	1359.9	1359.1	1358.3	1357.5	1356.7	1356.8
160°	1378.5	1379.7	1381.1	1382.3	1383.6	1383.8	1383.1	1382.3	1381.5	1380.8	1381.1
162.5°	1401.6	1402.9	1404.2	1405.4	1406.8	1406.7	1405.3	1403.9	1402.6	1401.1	1401.4
165°	1431.6	1432.7	1433.7	1434.8	1435.8	1435.6	1434.0	1432.4	1430.9	1429.3	1429.9
167.5°	1453.2	1454.8	1456.3	1457.9	1459.6	1459.6	1458.0	1456.5	1455.0	1453.4	1453.4
170°	1465.3	1467.0	1468.8	1470.6	1472.4	1472.6	1471.0	1469.5	1467.9	1466.3	1466.2
172.5°	1475.4	1477.2	1479.0	1480.8	1482.6	1482.6	1480.9	1479.1	1477.4	1475.6	1475.6
175°	1486.0	1487.8	1489.6	1491.4	1493.3	1493.3	1491.4	1489.6	1487.8	1486.0	1486.3
177.5°	1491.6	1493.3	1494.9	1496.6	1498.2	1498.3	1496.8	1495.4	1494.0	1492.5	1492.5
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1773.9	1765.9	1760.2	1755.7	1743.1	1735.7	1730.0	1722.1	1713.0	1703.3	1691.3
5°	1874.6	1850.4	1832.6	1805.5	1779.9	1758.5	1736.4	1716.5	1692.3	1666.0	1646.7
7.5°	1980.4	1944.4	1898.2	1858.2	1813.2	1774.1	1739.0	1703.2	1665.8	1629.7	1596.5
10°	2047.5	2001.3	1950.0	1889.5	1832.6	1782.0	1735.0	1689.4	1645.3	1601.2	1563.4
12.5°	2120.0	2062.3	1986.5	1915.8	1851.9	1784.3	1727.6	1671.8	1618.5	1572.2	1528.1
15°	2217.1	2133.7	2046.1	1951.4	1867.4	1788.4	1710.8	1640.3	1580.6	1519.3	1476.6
17.5°	2276.7	2173.6	2073.5	1974.5	1872.9	1773.2	1689.4	1608.2	1533.3	1472.5	1418.6
20°	2316.0	2213.5	2088.8	1989.9	1868.8	1766.4	1669.6	1579.1	1500.8	1436.0	1380.5
22.5°	2350.2	2231.7	2107.1	1976.8	1856.4	1747.6	1641.6	1550.6	1470.6	1402.4	1349.2
25°	2368.7	2232.7	2097.4	1967.8	1831.1	1702.3	1606.1	1499.4	1413.9	1342.0	1285.0
27.5°	2370.7	2225.3	2072.2	1928.2	1787.2	1667.1	1545.8	1450.4	1361.6	1285.7	1231.0
30°	2364.4	2212.8	2048.3	1892.4	1750.7	1620.4	1515.0	1411.1	1320.7	1245.2	1188.2
32.5°	2344.5	2186.6	2017.5	1852.5	1705.7	1578.2	1469.5	1370.6	1282.5	1208.2	1148.3
35°	2286.8	2130.8	1950.7	1779.1	1629.0	1500.1	1401.9	1301.5	1213.2	1142.7	1085.0
37.5°	2196.6	2055.7	1872.6	1695.1	1547.5	1418.1	1320.7	1229.9	1150.4	1078.8	1019.7
40°	2118.1	1994.2	1810.5	1637.4	1478.0	1354.9	1263.7	1180.4	1101.4	1033.8	977.5
42.5°	2027.5	1919.6	1750.2	1566.8	1413.1	1289.3	1200.5	1125.7	1051.2	988.7	932.6
45°	1866.0	1794.8	1635.4	1465.9	1305.7	1188.9	1104.2	1038.8	976.1	914.9	867.9
47.5°	1680.3	1645.0	1510.7	1349.9	1197.7	1082.7	1009.2	948.8	893.8	842.0	800.5
50°	1555.6	1538.6	1422.5	1267.3	1122.0	1013.8	939.8	887.8	840.8	795.2	756.1
52.5°	1432.6	1432.0	1327.4	1185.3	1050.9	946.6	873.2	824.6	783.9	746.8	711.7
55°	1244.5	1264.4	1182.6	1055.8	935.5	841.5	775.3	731.9	703.4	672.8	646.5
57.5°	1071.7	1104.8	1037.3	925.7	825.3	738.7	681.1	648.5	618.1	599.6	580.4
60°	959.0	990.3	937.6	843.6	748.9	674.9	620.1	590.9	564.5	551.8	538.2
62.5°	858.7	886.6	847.7	760.5	678.3	607.2	560.9	532.8	515.1	501.1	492.1
65°	715.5	739.0	705.5	642.2	571.7	514.8	477.0	455.0	437.8	432.1	422.2
67.5°	578.4	599.8	581.7	527.8	471.3	428.2	398.7	377.5	367.4	362.4	355.3
70°	497.0	518.3	499.1	452.1	408.7	372.4	344.6	332.5	321.8	319.7	309.7
72.5°	428.0	442.6	423.3	386.6	349.5	318.8	297.3	284.6	279.1	275.3	269.8
75°	321.1	333.9	321.1	292.6	266.3	245.0	226.4	221.4	215.0	212.9	209.3
77.5°	227.3	238.4	228.5	210.7	191.1	174.6	164.6	158.2	156.8	153.1	154.8
80°	173.7	180.8	171.6	159.4	143.8	132.4	125.3	121.7	117.4	116.0	118.9
82.5°	124.8	127.9	123.1	115.0	103.3	95.9	91.1	87.0	86.1	86.4	86.4
85°	64.8	64.1	63.4	56.3	52.7	47.7	44.9	44.1	43.4	44.9	46.3
87.5°	25.9	26.0	25.1	22.3	20.1	17.7	16.7	15.5	16.7	17.7	18.9
90°	21.3	19.3	17.2	14.8	11.9	9.1	6.3	3.5	6.3	9.1	11.9
92.5°	42.9	41.5	40.0	37.7	34.4	31.2	28.0	24.8	28.0	31.2	34.4
95°	84.3	82.5	80.7	78.6	76.3	74.0	71.7	69.4	71.7	74.0	76.3
97.5°	134.8	132.7	130.5	128.6	126.7	124.9	123.1	121.2	123.1	124.9	126.7
100°	172.3	170.0	167.6	166.0	165.0	164.0	162.9	161.9	162.9	164.0	165.0
102.5°	211.6	209.5	207.3	206.1	205.7	205.3	204.9	204.5	204.9	205.3	205.7
105°	273.2	272.2	271.1	270.5	270.2	270.0	269.7	269.5	269.7	270.0	270.2
107.5°	339.5	339.3	339.1	338.9	338.6	338.3	338.0	337.7	338.0	338.3	338.6
110°	385.6	385.8	386.1	386.0	385.5	385.0	384.4	384.0	384.4	385.0	385.5





TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	431.3	431.9	432.3	432.5	432.4	432.2	432.1	432.0	432.1	432.2	432.4
115°	502.9	503.5	504.0	504.2	504.2	504.2	504.2	504.2	504.2	504.2	504.2
117.5°	572.2	572.6	572.9	573.0	572.8	572.7	572.4	572.2	572.4	572.7	572.8
120°	620.3	621.0	621.8	621.6	620.6	619.6	618.6	617.5	618.6	619.6	620.6
122.5°	665.7	666.0	666.4	666.4	665.9	665.6	665.1	664.7	665.1	665.6	665.9
125°	733.7	734.0	734.2	734.3	734.3	734.3	734.3	734.3	734.3	734.3	734.3
127.5°	800.0	800.3	800.8	800.6	799.8	799.1	798.3	797.5	798.3	799.1	799.8
130°	845.3	845.3	845.3	845.0	844.2	843.5	842.7	841.9	842.7	843.5	844.2
132.5°	889.2	889.5	889.7	889.5	888.9	888.3	887.8	887.3	887.8	888.3	888.9
135°	954.0	954.0	954.0	953.3	951.7	950.2	948.7	947.1	948.7	950.2	951.7
137.5°	1016.6	1016.2	1015.8	1015.2	1014.5	1013.8	1013.1	1012.4	1013.1	1013.8	1014.5
140°	1058.1	1058.1	1058.1	1057.9	1057.4	1056.9	1056.3	1055.9	1056.3	1056.9	1057.4
142.5°	1097.4	1097.6	1097.8	1097.7	1097.2	1096.6	1096.1	1095.6	1096.1	1096.6	1097.2
145°	1155.9	1155.7	1155.4	1154.8	1153.8	1152.7	1151.7	1150.7	1151.7	1152.7	1153.8
147.5°	1210.3	1210.5	1210.7	1210.1	1209.0	1207.7	1206.5	1205.2	1206.5	1207.7	1209.0
150°	1243.1	1243.1	1243.1	1242.7	1241.6	1240.6	1239.6	1238.6	1239.6	1240.6	1241.6
152.5°	1273.3	1273.1	1272.9	1272.5	1271.8	1271.2	1270.6	1270.0	1270.6	1271.2	1271.8
155°	1317.7	1317.9	1318.2	1318.3	1318.3	1318.3	1318.3	1318.3	1318.3	1318.3	1318.3
157.5°	1356.8	1356.9	1356.9	1357.2	1357.6	1358.2	1358.6	1359.1	1358.6	1358.2	1357.6
160°	1381.3	1381.5	1381.8	1382.1	1382.3	1382.6	1382.9	1383.1	1382.9	1382.6	1382.3
162.5°	1401.7	1401.9	1402.2	1402.7	1403.3	1404.0	1404.6	1405.3	1404.6	1404.0	1403.3
165°	1430.4	1430.9	1431.5	1432.1	1432.8	1433.6	1434.4	1435.1	1434.4	1433.6	1432.8
167.5°	1453.3	1453.3	1453.2	1453.8	1454.8	1455.9	1457.0	1458.0	1457.0	1455.9	1454.8
170°	1465.9	1465.6	1465.3	1465.9	1467.1	1468.5	1469.7	1471.0	1469.7	1468.5	1467.1
172.5°	1475.5	1475.5	1475.4	1476.0	1477.0	1478.1	1479.2	1480.2	1479.2	1478.1	1477.0
175°	1486.6	1486.8	1487.0	1487.8	1489.2	1490.4	1491.7	1493.0	1491.7	1490.4	1489.2
177.5°	1492.5	1492.5	1492.5	1493.0	1494.1	1495.0	1496.1	1497.1	1496.1	1495.0	1494.1
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1685.6	1680.5	1673.1	1662.9	1654.3	1645.2	1642.9	1639.5	1646.3	1640.7	1638.9
5°	1630.4	1615.4	1596.2	1574.1	1561.3	1542.8	1539.3	1532.1	1525.0	1524.3	1517.2
7.5°	1571.8	1549.9	1524.7	1502.2	1481.4	1461.2	1448.0	1445.1	1434.6	1428.4	1421.3
10°	1534.3	1507.2	1478.0	1456.7	1432.4	1411.1	1396.2	1387.6	1380.5	1372.6	1365.6
12.5°	1489.9	1461.1	1437.0	1413.9	1385.2	1369.0	1344.3	1329.5	1328.1	1328.2	1309.7
15°	1438.2	1409.7	1372.6	1339.9	1324.2	1292.9	1279.3	1262.3	1251.6	1240.9	1232.4
17.5°	1379.0	1343.6	1314.6	1277.1	1247.2	1222.3	1204.5	1194.3	1178.1	1163.1	1152.1
20°	1342.0	1304.3	1273.7	1233.8	1201.0	1170.5	1155.5	1141.3	1129.2	1116.3	1104.2
22.5°	1304.4	1265.0	1227.5	1188.8	1158.3	1126.1	1111.6	1092.3	1080.8	1073.6	1061.5
25°	1245.2	1202.5	1159.8	1122.8	1091.5	1062.9	1043.7	1028.8	1015.9	1010.2	1002.5
27.5°	1180.8	1138.4	1097.2	1055.1	1019.5	998.9	983.5	972.2	964.8	957.3	953.8
30°	1139.9	1095.7	1051.6	1012.4	979.6	959.0	944.8	936.9	931.2	927.6	924.1
32.5°	1098.2	1054.7	1008.3	972.5	943.2	924.8	914.0	906.2	903.3	902.1	900.8
35°	1031.6	987.5	944.8	912.8	884.9	877.8	868.6	864.3	862.9	867.9	870.0
37.5°	967.1	926.1	886.8	855.8	837.6	827.2	824.0	824.1	829.3	833.7	838.8
40°	925.5	885.6	848.6	821.6	804.5	798.1	796.7	800.2	805.9	810.9	816.6
42.5°	885.1	845.8	812.2	786.8	774.9	769.0	769.9	773.5	781.4	787.6	796.1
45°	822.3	789.5	756.8	736.2	726.2	727.6	727.6	734.1	741.8	751.1	760.4
47.5°	763.2	730.2	703.3	685.9	680.7	679.5	683.5	691.9	703.1	714.5	727.5
50°	723.4	692.1	668.5	652.8	647.2	649.3	655.0	662.8	676.4	690.6	704.1
52.5°	682.9	654.4	632.7	618.1	614.1	618.0	623.7	636.1	647.9	663.3	679.7
55°	620.1	595.9	578.8	568.1	566.7	568.8	575.2	588.8	605.8	625.1	640.8
57.5°	557.6	537.3	521.7	514.3	515.1	517.0	527.5	543.7	561.9	582.4	602.6
60°	515.4	497.0	484.1	478.4	479.1	483.4	496.2	511.2	534.0	553.9	575.2
62.5°	475.5	459.3	447.1	442.0	441.0	450.4	462.6	478.1	501.0	523.2	546.2
65°	411.5	398.7	388.7	385.8	388.0	395.1	410.8	431.4	450.7	474.1	498.4
67.5°	348.8	338.3	331.4	332.8	335.4	345.9	359.0	376.7	398.6	422.9	446.8
70°	309.0	299.0	293.3	294.0	298.3	311.1	322.5	340.3	363.8	388.7	408.7
72.5°	268.0	261.4	256.3	259.3	263.6	272.4	286.6	304.4	325.1	348.3	369.3
75°	205.7	205.7	202.9	205.0	211.4	220.0	230.7	249.1	269.8	288.4	305.4
77.5°	152.7	151.1	152.9	155.5	159.2	169.3	181.6	194.7	210.4	228.8	242.9
80°	116.7	117.4	121.0	125.3	126.7	134.6	147.4	159.4	171.6	187.3	200.8
82.5°	87.7	88.5	90.2	95.7	97.1	105.5	113.8	125.9	136.9	147.4	158.6
85°	47.7	47.7	51.3	53.4	57.0	62.7	67.6	74.7	84.7	91.8	102.5
87.5°	21.2	21.7	24.3	25.9	28.0	31.3	32.7	39.3	41.9	45.0	50.4
90°	14.8	17.2	19.3	21.3	23.4	25.4	27.0	28.5	30.1	31.6	32.6
92.5°	37.7	40.0	41.5	42.9	44.3	45.8	46.7	47.6	48.6	49.5	50.1
95°	78.6	80.7	82.5	84.3	86.1	87.9	88.6	89.4	90.2	91.0	91.4
97.5°	128.6	130.5	132.7	134.8	136.9	139.0	139.9	140.9	141.8	142.7	143.2
100°	166.0	167.6	170.0	172.3	174.6	176.9	177.5	178.0	178.5	179.0	179.2
102.5°	206.1	207.3	209.5	211.6	213.7	215.8	216.5	217.2	217.9	218.6	219.1
105°	270.5	271.1	272.2	273.2	274.2	275.3	276.0	276.8	277.6	278.3	279.1
107.5°	338.9	339.1	339.3	339.5	339.7	339.7	340.5	341.2	341.9	342.7	343.0
110°	386.0	386.1	385.8	385.6	385.4	385.1	384.6	384.1	383.5	383.1	383.2



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	432.5	432.3	431.9	431.3	430.9	430.4	430.3	430.3	430.2	430.0	430.1
115°	504.2	504.0	503.5	502.9	502.4	501.9	501.7	501.4	501.1	500.9	500.6
117.5°	573.0	572.9	572.6	572.2	571.9	571.5	570.6	569.8	568.9	568.0	567.3
120°	621.6	621.8	621.0	620.3	619.5	618.7	617.4	616.2	614.8	613.6	613.1
122.5°	666.4	666.4	666.0	665.7	665.3	664.9	664.1	663.2	662.4	661.5	660.6
125°	734.3	734.2	734.0	733.7	733.4	733.2	732.6	732.2	731.6	731.1	730.6
127.5°	800.6	800.8	800.3	800.0	799.5	799.1	798.6	798.1	797.5	797.0	796.6
130°	845.0	845.3	845.3	845.3	845.3	845.3	844.8	844.4	843.8	843.3	842.6
132.5°	889.5	889.7	889.5	889.2	889.0	888.9	888.3	887.8	887.3	886.8	886.4
135°	953.3	954.0	954.0	954.0	954.0	954.0	953.6	953.1	952.5	952.0	951.4
137.5°	1015.2	1015.8	1016.2	1016.6	1017.0	1017.4	1016.7	1016.1	1015.5	1014.8	1014.5
140°	1057.9	1058.1	1058.1	1058.1	1058.1	1058.1	1057.9	1057.7	1057.4	1057.1	1056.9
142.5°	1097.7	1097.8	1097.6	1097.4	1097.3	1097.0	1097.0	1096.9	1096.9	1096.8	1096.7
145°	1154.8	1155.4	1155.7	1155.9	1156.2	1156.5	1156.2	1155.9	1155.7	1155.4	1154.9
147.5°	1210.1	1210.7	1210.5	1210.3	1210.1	1209.9	1209.7	1209.4	1209.2	1209.1	1208.8
150°	1242.7	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1243.0
152.5°	1272.5	1272.9	1273.1	1273.3	1273.5	1273.7	1274.3	1275.0	1275.6	1276.2	1276.1
155°	1318.3	1318.2	1317.9	1317.7	1317.4	1317.2	1318.2	1319.3	1320.3	1321.3	1321.3
157.5°	1357.2	1356.9	1356.9	1356.8	1356.8	1356.7	1357.5	1358.3	1359.1	1359.9	1359.8
160°	1382.1	1381.8	1381.5	1381.3	1381.1	1380.8	1381.5	1382.3	1383.1	1383.8	1383.6
162.5°	1402.7	1402.2	1401.9	1401.7	1401.4	1401.1	1402.6	1403.9	1405.3	1406.7	1406.8
165°	1432.1	1431.5	1430.9	1430.4	1429.9	1429.3	1430.9	1432.4	1434.0	1435.6	1435.8
167.5°	1453.8	1453.2	1453.3	1453.3	1453.4	1453.4	1455.0	1456.5	1458.0	1459.6	1459.6
170°	1465.9	1465.3	1465.6	1465.9	1466.2	1466.3	1467.9	1469.5	1471.0	1472.6	1472.4
172.5°	1476.0	1475.4	1475.5	1475.5	1475.6	1475.6	1477.4	1479.1	1480.9	1482.6	1482.6
175°	1487.8	1487.0	1486.8	1486.6	1486.3	1486.0	1487.8	1489.6	1491.4	1493.3	1493.3
177.5°	1493.0	1492.5	1492.5	1492.5	1492.5	1492.5	1494.0	1495.4	1496.8	1498.3	1498.2
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1637.8	1636.6	1632.6	1632.1	1632.6	1636.6	1637.8	1638.9	1640.7	1646.3	1639.5
5°	1512.9	1509.3	1507.2	1515.0	1507.2	1509.3	1512.9	1517.2	1524.3	1525.0	1532.1
7.5°	1418.8	1415.9	1409.7	1407.7	1409.7	1415.9	1418.8	1421.3	1428.4	1434.6	1445.1
10°	1358.4	1355.6	1349.9	1348.4	1349.9	1355.6	1358.4	1365.6	1372.6	1380.5	1387.6
12.5°	1300.3	1294.6	1293.5	1294.9	1293.5	1294.6	1300.3	1309.7	1328.2	1328.1	1329.5
15°	1223.2	1220.3	1212.5	1214.6	1212.5	1220.3	1223.2	1232.4	1240.9	1251.6	1262.3
17.5°	1147.1	1143.7	1134.2	1142.5	1134.2	1143.7	1147.1	1152.1	1163.1	1178.1	1194.3
20°	1099.2	1093.6	1088.6	1087.9	1088.6	1093.6	1099.2	1104.2	1116.3	1129.2	1141.3
22.5°	1053.6	1048.6	1048.1	1043.5	1048.1	1048.6	1053.6	1061.5	1073.6	1080.8	1092.3
25°	996.8	991.8	990.3	986.8	990.3	991.8	996.8	1002.5	1010.2	1015.9	1028.8
27.5°	953.1	950.6	948.1	949.1	948.1	950.6	953.1	953.8	957.3	964.8	972.2
30°	926.2	925.5	924.1	924.1	924.1	925.5	926.2	924.1	927.6	931.2	936.9
32.5°	904.0	903.9	904.7	904.7	904.7	903.9	904.0	900.8	902.1	903.3	906.2
35°	872.9	874.9	876.4	874.2	876.4	874.9	872.9	870.0	867.9	862.9	864.3
37.5°	844.6	846.8	848.8	851.2	848.8	846.8	844.6	838.8	833.7	829.3	824.1
40°	823.0	828.0	829.4	832.9	829.4	828.0	823.0	816.6	810.9	805.9	800.2
42.5°	802.5	808.1	811.7	812.4	811.7	808.1	802.5	796.1	787.6	781.4	773.5
45°	771.1	776.8	781.8	781.8	781.8	776.8	771.1	760.4	751.1	741.8	734.1
47.5°	738.4	746.7	751.7	753.0	751.7	746.7	738.4	727.5	714.5	703.1	691.9
50°	716.2	726.2	731.2	734.8	731.2	726.2	716.2	704.1	690.6	676.4	662.8
52.5°	694.6	704.5	711.2	713.1	711.2	704.5	694.6	679.7	663.3	647.9	636.1
55°	657.1	671.4	679.2	682.1	679.2	671.4	657.1	640.8	625.1	605.8	588.8
57.5°	621.8	634.9	644.0	646.1	644.0	634.9	621.8	602.6	582.4	561.9	543.7
60°	594.5	608.7	620.1	622.2	620.1	608.7	594.5	575.2	553.9	534.0	511.2
62.5°	566.6	581.4	591.7	597.2	591.7	581.4	566.6	546.2	523.2	501.0	478.1
65°	518.3	533.2	543.2	545.4	543.2	533.2	518.3	498.4	474.1	450.7	431.4
67.5°	465.7	480.5	487.1	491.2	487.1	480.5	465.7	446.8	422.9	398.6	376.7
70°	428.6	440.7	447.8	451.4	447.8	440.7	428.6	408.7	388.7	363.8	340.3
72.5°	386.5	399.1	407.4	408.0	407.4	399.1	386.5	369.3	348.3	325.1	304.4
75°	321.8	333.2	337.4	337.4	337.4	333.2	321.8	305.4	288.4	269.8	249.1
77.5°	254.8	260.6	266.0	267.2	266.0	260.6	254.8	242.9	228.8	210.4	194.7
80°	211.4	215.0	219.3	219.3	219.3	215.0	211.4	200.8	187.3	171.6	159.4
82.5°	167.0	170.0	174.3	173.7	174.3	170.0	167.0	158.6	147.4	136.9	125.9
85°	101.1	107.5	106.8	105.4	106.8	107.5	101.1	102.5	91.8	84.7	74.7
87.5°	52.2	52.9	54.7	55.9	54.7	52.9	52.2	50.4	45.0	41.9	39.3
90°	33.2	33.7	34.2	34.7	34.2	33.7	33.2	32.6	31.6	30.1	28.5
92.5°	50.4	50.7	51.0	51.4	51.0	50.7	50.4	50.1	49.5	48.6	47.6
95°	91.4	91.4	91.4	91.4	91.4	91.4	91.4	91.4	91.0	90.2	89.4
97.5°	143.2	143.2	143.2	143.2	143.2	143.2	143.2	143.2	142.7	141.8	140.9
100°	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.2	179.0	178.5	178.0
102.5°	219.4	219.5	219.7	220.0	219.7	219.5	219.4	219.1	218.6	217.9	217.2
105°	279.8	280.6	281.4	282.1	281.4	280.6	279.8	279.1	278.3	277.6	276.8
107.5°	343.0	342.9	342.9	342.8	342.9	342.9	343.0	343.0	342.7	341.9	341.2
110°	384.0	384.7	385.5	386.3	385.5	384.7	384.0	383.2	383.1	383.5	384.1



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	430.2	430.3	430.5	430.7	430.5	430.3	430.2	430.1	430.0	430.2	430.3
115°	500.3	500.1	499.8	499.6	499.8	500.1	500.3	500.6	500.9	501.1	501.4
117.5°	566.8	566.3	565.8	565.3	565.8	566.3	566.8	567.3	568.0	568.9	569.8
120°	613.7	614.2	614.7	615.2	614.7	614.2	613.7	613.1	613.6	614.8	616.2
122.5°	659.6	658.7	657.8	656.8	657.8	658.7	659.6	660.6	661.5	662.4	663.2
125°	730.1	729.6	729.1	728.5	729.1	729.6	730.1	730.6	731.1	731.6	732.2
127.5°	796.2	795.8	795.3	795.0	795.3	795.8	796.2	796.6	797.0	797.5	798.1
130°	841.5	840.4	839.5	838.4	839.5	840.4	841.5	842.6	843.3	843.8	844.4
132.5°	885.9	885.5	885.1	884.7	885.1	885.5	885.9	886.4	886.8	887.3	887.8
135°	950.6	949.9	949.0	948.2	949.0	949.9	950.6	951.4	952.0	952.5	953.1
137.5°	1014.7	1014.9	1014.9	1015.1	1014.9	1014.9	1014.7	1014.5	1014.8	1015.5	1016.1
140°	1056.6	1056.3	1056.1	1055.9	1056.1	1056.3	1056.6	1056.9	1057.1	1057.4	1057.7
142.5°	1096.7	1096.6	1096.6	1096.5	1096.6	1096.6	1096.7	1096.7	1096.8	1096.9	1096.9
145°	1154.1	1153.3	1152.6	1151.8	1152.6	1153.3	1154.1	1154.9	1155.4	1155.7	1155.9
147.5°	1208.5	1208.3	1208.1	1207.8	1208.1	1208.3	1208.5	1208.8	1209.1	1209.2	1209.4
150°	1242.8	1242.5	1242.2	1242.1	1242.2	1242.5	1242.8	1243.0	1243.1	1243.1	1243.1
152.5°	1275.5	1274.8	1274.2	1273.5	1274.2	1274.8	1275.5	1276.1	1276.2	1275.6	1275.0
155°	1320.3	1319.3	1318.2	1317.2	1318.2	1319.3	1320.3	1321.3	1321.3	1320.3	1319.3
157.5°	1358.9	1358.0	1357.2	1356.3	1357.2	1358.0	1358.9	1359.8	1359.9	1359.1	1358.3
160°	1382.3	1381.1	1379.7	1378.5	1379.7	1381.1	1382.3	1383.6	1383.8	1383.1	1382.3
162.5°	1405.4	1404.2	1402.9	1401.6	1402.9	1404.2	1405.4	1406.8	1406.7	1405.3	1403.9
165°	1434.8	1433.7	1432.7	1431.6	1432.7	1433.7	1434.8	1435.8	1435.6	1434.0	1432.4
167.5°	1457.9	1456.3	1454.8	1453.2	1454.8	1456.3	1457.9	1459.6	1459.6	1458.0	1456.5
170°	1470.6	1468.8	1467.0	1465.3	1467.0	1468.8	1470.6	1472.4	1472.6	1471.0	1469.5
172.5°	1480.8	1479.0	1477.2	1475.4	1477.2	1479.0	1480.8	1482.6	1482.6	1480.9	1479.1
175°	1491.4	1489.6	1487.8	1486.0	1487.8	1489.6	1491.4	1493.3	1493.3	1491.4	1489.6
177.5°	1496.6	1494.9	1493.3	1491.6	1493.3	1494.9	1496.6	1498.2	1498.3	1496.8	1495.4
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1642.9	1645.2	1654.3	1662.9	1673.1	1680.5	1685.6	1691.3	1703.3	1713.0	1722.1
5°	1539.3	1542.8	1561.3	1574.1	1596.2	1615.4	1630.4	1646.7	1666.0	1692.3	1716.5
7.5°	1448.0	1461.2	1481.4	1502.2	1524.7	1549.9	1571.8	1596.5	1629.7	1665.8	1703.2
10°	1396.2	1411.1	1432.4	1456.7	1478.0	1507.2	1534.3	1563.4	1601.2	1645.3	1689.4
12.5°	1344.3	1369.0	1385.2	1413.9	1437.0	1461.1	1489.9	1528.1	1572.2	1618.5	1671.8
15°	1279.3	1292.9	1324.2	1339.9	1372.6	1409.7	1438.2	1476.6	1519.3	1580.6	1640.3
17.5°	1204.5	1222.3	1247.2	1277.1	1314.6	1343.6	1379.0	1418.6	1472.5	1533.3	1608.2
20°	1155.5	1170.5	1201.0	1233.8	1273.7	1304.3	1342.0	1380.5	1436.0	1500.8	1579.1
22.5°	1111.6	1126.1	1158.3	1188.8	1227.5	1265.0	1304.4	1349.2	1402.4	1470.6	1550.6
25°	1043.7	1062.9	1091.5	1122.8	1159.8	1202.5	1245.2	1285.0	1342.0	1413.9	1499.4
27.5°	983.5	998.9	1019.5	1055.1	1097.2	1138.4	1180.8	1231.0	1285.7	1361.6	1450.4
30°	944.8	959.0	979.6	1012.4	1051.6	1095.7	1139.9	1188.2	1245.2	1320.7	1411.1
32.5°	914.0	924.8	943.2	972.5	1008.3	1054.7	1098.2	1148.3	1208.2	1282.5	1370.6
35°	868.6	877.8	884.9	912.8	944.8	987.5	1031.6	1085.0	1142.7	1213.2	1301.5
37.5°	824.0	827.2	837.6	855.8	886.8	926.1	967.1	1019.7	1078.8	1150.4	1229.9
40°	796.7	798.1	804.5	821.6	848.6	885.6	925.5	977.5	1033.8	1101.4	1180.4
42.5°	769.9	769.0	774.9	786.8	812.2	845.8	885.1	932.6	988.7	1051.2	1125.7
45°	727.6	727.6	726.2	736.2	756.8	789.5	822.3	867.9	914.9	976.1	1038.8
47.5°	683.5	679.5	680.7	685.9	703.3	730.2	763.2	800.5	842.0	893.8	948.8
50°	655.0	649.3	647.2	652.8	668.5	692.1	723.4	756.1	795.2	840.8	887.8
52.5°	623.7	618.0	614.1	618.1	632.7	654.4	682.9	711.7	746.8	783.9	824.6
55°	575.2	568.8	566.7	568.1	578.8	595.9	620.1	646.5	672.8	703.4	731.9
57.5°	527.5	517.0	515.1	514.3	521.7	537.3	557.6	580.4	599.6	618.1	648.5
60°	496.2	483.4	479.1	478.4	484.1	497.0	515.4	538.2	551.8	564.5	590.9
62.5°	462.6	450.4	441.0	442.0	447.1	459.3	475.5	492.1	501.1	515.1	532.8
65°	410.8	395.1	388.0	385.8	388.7	398.7	411.5	422.2	432.1	437.8	455.0
67.5°	359.0	345.9	335.4	332.8	331.4	338.3	348.8	355.3	362.4	367.4	377.5
70°	322.5	311.1	298.3	294.0	293.3	299.0	309.0	309.7	319.7	321.8	332.5
72.5°	286.6	272.4	263.6	259.3	256.3	261.4	268.0	269.8	275.3	279.1	284.6
75°	230.7	220.0	211.4	205.0	202.9	205.7	205.7	209.3	212.9	215.0	221.4
77.5°	181.6	169.3	159.2	155.5	152.9	151.1	152.7	154.8	153.1	156.8	158.2
80°	147.4	134.6	126.7	125.3	121.0	117.4	116.7	118.9	116.0	117.4	121.7
82.5°	113.8	105.5	97.1	95.7	90.2	88.5	87.7	86.4	86.4	86.1	87.0
85°	67.6	62.7	57.0	53.4	51.3	47.7	47.7	46.3	44.9	43.4	44.1
87.5°	32.7	31.3	28.0	25.9	24.3	21.7	21.2	18.9	17.7	16.7	15.5
90°	27.0	25.4	23.4	21.3	19.3	17.2	14.8	11.9	9.1	6.3	3.5
92.5°	46.7	45.8	44.3	42.9	41.5	40.0	37.7	34.4	31.2	28.0	24.8
95°	88.6	87.9	86.1	84.3	82.5	80.7	78.6	76.3	74.0	71.7	69.4
97.5°	139.9	139.0	136.9	134.8	132.7	130.5	128.6	126.7	124.9	123.1	121.2
100°	177.5	176.9	174.6	172.3	170.0	167.6	166.0	165.0	164.0	162.9	161.9
102.5°	216.5	215.8	213.7	211.6	209.5	207.3	206.1	205.7	205.3	204.9	204.5
105°	276.0	275.3	274.2	273.2	272.2	271.1	270.5	270.2	270.0	269.7	269.5
107.5°	340.5	339.7	339.7	339.5	339.3	339.1	338.9	338.6	338.3	338.0	337.7
110°	384.6	385.1	385.4	385.6	385.8	386.1	386.0	385.5	385.0	384.4	384.0



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	430.3	430.4	430.9	431.3	431.9	432.3	432.5	432.4	432.2	432.1	432.0
115°	501.7	501.9	502.4	502.9	503.5	504.0	504.2	504.2	504.2	504.2	504.2
117.5°	570.6	571.5	571.9	572.2	572.6	572.9	573.0	572.8	572.7	572.4	572.2
120°	617.4	618.7	619.5	620.3	621.0	621.8	621.6	620.6	619.6	618.6	617.5
122.5°	664.1	664.9	665.3	665.7	666.0	666.4	666.4	665.9	665.6	665.1	664.7
125°	732.6	733.2	733.4	733.7	734.0	734.2	734.3	734.3	734.3	734.3	734.3
127.5°	798.6	799.1	799.5	800.0	800.3	800.8	800.6	799.8	799.1	798.3	797.5
130°	844.8	845.3	845.3	845.3	845.3	845.3	845.0	844.2	843.5	842.7	841.9
132.5°	888.3	888.9	889.0	889.2	889.5	889.7	889.5	888.9	888.3	887.8	887.3
135°	953.6	954.0	954.0	954.0	954.0	954.0	953.3	951.7	950.2	948.7	947.1
137.5°	1016.7	1017.4	1017.0	1016.6	1016.2	1015.8	1015.2	1014.5	1013.8	1013.1	1012.4
140°	1057.9	1058.1	1058.1	1058.1	1058.1	1058.1	1057.9	1057.4	1056.9	1056.3	1055.9
142.5°	1097.0	1097.0	1097.3	1097.4	1097.6	1097.8	1097.7	1097.2	1096.6	1096.1	1095.6
145°	1156.2	1156.5	1156.2	1155.9	1155.7	1155.4	1154.8	1153.8	1152.7	1151.7	1150.7
147.5°	1209.7	1209.9	1210.1	1210.3	1210.5	1210.7	1210.1	1209.0	1207.7	1206.5	1205.2
150°	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1242.7	1241.6	1240.6	1239.6	1238.6
152.5°	1274.3	1273.7	1273.5	1273.3	1273.1	1272.9	1272.5	1271.8	1271.2	1270.6	1270.0
155°	1318.2	1317.2	1317.4	1317.7	1317.9	1318.2	1318.3	1318.3	1318.3	1318.3	1318.3
157.5°	1357.5	1356.7	1356.8	1356.8	1356.9	1356.9	1357.2	1357.6	1358.2	1358.6	1359.1
160°	1381.5	1380.8	1381.1	1381.3	1381.5	1381.8	1382.1	1382.3	1382.6	1382.9	1383.1
162.5°	1402.6	1401.1	1401.4	1401.7	1401.9	1402.2	1402.7	1403.3	1404.0	1404.6	1405.3
165°	1430.9	1429.3	1429.9	1430.4	1430.9	1431.5	1432.1	1432.8	1433.6	1434.4	1435.1
167.5°	1455.0	1453.4	1453.4	1453.3	1453.3	1453.2	1453.8	1454.8	1455.9	1457.0	1458.0
170°	1467.9	1466.3	1466.2	1465.9	1465.6	1465.3	1465.9	1467.1	1468.5	1469.7	1471.0
172.5°	1477.4	1475.6	1475.6	1475.5	1475.5	1475.4	1476.0	1477.0	1478.1	1479.2	1480.2
175°	1487.8	1486.0	1486.3	1486.6	1486.8	1487.0	1487.8	1489.2	1490.4	1491.7	1493.0
177.5°	1494.0	1492.5	1492.5	1492.5	1492.5	1492.5	1493.0	1494.1	1495.0	1496.1	1497.1
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1730.0	1735.7	1743.1	1755.7	1760.2	1765.9	1773.9	1773.3	1775.6	1784.1	1802.4
5°	1736.4	1758.5	1779.9	1805.5	1832.6	1850.4	1874.6	1889.5	1904.5	1923.7	1956.4
7.5°	1739.0	1774.1	1813.2	1858.2	1898.2	1944.4	1980.4	2014.3	2044.9	2085.4	2124.5
10°	1735.0	1782.0	1832.6	1889.5	1950.0	2001.3	2047.5	2100.2	2145.1	2194.2	2238.4
12.5°	1727.6	1784.3	1851.9	1915.8	1986.5	2062.3	2120.0	2173.2	2232.8	2289.4	2357.4
15°	1710.8	1788.4	1867.4	1951.4	2046.1	2133.7	2217.1	2286.1	2350.2	2434.9	2523.9
17.5°	1689.4	1773.2	1872.9	1974.5	2073.5	2173.6	2276.7	2380.5	2461.4	2566.6	2636.3
20°	1669.6	1766.4	1868.8	1989.9	2088.8	2213.5	2316.0	2416.4	2527.5	2632.1	2715.3
22.5°	1641.6	1747.6	1856.4	1976.8	2107.1	2231.7	2350.2	2459.1	2570.2	2684.0	2784.9
25°	1606.1	1702.3	1831.1	1967.8	2097.4	2232.7	2368.7	2505.4	2624.9	2745.3	2839.3
27.5°	1545.8	1667.1	1787.2	1928.2	2072.2	2225.3	2370.7	2513.7	2639.1	2738.0	2796.2
30°	1515.0	1620.4	1750.7	1892.4	2048.3	2212.8	2364.4	2504.6	2621.5	2700.5	2723.9
32.5°	1469.5	1578.2	1705.7	1852.5	2017.5	2186.6	2344.5	2476.7	2574.1	2615.6	2587.2
35°	1401.9	1500.1	1629.0	1779.1	1950.7	2130.8	2286.8	2398.5	2448.4	2409.2	2311.7
37.5°	1320.7	1418.1	1547.5	1695.1	1872.6	2055.7	2196.6	2277.1	2260.6	2163.2	2017.9
40°	1263.7	1354.9	1478.0	1637.4	1810.5	1994.2	2118.1	2161.5	2115.9	1976.4	1821.9
42.5°	1200.5	1289.3	1413.1	1566.8	1750.2	1919.6	2027.5	2031.0	1954.7	1787.9	1632.8
45°	1104.2	1188.9	1305.7	1465.9	1635.4	1794.8	1866.0	1831.1	1690.1	1529.3	1373.3
47.5°	1009.2	1082.7	1197.7	1349.9	1510.7	1645.0	1680.3	1617.6	1467.3	1311.2	1166.6
50°	939.8	1013.8	1122.0	1267.3	1422.5	1538.6	1555.6	1472.3	1324.9	1167.6	1054.4
52.5°	873.2	946.6	1050.9	1185.3	1327.4	1432.0	1432.6	1336.2	1189.4	1049.1	943.9
55°	775.3	841.5	935.5	1055.8	1182.6	1264.4	1244.5	1144.8	1017.4	895.6	803.8
57.5°	681.1	738.7	825.3	925.7	1037.3	1104.8	1071.7	975.8	862.0	758.8	689.2
60°	620.1	674.9	748.9	843.6	937.6	990.3	959.0	872.2	767.5	684.2	623.7
62.5°	560.9	607.2	678.3	760.5	847.7	886.6	858.7	773.0	682.6	607.3	558.2
65°	477.0	514.8	571.7	642.2	705.5	739.0	715.5	635.8	566.7	512.6	473.4
67.5°	398.7	428.2	471.3	527.8	581.7	599.8	578.4	522.9	464.3	421.1	393.4
70°	344.6	372.4	408.7	452.1	499.1	518.3	497.0	452.8	405.1	365.2	338.1
72.5°	297.3	318.8	349.5	386.6	423.3	442.6	428.0	385.6	345.3	315.7	292.6
75°	226.4	245.0	266.3	292.6	321.1	333.9	321.1	291.9	264.1	242.1	225.7
77.5°	164.6	174.6	191.1	210.7	228.5	238.4	227.3	207.5	190.6	175.4	167.3
80°	125.3	132.4	143.8	159.4	171.6	180.8	173.7	157.3	143.8	133.8	130.3
82.5°	91.1	95.9	103.3	115.0	123.1	127.9	124.8	112.9	107.4	98.5	95.0
85°	44.9	47.7	52.7	56.3	63.4	64.1	64.8	59.8	54.8	52.7	49.8
87.5°	16.7	17.7	20.1	22.3	25.1	26.0	25.9	26.3	24.4	24.2	22.2
90°	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0	28.5
92.5°	28.0	31.2	34.4	37.7	40.0	41.5	42.9	44.3	45.8	46.7	47.6
95°	71.7	74.0	76.3	78.6	80.7	82.5	84.3	86.1	87.9	88.6	89.4
97.5°	123.1	124.9	126.7	128.6	130.5	132.7	134.8	136.9	139.0	139.9	140.9
100°	162.9	164.0	165.0	166.0	167.6	170.0	172.3	174.6	176.9	177.5	178.0
102.5°	204.9	205.3	205.7	206.1	207.3	209.5	211.6	213.7	215.8	216.5	217.2
105°	269.7	270.0	270.2	270.5	271.1	272.2	273.2	274.2	275.3	276.0	276.8
107.5°	338.0	338.3	338.6	338.9	339.1	339.3	339.5	339.7	339.7	340.5	341.2
110°	384.4	385.0	385.5	386.0	386.1	385.8	385.6	385.4	385.1	384.6	384.1





TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	432.1	432.2	432.4	432.5	432.3	431.9	431.3	430.9	430.4	430.3	430.3
115°	504.2	504.2	504.2	504.2	504.0	503.5	502.9	502.4	501.9	501.7	501.4
117.5°	572.4	572.7	572.8	573.0	572.9	572.6	572.2	571.9	571.5	570.6	569.8
120°	618.6	619.6	620.6	621.6	621.8	621.0	620.3	619.5	618.7	617.4	616.2
122.5°	665.1	665.6	665.9	666.4	666.4	666.0	665.7	665.3	664.9	664.1	663.2
125°	734.3	734.3	734.3	734.3	734.2	734.0	733.7	733.4	733.2	732.6	732.2
127.5°	798.3	799.1	799.8	800.6	800.8	800.3	800.0	799.5	799.1	798.6	798.1
130°	842.7	843.5	844.2	845.0	845.3	845.3	845.3	845.3	845.3	844.8	844.4
132.5°	887.8	888.3	888.9	889.5	889.7	889.5	889.2	889.0	888.9	888.3	887.8
135°	948.7	950.2	951.7	953.3	954.0	954.0	954.0	954.0	954.0	953.6	953.1
137.5°	1013.1	1013.8	1014.5	1015.2	1015.8	1016.2	1016.6	1017.0	1017.4	1016.7	1016.1
140°	1056.3	1056.9	1057.4	1057.9	1058.1	1058.1	1058.1	1058.1	1058.1	1057.9	1057.7
142.5°	1096.1	1096.6	1097.2	1097.7	1097.8	1097.6	1097.4	1097.3	1097.0	1097.0	1096.9
145°	1151.7	1152.7	1153.8	1154.8	1155.4	1155.7	1155.9	1156.2	1156.5	1156.2	1155.9
147.5°	1206.5	1207.7	1209.0	1210.1	1210.7	1210.5	1210.3	1210.1	1209.9	1209.7	1209.4
150°	1239.6	1240.6	1241.6	1242.7	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1
152.5°	1270.6	1271.2	1271.8	1272.5	1272.9	1273.1	1273.3	1273.5	1273.7	1274.3	1275.0
155°	1318.3	1318.3	1318.3	1318.3	1318.2	1317.9	1317.7	1317.4	1317.2	1318.2	1319.3
157.5°	1358.6	1358.2	1357.6	1357.2	1356.9	1356.9	1356.8	1356.8	1356.7	1357.5	1358.3
160°	1382.9	1382.6	1382.3	1382.1	1381.8	1381.5	1381.3	1381.1	1380.8	1381.5	1382.3
162.5°	1404.6	1404.0	1403.3	1402.7	1402.2	1401.9	1401.7	1401.4	1401.1	1402.6	1403.9
165°	1434.4	1433.6	1432.8	1432.1	1431.5	1430.9	1430.4	1429.9	1429.3	1430.9	1432.4
167.5°	1457.0	1455.9	1454.8	1453.8	1453.2	1453.3	1453.3	1453.4	1453.4	1455.0	1456.5
170°	1469.7	1468.5	1467.1	1465.9	1465.3	1465.6	1465.9	1466.2	1466.3	1467.9	1469.5
172.5°	1479.2	1478.1	1477.0	1476.0	1475.4	1475.5	1475.5	1475.6	1475.6	1477.4	1479.1
175°	1491.7	1490.4	1489.2	1487.8	1487.0	1486.8	1486.6	1486.3	1486.0	1487.8	1489.6
177.5°	1496.1	1495.0	1494.1	1493.0	1492.5	1492.5	1492.5	1492.5	1492.5	1494.0	1495.4
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1811.5	1812.7	1817.8	1821.8	1822.9	1828.5	1829.2
5°	1970.7	1982.8	2006.3	2008.4	2012.0	2030.5	2016.2
7.5°	2157.2	2188.0	2208.5	2226.6	2233.1	2241.2	2239.5
10°	2276.8	2322.4	2345.2	2381.5	2382.9	2392.2	2386.5
12.5°	2397.0	2450.0	2491.5	2498.2	2528.7	2533.4	2541.4
15°	2567.3	2623.5	2681.2	2701.9	2743.9	2753.9	2769.5
17.5°	2727.4	2784.9	2825.3	2878.7	2895.9	2919.0	2903.3
20°	2815.0	2877.7	2929.0	2971.0	2988.7	3001.6	3000.2
22.5°	2868.0	2931.2	2972.8	3004.6	3021.2	3026.6	3026.4
25°	2901.2	2937.5	2950.3	2962.4	2943.9	2937.5	2940.3
27.5°	2809.0	2799.5	2766.1	2722.2	2676.6	2640.4	2620.8
30°	2681.9	2626.4	2575.9	2487.5	2442.0	2414.9	2390.8
32.5°	2502.0	2414.0	2316.7	2235.8	2184.0	2143.9	2137.9
35°	2193.5	2061.1	1942.2	1843.3	1792.0	1748.6	1738.6
37.5°	1864.9	1727.3	1620.2	1533.1	1478.0	1447.4	1418.8
40°	1646.7	1528.6	1423.2	1349.2	1307.2	1285.0	1267.3
42.5°	1478.7	1370.8	1266.0	1209.6	1171.6	1158.1	1147.6
45°	1246.6	1146.2	1073.6	1030.9	1008.8	986.1	975.4
47.5°	1060.8	979.1	931.2	894.9	871.3	857.7	851.0
50°	955.5	888.5	845.8	818.1	796.7	786.0	780.3
52.5°	862.0	807.1	771.2	749.1	734.6	726.7	724.5
55°	742.5	700.5	677.8	658.5	647.9	640.8	637.9
57.5°	645.4	613.1	594.6	578.8	574.7	568.7	566.7
60°	581.7	556.8	541.1	530.4	526.8	519.7	521.1
62.5°	525.3	504.9	491.5	485.4	480.7	474.7	476.7
65°	444.3	429.3	422.2	416.5	410.8	407.2	410.1
67.5°	372.7	362.6	352.8	349.6	346.7	346.2	343.1
70°	326.1	317.5	309.0	306.8	306.8	304.0	303.3
72.5°	281.1	274.8	269.1	267.5	265.3	266.4	263.4
75°	217.1	212.1	210.0	207.9	207.1	207.1	205.0
77.5°	160.5	156.8	153.4	153.4	150.8	149.8	149.5
80°	121.7	120.3	117.4	117.4	116.0	116.7	115.3
82.5°	91.6	89.5	89.0	87.8	85.9	86.0	84.6
85°	49.1	47.0	46.3	44.1	42.7	44.1	42.7
87.5°	23.1	22.8	22.5	21.4	21.0	21.0	19.4
90°	30.1	31.6	32.6	33.2	33.7	34.2	34.7
92.5°	48.6	49.5	50.1	50.4	50.7	51.0	51.4
95°	90.2	91.0	91.4	91.4	91.4	91.4	91.4
97.5°	141.8	142.7	143.2	143.2	143.2	143.2	143.2
100°	178.5	179.0	179.2	179.2	179.2	179.2	179.2
102.5°	217.9	218.6	219.1	219.4	219.5	219.7	220.0
105°	277.6	278.3	279.1	279.8	280.6	281.4	282.1
107.5°	341.9	342.7	343.0	343.0	342.9	342.9	342.8
110°	383.5	383.1	383.2	384.0	384.7	385.5	386.3



TEST NUMBER: P332854-940

CATALOG NUMBER: S124DIW-S1195D1340U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	430.2	430.0	430.1	430.2	430.3	430.5	430.7
115°	501.1	500.9	500.6	500.3	500.1	499.8	499.6
117.5°	568.9	568.0	567.3	566.8	566.3	565.8	565.3
120°	614.8	613.6	613.1	613.7	614.2	614.7	615.2
122.5°	662.4	661.5	660.6	659.6	658.7	657.8	656.8
125°	731.6	731.1	730.6	730.1	729.6	729.1	728.5
127.5°	797.5	797.0	796.6	796.2	795.8	795.3	795.0
130°	843.8	843.3	842.6	841.5	840.4	839.5	838.4
132.5°	887.3	886.8	886.4	885.9	885.5	885.1	884.7
135°	952.5	952.0	951.4	950.6	949.9	949.0	948.2
137.5°	1015.5	1014.8	1014.5	1014.7	1014.9	1014.9	1015.1
140°	1057.4	1057.1	1056.9	1056.6	1056.3	1056.1	1055.9
142.5°	1096.9	1096.8	1096.7	1096.7	1096.6	1096.6	1096.5
145°	1155.7	1155.4	1154.9	1154.1	1153.3	1152.6	1151.8
147.5°	1209.2	1209.1	1208.8	1208.5	1208.3	1208.1	1207.8
150°	1243.1	1243.1	1243.0	1242.8	1242.5	1242.2	1242.1
152.5°	1275.6	1276.2	1276.1	1275.5	1274.8	1274.2	1273.5
155°	1320.3	1321.3	1321.3	1320.3	1319.3	1318.2	1317.2
157.5°	1359.1	1359.9	1359.8	1358.9	1358.0	1357.2	1356.3
160°	1383.1	1383.8	1383.6	1382.3	1381.1	1379.7	1378.5
162.5°	1405.3	1406.7	1406.8	1405.4	1404.2	1402.9	1401.6
165°	1434.0	1435.6	1435.8	1434.8	1433.7	1432.7	1431.6
167.5°	1458.0	1459.6	1459.6	1457.9	1456.3	1454.8	1453.2
170°	1471.0	1472.6	1472.4	1470.6	1468.8	1467.0	1465.3
172.5°	1480.9	1482.6	1482.6	1480.8	1479.0	1477.2	1475.4
175°	1491.4	1493.3	1493.3	1491.4	1489.6	1487.8	1486.0
177.5°	1496.8	1498.3	1498.2	1496.6	1494.9	1493.3	1491.6
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3

(END OF REPORT)