

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333368-830

Luminaire Tested: **S125DIW-S375D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333368-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7314.5 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20																				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16																				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14																				
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12																				
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10																				
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9																				
6	58	46	39	33	51	41	35	30	32	27	24	22	20	17	14	12	11	8																				
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10	7																				
8	49	38	30	25	43	34	27	23	26	21	18	19	16	13	12	10	9	6																				
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5																				
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	0.7
10°-20°	146.6	2.0
20°-30°	216.5	3.0
30°-40°	252.7	3.5
40°-50°	253.8	3.5
50°-60°	222.8	3.0
60°-70°	166.0	2.3
70°-80°	94.9	1.3
80°-90°	31.6	0.4
90°-100°	69.6	1.0
100°-110°	428.7	5.9
110°-120°	777.5	10.6
120°-130°	997.8	13.6
130°-140°	1073.2	14.7
140°-150°	1007.4	13.8
150°-160°	814.9	11.1
160°-170°	527.0	7.2
170°-180°	181.8	2.5
0°-30°	415.1	5.7
0°-40°	667.8	9.1
0°-60°	1144.3	15.6
0°-90°	1436.8	19.6
90°-120°	1275.7	17.4
90°-150°	4354.1	59.5
90°-180°	5878.0	80.4
0°-180°	7314.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	1	13	23	30	34	5
95°	81	74	23	29	30	103
105°	417	422	423	423	421	442
115°	783	790	792	786	778	776
125°	1114	1123	1124	1118	1114	994
135°	1389	1397	1395	1392	1383	1070
145°	1610	1613	1613	1614	1606	1007
155°	1774	1766	1768	1771	1761	817
165°	1872	1864	1864	1872	1862	528
175°	1914	1906	1907	1917	1906	182
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.7	10.2	10.7	11.2	11.7	12.2	12.5	12.9	13.2	13.6	13.9
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	21.9	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3
95°	80.9	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3
97.5°	168.8	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9
100°	237.0	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9
102.5°	306.2	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1
105°	417.2	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3
110°	607.3	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	677.7	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6
115°	783.3	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4
117.5°	892.5	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9
120°	960.5	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8
122.5°	1020.8	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5
125°	1113.8	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5
127.5°	1202.6	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2
130°	1257.1	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7
132.5°	1311.5	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5
135°	1389.0	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1
137.5°	1460.3	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3
140°	1506.8	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9
142.5°	1548.8	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7
145°	1610.4	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5
147.5°	1664.3	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8
150°	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0
152.5°	1731.3	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5
155°	1773.6	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9
157.5°	1806.2	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4
160°	1828.9	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1
162.5°	1847.1	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7
165°	1871.5	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2
167.5°	1889.6	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5
170°	1899.9	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9
172.5°	1906.7	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6
175°	1914.0	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5
177.5°	1917.4	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	14.2	14.5	14.9	15.1	15.1	15.1	15.2	15.2
90°	25.8	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	25.8	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	25.8	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	52.0	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	152.9	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	297.2	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	608.2	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333368-830

CATALOG NUMBER: S125DIW-S375D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	680.3	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	789.2	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	894.3	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	962.1	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.8	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1121.2	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1207.5	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1263.8	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.4	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1393.5	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.4	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1509.5	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.7	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1613.9	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.2	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1699.6	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.2	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1769.8	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1803.4	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1824.3	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1843.5	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1868.1	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1886.8	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1896.4	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1903.8	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1911.9	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1915.3	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)