

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332839-940

Luminaire Tested: **S124DIW-S1195D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332839-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6233.0 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	33
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	2.7
10°-20°	471.5	7.6
20°-30°	694.0	11.1
30°-40°	806.8	12.9
40°-50°	806.8	12.9
50°-60°	705.8	11.3
60°-70°	524.1	8.4
70°-80°	297.8	4.8
80°-90°	87.5	1.4
90°-100°	18.5	0.3
100°-110°	117.8	1.9
110°-120°	225.4	3.6
120°-130°	286.1	4.6
130°-140°	306.1	4.9
140°-150°	286.3	4.6
150°-160°	230.9	3.7
160°-170°	148.9	2.4
170°-180°	51.3	0.8
0°-30°	1332.9	21.4
0°-40°	2139.7	34.3
0°-60°	3652.3	58.6
0°-90°	4561.7	73.2
90°-120°	361.7	5.8
90°-150°	1240.3	19.9
90°-180°	1671.0	26.8
0°-180°	6233.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	1	6	9	11	12	5
95°	22	9	9	11	12	29
105°	122	124	126	129	115	127
115°	227	228	228	229	229	223
125°	319	321	320	321	322	285
135°	396	396	397	398	399	305
145°	457	458	458	458	459	285
155°	501	501	500	501	500	231
165°	528	526	526	529	526	149
175°	540	538	538	541	537	51
180°	540	540	540	540	540	



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	29.9	29.8	29.8	29.7	29.6	29.5	29.4	29.3	29.2	29.2	29.2
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	5.1	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1
95°	22.2	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5
97.5°	47.2	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7
100°	66.3	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2
102.5°	87.7	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2
105°	121.6	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9
107.5°	153.3	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6
110°	174.6	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.3	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6
115°	227.1	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1
117.5°	255.8	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2
120°	275.2	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6
122.5°	293.3	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0
125°	319.2	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3
127.5°	343.8	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1
130°	359.6	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4
132.5°	374.3	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6
135°	396.0	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4
137.5°	415.4	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5
140°	427.9	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9
142.5°	439.3	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4
145°	456.6	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0
147.5°	470.5	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4
150°	480.5	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7
152.5°	488.9	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6
155°	500.7	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2
157.5°	510.7	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5
160°	516.5	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4
162.5°	521.7	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2
165°	528.2	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9
167.5°	533.3	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8
170°	536.3	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9
172.5°	538.2	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9
175°	540.3	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1
177.5°	541.3	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	29.3	29.4	29.5	29.6	29.7	29.7	29.7	29.8
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	9.6	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.0	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	14.7	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	52.7	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	127.7	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.0	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.6	178.8	179.0	179.1	179.4	179.7	179.9	180.2



TEST NUMBER: P332839-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.5	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.3	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.1	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.6	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	346.0	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.5	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.6	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.7	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.2	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.6	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.1	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.7	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	500.6	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	520.8	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	527.6	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	532.6	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	535.7	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	537.6	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	539.9	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	540.8	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)