

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333351-830

Luminaire Tested: **S125DIW-S375D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333351-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D770U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3943.6 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62		52	50	49		38	38	37	31
2	86	79	73	68	78	72	67	62	58	54	51		45	43	41		34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43		40	37	34		30	28	26	22
4	72	61	53	48	65	56	49	44	45	40	37		36	32	29		27	24	23	19
5	66	54	47	41	59	50	43	38	40	35	31		32	28	25		24	22	20	16
6	61	49	41	35	55	44	38	32	36	31	27		29	25	22		22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24		26	22	20		20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21		24	20	17		18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19		22	18	16		17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17		20	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	1.3
10°-20°	146.6	3.7
20°-30°	216.5	5.5
30°-40°	252.7	6.4
40°-50°	253.8	6.4
50°-60°	222.8	5.6
60°-70°	166.0	4.2
70°-80°	94.9	2.4
80°-90°	29.6	0.7
90°-100°	60.2	1.5
100°-110°	177.8	4.5
110°-120°	301.2	7.6
120°-130°	396.4	10.1
130°-140°	444.2	11.3
140°-150°	435.3	11.0
150°-160°	365.6	9.3
160°-170°	243.1	6.2
170°-180°	85.1	2.2
0°-30°	415.1	10.5
0°-40°	667.8	16.9
0°-60°	1144.3	29.0
0°-90°	1434.7	36.4
90°-120°	539.3	13.7
90°-150°	1815.1	46.0
90°-180°	2509.0	63.6
0°-180°	3943.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	1	6	11	15	17	4
95°	46	47	54	59	60	49
105°	160	163	167	171	174	170
115°	302	304	306	305	304	298
125°	440	444	445	444	443	394
135°	572	576	577	577	574	441
145°	693	696	698	698	696	433
155°	793	793	794	797	793	365
165°	863	861	862	864	861	243
175°	897	894	894	898	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.5	9.8	10.1	10.3	10.6	10.7	10.8	11.0	11.1	11.3	11.5
90°	0.7	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0
92.5°	17.0	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9
95°	45.5	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0
97.5°	75.6	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8
100°	97.9	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5
102.5°	122.1	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0
105°	159.6	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1
107.5°	201.0	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1
110°	229.5	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.6	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3
115°	301.6	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6
117.5°	344.7	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3
120°	371.6	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7
122.5°	400.7	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6
125°	440.1	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7
127.5°	482.1	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1
130°	507.3	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0
132.5°	532.4	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8
135°	572.3	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2
137.5°	609.8	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7
140°	634.0	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8
142.5°	658.0	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7
145°	693.4	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3
147.5°	726.1	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7
150°	748.0	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1
152.5°	765.9	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4
155°	793.4	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8
157.5°	818.1	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8
160°	832.6	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9
162.5°	845.6	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9
165°	862.7	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6
167.5°	877.3	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4
170°	885.1	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3
172.5°	890.7	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8
175°	897.0	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1
177.5°	900.2	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	11.6	11.8	11.9	12.0	11.9	11.9	11.8	11.7
90°	12.7	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	28.9	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	56.1	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	87.8	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	109.8	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	132.5	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	169.1	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	208.6	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.0	236.5	237.0	237.1	237.0	236.8	236.7	236.5



TEST NUMBER: P333351-830

CATALOG NUMBER: S125DIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	263.5	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.5	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.4	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.5	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.4	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	485.0	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.9	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.6	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	615.9	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.2	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	663.9	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.1	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	768.7	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	795.4	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	818.5	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	832.5	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	845.6	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.3	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	876.4	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	884.2	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	889.8	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	896.1	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	898.9	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)