

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332840-940

Luminaire Tested: **S124DIW-S1195D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332840-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6011.2 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	71	69	67	64
2	94	86	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	72	60	52	45	69	58	50	44	53	46	41	49	43	39	44	40	36	34
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	2.8
10°-20°	471.5	7.8
20°-30°	694.0	11.5
30°-40°	806.8	13.4
40°-50°	806.8	13.4
50°-60°	705.8	11.7
60°-70°	524.1	8.7
70°-80°	297.8	5.0
80°-90°	87.5	1.5
90°-100°	34.5	0.6
100°-110°	102.1	1.7
110°-120°	173.3	2.9
120°-130°	228.5	3.8
130°-140°	256.6	4.3
140°-150°	252.1	4.2
150°-160°	212.1	3.5
160°-170°	141.1	2.3
170°-180°	49.4	0.8
0°-30°	1332.9	22.2
0°-40°	2139.7	35.6
0°-60°	3652.3	60.8
0°-90°	4561.7	75.9
90°-120°	309.8	5.2
90°-150°	1047.0	17.4
90°-180°	1450.0	24.1
0°-180°	6011.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	1	6	9	11	12	6
95°	24	28	31	32	32	27
105°	94	95	96	97	99	100
115°	176	176	175	175	175	174
125°	256	256	256	255	255	229
135°	331	333	333	332	331	256
145°	402	404	404	404	402	252
155°	461	461	460	462	460	212
165°	501	500	499	502	500	141
175°	522	520	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	29.9	29.8	29.8	29.7	29.6	29.5	29.4	29.3	29.2	29.2	29.2
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	8.6	9.8	10.9	12.0	13.2	14.0	14.5	15.0	15.5	16.0	16.3
95°	24.3	25.1	25.9	26.7	27.5	28.2	28.8	29.4	30.1	30.7	30.9
97.5°	42.4	43.0	43.6	44.3	44.9	45.7	46.4	47.1	47.8	48.6	48.9
100°	56.5	56.9	57.2	57.6	58.1	58.6	59.4	60.2	61.0	61.8	62.0
102.5°	71.4	71.6	71.7	71.9	72.1	72.5	73.2	73.9	74.6	75.4	75.6
105°	94.2	94.3	94.3	94.4	94.5	94.7	95.1	95.4	95.8	96.1	96.4
107.5°	118.0	118.1	118.2	118.3	118.4	118.5	118.6	118.6	118.7	118.7	119.0
110°	134.1	134.3	134.5	134.6	134.8	134.9	134.8	134.7	134.6	134.6	134.4



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	151.0	151.0	151.1	151.1	151.1	151.1	150.9	150.7	150.5	150.4	150.3
115°	176.2	176.2	176.2	176.2	176.2	176.1	175.9	175.8	175.6	175.4	175.3
117.5°	199.9	200.0	200.1	200.2	200.2	200.2	200.1	199.9	199.8	199.7	199.4
120°	215.8	216.2	216.5	216.9	217.2	217.2	217.0	216.7	216.4	216.2	215.7
122.5°	232.3	232.4	232.6	232.6	232.8	232.8	232.7	232.6	232.5	232.4	232.0
125°	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.3	256.2	256.0
127.5°	278.7	278.9	279.2	279.5	279.7	279.8	279.6	279.5	279.4	279.2	279.0
130°	294.2	294.4	294.7	295.0	295.2	295.3	295.3	295.3	295.3	295.3	295.2
132.5°	310.0	310.2	310.4	310.6	310.8	310.9	310.8	310.7	310.7	310.6	310.4
135°	330.9	331.4	332.0	332.5	333.1	333.3	333.3	333.3	333.3	333.3	333.1
137.5°	353.7	354.0	354.2	354.5	354.7	354.9	355.1	355.3	355.3	355.5	355.3
140°	368.9	369.1	369.3	369.4	369.6	369.7	369.7	369.7	369.7	369.7	369.6
142.5°	382.8	383.0	383.2	383.3	383.5	383.6	383.5	383.4	383.3	383.3	383.3
145°	402.1	402.4	402.8	403.1	403.5	403.7	403.8	403.9	403.9	404.0	403.9
147.5°	421.2	421.5	422.0	422.4	422.8	423.0	422.9	422.8	422.8	422.8	422.7
150°	432.7	433.1	433.5	433.8	434.2	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	443.7	444.0	444.2	444.4	444.6	444.8	444.8	444.9	445.0	445.1	445.2
155°	460.7	460.7	460.7	460.7	460.7	460.6	460.5	460.4	460.3	460.2	460.6
157.5°	474.8	474.7	474.6	474.4	474.2	474.1	474.1	474.1	474.0	474.0	474.3
160°	483.3	483.2	483.1	483.0	483.0	482.9	482.8	482.7	482.6	482.5	482.8
162.5°	491.1	490.8	490.5	490.4	490.1	489.9	489.8	489.7	489.6	489.5	490.1
165°	501.4	501.1	500.9	500.6	500.3	500.2	500.0	499.8	499.6	499.4	500.0
167.5°	509.4	509.1	508.7	508.4	507.9	507.7	507.7	507.8	507.8	507.8	508.4
170°	514.0	513.5	513.1	512.6	512.2	512.0	512.1	512.2	512.3	512.4	512.9
172.5°	517.2	516.8	516.5	516.1	515.7	515.5	515.5	515.6	515.6	515.6	516.2
175°	521.7	521.2	520.8	520.3	519.9	519.6	519.5	519.4	519.3	519.2	519.9
177.5°	523.1	522.7	522.4	522.0	521.7	521.5	521.5	521.5	521.5	521.5	522.0
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	29.3	29.4	29.5	29.6	29.7	29.7	29.7	29.8
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.7	16.9	17.3	17.5	17.7	17.7	17.8	17.9
95°	31.2	31.5	31.7	31.9	31.9	31.9	31.9	31.9
97.5°	49.2	49.6	49.8	50.0	50.0	50.0	50.0	50.0
100°	62.2	62.3	62.5	62.6	62.6	62.6	62.6	62.6
102.5°	75.9	76.2	76.4	76.6	76.6	76.7	76.8	76.9
105°	96.8	97.0	97.3	97.6	97.8	98.1	98.4	98.6
107.5°	119.2	119.5	119.8	119.8	119.8	119.8	119.8	119.8
110°	134.2	134.0	133.8	133.8	134.1	134.4	134.6	134.9



TEST NUMBER: P332840-940

CATALOG NUMBER: S124DIW-S1195D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	150.3	150.3	150.3	150.3	150.3	150.3	150.4	150.4
115°	175.2	175.1	175.0	175.0	174.9	174.8	174.7	174.6
117.5°	199.1	198.8	198.5	198.2	198.0	197.9	197.7	197.5
120°	215.3	214.8	214.4	214.3	214.5	214.6	214.8	215.0
122.5°	231.8	231.4	231.1	230.8	230.5	230.2	229.8	229.5
125°	255.8	255.7	255.5	255.3	255.1	254.9	254.8	254.6
127.5°	278.8	278.7	278.5	278.3	278.2	278.0	277.9	277.8
130°	295.0	294.8	294.6	294.4	294.0	293.6	293.3	292.9
132.5°	310.2	310.0	309.9	309.7	309.5	309.4	309.2	309.2
135°	333.0	332.8	332.6	332.4	332.2	331.9	331.6	331.4
137.5°	355.0	354.8	354.5	354.5	354.5	354.5	354.6	354.7
140°	369.5	369.4	369.3	369.3	369.2	369.1	369.0	368.9
142.5°	383.3	383.3	383.3	383.2	383.2	383.2	383.2	383.2
145°	403.9	403.8	403.7	403.5	403.2	403.0	402.7	402.4
147.5°	422.6	422.5	422.5	422.4	422.3	422.2	422.1	422.0
150°	434.4	434.4	434.4	434.4	434.3	434.2	434.1	434.0
152.5°	445.5	445.7	445.9	445.9	445.7	445.4	445.2	445.0
155°	460.9	461.3	461.6	461.6	461.3	460.9	460.6	460.2
157.5°	474.6	474.8	475.1	475.1	474.8	474.5	474.2	473.9
160°	483.0	483.3	483.6	483.5	483.0	482.6	482.1	481.6
162.5°	490.5	491.1	491.5	491.5	491.1	490.6	490.2	489.7
165°	500.5	501.1	501.6	501.7	501.3	501.0	500.6	500.2
167.5°	508.9	509.4	510.0	510.0	509.4	508.9	508.3	507.7
170°	513.4	514.0	514.5	514.4	513.8	513.2	512.6	511.9
172.5°	516.8	517.5	518.0	518.0	517.4	516.7	516.1	515.5
175°	520.5	521.1	521.7	521.7	521.1	520.5	519.9	519.2
177.5°	522.5	523.0	523.5	523.4	522.9	522.4	521.7	521.2
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5

(END OF REPORT)