

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333399-830

Luminaire Tested: **S125DIW-S610D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333399-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7456.5 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	39	39	39	32		
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	33	33	33	33	33	33	27		
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	28	28	28	28	28	28	22		
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	24	24	24	24	24	24	19		
4	71	60	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	20	20	20	20	20	20	16		
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	18	18	18	18	18	18	14		
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15	15	15	15	15	15	15	12		
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	16	14	14	14	14	14	14	14	11		
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	12	12	12	12	12	12	10		
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11	11	11	11	11	11	11	9		
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	10	10	10	10	10	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5846	5846	5846
5°	5859	5803	5841
10°	5823	5762	5795
15°	5760	5693	5717
20°	5670	5597	5606
25°	5573	5481	5476
30°	5452	5357	5330
35°	5324	5222	5149
40°	5193	5078	5005
45°	5050	4945	4847
50°	4893	4786	4641
55°	4741	4604	4476
60°	4561	4421	4265
65°	4345	4202	4060
70°	4137	3950	3814
75°	3770	3646	3521
80°	3355	3303	3221
85°	2920	2971	2816



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	1.1
10°-20°	241.1	3.2
20°-30°	356.0	4.8
30°-40°	415.4	5.6
40°-50°	417.2	5.6
50°-60°	366.2	4.9
60°-70°	272.9	3.7
70°-80°	156.0	2.1
80°-90°	49.4	0.7
90°-100°	122.3	1.6
100°-110°	361.3	4.8
110°-120°	611.9	8.2
120°-130°	805.3	10.8
130°-140°	902.4	12.1
140°-150°	884.4	11.9
150°-160°	742.8	10.0
160°-170°	493.8	6.6
170°-180°	172.8	2.3
0°-30°	682.4	9.2
0°-40°	1097.8	14.7
0°-60°	1881.2	25.2
0°-90°	2359.4	31.6
90°-120°	1095.5	14.7
90°-150°	3687.7	49.5
90°-180°	5097.0	68.4
0°-180°	7456.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	904	902	895	901	901	86
15°	862	859	852	855	855	243
25°	782	778	769	770	768	360
35°	675	672	662	659	653	422
45°	553	550	541	533	531	426
55°	421	418	409	403	398	376
65°	284	282	275	269	266	282
75°	151	150	146	144	141	161
85°	39	40	40	39	38	44
90°	1	13	23	30	34	7
95°	92	96	109	119	122	99
105°	324	331	340	348	352	346
115°	613	618	621	620	618	606
125°	894	902	904	901	900	800
135°	1163	1171	1173	1172	1167	896
145°	1409	1414	1419	1418	1414	880
155°	1612	1612	1613	1618	1612	742
165°	1753	1750	1751	1756	1748	494
175°	1822	1817	1817	1824	1815	173
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	907.5	907.1	906.7	906.3	906.0	905.1	903.9	902.6	901.4	900.0	901.4
5°	903.8	903.4	903.1	902.8	902.5	901.5	899.9	898.3	896.7	895.1	896.6
7.5°	895.4	895.1	894.8	894.5	894.2	893.2	891.4	889.7	887.9	886.2	887.5
10°	888.0	887.7	887.4	887.0	886.7	885.7	883.9	882.2	880.4	878.7	880.0
12.5°	878.8	878.3	877.7	877.1	876.6	875.4	873.8	872.2	870.5	868.9	870.0
15°	861.5	861.0	860.5	860.1	859.6	858.5	856.8	855.0	853.2	851.5	852.2
17.5°	841.6	840.9	840.2	839.5	838.8	837.5	835.8	833.9	832.1	830.3	831.2
20°	825.0	824.6	824.3	824.1	823.7	822.6	820.5	818.4	816.3	814.3	815.4
22.5°	808.3	807.8	807.2	806.6	806.1	804.8	802.9	801.0	799.0	797.0	797.8
25°	782.0	781.2	780.4	779.7	778.8	777.4	775.3	773.3	771.2	769.1	769.5
27.5°	751.2	750.7	750.3	749.8	749.3	748.0	745.8	743.8	741.6	739.5	739.5
30°	731.1	730.7	730.2	729.7	729.2	727.8	725.5	723.0	720.7	718.3	717.9
32.5°	709.4	708.7	707.9	707.2	706.4	705.0	702.9	700.8	698.6	696.5	696.0
35°	675.3	674.7	674.0	673.4	672.8	671.4	669.1	666.8	664.7	662.4	661.7
37.5°	639.9	639.1	638.4	637.5	636.8	635.3	633.2	631.1	629.0	626.9	625.8
40°	615.9	615.1	614.3	613.5	612.7	611.1	609.0	606.7	604.5	602.3	600.9
42.5°	590.1	589.5	588.7	588.1	587.4	586.0	583.7	581.5	579.3	577.0	575.8
45°	552.9	552.2	551.6	550.9	550.4	549.0	547.1	545.3	543.3	541.4	539.5
47.5°	512.7	512.7	512.8	512.8	512.8	511.7	509.4	507.2	504.9	502.6	500.7
50°	487.0	486.4	486.0	485.5	485.0	483.9	481.9	480.0	478.2	476.3	474.2
52.5°	460.6	460.2	460.0	459.6	459.2	458.0	456.0	453.9	451.9	449.9	448.1
55°	421.1	420.6	420.1	419.6	419.1	417.8	415.6	413.4	411.1	408.9	407.5
57.5°	379.4	379.2	378.9	378.6	378.4	377.3	375.4	373.5	371.6	369.9	368.0
60°	353.1	352.4	351.8	351.1	350.5	349.3	347.6	345.8	344.0	342.3	340.7
62.5°	325.6	325.1	324.5	324.0	323.5	322.5	321.0	319.5	318.0	316.5	314.8
65°	284.3	284.0	283.7	283.3	283.0	282.0	280.2	278.5	276.7	275.0	273.5
67.5°	244.3	243.6	243.0	242.3	241.7	240.7	239.4	238.1	236.8	235.4	234.2
70°	219.1	218.4	217.5	216.8	215.9	214.8	213.4	212.0	210.6	209.2	208.1
72.5°	191.6	191.1	190.6	190.0	189.5	188.7	187.8	186.9	186.0	185.0	184.0
75°	151.1	150.8	150.4	150.1	149.9	149.3	148.5	147.7	146.8	146.1	145.6
77.5°	113.8	113.6	113.5	113.3	113.2	112.9	112.4	112.1	111.6	111.1	110.8
80°	90.2	90.2	90.2	90.2	90.2	90.1	89.7	89.4	89.2	88.8	88.6
82.5°	69.7	69.4	69.1	68.8	68.6	68.4	68.3	68.3	68.2	68.1	67.9
85°	39.4	39.6	39.7	39.9	40.1	40.1	40.1	40.1	40.1	40.1	40.0
87.5°	15.7	16.2	16.8	17.2	17.8	18.2	18.5	18.9	19.1	19.4	19.8
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	34.4	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6
95°	92.4	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7
97.5°	153.5	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3
100°	199.0	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4
102.5°	247.9	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1
105°	324.1	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7
107.5°	408.2	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8
110°	466.3	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9
115°	612.7	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9
117.5°	700.2	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6
120°	754.8	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4
122.5°	814.0	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9
125°	894.1	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4
127.5°	979.4	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6
130°	1030.6	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2
132.5°	1081.8	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5
135°	1162.8	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7
137.5°	1239.0	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8
140°	1287.9	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9
142.5°	1336.8	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5
145°	1408.7	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6
147.5°	1475.3	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5
150°	1519.6	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9
152.5°	1555.9	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0
155°	1612.0	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7
157.5°	1662.0	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6
160°	1691.6	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0
162.5°	1717.8	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5
165°	1752.8	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6
167.5°	1782.3	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5
170°	1798.2	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4
172.5°	1809.6	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8
175°	1822.4	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5
177.5°	1828.9	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	902.6	903.9	905.1	905.7	905.6	905.4	905.3	905.2
5°	898.1	899.5	900.9	901.5	901.4	901.3	901.1	900.9
7.5°	888.9	890.3	891.7	892.4	892.2	892.0	891.9	891.7
10°	881.3	882.5	883.8	884.4	884.2	884.0	883.8	883.7
12.5°	871.0	872.0	873.0	873.5	873.5	873.5	873.5	873.4
15°	853.1	853.8	854.7	855.1	855.1	855.1	855.1	855.1
17.5°	832.3	833.2	834.2	834.3	833.5	832.7	832.0	831.1
20°	816.4	817.6	818.7	818.9	818.0	817.3	816.4	815.7
22.5°	798.5	799.3	800.0	800.1	799.6	799.0	798.4	798.0
25°	769.8	770.1	770.4	770.3	769.9	769.4	768.9	768.5
27.5°	739.6	739.7	739.7	739.5	739.0	738.6	738.1	737.6
30°	717.7	717.4	717.0	716.6	716.1	715.7	715.2	714.7
32.5°	695.4	694.7	694.2	693.5	692.7	691.8	690.9	690.0
35°	660.8	660.1	659.2	658.2	657.0	655.6	654.4	653.1
37.5°	624.5	623.4	622.2	621.2	620.5	619.8	619.1	618.3
40°	599.4	597.9	596.5	595.6	595.1	594.7	594.2	593.7
42.5°	574.5	573.2	571.8	570.8	570.0	569.4	568.6	567.9
45°	537.5	535.6	533.8	532.5	532.1	531.6	531.1	530.7
47.5°	498.7	496.7	494.8	493.3	492.2	491.1	489.9	488.8
50°	472.1	470.0	468.0	466.4	465.2	464.1	463.0	461.9
52.5°	446.2	444.4	442.6	441.1	439.9	438.6	437.3	436.1
55°	406.0	404.6	403.2	401.9	400.8	399.6	398.6	397.5
57.5°	366.1	364.3	362.4	361.2	360.6	360.0	359.4	358.8
60°	339.1	337.5	335.9	334.6	333.5	332.3	331.2	330.2
62.5°	313.1	311.4	309.6	308.4	307.6	306.6	305.8	304.9
65°	272.1	270.7	269.3	268.2	267.6	266.9	266.4	265.7
67.5°	233.1	231.9	230.6	229.8	229.4	229.0	228.7	228.3
70°	207.2	206.2	205.3	204.5	203.9	203.2	202.6	202.0
72.5°	182.9	181.8	180.7	179.8	179.2	178.6	178.0	177.3
75°	145.2	144.7	144.2	143.6	143.0	142.3	141.8	141.1
77.5°	110.6	110.3	110.0	109.6	109.1	108.8	108.3	107.8
80°	88.5	88.3	88.1	87.9	87.6	87.3	87.0	86.6
82.5°	67.6	67.3	67.0	66.8	66.8	66.7	66.6	66.6
85°	39.8	39.6	39.5	39.2	38.9	38.5	38.3	38.0
87.5°	20.1	20.4	20.7	20.8	20.7	20.7	20.6	20.5
90°	25.9	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	58.7	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	113.9	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	178.4	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	223.2	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	269.2	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	343.6	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	423.8	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	479.6	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333399-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	535.4	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.6	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	705.9	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.7	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.9	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.3	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.9	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1092.2	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.1	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1300.5	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1348.9	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1483.3	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1561.8	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1615.9	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1662.8	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1691.3	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1718.0	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1753.8	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1780.4	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1796.3	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1807.7	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1820.5	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1826.3	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)