

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333416-830

Luminaire Tested: **S125DIW-S850D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333416-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7171.3 lumens  
Efficiency: N/A  
Efficacy: 136.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.7	1.6
10°-20°	329.6	4.6
20°-30°	486.6	6.8
30°-40°	567.8	7.9
40°-50°	570.3	8.0
50°-60°	500.6	7.0
60°-70°	373.0	5.2
70°-80°	213.3	3.0
80°-90°	64.7	0.9
90°-100°	46.7	0.7
100°-110°	288.0	4.0
110°-120°	522.3	7.3
120°-130°	670.4	9.3
130°-140°	721.0	10.1
140°-150°	676.8	9.4
150°-160°	547.5	7.6
160°-170°	354.1	4.9
170°-180°	122.1	1.7
0°-30°	932.8	13.0
0°-40°	1500.6	20.9
0°-60°	2571.4	35.9
0°-90°	3222.4	44.9
90°-120°	857.1	12.0
90°-150°	2925.3	40.8
90°-180°	3949.0	55.1
0°-180°	7171.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	8	15	20	23	5
95°	54	50	15	20	20	69
105°	280	284	284	284	283	297
115°	526	531	532	528	522	521
125°	748	755	755	751	748	668
135°	933	939	937	935	929	719
145°	1082	1084	1084	1084	1079	676
155°	1192	1186	1188	1190	1183	549
165°	1257	1252	1252	1258	1251	355
175°	1286	1281	1281	1288	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.3	21.7	22.1	22.3	22.7	22.9	23.0	23.2	23.3	23.4	23.7
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	14.7	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3
95°	54.3	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3
97.5°	113.5	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9
100°	159.2	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3
102.5°	205.8	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7
105°	280.2	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6
110°	408.0	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3



TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.2	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9
115°	526.2	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0
117.5°	599.6	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9
120°	645.4	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9
122.5°	685.8	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3
125°	748.3	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1
127.5°	807.9	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7
130°	844.6	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7
132.5°	881.2	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5
135°	933.2	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6
137.5°	981.1	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4
140°	1012.4	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7
142.5°	1040.6	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1
145°	1081.9	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1
147.5°	1118.1	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2
150°	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5
152.5°	1163.2	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3
155°	1191.6	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4
157.5°	1213.5	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0
160°	1228.8	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8
162.5°	1241.0	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4
165°	1257.4	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9
167.5°	1269.5	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1
170°	1276.4	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4
172.5°	1281.0	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5
175°	1285.9	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9
177.5°	1288.3	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	23.8	24.0	24.2	24.2	24.0	23.8	23.6	23.4
90°	17.3	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	17.3	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	17.3	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	35.0	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	102.7	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	199.6	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.6	408.0	407.4	407.2	407.4	407.6	407.7	408.0





TEST NUMBER: P333416-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.1	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	530.2	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	600.9	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.4	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.8	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	753.3	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	811.2	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	849.0	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.4	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	936.2	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.5	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.2	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.2	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.3	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.5	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1141.9	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1161.7	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.0	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1211.6	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1225.7	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1238.6	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1255.1	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1267.6	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1274.1	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1279.1	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1284.6	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1286.8	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)