

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333417-830

Luminaire Tested: **S125DIW-S850D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333417-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1050U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6646.9 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41				41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34				34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29				29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25				25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25	21				21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19				19
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17				17
8	54	41	34	28	49	38	31	27	33	27	23	28	24	20	23	20	17	15				15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13				13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	1.8
10°-20°	329.6	5.0
20°-30°	486.6	7.3
30°-40°	567.8	8.5
40°-50°	570.3	8.6
50°-60°	500.6	7.5
60°-70°	373.0	5.6
70°-80°	213.3	3.2
80°-90°	64.7	1.0
90°-100°	82.2	1.2
100°-110°	242.7	3.7
110°-120°	411.1	6.2
120°-130°	541.1	8.1
130°-140°	606.3	9.1
140°-150°	594.2	8.9
150°-160°	499.1	7.5
160°-170°	331.7	5.0
170°-180°	116.1	1.7
0°-30°	932.8	14.0
0°-40°	1500.6	22.6
0°-60°	2571.4	38.7
0°-90°	3222.4	48.5
90°-120°	736.0	11.1
90°-150°	2477.6	37.3
90°-180°	3424.0	51.5
0°-180°	6646.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	8	15	20	23	6
95°	62	64	74	80	82	66
105°	218	223	228	234	237	233
115°	412	415	417	416	416	407
125°	601	606	607	606	604	538
135°	781	787	788	788	784	602
145°	946	950	953	953	950	591
155°	1083	1083	1084	1087	1083	499
165°	1178	1176	1177	1180	1175	332
175°	1224	1221	1220	1226	1220	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.3	21.7	22.1	22.3	22.7	22.9	23.1	23.2	23.3	23.4	23.7
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	23.1	24.3	25.4	26.7	27.9	29.4	31.2	33.0	34.9	36.7	38.1
95°	62.1	62.5	63.0	63.3	63.8	65.0	67.2	69.3	71.4	73.5	75.0
97.5°	103.1	103.3	103.5	103.7	103.9	105.4	108.3	111.2	114.1	117.1	118.5
100°	133.7	133.7	133.7	133.7	133.7	135.1	137.8	140.6	143.4	146.1	148.1
102.5°	166.5	167.4	168.2	169.1	169.9	171.1	172.5	173.9	175.3	176.7	178.8
105°	217.7	218.8	219.9	220.9	222.0	223.2	224.4	225.7	227.0	228.3	229.5
107.5°	274.3	275.3	276.4	277.5	278.5	279.6	280.5	281.5	282.5	283.4	284.1
110°	313.2	314.3	315.4	316.4	317.5	318.4	319.0	319.6	320.3	320.9	321.5



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.0	353.5	354.1	354.7	355.2	355.9	356.7	357.5	358.3	359.1	359.4
115°	411.6	412.5	413.3	414.2	415.0	415.7	416.0	416.5	416.9	417.4	417.2
117.5°	470.4	470.8	471.2	471.6	472.0	472.4	472.8	473.2	473.5	473.9	474.1
120°	507.1	508.2	509.3	510.3	511.3	512.0	512.2	512.5	512.6	512.8	512.8
122.5°	546.9	547.2	547.6	548.0	548.4	548.8	549.4	550.0	550.5	551.1	550.9
125°	600.7	602.0	603.2	604.5	605.8	606.5	606.8	607.0	607.2	607.4	607.0
127.5°	658.0	658.7	659.5	660.2	660.9	661.4	661.7	661.9	662.1	662.4	662.2
130°	692.4	693.4	694.6	695.6	696.6	697.4	697.9	698.2	698.7	699.1	698.9
132.5°	726.8	728.5	730.3	732.0	733.8	734.6	734.5	734.4	734.3	734.2	734.1
135°	781.2	782.5	783.7	785.0	786.4	787.0	787.3	787.5	787.7	787.9	787.9
137.5°	832.5	833.7	834.9	836.1	837.4	838.2	838.7	839.1	839.6	840.1	840.3
140°	865.3	866.3	867.4	868.5	869.5	870.3	871.0	871.7	872.2	872.9	873.4
142.5°	898.1	899.0	899.9	900.8	901.7	902.6	903.3	904.2	904.9	905.8	906.0
145°	946.4	947.3	948.1	949.0	949.8	950.6	951.2	951.9	952.5	953.1	953.1
147.5°	991.2	991.6	992.1	992.5	993.0	993.5	994.0	994.5	995.0	995.5	996.1
150°	1021.0	1020.8	1020.5	1020.3	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8
152.5°	1045.4	1045.7	1045.9	1046.3	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8
155°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9
157.5°	1116.6	1116.2	1115.7	1115.2	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3
160°	1136.5	1135.9	1135.2	1134.6	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5
162.5°	1154.0	1153.6	1153.1	1152.6	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2
165°	1177.6	1177.1	1176.7	1176.3	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4
167.5°	1197.4	1196.6	1195.7	1194.9	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9
170°	1208.2	1207.3	1206.5	1205.6	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6
172.5°	1215.8	1214.9	1214.1	1213.2	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2
175°	1224.4	1223.5	1222.7	1221.8	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8
177.5°	1228.8	1228.0	1227.4	1226.7	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	23.8	24.0	24.2	24.2	24.0	23.8	23.6	23.4
90°	17.4	18.5	19.5	20.4	21.0	21.7	22.2	22.9
92.5°	39.5	40.9	42.3	43.2	43.6	44.1	44.6	45.1
95°	76.5	77.9	79.5	80.4	80.9	81.2	81.7	82.1
97.5°	119.9	121.3	122.7	123.5	123.8	124.0	124.3	124.5
100°	150.0	151.8	153.7	155.0	155.3	155.8	156.2	156.7
102.5°	180.9	182.9	185.0	186.3	186.9	187.6	188.1	188.7
105°	230.8	232.1	233.4	234.3	235.0	235.5	236.2	236.9
107.5°	284.7	285.4	286.0	286.3	286.3	286.3	286.2	286.2
110°	322.2	322.8	323.5	323.7	323.5	323.2	323.0	322.8



TEST NUMBER: P333417-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	359.7	360.0	360.2	360.2	359.9	359.5	359.1	358.7
115°	416.9	416.7	416.5	416.3	416.0	415.8	415.7	415.5
117.5°	474.2	474.4	474.6	474.2	473.3	472.5	471.6	470.8
120°	512.8	512.8	512.8	512.5	511.6	510.8	509.9	509.1
122.5°	550.7	550.5	550.4	550.0	549.3	548.6	547.9	547.2
125°	606.5	606.1	605.7	605.4	605.2	604.9	604.7	604.5
127.5°	661.9	661.8	661.6	661.3	660.8	660.4	660.0	659.6
130°	698.7	698.4	698.2	698.0	697.5	697.1	696.6	696.3
132.5°	733.8	733.6	733.4	733.0	732.4	731.8	731.2	730.6
135°	787.9	787.9	787.9	787.5	786.6	785.8	784.9	784.1
137.5°	840.6	840.8	841.0	840.7	839.6	838.6	837.4	836.4
140°	873.7	874.2	874.6	874.3	873.3	872.1	871.1	870.1
142.5°	906.3	906.5	906.8	906.3	905.3	904.3	903.2	902.1
145°	953.1	953.1	953.1	952.8	952.2	951.5	950.9	950.3
147.5°	996.6	997.0	997.6	997.1	995.7	994.2	992.8	991.4
150°	1023.8	1023.8	1023.8	1023.6	1023.1	1022.8	1022.3	1021.9
152.5°	1049.2	1049.8	1050.3	1050.2	1049.4	1048.7	1047.8	1047.1
155°	1085.7	1086.6	1087.4	1087.2	1086.2	1085.1	1084.1	1083.0
157.5°	1117.2	1118.0	1118.9	1118.6	1117.2	1115.8	1114.4	1113.0
160°	1136.3	1137.2	1138.0	1137.8	1136.8	1135.8	1134.7	1133.6
162.5°	1154.2	1155.2	1156.2	1156.1	1154.9	1153.7	1152.4	1151.2
165°	1178.3	1179.1	1180.0	1179.8	1178.6	1177.2	1176.0	1174.7
167.5°	1196.2	1197.4	1198.7	1198.7	1197.4	1196.1	1194.8	1193.4
170°	1206.8	1208.2	1209.4	1209.3	1207.8	1206.4	1204.9	1203.3
172.5°	1214.5	1215.8	1217.0	1217.0	1215.7	1214.4	1213.1	1211.7
175°	1223.0	1224.4	1225.7	1225.5	1224.1	1222.6	1221.1	1219.6
177.5°	1227.0	1228.0	1229.0	1228.9	1227.8	1226.5	1225.4	1224.2
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2

(END OF REPORT)