

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332726-940

Luminaire Tested: **S124DIW-S350D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332726-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D770U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3728.4 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19
5	66	54	47	41	59	50	43	38	41	35	31	32	28	25	24	22	20	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.6	1.3
10°-20°	139.8	3.7
20°-30°	205.7	5.5
30°-40°	239.2	6.4
40°-50°	239.2	6.4
50°-60°	209.2	5.6
60°-70°	155.4	4.2
70°-80°	88.3	2.4
80°-90°	28.0	0.8
90°-100°	56.4	1.5
100°-110°	167.2	4.5
110°-120°	283.8	7.6
120°-130°	374.2	10.0
130°-140°	420.2	11.3
140°-150°	413.0	11.1
150°-160°	347.3	9.3
160°-170°	231.1	6.2
170°-180°	80.9	2.2
0°-30°	395.1	10.6
0°-40°	634.2	17.0
0°-60°	1082.6	29.0
0°-90°	1354.3	36.3
90°-120°	507.4	13.6
90°-150°	1714.8	46.0
90°-180°	2374.0	63.7
0°-180°	3728.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	2	9	14	18	20	4
95°	40	46	50	52	52	44
105°	154	155	158	160	162	164
115°	289	288	287	287	286	284
125°	420	420	420	418	417	374
135°	542	546	546	545	543	419
145°	658	661	662	661	659	412
155°	754	754	754	756	754	347
165°	821	819	818	822	819	231
175°	854	851	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	9.2	9.5	9.6	9.9	10.2	10.3	10.5	10.7	10.9	11.1	11.2
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	14.2	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8
95°	39.7	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7
97.5°	69.4	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1
100°	92.6	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6
102.5°	117.0	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9
105°	154.2	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9
107.5°	193.2	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8
110°	219.7	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1



TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	247.3	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3
115°	288.6	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0
117.5°	327.4	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5
120°	353.4	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3
122.5°	380.4	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0
125°	420.3	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3
127.5°	456.4	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0
130°	481.8	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5
132.5°	507.7	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4
135°	542.1	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7
137.5°	579.3	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8
140°	604.2	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4
142.5°	627.0	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8
145°	658.5	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	689.7	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2
150°	708.8	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	726.8	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2
155°	754.5	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4
157.5°	777.8	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9
160°	791.6	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7
162.5°	804.2	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6
165°	821.4	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9
167.5°	834.4	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7
170°	841.9	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1
172.5°	847.1	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5
175°	854.4	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5
177.5°	856.8	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	11.3	11.5	11.7	11.9	11.9	11.9	12.0	12.0
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.3	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.2	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	80.6	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	101.8	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.3	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.4	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.3	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.8	219.5	219.2	219.3	219.7	220.2	220.6	221.1





TEST NUMBER: P332726-940

CATALOG NUMBER: S124DIW-S350D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.2	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	287.0	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	326.1	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	352.6	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.5	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	419.0	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.7	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	483.2	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	508.1	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.4	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.5	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.3	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.8	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.6	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.3	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.1	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	803.4	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	819.7	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	833.6	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.0	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	846.5	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	855.8	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)