

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332761-940

Luminaire Tested: **S124DIW-S575D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332761-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1050U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5962.2 lumens  
Efficiency: N/A  
Efficacy: 131.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.6	1.4
10°-20°	229.8	3.9
20°-30°	338.2	5.7
30°-40°	393.2	6.6
40°-50°	393.2	6.6
50°-60°	343.9	5.8
60°-70°	255.4	4.3
70°-80°	145.1	2.4
80°-90°	45.4	0.8
90°-100°	41.3	0.7
100°-110°	263.4	4.4
110°-120°	503.9	8.5
120°-130°	639.7	10.7
130°-140°	684.4	11.5
140°-150°	640.0	10.7
150°-160°	516.1	8.7
160°-170°	332.9	5.6
170°-180°	114.7	1.9
0°-30°	649.5	10.9
0°-40°	1042.7	17.5
0°-60°	1779.8	29.9
0°-90°	2225.7	37.3
90°-120°	808.6	13.6
90°-150°	2772.8	46.5
90°-180°	3737.0	62.7
0°-180°	5962.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	3	12	20	25	27	4
95°	50	21	20	25	26	64
105°	272	277	282	288	258	285
115°	508	510	510	511	511	499
125°	714	717	716	718	719	637
135°	885	885	888	890	892	682
145°	1021	1023	1024	1025	1026	638
155°	1119	1120	1118	1121	1118	516
165°	1181	1177	1176	1183	1175	334
175°	1208	1203	1204	1210	1201	115
180°	1208	1208	1208	1208	1208	



TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	15.0	15.3	15.6	16.0	16.2	16.5	16.7	16.9	17.1	17.3	17.6
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	11.4	11.5	11.6	11.8	11.9	12.8	14.4	16.0	17.6	19.2	20.3
95°	49.7	42.9	36.0	29.2	22.4	19.1	19.3	19.4	19.7	19.9	21.0
97.5°	105.5	109.8	114.0	118.3	122.5	113.5	91.0	68.7	46.3	23.8	24.0
100°	148.2	151.8	155.4	159.0	162.6	150.6	122.9	95.1	67.5	39.8	36.4
102.5°	195.9	198.5	201.2	203.8	206.4	206.0	202.4	198.8	195.1	191.5	154.7
105°	272.0	273.1	274.4	275.5	276.8	277.9	278.8	279.9	280.9	281.9	283.7
107.5°	342.6	343.2	343.8	344.4	345.0	346.0	347.3	348.7	350.1	351.4	352.3
110°	390.3	390.9	391.5	392.1	392.7	393.6	394.8	396.0	397.3	398.4	398.9



TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.6	437.7	438.7	439.8	440.9	441.8	442.3	442.8	443.4	444.0	443.9
115°	507.7	508.4	509.0	509.5	510.1	510.3	510.1	510.0	509.8	509.5	510.0
117.5°	571.9	572.7	573.5	574.3	575.1	575.7	576.1	576.6	577.0	577.5	577.4
120°	615.3	616.1	616.9	617.7	618.5	618.8	618.6	618.4	618.1	618.0	618.4
122.5°	655.8	656.2	656.7	657.2	657.6	658.1	658.4	658.6	658.9	659.2	659.4
125°	713.7	714.5	715.3	716.1	716.9	717.1	716.8	716.3	716.0	715.5	716.1
127.5°	768.7	768.8	769.1	769.3	769.5	770.0	771.0	771.9	772.8	773.7	773.6
130°	804.1	804.3	804.5	804.7	804.9	805.3	805.9	806.5	807.1	807.7	807.9
132.5°	836.6	837.0	837.3	837.7	838.0	838.7	839.4	840.2	840.9	841.7	841.9
135°	885.4	885.2	885.0	884.8	884.6	884.9	885.7	886.5	887.3	888.1	888.5
137.5°	928.5	928.6	928.7	928.8	928.9	929.3	930.2	931.1	932.0	932.9	933.4
140°	956.8	957.2	957.6	958.0	958.4	958.8	959.2	959.6	960.0	960.4	961.0
142.5°	982.0	982.8	983.5	984.3	985.0	985.4	985.7	985.9	986.1	986.4	986.9
145°	1020.9	1021.5	1022.1	1022.7	1023.3	1023.6	1023.6	1023.6	1023.6	1023.6	1023.9
147.5°	1051.8	1052.9	1054.1	1055.2	1056.3	1056.8	1056.6	1056.4	1056.1	1056.0	1056.1
150°	1074.2	1075.0	1075.8	1076.7	1077.5	1077.7	1077.5	1077.4	1077.1	1076.9	1076.9
152.5°	1093.0	1093.7	1094.3	1094.9	1095.6	1095.7	1095.4	1095.0	1094.7	1094.3	1094.6
155°	1119.4	1119.6	1119.8	1120.0	1120.2	1120.0	1119.4	1118.8	1118.2	1117.6	1118.4
157.5°	1141.7	1141.5	1141.4	1141.2	1141.1	1140.8	1140.1	1139.3	1138.7	1138.0	1139.1
160°	1154.6	1154.1	1153.4	1152.8	1152.2	1151.8	1151.6	1151.4	1151.2	1151.0	1152.2
162.5°	1166.2	1165.5	1164.7	1163.9	1163.1	1162.6	1162.4	1162.3	1162.1	1161.8	1163.1
165°	1180.8	1179.8	1178.8	1177.8	1176.8	1176.3	1176.3	1176.3	1176.3	1176.3	1177.9
167.5°	1192.4	1191.3	1190.3	1189.3	1188.2	1187.7	1187.5	1187.4	1187.3	1187.1	1188.9
170°	1198.9	1197.7	1196.5	1195.2	1194.1	1193.6	1193.7	1194.0	1194.2	1194.4	1196.0
172.5°	1203.2	1202.0	1200.8	1199.6	1198.4	1197.9	1198.1	1198.3	1198.5	1198.7	1200.3
175°	1207.9	1206.8	1205.5	1204.3	1203.1	1202.7	1202.8	1203.0	1203.2	1203.5	1205.2
177.5°	1210.1	1209.0	1207.8	1206.8	1205.6	1205.2	1205.5	1205.9	1206.1	1206.5	1207.7
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	17.7	18.0	18.3	18.5	18.5	18.5	18.6	18.7
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	21.6	22.7	24.0	24.6	24.7	24.8	24.9	25.0
95°	22.3	23.5	24.7	25.4	25.6	25.8	26.0	26.2
97.5°	24.1	24.3	24.3	24.5	24.7	24.9	25.1	25.3
100°	32.9	29.5	26.1	24.5	24.7	24.9	25.1	25.3
102.5°	117.9	81.1	44.2	25.9	25.9	25.9	25.9	26.0
105°	285.5	287.3	289.1	286.4	279.2	272.0	264.7	257.5
107.5°	353.2	354.1	355.0	355.8	356.6	357.3	358.1	358.8
110°	399.2	399.7	400.0	400.6	401.2	401.7	402.3	403.0





TEST NUMBER: P332761-940

CATALOG NUMBER: S124DIW-S575D1050U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	443.8	443.7	443.6	444.0	444.8	445.5	446.3	447.0
115°	510.3	510.8	511.1	511.4	511.4	511.4	511.4	511.4
117.5°	577.3	577.3	577.2	577.1	577.0	576.9	576.8	576.8
120°	618.8	619.2	619.6	619.6	619.2	618.8	618.4	618.0
122.5°	659.7	659.9	660.1	660.0	659.7	659.2	658.9	658.4
125°	716.8	717.4	717.9	718.4	718.5	718.7	719.0	719.2
127.5°	773.5	773.4	773.2	773.1	772.9	772.8	772.6	772.5
130°	808.1	808.3	808.5	808.6	808.6	808.6	808.6	808.6
132.5°	842.0	842.3	842.5	842.5	842.3	842.1	842.0	841.9
135°	888.9	889.3	889.7	890.1	890.6	890.9	891.4	891.7
137.5°	933.8	934.2	934.7	934.9	934.7	934.6	934.5	934.3
140°	961.6	962.2	962.8	963.2	963.4	963.6	963.8	964.0
142.5°	987.3	987.7	988.2	988.4	988.5	988.5	988.6	988.6
145°	1024.0	1024.2	1024.4	1024.8	1025.1	1025.6	1025.9	1026.4
147.5°	1056.3	1056.4	1056.6	1056.8	1057.0	1057.2	1057.4	1057.6
150°	1076.9	1076.9	1076.9	1077.0	1077.2	1077.5	1077.6	1077.8
152.5°	1094.9	1095.2	1095.6	1095.6	1095.6	1095.4	1095.3	1095.2
155°	1119.2	1120.0	1120.8	1120.9	1120.3	1119.7	1119.1	1118.5
157.5°	1140.1	1141.1	1142.2	1142.2	1141.1	1140.1	1139.1	1138.0
160°	1153.4	1154.6	1155.8	1155.8	1154.6	1153.4	1152.2	1151.0
162.5°	1164.2	1165.5	1166.6	1166.6	1165.2	1163.9	1162.5	1161.1
165°	1179.6	1181.2	1182.8	1182.6	1180.8	1179.0	1177.2	1175.4
167.5°	1190.7	1192.5	1194.2	1194.1	1192.1	1190.1	1188.1	1186.1
170°	1197.6	1199.2	1200.8	1200.6	1198.5	1196.6	1194.5	1192.6
172.5°	1201.9	1203.5	1205.1	1204.9	1202.7	1200.5	1198.4	1196.1
175°	1207.0	1208.8	1210.7	1210.3	1207.9	1205.5	1203.1	1200.7
177.5°	1209.1	1210.3	1211.7	1211.3	1209.3	1207.5	1205.5	1203.6
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9

(END OF REPORT)