

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333422-830

Luminaire Tested: **S125DIW-S850D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333422-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8278.5 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	1.4
10°-20°	329.6	4.0
20°-30°	486.6	5.9
30°-40°	567.8	6.9
40°-50°	570.3	6.9
50°-60°	500.6	6.0
60°-70°	373.0	4.5
70°-80°	213.3	2.6
80°-90°	65.5	0.8
90°-100°	59.8	0.7
100°-110°	368.7	4.5
110°-120°	668.7	8.1
120°-130°	858.2	10.4
130°-140°	923.1	11.2
140°-150°	866.4	10.5
150°-160°	700.9	8.5
160°-170°	453.3	5.5
170°-180°	156.3	1.9
0°-30°	932.8	11.3
0°-40°	1500.6	18.1
0°-60°	2571.4	31.1
0°-90°	3223.2	38.9
90°-120°	1097.2	13.3
90°-150°	3744.9	45.2
90°-180°	5055.0	61.1
0°-180°	8278.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	11	20	26	29	6
95°	70	64	20	25	26	89
105°	359	363	364	364	362	380
115°	674	680	681	676	669	668
125°	958	966	966	962	958	855
135°	1195	1202	1200	1197	1190	921
145°	1385	1387	1388	1388	1382	866
155°	1525	1519	1521	1523	1514	703
165°	1610	1603	1604	1610	1601	455
175°	1646	1639	1640	1649	1639	157
180°	1646	1646	1646	1646	1646	



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.4	21.9	22.2	22.7	23.1	23.5	23.7	23.8	24.0	24.2	24.5
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.5	20.9
92.5°	18.8	17.2	15.7	14.2	12.7	12.8	14.5	16.1	17.8	19.5	20.9
95°	69.6	68.7	68.0	67.1	66.3	60.7	50.4	40.2	29.8	19.5	20.9
97.5°	145.2	146.7	148.2	149.6	151.1	141.6	121.2	100.9	80.4	60.0	52.4
100°	203.8	204.6	205.4	206.2	207.1	208.0	209.1	210.2	211.2	212.4	171.9
102.5°	263.3	264.4	265.4	266.5	267.5	268.3	269.0	269.7	270.2	270.9	263.3
105°	358.8	359.9	361.0	362.0	363.2	363.6	363.6	363.6	363.6	363.6	363.6
107.5°	457.9	457.9	457.9	457.9	457.9	458.2	458.7	459.2	459.8	460.3	460.3
110°	522.4	522.4	522.4	522.4	522.4	522.5	523.1	523.7	524.2	524.7	524.0



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	582.9	583.5	584.2	584.8	585.4	586.0	586.3	586.5	586.9	587.2	586.2
115°	673.6	675.0	676.4	677.7	679.1	679.9	680.1	680.4	680.7	681.0	679.9
117.5°	767.6	767.5	767.5	767.4	767.4	767.9	768.9	770.0	771.0	772.0	770.6
120°	826.1	826.0	825.7	825.4	825.1	825.4	826.1	827.0	827.8	828.6	828.1
122.5°	877.9	878.9	880.0	881.0	882.0	882.8	883.2	883.5	883.9	884.3	883.7
125°	958.0	959.9	961.8	963.7	965.5	966.5	966.5	966.5	966.5	966.5	965.4
127.5°	1034.3	1035.8	1037.1	1038.4	1039.8	1040.4	1040.2	1040.1	1039.9	1039.7	1039.2
130°	1081.2	1082.6	1083.9	1085.3	1086.7	1087.5	1087.8	1088.0	1088.3	1088.5	1087.8
132.5°	1128.1	1129.6	1131.2	1132.8	1134.3	1134.9	1134.3	1133.7	1133.1	1132.5	1132.4
135°	1194.8	1196.4	1198.0	1199.6	1201.3	1201.7	1201.3	1200.7	1200.1	1199.6	1199.1
137.5°	1256.0	1257.4	1258.8	1260.2	1261.6	1262.1	1261.6	1261.1	1260.7	1260.2	1260.3
140°	1296.0	1296.6	1297.1	1297.6	1298.2	1298.4	1298.1	1297.8	1297.5	1297.2	1297.8
142.5°	1332.1	1332.5	1332.8	1333.1	1333.4	1333.8	1334.2	1334.5	1334.9	1335.3	1335.4
145°	1385.1	1385.6	1386.2	1386.8	1387.2	1387.5	1387.5	1387.5	1387.5	1387.5	1387.8
147.5°	1431.4	1431.3	1431.3	1431.2	1431.1	1431.2	1431.4	1431.8	1432.1	1432.5	1432.8
150°	1460.8	1460.2	1459.7	1459.2	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8	1461.3
152.5°	1489.0	1487.9	1486.7	1485.5	1484.3	1483.9	1484.5	1485.1	1485.6	1486.1	1486.7
155°	1525.4	1523.8	1522.2	1520.6	1518.9	1518.4	1518.9	1519.5	1520.0	1520.6	1521.4
157.5°	1553.5	1552.6	1551.5	1550.6	1549.6	1549.2	1549.2	1549.3	1549.4	1549.4	1550.2
160°	1573.0	1571.4	1569.8	1568.1	1566.5	1565.8	1566.1	1566.4	1566.7	1567.0	1568.0
162.5°	1588.7	1587.1	1585.4	1583.8	1582.2	1581.5	1581.8	1582.1	1582.2	1582.5	1584.0
165°	1609.7	1608.0	1606.4	1604.8	1603.2	1602.4	1602.7	1603.0	1603.3	1603.5	1605.1
167.5°	1625.2	1623.6	1621.9	1620.2	1618.5	1617.9	1618.1	1618.3	1618.6	1618.9	1620.9
170°	1634.1	1632.2	1630.2	1628.3	1626.5	1625.6	1625.9	1626.2	1626.5	1626.7	1628.9
172.5°	1639.9	1638.0	1636.2	1634.2	1632.3	1631.6	1632.1	1632.6	1633.0	1633.5	1635.5
175°	1646.2	1644.6	1643.0	1641.3	1639.7	1639.1	1639.4	1639.6	1639.9	1640.1	1642.3
177.5°	1649.2	1647.8	1646.6	1645.3	1644.0	1643.4	1643.7	1643.9	1644.1	1644.3	1645.9
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	24.8	25.1	25.4	25.4	25.2	25.0	24.9	24.7
90°	22.2	23.6	25.0	26.0	26.9	27.6	28.5	29.3
92.5°	22.2	23.6	25.0	25.8	26.2	26.6	27.0	27.3
95°	22.2	23.6	25.0	25.6	25.6	25.6	25.6	25.6
97.5°	44.8	37.1	29.4	25.6	25.6	25.6	25.6	25.6
100°	131.5	91.1	50.7	30.0	28.8	27.8	26.7	25.6
102.5°	255.6	248.0	240.3	227.2	208.9	190.4	171.9	153.5
105°	363.6	363.6	363.6	363.5	363.3	363.0	362.7	362.4
107.5°	460.4	460.5	460.5	460.1	459.3	458.5	457.7	456.9
110°	523.1	522.4	521.5	521.2	521.5	521.8	522.1	522.4



TEST NUMBER: P333422-830

CATALOG NUMBER: S125DIW-S850D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.1	584.2	583.2	582.4	582.0	581.6	581.3	580.9
115°	678.8	677.7	676.7	675.2	673.6	672.0	670.3	668.7
117.5°	769.2	767.8	766.4	765.3	764.6	763.9	763.2	762.5
120°	827.6	827.0	826.4	825.5	824.2	822.7	821.4	820.1
122.5°	883.2	882.6	882.1	881.0	879.5	877.9	876.3	874.8
125°	964.3	963.3	962.1	961.2	960.5	959.6	958.8	958.0
127.5°	1038.6	1037.9	1037.4	1036.0	1034.1	1032.1	1030.0	1028.0
130°	1086.9	1086.1	1085.3	1084.2	1082.9	1081.5	1080.2	1078.8
132.5°	1132.2	1132.0	1131.8	1131.1	1129.7	1128.4	1127.0	1125.7
135°	1198.5	1198.0	1197.4	1196.4	1194.8	1193.1	1191.5	1189.9
137.5°	1260.4	1260.5	1260.6	1259.9	1258.5	1257.1	1255.7	1254.2
140°	1298.4	1298.8	1299.4	1298.8	1297.2	1295.6	1294.0	1292.3
142.5°	1335.5	1335.7	1335.8	1335.0	1333.3	1331.7	1330.1	1328.5
145°	1388.1	1388.4	1388.6	1388.0	1386.3	1384.7	1383.1	1381.5
147.5°	1433.1	1433.4	1433.8	1432.9	1431.0	1429.0	1427.1	1425.1
150°	1461.9	1462.4	1462.9	1462.1	1459.9	1457.7	1455.6	1453.4
152.5°	1487.2	1487.8	1488.3	1487.6	1485.6	1483.8	1481.8	1479.8
155°	1522.2	1523.0	1523.8	1523.1	1521.0	1518.8	1516.6	1514.5
157.5°	1551.1	1552.0	1552.8	1552.2	1550.0	1547.8	1545.7	1543.5
160°	1569.1	1570.2	1571.3	1570.7	1568.6	1566.4	1564.2	1562.1
162.5°	1585.5	1587.1	1588.7	1588.2	1585.8	1583.4	1581.0	1578.7
165°	1606.8	1608.4	1610.1	1609.8	1607.6	1605.4	1603.3	1601.1
167.5°	1622.9	1624.8	1626.7	1626.5	1624.0	1621.6	1619.2	1616.7
170°	1631.1	1633.2	1635.4	1635.3	1632.9	1630.4	1628.0	1625.5
172.5°	1637.5	1639.5	1641.3	1641.2	1638.7	1636.3	1633.8	1631.4
175°	1644.5	1646.6	1648.8	1648.7	1646.2	1643.8	1641.3	1638.9
177.5°	1647.4	1648.9	1650.4	1650.3	1648.5	1646.8	1645.0	1643.3
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2

(END OF REPORT)