

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333406-830

Luminaire Tested: **S125DIW-S850D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333406-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D770U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6148.8 lumens
Efficiency: N/A
Efficacy: 136.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.8
10°-20°	330.5	5.4
20°-30°	536.7	8.7
30°-40°	654.6	10.6
40°-50°	595.5	9.7
50°-60°	474.4	7.7
60°-70°	330.4	5.4
70°-80°	176.2	2.9
80°-90°	46.4	0.8
90°-100°	34.2	0.6
100°-110°	211.0	3.4
110°-120°	382.7	6.2
120°-130°	491.1	8.0
130°-140°	528.2	8.6
140°-150°	495.8	8.1
150°-160°	401.1	6.5
160°-170°	259.4	4.2
170°-180°	89.5	1.5
0°-30°	978.2	15.9
0°-40°	1632.8	26.6
0°-60°	2702.7	44.0
0°-90°	3255.7	52.9
90°-120°	627.9	10.2
90°-150°	2143.1	34.9
90°-180°	2893.0	47.0
0°-180°	6148.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	38
90°	17	1	17	1	17	8
95°	15	40	15	40	15	12
105°	208	205	208	205	208	188
115°	383	386	383	386	383	380
125°	548	548	548	548	548	488
135°	681	684	681	684	681	525
145°	791	793	791	793	791	494
155°	867	873	867	873	867	399
165°	916	921	916	921	916	259
175°	938	942	938	942	938	89
180°	942	942	942	942	942	



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	12.7	13.5	13.8	13.7	13.9	13.9	15.3	15.1	16.1	17.2	18.5
90°	16.8	16.3	15.8	15.4	14.9	14.2	13.5	12.7	12.0	11.2	10.1
92.5°	15.6	15.5	15.2	15.0	14.8	14.2	13.5	12.7	12.0	11.2	10.2
95°	14.7	14.7	14.7	14.7	14.7	14.2	13.5	12.7	12.0	11.2	17.1
97.5°	14.7	14.7	14.7	14.7	14.7	16.9	21.2	25.6	30.0	34.4	46.0
100°	14.7	15.3	15.9	16.5	17.2	29.0	52.1	75.3	98.4	121.5	120.9
102.5°	87.8	98.4	109.0	119.5	130.1	137.5	141.9	146.3	150.7	155.0	154.7
105°	207.5	207.5	207.7	207.9	208.0	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	261.5	261.9	262.4	262.9	263.3	263.5	263.5	263.5	263.4	263.4	263.2
110°	298.9	298.8	298.6	298.4	298.3	298.4	298.9	299.4	299.8	300.3	300.0



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.4	332.6	332.9	333.1	333.3	333.7	334.3	334.9	335.5	336.1	335.9
115°	382.7	383.6	384.6	385.5	386.4	387.2	387.9	388.4	389.1	389.7	389.6
117.5°	436.4	436.8	437.2	437.5	438.0	438.6	439.4	440.2	441.0	441.8	441.2
120°	469.3	470.1	470.9	471.6	472.4	473.0	473.3	473.6	473.9	474.2	473.7
122.5°	500.6	501.5	502.4	503.3	504.2	504.8	505.1	505.4	505.8	506.1	505.9
125°	548.3	548.7	549.1	549.6	550.1	550.6	551.3	551.9	552.5	553.1	553.1
127.5°	588.3	589.5	590.6	591.7	593.0	593.7	594.0	594.4	594.7	595.0	595.1
130°	617.4	618.1	619.0	619.7	620.5	621.1	621.6	622.1	622.5	622.9	622.8
132.5°	644.2	645.0	645.7	646.5	647.3	647.7	647.8	647.9	648.0	648.1	648.5
135°	680.9	681.8	682.8	683.7	684.7	685.3	685.6	685.9	686.2	686.5	686.8
137.5°	717.8	718.6	719.4	720.2	721.0	721.4	721.3	721.3	721.2	721.1	721.4
140°	739.6	740.6	741.5	742.3	743.3	743.7	743.3	743.0	742.7	742.3	742.5
142.5°	760.3	761.2	762.1	763.1	764.0	764.4	764.4	764.3	764.2	764.2	763.9
145°	790.6	791.5	792.4	793.3	794.3	794.7	794.6	794.4	794.2	794.1	794.1
147.5°	815.6	816.7	817.8	819.0	820.0	820.5	820.3	820.1	819.9	819.7	819.5
150°	831.8	833.0	834.2	835.5	836.8	837.3	836.9	836.6	836.3	835.9	835.7
152.5°	846.9	848.0	849.1	850.2	851.3	851.8	851.4	851.1	850.8	850.5	850.2
155°	866.7	868.0	869.2	870.4	871.7	872.0	871.6	871.1	870.6	870.2	869.9
157.5°	883.4	884.6	885.8	887.0	888.3	888.6	888.2	887.7	887.2	886.6	886.6
160°	893.9	895.2	896.5	897.7	898.9	899.2	898.6	898.0	897.4	896.7	896.5
162.5°	903.4	904.8	906.2	907.6	908.9	909.2	908.2	907.4	906.5	905.7	905.5
165°	916.2	917.6	918.8	920.0	921.2	921.4	920.5	919.5	918.6	917.7	917.6
167.5°	925.2	926.6	928.0	929.4	930.9	930.9	929.8	928.7	927.6	926.5	926.3
170°	930.3	931.6	933.0	934.4	935.9	935.9	934.7	933.4	932.2	930.9	930.8
172.5°	933.6	935.0	936.4	937.8	939.1	939.3	938.2	937.1	935.9	934.9	934.6
175°	937.9	939.3	940.8	942.2	943.5	943.6	942.4	941.1	939.9	938.7	938.5
177.5°	940.5	941.4	942.4	943.4	944.4	944.5	943.6	942.7	941.9	941.0	940.8
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	19.0	18.0	16.2	14.8	12.6	11.2	10.6	10.7	9.8	9.6	10.3
90°	9.0	7.9	6.8	5.7	4.4	3.2	2.0	0.7	2.0	3.2	4.4
92.5°	9.2	8.3	7.4	7.3	8.1	9.0	9.9	10.7	9.9	9.0	8.1
95°	23.0	28.8	34.8	38.0	38.5	38.8	39.3	39.8	39.3	38.8	38.5
97.5°	57.7	69.4	81.1	86.4	85.6	84.8	84.0	83.1	84.0	84.8	85.6
100°	120.3	119.7	119.0	118.5	118.0	117.5	117.1	116.6	117.1	117.5	118.0
102.5°	154.3	153.9	153.5	153.1	152.5	151.9	151.3	150.7	151.3	151.9	152.5
105°	208.1	208.1	208.1	207.8	207.2	206.6	205.9	205.3	205.9	206.6	207.2
107.5°	262.8	262.5	262.2	262.0	262.0	262.0	262.0	262.0	262.0	262.0	262.0
110°	299.7	299.4	299.1	298.9	298.9	298.9	298.9	298.9	298.9	298.9	298.9



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	335.7	335.5	335.4	335.1	334.7	334.3	333.9	333.6	333.9	334.3	334.7
115°	389.4	389.3	389.1	388.6	387.9	387.1	386.3	385.5	386.3	387.1	387.9
117.5°	440.6	440.1	439.4	439.1	439.2	439.2	439.2	439.3	439.2	439.2	439.2
120°	473.3	472.8	472.3	472.2	472.3	472.5	472.7	472.8	472.7	472.5	472.3
122.5°	505.6	505.4	505.2	504.8	504.2	503.6	503.0	502.4	503.0	503.6	504.2
125°	553.1	553.1	553.1	552.6	551.5	550.4	549.3	548.3	549.3	550.4	551.5
127.5°	595.2	595.3	595.4	595.0	594.3	593.5	592.8	591.9	592.8	593.5	594.3
130°	622.6	622.5	622.4	621.9	621.1	620.3	619.5	618.8	619.5	620.3	621.1
132.5°	648.8	649.1	649.5	649.2	648.3	647.4	646.5	645.5	646.5	647.4	648.3
135°	687.1	687.5	687.8	687.5	686.5	685.6	684.7	683.7	684.7	685.6	686.5
137.5°	721.7	722.0	722.3	722.0	721.2	720.4	719.6	718.8	719.6	720.4	721.2
140°	742.7	742.8	743.0	742.9	742.6	742.3	742.0	741.7	742.0	742.3	742.6
142.5°	763.7	763.6	763.3	763.1	762.9	762.7	762.5	762.3	762.5	762.7	762.9
145°	794.1	794.1	794.1	793.9	793.6	793.3	793.0	792.7	793.0	793.3	793.6
147.5°	819.4	819.3	819.1	819.0	819.1	819.1	819.2	819.3	819.2	819.1	819.1
150°	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	835.7	835.4	835.0
152.5°	849.9	849.6	849.2	849.4	850.2	850.8	851.5	852.2	851.5	850.8	850.2
155°	869.6	869.3	868.9	869.3	870.2	871.1	872.0	873.0	872.0	871.1	870.2
157.5°	886.6	886.6	886.6	886.8	887.4	888.0	888.5	889.0	888.5	888.0	887.4
160°	896.5	896.3	896.1	896.5	897.4	898.3	899.3	900.2	899.3	898.3	897.4
162.5°	905.4	905.2	905.0	905.4	906.3	907.3	908.2	909.2	908.2	907.3	906.3
165°	917.4	917.2	917.1	917.5	918.4	919.4	920.2	921.1	920.2	919.4	918.4
167.5°	926.1	926.0	925.9	926.2	927.3	928.2	929.2	930.1	929.2	928.2	927.3
170°	930.7	930.5	930.3	930.8	931.9	932.9	934.1	935.2	934.1	932.9	931.9
172.5°	934.3	934.1	933.8	934.2	935.2	936.3	937.5	938.5	937.5	936.3	935.2
175°	938.3	938.2	938.0	938.4	939.3	940.3	941.2	942.2	941.2	940.3	939.3
177.5°	940.8	940.7	940.5	940.8	941.6	942.4	943.0	943.8	943.0	942.4	941.6
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	10.9	12.0	11.8	12.3	12.6	13.6	13.4	15.1	16.0	17.0	16.7
90°	5.7	6.8	7.9	9.0	10.1	11.2	12.0	12.7	13.5	14.2	14.9
92.5°	7.3	7.4	8.3	9.2	10.2	11.2	12.0	12.7	13.5	14.2	14.8
95°	38.0	34.8	28.8	23.0	17.1	11.2	12.0	12.7	13.5	14.2	14.7
97.5°	86.4	81.1	69.4	57.7	46.0	34.4	30.0	25.6	21.2	16.9	14.7
100°	118.5	119.0	119.7	120.3	120.9	121.5	98.4	75.3	52.1	29.0	17.2
102.5°	153.1	153.5	153.9	154.3	154.7	155.0	150.7	146.3	141.9	137.5	130.1
105°	207.8	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.0
107.5°	262.0	262.2	262.5	262.8	263.2	263.4	263.4	263.5	263.5	263.5	263.3
110°	298.9	299.1	299.4	299.7	300.0	300.3	299.8	299.4	298.9	298.4	298.3



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	335.1	335.4	335.5	335.7	335.9	336.1	335.5	334.9	334.3	333.7	333.3
115°	388.6	389.1	389.3	389.4	389.6	389.7	389.1	388.4	387.9	387.2	386.4
117.5°	439.1	439.4	440.1	440.6	441.2	441.8	441.0	440.2	439.4	438.6	438.0
120°	472.2	472.3	472.8	473.3	473.7	474.2	473.9	473.6	473.3	473.0	472.4
122.5°	504.8	505.2	505.4	505.6	505.9	506.1	505.8	505.4	505.1	504.8	504.2
125°	552.6	553.1	553.1	553.1	553.1	553.1	552.5	551.9	551.3	550.6	550.1
127.5°	595.0	595.4	595.3	595.2	595.1	595.0	594.7	594.4	594.0	593.7	593.0
130°	621.9	622.4	622.5	622.6	622.8	622.9	622.5	622.1	621.6	621.1	620.5
132.5°	649.2	649.5	649.1	648.8	648.5	648.1	648.0	647.9	647.8	647.7	647.3
135°	687.5	687.8	687.5	687.1	686.8	686.5	686.2	685.9	685.6	685.3	684.7
137.5°	722.0	722.3	722.0	721.7	721.4	721.1	721.2	721.3	721.3	721.4	721.0
140°	742.9	743.0	742.8	742.7	742.5	742.3	742.7	743.0	743.3	743.7	743.3
142.5°	763.1	763.3	763.6	763.7	763.9	764.2	764.2	764.3	764.4	764.4	764.0
145°	793.9	794.1	794.1	794.1	794.1	794.1	794.2	794.4	794.6	794.7	794.3
147.5°	819.0	819.1	819.3	819.4	819.5	819.7	819.9	820.1	820.3	820.5	820.0
150°	834.7	834.7	835.0	835.4	835.7	835.9	836.3	836.6	836.9	837.3	836.8
152.5°	849.4	849.2	849.6	849.9	850.2	850.5	850.8	851.1	851.4	851.8	851.3
155°	869.3	868.9	869.3	869.6	869.9	870.2	870.6	871.1	871.6	872.0	871.7
157.5°	886.8	886.6	886.6	886.6	886.6	886.6	887.2	887.7	888.2	888.6	888.3
160°	896.5	896.1	896.3	896.5	896.5	896.7	897.4	898.0	898.6	899.2	898.9
162.5°	905.4	905.0	905.2	905.4	905.5	905.7	906.5	907.4	908.2	909.2	908.9
165°	917.5	917.1	917.2	917.4	917.6	917.7	918.6	919.5	920.5	921.4	921.2
167.5°	926.2	925.9	926.0	926.1	926.3	926.5	927.6	928.7	929.8	930.9	930.9
170°	930.8	930.3	930.5	930.7	930.8	930.9	932.2	933.4	934.7	935.9	935.9
172.5°	934.2	933.8	934.1	934.3	934.6	934.9	935.9	937.1	938.2	939.3	939.1
175°	938.4	938.0	938.2	938.3	938.5	938.7	939.9	941.1	942.4	943.6	943.5
177.5°	940.8	940.5	940.7	940.8	940.8	941.0	941.9	942.7	943.6	944.5	944.4
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	17.5	17.2	17.3	18.2	17.3	17.2	17.5	16.7	17.0	16.0	15.1
90°	15.4	15.8	16.3	16.8	16.3	15.8	15.4	14.9	14.2	13.5	12.7
92.5°	15.0	15.2	15.5	15.6	15.5	15.2	15.0	14.8	14.2	13.5	12.7
95°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.2	13.5	12.7
97.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.9	21.2	25.6
100°	16.5	15.9	15.3	14.7	15.3	15.9	16.5	17.2	29.0	52.1	75.3
102.5°	119.5	109.0	98.4	87.8	98.4	109.0	119.5	130.1	137.5	141.9	146.3
105°	207.9	207.7	207.5	207.5	207.5	207.7	207.9	208.0	208.1	208.1	208.1
107.5°	262.9	262.4	261.9	261.5	261.9	262.4	262.9	263.3	263.5	263.5	263.5
110°	298.4	298.6	298.8	298.9	298.8	298.6	298.4	298.3	298.4	298.9	299.4



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	333.1	332.9	332.6	332.4	332.6	332.9	333.1	333.3	333.7	334.3	334.9
115°	385.5	384.6	383.6	382.7	383.6	384.6	385.5	386.4	387.2	387.9	388.4
117.5°	437.5	437.2	436.8	436.4	436.8	437.2	437.5	438.0	438.6	439.4	440.2
120°	471.6	470.9	470.1	469.3	470.1	470.9	471.6	472.4	473.0	473.3	473.6
122.5°	503.3	502.4	501.5	500.6	501.5	502.4	503.3	504.2	504.8	505.1	505.4
125°	549.6	549.1	548.7	548.3	548.7	549.1	549.6	550.1	550.6	551.3	551.9
127.5°	591.7	590.6	589.5	588.3	589.5	590.6	591.7	593.0	593.7	594.0	594.4
130°	619.7	619.0	618.1	617.4	618.1	619.0	619.7	620.5	621.1	621.6	622.1
132.5°	646.5	645.7	645.0	644.2	645.0	645.7	646.5	647.3	647.7	647.8	647.9
135°	683.7	682.8	681.8	680.9	681.8	682.8	683.7	684.7	685.3	685.6	685.9
137.5°	720.2	719.4	718.6	717.8	718.6	719.4	720.2	721.0	721.4	721.3	721.3
140°	742.3	741.5	740.6	739.6	740.6	741.5	742.3	743.3	743.7	743.3	743.0
142.5°	763.1	762.1	761.2	760.3	761.2	762.1	763.1	764.0	764.4	764.4	764.3
145°	793.3	792.4	791.5	790.6	791.5	792.4	793.3	794.3	794.7	794.6	794.4
147.5°	819.0	817.8	816.7	815.6	816.7	817.8	819.0	820.0	820.5	820.3	820.1
150°	835.5	834.2	833.0	831.8	833.0	834.2	835.5	836.8	837.3	836.9	836.6
152.5°	850.2	849.1	848.0	846.9	848.0	849.1	850.2	851.3	851.8	851.4	851.1
155°	870.4	869.2	868.0	866.7	868.0	869.2	870.4	871.7	872.0	871.6	871.1
157.5°	887.0	885.8	884.6	883.4	884.6	885.8	887.0	888.3	888.6	888.2	887.7
160°	897.7	896.5	895.2	893.9	895.2	896.5	897.7	898.9	899.2	898.6	898.0
162.5°	907.6	906.2	904.8	903.4	904.8	906.2	907.6	908.9	909.2	908.2	907.4
165°	920.0	918.8	917.6	916.2	917.6	918.8	920.0	921.2	921.4	920.5	919.5
167.5°	929.4	928.0	926.6	925.2	926.6	928.0	929.4	930.9	930.9	929.8	928.7
170°	934.4	933.0	931.6	930.3	931.6	933.0	934.4	935.9	935.9	934.7	933.4
172.5°	937.8	936.4	935.0	933.6	935.0	936.4	937.8	939.1	939.3	938.2	937.1
175°	942.2	940.8	939.3	937.9	939.3	940.8	942.2	943.5	943.6	942.4	941.1
177.5°	943.4	942.4	941.4	940.5	941.4	942.4	943.4	944.4	944.5	943.6	942.7
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	13.4	13.6	12.6	12.3	11.8	12.0	10.9	10.3	9.6	9.8	10.7
90°	12.0	11.2	10.1	9.0	7.9	6.8	5.7	4.4	3.2	2.0	0.7
92.5°	12.0	11.2	10.2	9.2	8.3	7.4	7.3	8.1	9.0	9.9	10.7
95°	12.0	11.2	17.1	23.0	28.8	34.8	38.0	38.5	38.8	39.3	39.8
97.5°	30.0	34.4	46.0	57.7	69.4	81.1	86.4	85.6	84.8	84.0	83.1
100°	98.4	121.5	120.9	120.3	119.7	119.0	118.5	118.0	117.5	117.1	116.6
102.5°	150.7	155.0	154.7	154.3	153.9	153.5	153.1	152.5	151.9	151.3	150.7
105°	208.1	208.1	208.1	208.1	208.1	208.1	207.8	207.2	206.6	205.9	205.3
107.5°	263.4	263.4	263.2	262.8	262.5	262.2	262.0	262.0	262.0	262.0	262.0
110°	299.8	300.3	300.0	299.7	299.4	299.1	298.9	298.9	298.9	298.9	298.9



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.5	336.1	335.9	335.7	335.5	335.4	335.1	334.7	334.3	333.9	333.6
115°	389.1	389.7	389.6	389.4	389.3	389.1	388.6	387.9	387.1	386.3	385.5
117.5°	441.0	441.8	441.2	440.6	440.1	439.4	439.1	439.2	439.2	439.2	439.3
120°	473.9	474.2	473.7	473.3	472.8	472.3	472.2	472.3	472.5	472.7	472.8
122.5°	505.8	506.1	505.9	505.6	505.4	505.2	504.8	504.2	503.6	503.0	502.4
125°	552.5	553.1	553.1	553.1	553.1	553.1	552.6	551.5	550.4	549.3	548.3
127.5°	594.7	595.0	595.1	595.2	595.3	595.4	595.0	594.3	593.5	592.8	591.9
130°	622.5	622.9	622.8	622.6	622.5	622.4	621.9	621.1	620.3	619.5	618.8
132.5°	648.0	648.1	648.5	648.8	649.1	649.5	649.2	648.3	647.4	646.5	645.5
135°	686.2	686.5	686.8	687.1	687.5	687.8	687.5	686.5	685.6	684.7	683.7
137.5°	721.2	721.1	721.4	721.7	722.0	722.3	722.0	721.2	720.4	719.6	718.8
140°	742.7	742.3	742.5	742.7	742.8	743.0	742.9	742.6	742.3	742.0	741.7
142.5°	764.2	764.2	763.9	763.7	763.6	763.3	763.1	762.9	762.7	762.5	762.3
145°	794.2	794.1	794.1	794.1	794.1	794.1	793.9	793.6	793.3	793.0	792.7
147.5°	819.9	819.7	819.5	819.4	819.3	819.1	819.0	819.1	819.1	819.2	819.3
150°	836.3	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9
152.5°	850.8	850.5	850.2	849.9	849.6	849.2	849.4	850.2	850.8	851.5	852.2
155°	870.6	870.2	869.9	869.6	869.3	868.9	869.3	870.2	871.1	872.0	873.0
157.5°	887.2	886.6	886.6	886.6	886.6	886.6	886.8	887.4	888.0	888.5	889.0
160°	897.4	896.7	896.5	896.5	896.3	896.1	896.5	897.4	898.3	899.3	900.2
162.5°	906.5	905.7	905.5	905.4	905.2	905.0	905.4	906.3	907.3	908.2	909.2
165°	918.6	917.7	917.6	917.4	917.2	917.1	917.5	918.4	919.4	920.2	921.1
167.5°	927.6	926.5	926.3	926.1	926.0	925.9	926.2	927.3	928.2	929.2	930.1
170°	932.2	930.9	930.8	930.7	930.5	930.3	930.8	931.9	932.9	934.1	935.2
172.5°	935.9	934.9	934.6	934.3	934.1	933.8	934.2	935.2	936.3	937.5	938.5
175°	939.9	938.7	938.5	938.3	938.2	938.0	938.4	939.3	940.3	941.2	942.2
177.5°	941.9	941.0	940.8	940.8	940.7	940.5	940.8	941.6	942.4	943.0	943.8
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.6	11.2	12.6	14.8	16.2	18.0	19.0	18.5	17.2	16.1	15.1
90°	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0	12.7
92.5°	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0	12.7
95°	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0	12.7
97.5°	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0	25.6
100°	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4	75.3
102.5°	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7	146.3
105°	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4	263.5
110°	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8	299.4



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5	334.9
115°	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1	388.4
117.5°	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0	440.2
120°	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9	473.6
122.5°	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8	505.4
125°	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5	551.9
127.5°	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7	594.4
130°	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5	622.1
132.5°	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0	647.9
135°	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2	685.9
137.5°	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2	721.3
140°	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7	743.0
142.5°	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2	764.3
145°	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2	794.4
147.5°	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9	820.1
150°	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3	836.6
152.5°	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8	851.1
155°	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6	871.1
157.5°	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2	887.7
160°	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4	898.0
162.5°	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5	907.4
165°	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6	919.5
167.5°	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6	928.7
170°	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2	933.4
172.5°	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9	937.1
175°	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9	941.1
177.5°	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9	942.7
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	15.3	13.9	13.9	13.7	13.8	13.5	12.7
90°	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	298.9	298.4	298.3	298.4	298.6	298.8	298.9



TEST NUMBER: P333406-830

CATALOG NUMBER: S125DIW-S850D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)