

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332792-940

Luminaire Tested: **S124DIW-S795D1050U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332792-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1050U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6281.6 lumens  
Efficiency: N/A  
Efficacy: 119.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41				41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34				34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29				29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25				25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21				21
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19				19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17				17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15				15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	1.8
10°-20°	314.1	5.0
20°-30°	462.3	7.4
30°-40°	537.4	8.6
40°-50°	537.5	8.6
50°-60°	470.1	7.5
60°-70°	349.1	5.6
70°-80°	198.4	3.2
80°-90°	60.7	1.0
90°-100°	77.0	1.2
100°-110°	228.2	3.6
110°-120°	387.4	6.2
120°-130°	510.8	8.1
130°-140°	573.6	9.1
140°-150°	563.7	9.0
150°-160°	474.1	7.5
160°-170°	315.4	5.0
170°-180°	110.5	1.8
0°-30°	887.8	14.1
0°-40°	1425.3	22.7
0°-60°	2432.8	38.7
0°-90°	3041.1	48.4
90°-120°	692.6	11.0
90°-150°	2340.6	37.3
90°-180°	3241.0	51.6
0°-180°	6281.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	3	12	20	25	27	6
95°	54	62	69	71	71	60
105°	210	212	215	218	220	223
115°	394	394	392	391	390	388
125°	574	574	573	571	569	511
135°	740	745	745	743	741	572
145°	899	902	903	902	900	562
155°	1030	1030	1029	1032	1029	474
165°	1121	1118	1116	1121	1118	316
175°	1166	1162	1161	1166	1161	111
180°	1168	1168	1168	1168	1168	



TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.2	20.5	20.8	21.1	21.4	21.6	21.8	21.8	22.0	22.2	22.5
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	19.4	21.8	24.4	26.9	29.4	31.3	32.4	33.5	34.7	35.8	36.5
95°	54.2	56.0	57.8	59.7	61.4	63.0	64.5	65.8	67.2	68.7	69.3
97.5°	94.7	96.1	97.6	99.0	100.5	102.0	103.6	105.3	106.9	108.6	109.3
100°	126.4	127.2	128.0	128.9	129.7	131.0	132.8	134.6	136.4	138.2	138.6
102.5°	159.7	160.1	160.3	160.7	161.0	161.9	163.6	165.2	166.9	168.5	169.2
105°	210.4	210.7	210.9	211.1	211.2	211.8	212.6	213.4	214.2	215.0	215.6
107.5°	263.8	264.0	264.2	264.5	264.7	264.9	265.0	265.2	265.3	265.4	266.0
110°	299.9	300.3	300.7	301.1	301.5	301.6	301.4	301.2	301.0	300.8	300.4



TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	337.5	337.6	337.7	337.7	337.8	337.7	337.3	337.0	336.6	336.3	336.2
115°	393.9	393.9	393.9	393.9	393.9	393.7	393.2	392.9	392.4	392.1	391.8
117.5°	447.0	447.1	447.3	447.5	447.6	447.5	447.3	447.0	446.7	446.4	445.8
120°	482.4	483.2	484.0	484.8	485.6	485.7	485.1	484.5	483.9	483.3	482.3
122.5°	519.2	519.6	519.9	520.2	520.5	520.6	520.2	520.0	519.7	519.4	518.7
125°	573.6	573.6	573.6	573.6	573.6	573.5	573.3	573.1	572.9	572.7	572.3
127.5°	622.9	623.6	624.1	624.7	625.4	625.5	625.2	624.8	624.6	624.2	623.8
130°	657.6	658.3	658.8	659.4	660.0	660.3	660.3	660.3	660.3	660.3	660.0
132.5°	693.0	693.5	693.9	694.4	694.8	694.9	694.8	694.6	694.5	694.3	693.9
135°	739.9	741.0	742.3	743.4	744.7	745.3	745.3	745.3	745.3	745.3	744.8
137.5°	790.8	791.3	791.9	792.5	793.0	793.4	793.8	794.2	794.4	794.8	794.2
140°	824.7	825.2	825.5	826.0	826.3	826.5	826.5	826.5	826.5	826.5	826.3
142.5°	855.9	856.2	856.7	857.0	857.5	857.6	857.4	857.2	857.1	856.9	856.8
145°	898.8	899.6	900.4	901.3	902.1	902.5	902.8	902.9	903.1	903.3	903.1
147.5°	941.5	942.4	943.4	944.3	945.3	945.7	945.6	945.4	945.2	945.0	944.9
150°	967.5	968.3	969.1	969.9	970.7	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	992.0	992.6	993.0	993.5	994.0	994.3	994.4	994.6	994.8	995.0	995.4
155°	1029.8	1029.8	1029.8	1029.8	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7
157.5°	1061.6	1061.2	1060.9	1060.5	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4
160°	1080.4	1080.2	1080.0	1079.8	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1
162.5°	1097.7	1097.3	1096.7	1096.2	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6
165°	1121.1	1120.4	1119.8	1119.3	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8
167.5°	1138.9	1138.1	1137.3	1136.4	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5
170°	1149.1	1148.1	1147.0	1146.0	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7
172.5°	1156.3	1155.4	1154.6	1153.8	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1
175°	1166.2	1165.2	1164.2	1163.2	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2
177.5°	1169.5	1168.7	1167.9	1167.1	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	22.6	22.9	23.2	23.3	23.4	23.5	23.5	23.6
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	37.2	37.9	38.7	39.1	39.4	39.6	39.9	40.1
95°	69.8	70.4	71.1	71.3	71.3	71.3	71.3	71.3
97.5°	110.0	110.8	111.5	111.8	111.8	111.8	111.8	111.8
100°	139.0	139.4	139.8	140.0	140.0	140.0	140.0	140.0
102.5°	169.7	170.2	170.9	171.2	171.3	171.5	171.7	171.8
105°	216.2	216.8	217.4	218.0	218.6	219.2	219.8	220.4
107.5°	266.5	267.1	267.7	267.9	267.9	267.9	267.8	267.8
110°	300.0	299.6	299.2	299.3	299.9	300.5	301.1	301.8





TEST NUMBER: P332792-940

CATALOG NUMBER: S124DIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	336.1	336.0	335.9	335.9	336.1	336.2	336.3	336.4
115°	391.6	391.5	391.3	391.0	390.8	390.7	390.5	390.2
117.5°	445.1	444.3	443.7	443.2	442.7	442.4	441.9	441.6
120°	481.3	480.3	479.3	478.9	479.4	479.7	480.2	480.5
122.5°	518.1	517.4	516.7	515.9	515.2	514.5	513.8	513.1
125°	571.9	571.5	571.1	570.7	570.3	569.9	569.5	569.1
127.5°	623.4	623.0	622.6	622.2	621.9	621.6	621.3	621.0
130°	659.5	659.2	658.7	658.2	657.4	656.6	655.8	655.0
132.5°	693.5	693.1	692.7	692.3	692.1	691.7	691.3	691.1
135°	744.5	744.0	743.7	743.2	742.5	741.9	741.4	740.7
137.5°	793.7	793.2	792.6	792.5	792.6	792.7	792.8	792.9
140°	826.2	826.0	825.7	825.5	825.4	825.2	824.9	824.7
142.5°	856.8	856.8	856.8	856.7	856.7	856.7	856.6	856.6
145°	902.9	902.8	902.5	902.1	901.5	900.9	900.4	899.7
147.5°	944.8	944.6	944.4	944.2	944.1	943.9	943.6	943.4
150°	971.1	971.1	971.1	971.0	970.8	970.6	970.4	970.2
152.5°	995.9	996.4	996.8	996.8	996.3	995.8	995.2	994.8
155°	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9
157.5°	1061.0	1061.6	1062.2	1062.2	1061.5	1060.8	1060.2	1059.4
160°	1079.8	1080.4	1081.0	1080.8	1079.8	1078.8	1077.8	1076.7
162.5°	1096.6	1097.7	1098.9	1098.9	1097.9	1096.9	1095.8	1094.8
165°	1118.9	1120.2	1121.3	1121.5	1120.7	1119.9	1119.1	1118.3
167.5°	1137.7	1138.9	1140.1	1140.1	1138.9	1137.6	1136.4	1135.1
170°	1147.8	1149.1	1150.2	1150.1	1148.8	1147.4	1145.9	1144.5
172.5°	1155.4	1156.7	1158.2	1158.1	1156.7	1155.3	1153.9	1152.4
175°	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8
177.5°	1168.1	1169.2	1170.4	1170.3	1168.9	1167.7	1166.4	1165.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1

(END OF REPORT)