

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333716-830

Luminaire Tested: **S125RDIW-S1090D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333716-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9896.7 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	1.5
10°-20°	435.5	4.4
20°-30°	690.5	7.0
30°-40°	832.7	8.4
40°-50°	743.6	7.5
50°-60°	570.3	5.8
60°-70°	370.6	3.7
70°-80°	180.2	1.8
80°-90°	47.0	0.5
90°-100°	69.6	0.7
100°-110°	428.7	4.3
110°-120°	777.5	7.9
120°-130°	997.8	10.1
130°-140°	1073.2	10.8
140°-150°	1007.4	10.2
150°-160°	814.9	8.2
160°-170°	527.0	5.3
170°-180°	181.8	1.8
0°-30°	1274.6	12.9
0°-40°	2107.3	21.3
0°-60°	3421.2	34.6
0°-90°	4019.0	40.6
90°-120°	1275.7	12.9
90°-150°	4354.1	44.0
90°-180°	5878.0	59.4
0°-180°	9896.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	34	1	34	1	34	16
95°	30	81	30	81	30	25
105°	421	417	421	417	421	381
115°	778	783	778	783	778	772
125°	1114	1114	1114	1114	1114	991
135°	1383	1389	1383	1389	1383	1068
145°	1606	1610	1606	1610	1606	1003
155°	1761	1774	1761	1774	1761	812
165°	1862	1872	1862	1872	1862	525
175°	1906	1914	1906	1914	1906	181
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	18.0	17.3	16.6	16.4	16.8	17.5	16.7	15.8	15.6	15.3	15.3
90°	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8	24.3	22.7	20.5
92.5°	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8	24.3	22.7	20.7
95°	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8	24.3	22.7	34.7
97.5°	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0	60.9	69.8	93.5
100°	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9	199.9	246.9	245.6
102.5°	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2	306.1	315.0	314.2
105°	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4	535.3	535.2	534.6
110°	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2	609.2	610.1	609.4



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3	681.6	682.8	682.4
115°	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2	790.4	791.7	791.5
117.5°	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3	895.9	897.6	896.4
120°	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1	962.8	963.4	962.4
122.5°	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8	1027.5	1028.1	1027.7
125°	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2	1122.5	1123.7	1123.7
127.5°	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5	1208.2	1208.9	1209.1
130°	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8	1264.7	1265.6	1265.3
132.5°	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4	1316.5	1316.7	1317.4
135°	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5	1394.1	1394.8	1395.3
137.5°	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4	1465.3	1465.1	1465.7
140°	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5	1508.9	1508.3	1508.5
142.5°	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7	1552.7	1552.6	1552.1
145°	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9	1613.5	1613.3	1613.3
147.5°	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2	1665.8	1665.5	1665.1
150°	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6	1699.0	1698.4	1697.7
152.5°	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2	1728.5	1727.9	1727.3
155°	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8	1768.9	1767.9	1767.3
157.5°	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4	1802.4	1801.4	1801.3
160°	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3	1823.1	1821.8	1821.5
162.5°	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5	1841.7	1839.9	1839.7
165°	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1	1866.2	1864.3	1864.1
167.5°	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8	1884.5	1882.3	1882.0
170°	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4	1893.9	1891.3	1891.0
172.5°	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8	1901.6	1899.3	1898.8
175°	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9	1909.5	1907.0	1906.7
177.5°	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3	1913.5	1911.8	1911.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	15.4	14.9	15.0	14.5	13.5	15.6	16.6	16.6	16.0	15.6	15.0
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9	20.1	18.3	16.6
95°	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9	79.9	79.0	78.0
97.5°	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8	170.5	172.2	174.0
100°	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0	237.9	238.8	239.8
102.5°	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2	307.4	308.6	309.8
105°	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2	418.4	419.7	420.9
107.5°	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
110°	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7	678.4	679.2	680.0
115°	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3	784.8	786.4	788.0
117.5°	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5	892.4	892.3	892.3
120°	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5	960.3	960.0	959.6
122.5°	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8	1021.9	1023.1	1024.4
125°	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8	1116.0	1118.2	1120.4
127.5°	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6	1204.2	1205.8	1207.4
130°	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1	1258.7	1260.3	1261.9
132.5°	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5	1313.4	1315.2	1317.1
135°	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0	1390.9	1392.9	1394.8
137.5°	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3	1461.9	1463.6	1465.2
140°	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8	1507.5	1508.1	1508.7
142.5°	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8	1549.2	1549.5	1549.9
145°	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4	1611.0	1611.7	1612.3
147.5°	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3	1664.2	1664.1	1664.0
150°	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1697.7	1697.1	1696.5
152.5°	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3	1729.9	1728.5	1727.1
155°	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6	1771.7	1769.8	1767.9
157.5°	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2	1805.1	1803.9	1802.8
160°	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9	1827.0	1825.1	1823.3
162.5°	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1	1845.2	1843.3	1841.4
165°	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5	1869.6	1867.6	1865.8
167.5°	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6	1887.7	1885.7	1883.8
170°	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9	1897.6	1895.5	1893.2
172.5°	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7	1904.5	1902.2	1900.1
175°	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0	1912.1	1910.3	1908.4
177.5°	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4	1915.9	1914.4	1912.9
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	15.0	15.5	15.5	16.9	15.8	16.8	17.1	16.9	17.2	17.5	17.2
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8	27.4	29.0	30.3
92.5°	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8	27.4	29.0	30.0
95°	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8	27.4	29.0	29.8
97.5°	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0	43.2	34.2	29.8
100°	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9	105.9	59.0	34.9
102.5°	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2	288.3	279.5	264.3
105°	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.6
107.5°	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4	535.4	535.5	535.0
110°	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2	607.3	606.3	606.1



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3	679.2	678.0	677.1
115°	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2	788.0	786.6	785.1
117.5°	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3	892.7	891.0	889.8
120°	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1	961.5	960.9	959.8
122.5°	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8	1026.2	1025.6	1024.4
125°	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2	1119.9	1118.7	1117.6
127.5°	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5	1206.8	1206.1	1204.6
130°	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8	1262.8	1261.9	1260.6
132.5°	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4	1316.2	1316.0	1315.0
135°	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5	1392.9	1392.2	1390.9
137.5°	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4	1465.5	1465.7	1464.9
140°	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5	1510.1	1510.8	1510.1
142.5°	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7	1552.9	1553.0	1552.2
145°	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9	1614.2	1614.5	1613.7
147.5°	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2	1666.6	1667.0	1666.0
150°	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6	1700.3	1700.9	1700.0
152.5°	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2	1729.8	1730.4	1729.6
155°	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8	1770.8	1771.7	1770.8
157.5°	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4	1804.4	1805.4	1804.7
160°	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3	1825.6	1826.8	1826.3
162.5°	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5	1845.3	1847.0	1846.5
165°	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1	1870.1	1872.0	1871.6
167.5°	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8	1889.0	1891.3	1891.0
170°	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4	1898.9	1901.4	1901.3
172.5°	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8	1906.1	1908.4	1908.1
175°	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9	1914.5	1917.0	1916.8
177.5°	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3	1917.0	1918.8	1918.7
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	17.9	17.6	17.8	18.0	17.8	17.6	17.9	17.2	17.5	17.2	16.9
90°	31.2	32.1	33.1	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8
92.5°	30.4	30.9	31.4	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8
95°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8
97.5°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0
100°	33.6	32.3	31.1	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9
102.5°	242.8	221.4	199.9	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2
105°	422.4	422.1	421.7	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8
107.5°	534.0	533.1	532.2	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4
110°	606.3	606.6	607.0	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	676.7	676.3	675.8	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3
115°	783.3	781.3	779.4	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2
117.5°	889.0	888.2	887.3	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3
120°	958.2	956.6	955.1	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1
122.5°	1022.6	1020.7	1018.9	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8
125°	1116.6	1115.7	1114.7	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2
127.5°	1202.2	1200.0	1197.6	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5
130°	1259.0	1257.4	1255.8	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8
132.5°	1313.5	1311.9	1310.3	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4
135°	1389.0	1387.1	1385.3	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5
137.5°	1463.2	1461.6	1459.9	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4
140°	1508.3	1506.4	1504.5	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5
142.5°	1550.2	1548.3	1546.4	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7
145°	1611.8	1610.0	1608.1	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9
147.5°	1663.8	1661.5	1659.3	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2
150°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6
152.5°	1727.3	1725.0	1722.8	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2
155°	1768.4	1765.9	1763.3	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8
157.5°	1802.1	1799.6	1797.1	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4
160°	1823.7	1821.2	1818.6	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3
162.5°	1843.8	1841.0	1838.2	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5
165°	1869.2	1866.6	1864.1	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1
167.5°	1888.2	1885.4	1882.5	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8
170°	1898.5	1895.6	1892.7	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4
172.5°	1905.3	1902.4	1899.6	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8
175°	1914.0	1911.2	1908.4	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9
177.5°	1916.7	1914.7	1912.6	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	17.1	16.8	15.8	16.9	15.5	15.5	15.0	15.0	15.6	16.0	16.6
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	24.3	22.7	20.7	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9
95°	24.3	22.7	34.7	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9
97.5°	60.9	69.8	93.5	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8
100°	199.9	246.9	245.6	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0
102.5°	306.1	315.0	314.2	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2
105°	422.8	422.8	422.8	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2
107.5°	535.3	535.2	534.6	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3
110°	609.2	610.1	609.4	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	681.6	682.8	682.4	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7
115°	790.4	791.7	791.5	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3
117.5°	895.9	897.6	896.4	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5
120°	962.8	963.4	962.4	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5
122.5°	1027.5	1028.1	1027.7	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8
125°	1122.5	1123.7	1123.7	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8
127.5°	1208.2	1208.9	1209.1	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6
130°	1264.7	1265.6	1265.3	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1
132.5°	1316.5	1316.7	1317.4	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5
135°	1394.1	1394.8	1395.3	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0
137.5°	1465.3	1465.1	1465.7	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3
140°	1508.9	1508.3	1508.5	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8
142.5°	1552.7	1552.6	1552.1	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8
145°	1613.5	1613.3	1613.3	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4
147.5°	1665.8	1665.5	1665.1	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3
150°	1699.0	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1695.8	1696.5	1697.1	1697.7
152.5°	1728.5	1727.9	1727.3	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3
155°	1768.9	1767.9	1767.3	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6
157.5°	1802.4	1801.4	1801.3	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2
160°	1823.1	1821.8	1821.5	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9
162.5°	1841.7	1839.9	1839.7	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1
165°	1866.2	1864.3	1864.1	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5
167.5°	1884.5	1882.3	1882.0	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6
170°	1893.9	1891.3	1891.0	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9
172.5°	1901.6	1899.3	1898.8	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7
175°	1909.5	1907.0	1906.7	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0
177.5°	1913.5	1911.8	1911.5	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.6	15.6	13.5	14.5	15.0	14.9	15.4	15.3	15.3	15.6	15.8
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8
92.5°	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8
95°	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8
97.5°	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0
100°	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9
102.5°	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2
105°	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4
110°	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3
115°	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2
117.5°	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3
120°	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1
122.5°	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8
125°	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2
127.5°	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5
130°	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8
132.5°	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4
135°	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5
137.5°	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4
140°	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5
142.5°	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7
145°	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9
147.5°	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2
150°	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6
152.5°	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2
155°	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8
157.5°	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4
160°	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3
162.5°	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5
165°	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1
167.5°	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8
170°	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4
172.5°	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8
175°	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9
177.5°	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	16.7	17.5	16.8	16.4	16.6	17.3	18.0
90°	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333716-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)