

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332785-940

Luminaire Tested: **S124DIW-S795D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332785-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5777.6 lumens  
Efficiency: N/A  
Efficacy: 128.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42	37
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	21
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	1.9
10°-20°	314.1	5.4
20°-30°	462.3	8.0
30°-40°	537.4	9.3
40°-50°	537.5	9.3
50°-60°	470.1	8.1
60°-70°	349.1	6.0
70°-80°	198.4	3.4
80°-90°	59.8	1.0
90°-100°	30.3	0.5
100°-110°	193.0	3.3
110°-120°	369.2	6.4
120°-130°	468.7	8.1
130°-140°	501.4	8.7
140°-150°	468.9	8.1
150°-160°	378.1	6.5
160°-170°	243.9	4.2
170°-180°	84.1	1.5
0°-30°	887.8	15.4
0°-40°	1425.3	24.7
0°-60°	2432.8	42.1
0°-90°	3040.1	52.6
90°-120°	592.4	10.3
90°-150°	2031.4	35.2
90°-180°	2737.0	47.4
0°-180°	5777.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	2	9	14	18	20	4
95°	36	15	14	18	19	47
105°	199	203	206	211	189	208
115°	372	374	373	375	375	366
125°	523	525	524	526	527	467
135°	649	648	651	652	653	500
145°	748	750	750	751	752	467
155°	820	821	819	821	820	378
165°	865	862	862	866	861	244
175°	885	881	882	887	880	84
180°	885	885	885	885	885	



TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.2	20.2	20.4	20.6	20.8	20.9	21.0	21.0	21.0	21.1	21.3
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	8.4	8.5	8.6	8.6	8.6	9.4	10.5	11.7	12.8	14.0	14.9
95°	36.4	31.4	26.4	21.4	16.4	14.0	14.1	14.3	14.4	14.5	15.4
97.5°	77.3	80.4	83.6	86.7	89.8	83.1	66.7	50.3	33.9	17.5	17.6
100°	108.5	111.2	113.9	116.5	119.1	110.3	90.1	69.7	49.4	29.2	26.7
102.5°	143.5	145.4	147.4	149.4	151.2	150.9	148.3	145.6	142.9	140.4	113.3
105°	199.2	200.1	201.0	201.9	202.8	203.6	204.3	205.0	205.8	206.5	207.9
107.5°	251.0	251.5	251.9	252.4	252.8	253.5	254.5	255.5	256.5	257.4	258.2
110°	286.0	286.4	286.9	287.3	287.7	288.4	289.3	290.2	291.1	291.9	292.2



TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	319.9	320.7	321.5	322.2	323.0	323.6	324.0	324.4	324.9	325.3	325.2
115°	372.0	372.5	372.9	373.3	373.7	373.9	373.7	373.6	373.4	373.3	373.6
117.5°	419.0	419.5	420.2	420.7	421.3	421.8	422.1	422.4	422.8	423.1	423.0
120°	450.8	451.4	451.9	452.5	453.1	453.3	453.2	453.1	452.9	452.7	453.1
122.5°	480.5	480.7	481.1	481.4	481.8	482.1	482.3	482.5	482.7	483.0	483.1
125°	522.9	523.5	524.1	524.7	525.2	525.4	525.1	524.9	524.5	524.2	524.7
127.5°	563.1	563.3	563.5	563.6	563.7	564.2	564.8	565.5	566.1	566.9	566.8
130°	589.1	589.2	589.4	589.5	589.7	590.0	590.4	590.8	591.3	591.7	591.9
132.5°	613.0	613.2	613.5	613.7	613.9	614.4	614.9	615.5	616.1	616.6	616.8
135°	648.6	648.5	648.4	648.2	648.1	648.3	648.9	649.4	650.1	650.7	650.9
137.5°	680.3	680.4	680.5	680.5	680.6	680.9	681.5	682.2	682.9	683.5	683.8
140°	701.0	701.2	701.5	701.9	702.1	702.4	702.8	703.0	703.3	703.6	704.0
142.5°	719.5	720.1	720.6	721.0	721.6	721.9	722.1	722.3	722.5	722.6	723.0
145°	748.0	748.4	748.9	749.3	749.8	749.9	749.9	749.9	749.9	749.9	750.1
147.5°	770.6	771.4	772.2	773.0	773.9	774.2	774.1	773.9	773.7	773.6	773.7
150°	787.0	787.6	788.2	788.8	789.3	789.6	789.4	789.3	789.2	789.0	789.0
152.5°	800.8	801.2	801.7	802.2	802.6	802.7	802.5	802.3	802.0	801.7	801.9
155°	820.1	820.3	820.4	820.6	820.7	820.6	820.1	819.7	819.2	818.8	819.4
157.5°	836.4	836.3	836.2	836.2	836.1	835.7	835.3	834.7	834.2	833.7	834.5
160°	845.9	845.4	845.1	844.6	844.2	843.8	843.7	843.6	843.4	843.3	844.2
162.5°	854.3	853.8	853.3	852.7	852.1	851.8	851.7	851.5	851.3	851.2	852.1
165°	865.1	864.3	863.6	862.9	862.2	861.8	861.8	861.8	861.8	861.8	863.0
167.5°	873.6	872.8	872.1	871.3	870.5	870.1	870.0	870.0	869.9	869.8	871.0
170°	878.3	877.4	876.6	875.7	874.9	874.4	874.6	874.8	874.9	875.0	876.2
172.5°	881.5	880.7	879.8	878.9	878.0	877.6	877.8	877.9	878.1	878.2	879.4
175°	884.9	884.0	883.2	882.3	881.5	881.1	881.2	881.4	881.5	881.6	883.0
177.5°	886.5	885.7	884.9	884.0	883.2	883.0	883.2	883.4	883.7	883.9	884.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	21.5	21.7	21.8	21.9	22.0	22.0	22.1	22.2
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	15.8	16.7	17.6	18.0	18.1	18.2	18.2	18.3
95°	16.3	17.2	18.1	18.6	18.7	18.9	19.1	19.2
97.5°	17.7	17.7	17.8	17.9	18.1	18.3	18.4	18.5
100°	24.2	21.6	19.1	17.9	18.1	18.3	18.4	18.5
102.5°	86.4	59.4	32.5	18.9	19.0	19.0	19.0	19.1
105°	209.2	210.4	211.8	209.8	204.6	199.2	193.9	188.7
107.5°	258.8	259.4	260.1	260.6	261.3	261.8	262.3	262.9
110°	292.5	292.7	293.1	293.5	293.9	294.4	294.8	295.2





TEST NUMBER: P332785-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	325.1	325.1	325.0	325.3	325.8	326.4	327.0	327.5
115°	373.9	374.2	374.5	374.6	374.6	374.6	374.6	374.6
117.5°	422.9	422.9	422.8	422.8	422.8	422.7	422.6	422.6
120°	453.3	453.6	453.9	453.9	453.6	453.3	453.1	452.7
122.5°	483.3	483.5	483.7	483.6	483.3	483.0	482.7	482.4
125°	525.1	525.6	526.0	526.3	526.5	526.6	526.7	526.9
127.5°	566.7	566.6	566.5	566.4	566.3	566.1	566.1	566.0
130°	592.0	592.2	592.4	592.4	592.4	592.4	592.4	592.4
132.5°	616.9	617.1	617.2	617.2	617.2	617.0	616.9	616.8
135°	651.2	651.6	651.8	652.1	652.4	652.7	653.0	653.3
137.5°	684.1	684.5	684.7	684.9	684.8	684.7	684.7	684.6
140°	704.5	704.9	705.3	705.7	705.8	706.0	706.1	706.2
142.5°	723.4	723.6	724.0	724.2	724.2	724.2	724.2	724.2
145°	750.2	750.4	750.6	750.7	751.0	751.4	751.6	751.9
147.5°	773.8	774.0	774.1	774.3	774.4	774.5	774.7	774.8
150°	789.0	789.0	789.0	789.1	789.3	789.3	789.5	789.6
152.5°	802.2	802.4	802.6	802.7	802.6	802.5	802.5	802.4
155°	819.9	820.6	821.1	821.2	820.7	820.3	819.8	819.5
157.5°	835.3	836.1	836.8	836.8	836.1	835.3	834.5	833.7
160°	845.1	845.9	846.8	846.8	845.9	845.1	844.2	843.3
162.5°	853.0	853.8	854.7	854.7	853.7	852.7	851.7	850.7
165°	864.2	865.3	866.5	866.5	865.1	863.8	862.5	861.1
167.5°	872.4	873.6	874.9	874.9	873.3	871.9	870.4	869.0
170°	877.4	878.6	879.8	879.6	878.2	876.6	875.2	873.7
172.5°	880.6	881.7	882.9	882.7	881.1	879.6	878.0	876.4
175°	884.3	885.6	887.0	886.7	884.9	883.2	881.5	879.7
177.5°	885.8	886.7	887.7	887.4	886.0	884.6	883.2	881.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9

(END OF REPORT)