

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333731-830

Luminaire Tested: **S125RDIW-S1270D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333731-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8023.7 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54	49
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	50	47	46	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	49	53	48	44	46	42	39	40	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.3
10°-20°	511.3	6.4
20°-30°	741.4	9.2
30°-40°	845.0	10.5
40°-50°	823.6	10.3
50°-60°	693.3	8.6
60°-70°	486.0	6.1
70°-80°	249.8	3.1
80°-90°	65.8	0.8
90°-100°	82.2	1.0
100°-110°	242.7	3.0
110°-120°	411.1	5.1
120°-130°	541.1	6.7
130°-140°	606.3	7.6
140°-150°	594.2	7.4
150°-160°	499.1	6.2
160°-170°	331.7	4.1
170°-180°	116.1	1.4
0°-30°	1435.7	17.9
0°-40°	2280.6	28.4
0°-60°	3797.6	47.3
0°-90°	4599.2	57.3
90°-120°	736.0	9.2
90°-150°	2477.6	30.9
90°-180°	3424.0	42.7
0°-180°	8023.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	8	15	20	23	7
95°	62	64	74	80	82	66
105°	218	223	228	234	237	233
115°	412	415	417	416	416	407
125°	601	606	607	606	604	538
135°	781	787	788	788	784	602
145°	946	950	953	953	950	591
155°	1083	1083	1084	1087	1083	499
165°	1178	1176	1177	1180	1175	332
175°	1224	1221	1220	1226	1220	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.2	25.7	24.2	22.8	21.3	20.5	20.5	20.6	20.6	20.7	20.9
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	23.1	24.3	25.4	26.7	27.9	29.4	31.2	33.0	34.9	36.7	38.1
95°	62.1	62.5	63.0	63.3	63.8	65.0	67.2	69.3	71.4	73.5	75.0
97.5°	103.1	103.3	103.5	103.7	103.9	105.4	108.3	111.2	114.1	117.1	118.5
100°	133.7	133.7	133.7	133.7	133.7	135.1	137.8	140.6	143.4	146.1	148.1
102.5°	166.5	167.4	168.2	169.1	169.9	171.1	172.5	173.9	175.3	176.7	178.8
105°	217.7	218.8	219.9	220.9	222.0	223.2	224.4	225.7	227.0	228.3	229.5
107.5°	274.3	275.3	276.4	277.5	278.5	279.6	280.5	281.5	282.5	283.4	284.1
110°	313.2	314.3	315.4	316.4	317.5	318.4	319.0	319.6	320.3	320.9	321.5



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.0	353.5	354.1	354.7	355.2	355.9	356.7	357.5	358.3	359.1	359.4
115°	411.6	412.5	413.3	414.2	415.0	415.7	416.0	416.5	416.9	417.4	417.2
117.5°	470.4	470.8	471.2	471.6	472.0	472.4	472.8	473.2	473.5	473.9	474.1
120°	507.1	508.2	509.3	510.3	511.3	512.0	512.2	512.5	512.6	512.8	512.8
122.5°	546.9	547.2	547.6	548.0	548.4	548.8	549.4	550.0	550.5	551.1	550.9
125°	600.7	602.0	603.2	604.5	605.8	606.5	606.8	607.0	607.2	607.4	607.0
127.5°	658.0	658.7	659.5	660.2	660.9	661.4	661.7	661.9	662.1	662.4	662.2
130°	692.4	693.4	694.6	695.6	696.6	697.4	697.9	698.2	698.7	699.1	698.9
132.5°	726.8	728.5	730.3	732.0	733.8	734.6	734.5	734.4	734.3	734.2	734.1
135°	781.2	782.5	783.7	785.0	786.4	787.0	787.3	787.5	787.7	787.9	787.9
137.5°	832.5	833.7	834.9	836.1	837.4	838.2	838.7	839.1	839.6	840.1	840.3
140°	865.3	866.3	867.4	868.5	869.5	870.3	871.0	871.7	872.2	872.9	873.4
142.5°	898.1	899.0	899.9	900.8	901.7	902.6	903.3	904.2	904.9	905.8	906.0
145°	946.4	947.3	948.1	949.0	949.8	950.6	951.2	951.9	952.5	953.1	953.1
147.5°	991.2	991.6	992.1	992.5	993.0	993.5	994.0	994.5	995.0	995.5	996.1
150°	1021.0	1020.8	1020.5	1020.3	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8
152.5°	1045.4	1045.7	1045.9	1046.3	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8
155°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9
157.5°	1116.6	1116.2	1115.7	1115.2	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3
160°	1136.5	1135.9	1135.2	1134.6	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5
162.5°	1154.0	1153.6	1153.1	1152.6	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2
165°	1177.6	1177.1	1176.7	1176.3	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4
167.5°	1197.4	1196.6	1195.7	1194.9	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9
170°	1208.2	1207.3	1206.5	1205.6	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6
172.5°	1215.8	1214.9	1214.1	1213.2	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2
175°	1224.4	1223.5	1222.7	1221.8	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8
177.5°	1228.8	1228.0	1227.4	1226.7	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	21.1	21.3	21.6	21.6	21.5	21.3	21.2	21.0
90°	17.4	18.5	19.5	20.4	21.0	21.7	22.2	22.9
92.5°	39.5	40.9	42.3	43.2	43.6	44.1	44.6	45.1
95°	76.5	77.9	79.5	80.4	80.9	81.2	81.7	82.1
97.5°	119.9	121.3	122.7	123.5	123.8	124.0	124.3	124.5
100°	150.0	151.8	153.7	155.0	155.3	155.8	156.2	156.7
102.5°	180.9	182.9	185.0	186.3	186.9	187.6	188.1	188.7
105°	230.8	232.1	233.4	234.3	235.0	235.5	236.2	236.9
107.5°	284.7	285.4	286.0	286.3	286.3	286.3	286.2	286.2
110°	322.2	322.8	323.5	323.7	323.5	323.2	323.0	322.8



TEST NUMBER: P333731-830

CATALOG NUMBER: S125RDIW-S1270D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	359.7	360.0	360.2	360.2	359.9	359.5	359.1	358.7
115°	416.9	416.7	416.5	416.3	416.0	415.8	415.7	415.5
117.5°	474.2	474.4	474.6	474.2	473.3	472.5	471.6	470.8
120°	512.8	512.8	512.8	512.5	511.6	510.8	509.9	509.1
122.5°	550.7	550.5	550.4	550.0	549.3	548.6	547.9	547.2
125°	606.5	606.1	605.7	605.4	605.2	604.9	604.7	604.5
127.5°	661.9	661.8	661.6	661.3	660.8	660.4	660.0	659.6
130°	698.7	698.4	698.2	698.0	697.5	697.1	696.6	696.3
132.5°	733.8	733.6	733.4	733.0	732.4	731.8	731.2	730.6
135°	787.9	787.9	787.9	787.5	786.6	785.8	784.9	784.1
137.5°	840.6	840.8	841.0	840.7	839.6	838.6	837.4	836.4
140°	873.7	874.2	874.6	874.3	873.3	872.1	871.1	870.1
142.5°	906.3	906.5	906.8	906.3	905.3	904.3	903.2	902.1
145°	953.1	953.1	953.1	952.8	952.2	951.5	950.9	950.3
147.5°	996.6	997.0	997.6	997.1	995.7	994.2	992.8	991.4
150°	1023.8	1023.8	1023.8	1023.6	1023.1	1022.8	1022.3	1021.9
152.5°	1049.2	1049.8	1050.3	1050.2	1049.4	1048.7	1047.8	1047.1
155°	1085.7	1086.6	1087.4	1087.2	1086.2	1085.1	1084.1	1083.0
157.5°	1117.2	1118.0	1118.9	1118.6	1117.2	1115.8	1114.4	1113.0
160°	1136.3	1137.2	1138.0	1137.8	1136.8	1135.8	1134.7	1133.6
162.5°	1154.2	1155.2	1156.2	1156.1	1154.9	1153.7	1152.4	1151.2
165°	1178.3	1179.1	1180.0	1179.8	1178.6	1177.2	1176.0	1174.7
167.5°	1196.2	1197.4	1198.7	1198.7	1197.4	1196.1	1194.8	1193.4
170°	1206.8	1208.2	1209.4	1209.3	1207.8	1206.4	1204.9	1203.3
172.5°	1214.5	1215.8	1217.0	1217.0	1215.7	1214.4	1213.1	1211.7
175°	1223.0	1224.4	1225.7	1225.5	1224.1	1222.6	1221.1	1219.6
177.5°	1227.0	1228.0	1229.0	1228.9	1227.8	1226.5	1225.4	1224.2
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2

(END OF REPORT)