

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333089-940

Luminaire Tested: **S124RDIW-S1020D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333089-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8508.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66		57	56	54		45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55		50	48	46		40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46		45	41	39		35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40		40	36	33		32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34		36	32	29		29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30		33	29	25		26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26		30	26	23		24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24		27	23	20		22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21		25	21	18		20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19		23	19	16		19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	1.8
10°-20°	421.8	5.0
20°-30°	609.1	7.2
30°-40°	690.4	8.1
40°-50°	666.7	7.8
50°-60°	554.4	6.5
60°-70°	382.8	4.5
70°-80°	194.0	2.3
80°-90°	54.2	0.6
90°-100°	52.9	0.6
100°-110°	337.2	4.0
110°-120°	645.1	7.6
120°-130°	818.9	9.6
130°-140°	876.2	10.3
140°-150°	819.3	9.6
150°-160°	660.7	7.8
160°-170°	426.2	5.0
170°-180°	146.9	1.7
0°-30°	1182.1	13.9
0°-40°	1872.5	22.0
0°-60°	3093.5	36.4
0°-90°	3724.6	43.8
90°-120°	1035.2	12.2
90°-150°	3549.6	41.7
90°-180°	4783.0	56.2
0°-180°	8508.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	4	16	25	32	35	6
95°	64	26	25	32	34	82
105°	348	355	361	368	330	364
115°	650	653	652	654	655	639
125°	914	918	916	919	921	815
135°	1134	1133	1137	1139	1142	873
145°	1307	1310	1310	1312	1314	816
155°	1433	1434	1431	1435	1432	660
165°	1512	1506	1506	1514	1505	427
175°	1546	1540	1541	1550	1537	147
180°	1546	1546	1546	1546	1546	



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	23.4	22.2	21.0	19.8	18.6	18.1	18.3	18.5	18.7	18.9	19.0
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	14.5	14.7	14.9	15.1	15.2	16.3	18.4	20.4	22.5	24.5	26.0
95°	63.6	54.8	46.1	37.4	28.6	24.4	24.7	25.0	25.1	25.4	27.0
97.5°	135.1	140.5	146.0	151.4	156.9	145.3	116.5	87.9	59.2	30.5	30.7
100°	189.7	194.3	198.9	203.6	208.2	192.8	157.3	121.8	86.3	50.9	46.5
102.5°	250.7	254.1	257.5	260.9	264.3	263.7	259.0	254.5	249.9	245.2	198.0
105°	348.1	349.6	351.2	352.8	354.3	355.7	357.0	358.3	359.5	360.9	363.2
107.5°	438.5	439.3	440.1	440.9	441.7	442.9	444.7	446.4	448.2	450.0	451.0
110°	499.6	500.4	501.2	501.9	502.7	503.9	505.4	506.9	508.5	510.1	510.6



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.8	560.3	561.7	563.0	564.5	565.4	566.2	566.9	567.7	568.4	568.3
115°	650.0	650.8	651.6	652.3	653.1	653.4	653.1	652.8	652.6	652.3	652.8
117.5°	732.1	733.2	734.1	735.2	736.2	737.0	737.6	738.2	738.7	739.3	739.2
120°	787.6	788.6	789.7	790.8	791.8	792.1	791.9	791.7	791.4	791.1	791.7
122.5°	839.5	840.1	840.7	841.3	842.0	842.4	842.8	843.1	843.5	843.8	844.2
125°	913.7	914.7	915.8	916.8	917.8	918.1	917.6	917.0	916.5	916.1	916.8
127.5°	984.0	984.3	984.5	984.8	985.1	985.8	986.9	988.1	989.4	990.5	990.3
130°	1029.4	1029.7	1029.9	1030.1	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3
132.5°	1071.0	1071.5	1071.9	1072.4	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7
135°	1133.5	1133.2	1132.9	1132.7	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5
137.5°	1188.7	1188.8	1188.9	1189.1	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9
140°	1224.9	1225.4	1225.8	1226.4	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2
142.5°	1257.2	1258.1	1259.1	1260.0	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4
145°	1307.0	1307.7	1308.5	1309.3	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7
147.5°	1346.5	1347.9	1349.4	1350.9	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0
150°	1375.2	1376.3	1377.2	1378.3	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7
152.5°	1399.3	1400.1	1400.9	1401.7	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3
155°	1433.1	1433.2	1433.5	1433.8	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7
157.5°	1461.5	1461.3	1461.2	1461.0	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2
160°	1478.1	1477.4	1476.6	1475.8	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1
162.5°	1492.9	1491.9	1491.0	1490.0	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9
165°	1511.7	1510.4	1509.1	1507.8	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0
167.5°	1526.5	1525.2	1523.8	1522.5	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1
170°	1534.8	1533.3	1531.7	1530.2	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1
172.5°	1540.3	1538.8	1537.3	1535.7	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6
175°	1546.4	1544.8	1543.3	1541.8	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9
177.5°	1549.2	1547.7	1546.2	1544.8	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	19.1	19.2	19.3	19.4	19.8	20.1	20.4	20.8
90°	28.5	30.1	31.7	32.6	33.2	33.7	34.2	34.7
92.5°	27.6	29.2	30.7	31.5	31.7	31.7	31.8	31.9
95°	28.5	30.1	31.7	32.5	32.7	33.0	33.3	33.5
97.5°	30.9	31.0	31.1	31.4	31.7	31.8	32.1	32.4
100°	42.2	37.8	33.4	31.4	31.7	31.8	32.1	32.4
102.5°	151.0	103.8	56.6	33.1	33.2	33.2	33.3	33.3
105°	365.5	367.8	370.1	366.7	357.4	348.1	338.9	329.7
107.5°	452.2	453.3	454.4	455.5	456.5	457.4	458.4	459.4
110°	511.1	511.6	512.1	512.7	513.5	514.3	515.1	515.9



TEST NUMBER: P333089-940

CATALOG NUMBER: S124RDIW-S1020D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.1	568.0	567.9	568.4	569.4	570.3	571.3	572.3
115°	653.4	653.9	654.3	654.6	654.6	654.6	654.6	654.6
117.5°	739.0	739.0	738.9	738.8	738.7	738.6	738.5	738.3
120°	792.1	792.6	793.2	793.2	792.6	792.1	791.7	791.1
122.5°	844.5	844.8	845.1	845.0	844.5	843.9	843.5	842.9
125°	917.6	918.4	919.1	919.6	919.9	920.2	920.4	920.7
127.5°	990.2	990.1	989.9	989.7	989.5	989.3	989.1	988.9
130°	1034.5	1034.7	1035.0	1035.2	1035.2	1035.2	1035.2	1035.2
132.5°	1078.0	1078.3	1078.5	1078.5	1078.3	1078.2	1077.9	1077.7
135°	1138.0	1138.4	1139.0	1139.5	1140.1	1140.5	1141.0	1141.6
137.5°	1195.4	1196.0	1196.6	1196.8	1196.6	1196.5	1196.3	1196.1
140°	1231.0	1231.8	1232.5	1233.1	1233.3	1233.6	1233.9	1234.1
142.5°	1263.9	1264.4	1265.1	1265.3	1265.4	1265.4	1265.5	1265.5
145°	1310.9	1311.2	1311.4	1311.9	1312.3	1312.9	1313.4	1313.9
147.5°	1352.3	1352.5	1352.6	1352.9	1353.2	1353.4	1353.6	1353.9
150°	1378.7	1378.7	1378.7	1378.8	1379.0	1379.3	1379.6	1379.8
152.5°	1401.7	1402.1	1402.5	1402.7	1402.5	1402.3	1402.2	1402.0
155°	1432.8	1433.8	1434.9	1434.9	1434.2	1433.4	1432.6	1431.9
157.5°	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9
160°	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6
162.5°	1490.5	1492.0	1493.5	1493.4	1491.7	1490.0	1488.2	1486.5
165°	1510.0	1512.1	1514.1	1513.9	1511.7	1509.4	1507.1	1504.8
167.5°	1524.3	1526.5	1528.8	1528.7	1526.1	1523.5	1521.0	1518.4
170°	1533.1	1535.2	1537.2	1537.0	1534.5	1531.9	1529.3	1526.7
172.5°	1538.6	1540.8	1542.8	1542.5	1539.6	1536.9	1534.1	1531.3
175°	1545.2	1547.6	1549.9	1549.4	1546.4	1543.3	1540.2	1537.1
177.5°	1547.8	1549.4	1551.1	1550.7	1548.2	1545.8	1543.3	1540.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4

(END OF REPORT)