

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333733-830

Luminaire Tested: **S125RDIW-S1270D1340U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333733-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9024.5 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.6	1.9
10°-20°	503.0	5.6
20°-30°	797.5	8.8
30°-40°	961.7	10.7
40°-50°	858.8	9.5
50°-60°	658.6	7.3
60°-70°	428.0	4.7
70°-80°	208.1	2.3
80°-90°	53.1	0.6
90°-100°	105.2	1.2
100°-110°	310.7	3.4
110°-120°	526.3	5.8
120°-130°	692.7	7.7
130°-140°	776.1	8.6
140°-150°	760.7	8.4
150°-160°	638.9	7.1
160°-170°	424.7	4.7
170°-180°	148.6	1.6
0°-30°	1472.1	16.3
0°-40°	2433.8	27.0
0°-60°	3951.3	43.8
0°-90°	4640.5	51.4
90°-120°	942.3	10.4
90°-150°	3171.8	35.1
90°-180°	4384.0	48.6
0°-180°	9024.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	40
90°	29	1	29	1	29	19
95°	105	80	105	80	105	107
105°	303	279	303	279	303	321
115°	532	527	532	527	532	526
125°	774	769	774	769	774	691
135°	1004	1000	1004	1000	1004	774
145°	1216	1212	1216	1212	1216	759
155°	1386	1386	1386	1386	1386	638
165°	1504	1508	1504	1508	1504	424
175°	1561	1567	1561	1567	1561	148
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	18.8	18.0	17.3	17.2	17.5	18.5	17.6	16.8	16.5	16.2	16.5
90°	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2	20.9	19.6	17.6
92.5°	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5	48.7	46.9	44.6
95°	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9	96.0	94.2	91.4
97.5°	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4	151.7	149.9	146.2
100°	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0	189.5	187.1	183.5
102.5°	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5	228.8	226.2	224.4
105°	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5	293.9	292.2	290.6
107.5°	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5	363.7	362.9	361.7
110°	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5	411.6	410.8	410.0



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4	460.1	459.7	458.6
115°	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8	534.0	534.3	533.8
117.5°	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1	606.9	606.7	606.1
120°	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6	656.6	656.6	656.3
122.5°	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0	705.2	705.5	704.7
125°	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5	777.0	777.6	777.3
127.5°	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4	847.7	848.0	847.7
130°	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4	894.7	894.9	894.4
132.5°	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4	939.7	940.0	940.1
135°	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7	1008.7	1008.7	1008.4
137.5°	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1	1075.7	1075.4	1074.9
140°	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6	1118.0	1117.5	1116.6
142.5°	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2	1159.9	1159.5	1158.5
145°	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2	1220.2	1220.2	1219.4
147.5°	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7	1275.2	1274.5	1273.8
150°	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7	1310.7	1310.7	1309.6
152.5°	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2	1342.7	1342.0	1341.5
155°	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9	1388.7	1387.7	1387.4
157.5°	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2	1429.1	1428.0	1427.8
160°	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6	1453.6	1452.5	1452.2
162.5°	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6	1476.3	1475.0	1474.9
165°	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4	1507.4	1506.3	1506.0
167.5°	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3	1529.7	1528.0	1528.0
170°	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0	1543.4	1541.7	1541.7
172.5°	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8	1553.1	1551.5	1551.5
175°	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8	1564.1	1562.5	1562.5
177.5°	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7	1569.4	1568.1	1568.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	16.7	16.3	16.5	16.1	15.1	17.5	18.9	19.0	18.3	17.5	16.9
90°	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6	31.1	32.6	34.1
95°	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5	80.0	80.6	81.1
97.5°	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1	132.2	132.5	132.7
100°	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2	171.2	171.2	171.2
102.5°	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2	214.3	215.4	216.5
105°	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8	280.1	281.4	282.9
107.5°	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1	352.5	353.8	355.2
110°	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1	402.4	403.8	405.1





TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9	452.6	453.3	454.0
115°	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0	528.0	529.1	530.2
117.5°	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3	602.8	603.2	603.7
120°	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2	650.5	652.0	653.3
122.5°	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1	700.6	701.1	701.5
125°	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0	770.6	772.3	773.9
127.5°	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4	843.3	844.2	845.2
130°	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4	887.8	889.1	890.5
132.5°	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4	932.6	934.9	937.1
135°	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1	1001.7	1003.3	1005.0
137.5°	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6	1067.2	1068.8	1070.4
140°	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7	1109.1	1110.4	1111.8
142.5°	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8	1150.9	1152.1	1153.2
145°	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6	1212.7	1213.8	1214.8
147.5°	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9	1269.4	1270.1	1270.6
150°	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0	1306.7	1306.5	1306.2
152.5°	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3	1338.7	1339.1	1339.4
155°	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5	1428.9	1428.3	1427.7
160°	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9	1454.2	1453.3	1452.5
162.5°	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4	1476.9	1476.2	1475.6
165°	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5	1506.9	1506.4	1505.9
167.5°	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0	1531.8	1530.8	1529.7
170°	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6	1545.6	1544.5	1543.4
172.5°	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4	1555.3	1554.3	1553.1
175°	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4	1566.3	1565.3	1564.1
177.5°	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0	1572.2	1571.3	1570.5
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	16.7	17.1	16.9	18.5	17.1	18.0	18.3	18.0	18.3	18.5	18.2
90°	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2	23.7	25.0	26.1
92.5°	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5	52.3	54.1	55.3
95°	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9	99.8	101.8	102.9
97.5°	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4	155.2	157.0	158.2
100°	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0	194.4	196.8	198.3
102.5°	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5	234.1	236.9	238.6
105°	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5	297.1	298.7	299.9
107.5°	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5	365.3	366.2	366.6
110°	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5	413.2	414.1	414.3



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4	460.8	461.2	461.2
115°	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8	533.5	533.2	532.9
117.5°	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1	607.3	607.6	607.1
120°	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6	656.6	656.6	656.0
122.5°	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0	704.8	704.6	704.1
125°	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5	776.0	775.4	775.1
127.5°	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4	847.2	847.0	846.5
130°	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4	894.2	893.9	893.4
132.5°	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4	939.1	938.9	938.4
135°	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7	1008.7	1008.7	1008.1
137.5°	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1	1076.4	1076.8	1076.2
140°	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6	1119.1	1119.6	1119.3
142.5°	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2	1160.6	1160.8	1160.4
145°	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2	1220.2	1220.2	1219.7
147.5°	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7	1276.4	1277.1	1276.5
150°	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7	1310.7	1310.7	1310.4
152.5°	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2	1343.9	1344.5	1344.4
155°	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9	1390.9	1392.0	1391.9
157.5°	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2	1431.3	1432.4	1432.0
160°	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6	1455.8	1456.8	1456.7
162.5°	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6	1478.8	1480.2	1480.1
165°	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4	1509.6	1510.6	1510.3
167.5°	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3	1533.0	1534.6	1534.6
170°	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0	1546.6	1548.2	1548.1
172.5°	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8	1556.4	1558.0	1558.0
175°	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8	1567.4	1569.1	1568.9
177.5°	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7	1572.1	1573.4	1573.3
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	18.9	18.5	18.7	18.8	18.7	18.5	18.9	18.2	18.5	18.3	18.0
90°	26.9	27.7	28.6	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2
92.5°	55.9	56.6	57.1	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5
95°	103.5	104.1	104.6	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9
97.5°	158.4	158.8	159.1	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4
100°	198.9	199.4	200.0	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0
102.5°	239.3	240.1	240.8	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5
105°	300.8	301.6	302.4	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5
107.5°	366.5	366.4	366.4	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5
110°	414.1	413.8	413.5	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	460.7	460.2	459.7	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4
115°	532.6	532.3	532.2	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8
117.5°	606.1	604.9	603.9	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1
120°	654.9	653.8	652.7	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6
122.5°	703.1	702.3	701.4	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0
125°	774.8	774.5	774.2	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5
127.5°	846.0	845.5	844.9	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4
130°	893.0	892.4	891.8	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4
132.5°	937.6	936.8	936.0	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4
135°	1007.0	1006.0	1004.8	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7
137.5°	1074.9	1073.5	1072.1	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1
140°	1117.9	1116.5	1115.2	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6
142.5°	1159.0	1157.6	1156.2	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2
145°	1219.0	1218.1	1217.3	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2
147.5°	1274.6	1272.8	1270.9	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7
150°	1309.9	1309.3	1308.7	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7
152.5°	1343.4	1342.5	1341.4	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2
155°	1390.5	1389.2	1387.8	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9
157.5°	1430.2	1428.4	1426.6	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2
160°	1455.4	1454.0	1452.6	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6
162.5°	1478.5	1476.9	1475.4	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6
165°	1508.7	1507.1	1505.4	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4
167.5°	1532.9	1531.2	1529.5	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3
170°	1546.2	1544.4	1542.4	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0
172.5°	1556.3	1554.6	1552.9	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8
175°	1567.0	1565.1	1563.2	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8
177.5°	1571.7	1570.2	1568.7	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	18.3	18.0	17.1	18.5	16.9	17.1	16.7	16.9	17.5	18.3	19.0
90°	20.9	19.6	17.6	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	48.7	46.9	44.6	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6
95°	96.0	94.2	91.4	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5
97.5°	151.7	149.9	146.2	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1
100°	189.5	187.1	183.5	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2
102.5°	228.8	226.2	224.4	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2
105°	293.9	292.2	290.6	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8
107.5°	363.7	362.9	361.7	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1
110°	411.6	410.8	410.0	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	460.1	459.7	458.6	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9
115°	534.0	534.3	533.8	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0
117.5°	606.9	606.7	606.1	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3
120°	656.6	656.6	656.3	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2
122.5°	705.2	705.5	704.7	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1
125°	777.0	777.6	777.3	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0
127.5°	847.7	848.0	847.7	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4
130°	894.7	894.9	894.4	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4
132.5°	939.7	940.0	940.1	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4
135°	1008.7	1008.7	1008.4	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1
137.5°	1075.7	1075.4	1074.9	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6
140°	1118.0	1117.5	1116.6	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7
142.5°	1159.9	1159.5	1158.5	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8
145°	1220.2	1220.2	1219.4	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6
147.5°	1275.2	1274.5	1273.8	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9
150°	1310.7	1310.7	1309.6	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0
152.5°	1342.7	1342.0	1341.5	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3
155°	1388.7	1387.7	1387.4	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1429.1	1428.0	1427.8	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5
160°	1453.6	1452.5	1452.2	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9
162.5°	1476.3	1475.0	1474.9	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4
165°	1507.4	1506.3	1506.0	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5
167.5°	1529.7	1528.0	1528.0	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0
170°	1543.4	1541.7	1541.7	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6
172.5°	1553.1	1551.5	1551.5	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4
175°	1564.1	1562.5	1562.5	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4
177.5°	1569.4	1568.1	1568.4	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.9	17.5	15.1	16.1	16.5	16.3	16.7	16.5	16.2	16.5	16.8
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2
92.5°	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5
95°	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9
97.5°	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4
100°	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0
102.5°	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5
105°	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5
107.5°	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5
110°	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5





TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4
115°	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8
117.5°	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1
120°	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6
122.5°	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0
125°	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5
127.5°	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4
130°	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4
132.5°	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4
135°	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7
137.5°	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1
140°	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6
142.5°	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2
145°	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2
147.5°	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7
150°	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7
152.5°	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2
155°	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9
157.5°	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2
160°	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6
162.5°	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6
165°	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4
167.5°	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3
170°	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0
172.5°	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8
175°	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8
177.5°	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	17.6	18.5	17.5	17.2	17.3	18.0	18.8
90°	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	413.2	414.1	414.3	414.1	413.8	413.5	413.2



TEST NUMBER: P333733-830

CATALOG NUMBER: S125RDIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)