

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333092-940

Luminaire Tested: **S124RDIW-S1020D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333092-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8696.1 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28				
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12352	12352	12352	12352
5°	14327	12388	10950	12388
10°	16948	12336	9773	12336
15°	19578	12221	8398	12221
20°	21798	12064	7594	12064
25°	22502	11909	7050	11909
30°	19699	11723	6723	11723
35°	15334	11446	6525	11446
40°	11499	11129	6418	11129
45°	9079	10620	6361	10620
50°	7665	10034	6179	10034
55°	6681	9388	5847	9388
60°	6011	8719	5176	8719
65°	5299	7996	4451	7996
70°	4773	7246	4015	7246
75°	3999	6422	3425	6422
80°	3384	5472	3208	5472
85°	2862	4279	2862	4279



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.2	1.7
10°-20°	447.2	5.1
20°-30°	699.4	8.0
30°-40°	777.5	8.9
40°-50°	689.9	7.9
50°-60°	537.6	6.2
60°-70°	351.9	4.0
70°-80°	173.1	2.0
80°-90°	47.9	0.6
90°-100°	114.7	1.3
100°-110°	339.7	3.9
110°-120°	576.5	6.6
120°-130°	760.2	8.7
130°-140°	853.8	9.8
140°-150°	839.0	9.6
150°-160°	705.6	8.1
160°-170°	469.5	5.4
170°-180°	164.4	1.9
0°-30°	1294.9	14.9
0°-40°	2072.4	23.8
0°-60°	3299.8	37.9
0°-90°	3872.7	44.5
90°-120°	1030.9	11.9
90°-150°	3483.9	40.1
90°-180°	4823.0	55.5
0°-180°	8696.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1530	1530	1530	1530	1530	
5°	1768	1529	1351	1529	1768	179
15°	2342	1462	1005	1462	2342	666
25°	2526	1337	792	1337	2526	1121
35°	1556	1161	662	1161	1556	975
45°	795	930	557	930	795	630
55°	475	667	415	667	475	432
65°	277	419	233	419	277	279
75°	128	206	110	206	128	141
85°	31	46	31	46	31	36
90°	40	4	40	4	40	22
95°	106	81	106	81	106	111
105°	328	313	328	313	328	346
115°	581	586	581	586	581	574
125°	847	854	847	854	847	756
135°	1102	1101	1102	1101	1102	851
145°	1339	1338	1339	1338	1339	838
155°	1531	1533	1531	1533	1531	705
165°	1665	1669	1665	1669	1665	469
175°	1728	1736	1728	1736	1728	164
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1613.8	1618.3	1613.8	1613.4	1608.5	1607.0	1605.0	1598.6	1586.7	1579.8	1581.3
5°	1768.0	1783.3	1774.8	1773.5	1760.0	1746.4	1737.8	1718.1	1697.1	1682.9	1671.2
7.5°	1946.2	1955.1	1949.7	1941.1	1919.1	1906.7	1886.7	1860.6	1823.1	1794.3	1768.1
10°	2067.5	2074.9	2072.5	2056.5	2040.4	2007.8	1989.2	1952.9	1905.4	1867.9	1832.6
12.5°	2186.9	2194.8	2173.1	2173.8	2143.5	2117.7	2088.4	2042.6	1987.8	1939.3	1895.3
15°	2342.5	2332.6	2332.6	2320.3	2286.3	2250.7	2220.4	2172.4	2103.3	2045.3	1984.3
17.5°	2464.3	2467.7	2462.7	2433.6	2407.0	2370.0	2314.6	2258.5	2194.4	2116.7	2054.2
20°	2537.3	2537.3	2531.7	2512.0	2477.5	2438.0	2378.3	2317.2	2235.9	2157.6	2087.3
22.5°	2566.9	2568.8	2562.3	2546.0	2515.0	2476.5	2425.5	2363.6	2279.7	2191.6	2104.5
25°	2526.2	2537.9	2539.1	2534.8	2525.6	2502.1	2458.4	2394.9	2319.7	2224.1	2130.4
27.5°	2319.3	2334.1	2347.1	2368.4	2396.7	2411.5	2413.5	2381.2	2315.6	2223.7	2129.3
30°	2113.2	2125.5	2165.6	2218.0	2258.6	2295.6	2327.7	2336.3	2299.4	2216.7	2117.5
32.5°	1884.4	1901.1	1941.2	1997.5	2065.3	2128.0	2199.9	2236.7	2235.7	2186.1	2094.3
35°	1555.9	1568.3	1605.3	1664.4	1745.8	1838.9	1952.9	2041.7	2102.0	2097.7	2041.7
37.5°	1254.8	1268.7	1306.1	1355.2	1434.1	1549.3	1659.7	1782.0	1893.7	1956.5	1937.7
40°	1091.1	1091.7	1128.1	1178.7	1252.6	1353.1	1473.3	1608.9	1733.4	1835.1	1854.8
42.5°	961.9	962.0	986.1	1040.5	1093.9	1188.4	1303.1	1437.8	1583.5	1701.0	1753.3
45°	795.2	800.8	820.5	853.2	895.1	975.2	1067.0	1192.2	1355.6	1494.9	1581.8
47.5°	673.4	681.5	694.1	720.8	754.1	807.5	883.5	996.0	1128.8	1282.1	1405.8
50°	610.3	611.5	627.5	642.3	671.3	713.8	780.4	874.1	996.1	1143.5	1280.9
52.5°	556.1	555.8	565.4	584.2	607.7	640.9	694.6	779.9	888.1	1020.2	1162.1
55°	474.7	477.8	485.2	499.9	517.8	541.3	583.8	647.9	733.0	845.8	974.6
57.5°	412.8	414.4	420.2	426.4	442.8	459.9	491.8	536.3	608.1	700.4	820.5
60°	372.3	372.9	374.8	384.1	397.0	413.0	434.6	472.2	532.6	617.1	712.0
62.5°	332.9	333.9	336.8	343.6	353.6	364.7	387.3	417.5	467.5	539.7	625.2
65°	277.4	278.0	282.3	284.8	292.8	302.6	319.3	339.7	374.2	434.6	499.4
67.5°	231.8	231.8	232.0	235.3	240.9	247.4	257.4	273.7	299.7	336.8	393.9
70°	202.2	202.2	203.4	205.3	208.4	213.9	219.5	231.8	250.9	281.1	324.9
72.5°	174.6	175.0	176.3	176.6	178.3	182.8	186.9	194.8	209.0	231.8	267.2
75°	128.2	130.1	133.1	135.6	138.7	138.1	142.4	147.3	151.7	165.2	185.6
77.5°	95.4	94.4	94.8	96.9	97.3	97.9	100.9	104.8	108.0	114.4	121.7
80°	72.8	72.8	74.5	75.2	74.5	75.2	78.3	80.2	81.4	83.8	90.6
82.5°	55.0	56.0	55.4	56.0	56.4	57.0	59.6	59.9	61.2	62.2	65.0
85°	30.9	31.5	32.0	30.9	30.9	30.9	32.0	32.6	33.9	33.3	34.5
87.5°	18.9	18.3	18.6	18.5	18.9	18.2	18.4	19.0	17.7	17.7	17.3
90°	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2	31.4	29.6	27.2
92.5°	59.7	59.3	58.9	58.6	58.2	57.5	56.4	55.4	54.3	53.2	51.5
95°	106.2	106.2	106.2	106.2	106.2	105.8	104.9	104.0	103.1	102.2	100.1
97.5°	166.5	166.5	166.5	166.5	166.5	165.9	164.9	163.8	162.6	161.6	159.2
100°	208.4	208.4	208.4	208.4	208.4	208.1	207.5	206.9	206.3	205.7	203.0
102.5°	255.7	255.5	255.3	255.0	254.8	254.2	253.4	252.5	251.7	250.9	248.4
105°	328.1	327.2	326.3	325.4	324.5	323.6	322.7	321.8	320.9	320.0	318.8
107.5°	398.5	398.6	398.7	398.7	398.8	398.4	397.5	396.7	395.8	395.0	394.8
110°	449.1	448.2	447.3	446.4	445.5	445.3	445.9	446.6	447.1	447.7	448.0



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.7	500.5	500.3	500.2	500.0	500.0	500.1	500.2	500.3	500.4	501.0
115°	580.9	581.1	581.5	581.8	582.0	582.4	582.6	582.9	583.3	583.5	584.2
117.5°	657.2	657.8	658.4	659.0	659.6	660.4	661.5	662.5	663.4	664.5	664.9
120°	715.3	714.7	714.1	713.5	712.9	713.4	714.9	716.3	717.8	719.3	720.2
122.5°	763.8	764.8	765.9	767.0	768.0	769.1	770.1	771.1	772.1	773.1	773.6
125°	847.0	847.7	848.3	848.8	849.4	850.1	850.7	851.2	851.9	852.5	852.7
127.5°	924.3	924.7	925.2	925.7	926.1	926.7	927.3	927.9	928.4	929.1	929.6
130°	974.8	976.0	977.2	978.4	979.5	980.4	981.1	981.7	982.3	982.8	982.8
132.5°	1028.6	1029.0	1029.6	1030.0	1030.5	1031.0	1031.6	1032.2	1032.9	1033.4	1033.7
135°	1102.5	1103.4	1104.3	1105.2	1106.1	1106.9	1107.5	1108.0	1108.7	1109.3	1109.3
137.5°	1180.3	1180.1	1179.9	1179.7	1179.6	1179.8	1180.6	1181.4	1182.1	1182.9	1182.5
140°	1227.6	1227.9	1228.2	1228.5	1228.8	1229.0	1229.4	1229.7	1229.9	1230.3	1230.3
142.5°	1274.9	1275.0	1275.1	1275.1	1275.1	1275.2	1275.2	1275.3	1275.4	1275.4	1275.7
145°	1339.2	1340.1	1341.0	1341.8	1342.7	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1404.3	1404.5	1404.9	1405.2	1405.4	1405.7	1406.0	1406.2	1406.4	1406.7	1406.9
150°	1444.0	1444.4	1444.7	1444.9	1445.3	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1480.6	1481.4	1482.2	1482.9	1483.7	1483.7	1483.0	1482.3	1481.6	1480.9	1480.7
155°	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4	1531.8
157.5°	1576.9	1577.9	1579.0	1579.9	1580.9	1581.0	1580.1	1579.2	1578.3	1577.4	1577.5
160°	1602.7	1604.2	1605.7	1607.2	1608.6	1609.0	1608.1	1607.2	1606.3	1605.4	1605.7
162.5°	1629.6	1631.1	1632.6	1634.1	1635.6	1635.5	1633.9	1632.3	1630.7	1629.1	1629.3
165°	1664.6	1665.7	1667.0	1668.1	1669.4	1669.0	1667.2	1665.4	1663.7	1661.9	1662.5
167.5°	1689.5	1691.4	1693.3	1695.1	1697.0	1697.0	1695.2	1693.4	1691.7	1689.9	1689.8
170°	1703.5	1705.7	1707.7	1709.9	1711.9	1712.1	1710.3	1708.5	1706.6	1704.9	1704.6
172.5°	1715.4	1717.4	1719.6	1721.6	1723.8	1723.8	1721.7	1719.8	1717.7	1715.7	1715.6
175°	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8	1728.0
177.5°	1734.2	1736.2	1738.0	1739.9	1741.9	1742.0	1740.3	1738.7	1737.0	1735.3	1735.3
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1576.4	1569.5	1566.0	1558.1	1548.7	1543.8	1539.4	1532.9	1524.6	1515.7	1509.3
5°	1656.4	1641.6	1623.1	1600.9	1581.2	1562.1	1545.4	1528.7	1509.7	1490.0	1470.3
7.5°	1738.5	1709.4	1677.9	1641.6	1606.2	1574.0	1544.4	1516.1	1484.0	1455.3	1429.1
10°	1795.7	1756.2	1712.4	1666.3	1620.0	1579.9	1540.5	1504.8	1465.3	1430.1	1400.5
12.5°	1842.1	1795.7	1743.0	1685.5	1629.9	1581.4	1536.1	1489.4	1444.6	1406.5	1367.0
15°	1919.0	1855.5	1784.6	1715.6	1643.4	1577.4	1516.4	1462.2	1411.0	1357.5	1319.8
17.5°	1971.8	1896.6	1810.4	1727.4	1642.2	1564.4	1494.0	1429.4	1370.4	1315.6	1270.9
20°	2003.4	1920.2	1824.7	1730.4	1634.8	1551.6	1475.8	1404.3	1343.3	1284.1	1237.8
22.5°	2021.2	1929.1	1824.7	1725.9	1626.9	1536.8	1453.6	1379.1	1312.7	1253.5	1202.3
25°	2026.9	1928.2	1821.6	1708.2	1599.6	1504.1	1417.8	1337.0	1263.1	1203.9	1149.7
27.5°	2019.0	1902.8	1793.6	1677.2	1565.3	1464.5	1373.9	1289.1	1215.0	1151.6	1095.9
30°	2007.2	1882.6	1765.5	1644.7	1531.2	1434.5	1338.9	1257.6	1180.4	1114.5	1058.5
32.5°	1981.5	1858.0	1732.0	1608.2	1493.3	1393.6	1302.9	1221.0	1145.5	1078.1	1018.5
35°	1930.7	1805.5	1668.7	1541.8	1428.9	1325.3	1240.3	1161.4	1089.2	1017.2	954.2
37.5°	1863.8	1735.9	1599.8	1460.7	1347.8	1250.0	1172.0	1097.9	1027.5	961.6	892.0
40°	1800.6	1684.1	1543.6	1405.5	1289.6	1195.2	1123.2	1056.0	985.1	919.7	850.1
42.5°	1724.2	1625.0	1482.9	1344.3	1229.9	1139.1	1071.8	1006.1	941.6	878.3	805.7
45°	1596.6	1521.3	1388.2	1255.1	1139.8	1049.8	988.2	930.2	873.5	813.1	744.7
47.5°	1450.4	1399.5	1284.5	1148.2	1041.5	960.6	901.0	853.6	805.7	745.3	685.3
50°	1348.8	1316.1	1205.1	1080.7	978.9	904.3	843.3	798.9	758.8	700.9	647.3
52.5°	1240.3	1222.9	1129.2	1010.1	911.9	838.7	786.6	746.6	706.1	658.0	607.8
55°	1075.0	1084.3	1004.8	901.9	809.4	747.8	700.3	667.0	632.5	591.8	552.9
57.5°	906.2	940.0	886.5	796.2	709.5	652.6	616.8	588.8	559.8	526.1	492.9
60°	805.0	833.4	803.3	723.7	647.9	594.9	561.6	540.0	511.0	480.2	455.0
62.5°	706.4	736.7	718.9	654.7	584.2	538.7	509.3	489.2	467.6	440.8	414.5
65°	582.6	602.3	593.6	549.3	499.4	460.5	433.4	418.6	398.9	379.2	355.7
67.5°	446.2	484.3	479.2	455.7	412.5	382.2	364.4	351.3	333.4	318.7	302.8
70°	366.8	401.9	401.3	382.2	358.7	330.4	318.1	307.0	291.0	276.8	263.9
72.5°	300.2	332.4	337.2	322.5	306.5	285.1	273.2	265.6	250.0	240.3	229.8
75°	210.2	233.6	239.8	239.8	232.4	221.3	210.8	205.9	194.8	186.2	180.0
77.5°	137.9	152.7	162.3	164.4	165.6	161.8	153.3	149.8	141.2	138.2	132.3
80°	97.4	107.3	118.3	122.1	125.1	123.9	120.2	117.7	109.8	106.6	104.2
82.5°	67.3	72.8	81.9	90.0	89.2	92.4	89.2	87.2	81.1	80.0	77.6
85°	35.1	35.8	37.0	42.5	45.7	46.8	47.4	46.2	44.4	44.4	40.0
87.5°	16.8	15.8	16.3	15.8	15.6	16.9	17.7	17.6	16.8	16.0	15.1
90°	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0	7.3	10.6	13.9
92.5°	49.9	48.2	46.5	43.9	40.0	36.3	32.5	28.8	32.5	36.3	40.0
95°	98.0	95.9	93.8	91.4	88.7	86.1	83.4	80.7	83.4	86.1	88.7
97.5°	156.7	154.3	151.9	149.5	147.4	145.2	143.0	140.9	143.0	145.2	147.4
100°	200.4	197.7	194.9	193.1	191.8	190.6	189.4	188.2	189.4	190.6	191.8
102.5°	246.0	243.5	241.1	239.6	239.2	238.7	238.2	237.7	238.2	238.7	239.2
105°	317.6	316.4	315.2	314.5	314.1	313.9	313.6	313.3	313.6	313.9	314.1
107.5°	394.7	394.5	394.3	394.0	393.7	393.3	393.0	392.6	393.0	393.3	393.7
110°	448.4	448.6	449.0	448.8	448.2	447.5	447.0	446.4	447.0	447.5	448.2





TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	501.5	502.0	502.6	502.8	502.7	502.6	502.5	502.3	502.5	502.6	502.7
115°	584.7	585.3	585.9	586.2	586.2	586.2	586.2	586.2	586.2	586.2	586.2
117.5°	665.3	665.8	666.2	666.3	666.0	665.8	665.5	665.3	665.5	665.8	666.0
120°	721.1	722.0	722.9	722.7	721.6	720.4	719.2	718.0	719.2	720.4	721.6
122.5°	773.9	774.4	774.8	774.7	774.3	773.8	773.3	772.8	773.3	773.8	774.3
125°	853.0	853.4	853.6	853.8	853.8	853.8	853.8	853.8	853.8	853.8	853.8
127.5°	930.1	930.5	931.0	930.8	929.9	929.0	928.1	927.2	928.1	929.0	929.9
130°	982.8	982.8	982.8	982.4	981.5	980.6	979.7	978.8	979.7	980.6	981.5
132.5°	1033.9	1034.1	1034.4	1034.2	1033.5	1032.9	1032.2	1031.5	1032.2	1032.9	1033.5
135°	1109.3	1109.3	1109.3	1108.4	1106.6	1104.7	1103.0	1101.2	1103.0	1104.7	1106.6
137.5°	1182.0	1181.5	1181.1	1180.4	1179.6	1178.7	1177.9	1177.1	1177.9	1178.7	1179.6
140°	1230.3	1230.3	1230.3	1229.9	1229.4	1228.8	1228.2	1227.6	1228.2	1228.8	1229.4
142.5°	1275.9	1276.1	1276.4	1276.2	1275.6	1275.1	1274.4	1273.8	1274.4	1275.1	1275.6
145°	1344.0	1343.6	1343.4	1342.6	1341.4	1340.2	1339.0	1337.8	1339.0	1340.2	1341.4
147.5°	1407.1	1407.4	1407.7	1407.0	1405.6	1404.2	1402.8	1401.3	1402.8	1404.2	1405.6
150°	1445.4	1445.4	1445.4	1444.8	1443.6	1442.4	1441.2	1440.0	1441.2	1442.4	1443.6
152.5°	1480.4	1480.2	1480.0	1479.4	1478.7	1478.0	1477.3	1476.6	1477.3	1478.0	1478.7
155°	1532.0	1532.3	1532.7	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8
157.5°	1577.5	1577.6	1577.7	1578.0	1578.5	1579.0	1579.6	1580.1	1579.6	1579.0	1578.5
160°	1606.0	1606.3	1606.6	1606.9	1607.2	1607.5	1607.8	1608.1	1607.8	1607.5	1607.2
162.5°	1629.7	1630.0	1630.2	1630.8	1631.6	1632.4	1633.2	1633.9	1633.2	1632.4	1631.6
165°	1663.0	1663.7	1664.3	1665.0	1665.9	1666.8	1667.7	1668.6	1667.7	1666.8	1665.9
167.5°	1689.7	1689.7	1689.6	1690.2	1691.5	1692.7	1694.0	1695.2	1694.0	1692.7	1691.5
170°	1704.3	1704.0	1703.7	1704.3	1705.8	1707.3	1708.8	1710.3	1708.8	1707.3	1705.8
172.5°	1715.6	1715.5	1715.4	1716.0	1717.3	1718.5	1719.8	1721.0	1719.8	1718.5	1717.3
175°	1728.3	1728.7	1728.9	1729.8	1731.3	1732.9	1734.3	1735.8	1734.3	1732.9	1731.3
177.5°	1735.3	1735.3	1735.3	1735.9	1737.1	1738.3	1739.5	1740.6	1739.5	1738.3	1737.1
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1502.4	1497.4	1491.0	1483.6	1474.8	1466.9	1463.5	1466.4	1467.8	1463.9	1463.5
5°	1456.7	1441.3	1428.9	1410.4	1395.6	1383.3	1374.7	1371.0	1372.2	1362.4	1359.9
7.5°	1405.2	1387.0	1366.8	1344.8	1324.4	1306.3	1296.7	1291.6	1281.1	1276.7	1269.2
10°	1372.2	1347.6	1327.8	1301.9	1278.5	1257.0	1246.4	1237.8	1227.4	1222.4	1211.9
12.5°	1338.2	1309.6	1287.9	1261.0	1237.1	1211.0	1201.0	1185.1	1168.7	1158.3	1144.9
15°	1290.2	1255.7	1229.2	1197.1	1168.8	1139.2	1112.7	1083.1	1072.0	1048.6	1035.0
17.5°	1234.1	1199.1	1166.3	1123.3	1079.5	1042.8	1014.5	986.1	969.2	954.2	947.4
20°	1197.1	1165.1	1119.5	1069.5	1020.8	980.2	957.3	938.9	920.3	909.9	902.5
22.5°	1162.1	1121.1	1068.2	1014.3	965.6	933.8	914.4	895.5	880.4	870.4	860.6
25°	1103.4	1049.8	993.7	932.1	898.8	871.0	850.1	834.6	825.5	812.4	807.5
27.5°	1043.1	978.2	916.3	874.9	840.2	814.8	796.6	785.0	773.3	765.0	758.6
30°	996.8	930.9	875.4	835.9	800.8	779.8	765.0	751.4	742.2	735.4	730.5
32.5°	950.9	884.9	838.4	795.9	768.2	747.8	732.0	721.8	714.6	705.8	702.8
35°	884.6	826.0	785.3	747.2	718.8	700.3	688.0	677.4	671.3	668.9	667.0
37.5°	820.8	772.9	729.2	697.9	672.5	658.0	643.5	638.3	634.1	629.6	631.6
40°	780.4	735.4	696.6	663.3	642.9	627.0	618.3	612.2	608.4	608.4	608.4
42.5°	745.4	701.4	663.5	633.7	613.3	599.8	590.2	585.0	583.8	583.3	586.2
45°	691.1	650.3	612.2	587.5	570.2	556.6	551.1	546.8	546.8	549.3	549.8
47.5°	637.1	599.1	568.4	540.7	525.0	516.5	511.7	509.4	509.7	512.1	515.0
50°	604.1	566.5	536.3	511.7	496.9	488.8	484.6	483.3	484.6	484.6	488.8
52.5°	568.1	534.5	504.7	484.0	467.3	459.8	457.4	455.7	456.4	458.4	460.2
55°	515.3	485.2	456.8	437.0	424.7	419.8	414.3	414.8	413.7	414.8	414.8
57.5°	462.4	435.3	408.9	393.3	382.5	375.3	369.3	371.0	369.2	368.9	367.9
60°	428.5	398.9	377.9	363.7	351.3	345.2	339.7	340.9	339.0	337.8	335.4
62.5°	391.5	366.8	346.8	333.1	323.2	316.1	310.6	309.3	305.1	300.9	295.4
65°	337.8	317.4	299.6	286.7	277.4	271.9	267.5	263.9	254.6	244.7	239.8
67.5°	285.7	271.0	254.3	243.3	235.9	228.5	220.3	214.0	205.4	200.0	196.9
70°	252.1	237.9	223.7	213.3	205.3	198.5	189.2	184.9	178.8	176.3	173.3
72.5°	220.1	206.9	193.7	184.2	175.7	170.4	163.1	158.8	156.0	155.1	152.0
75°	171.4	160.9	151.1	142.4	135.6	131.9	128.9	125.7	124.5	119.0	115.9
77.5°	125.0	118.2	111.9	105.8	100.9	98.5	92.6	89.0	86.9	84.4	83.7
80°	97.4	92.5	86.3	82.6	75.8	73.4	70.9	70.3	69.6	69.0	68.4
82.5°	73.2	68.3	62.2	59.9	58.1	56.6	55.1	54.5	53.9	54.2	54.1
85°	37.0	34.5	34.5	33.9	33.3	32.6	32.0	32.0	31.5	32.0	31.5
87.5°	15.8	15.9	16.3	15.8	16.8	17.3	17.1	17.5	18.4	17.7	17.9
90°	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2	35.0	36.7	38.0
92.5°	43.9	46.5	48.2	49.9	51.5	53.2	54.3	55.4	56.4	57.5	58.2
95°	91.4	93.8	95.9	98.0	100.1	102.2	103.1	104.0	104.9	105.8	106.2
97.5°	149.5	151.9	154.3	156.7	159.2	161.6	162.6	163.8	164.9	165.9	166.5
100°	193.1	194.9	197.7	200.4	203.0	205.7	206.3	206.9	207.5	208.1	208.4
102.5°	239.6	241.1	243.5	246.0	248.4	250.9	251.7	252.5	253.4	254.2	254.8
105°	314.5	315.2	316.4	317.6	318.8	320.0	320.9	321.8	322.7	323.6	324.5
107.5°	394.0	394.3	394.5	394.7	394.8	395.0	395.8	396.7	397.5	398.4	398.8
110°	448.8	449.0	448.6	448.4	448.0	447.7	447.1	446.6	445.9	445.3	445.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	502.8	502.6	502.0	501.5	501.0	500.4	500.3	500.2	500.1	500.0	500.0
115°	586.2	585.9	585.3	584.7	584.2	583.5	583.3	582.9	582.6	582.4	582.0
117.5°	666.3	666.2	665.8	665.3	664.9	664.5	663.4	662.5	661.5	660.4	659.6
120°	722.7	722.9	722.0	721.1	720.2	719.3	717.8	716.3	714.9	713.4	712.9
122.5°	774.7	774.8	774.4	773.9	773.6	773.1	772.1	771.1	770.1	769.1	768.0
125°	853.8	853.6	853.4	853.0	852.7	852.5	851.9	851.2	850.7	850.1	849.4
127.5°	930.8	931.0	930.5	930.1	929.6	929.1	928.4	927.9	927.3	926.7	926.1
130°	982.4	982.8	982.8	982.8	982.8	982.8	982.3	981.7	981.1	980.4	979.5
132.5°	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9	1032.2	1031.6	1031.0	1030.5
135°	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7	1108.0	1107.5	1106.9	1106.1
137.5°	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1	1181.4	1180.6	1179.8	1179.6
140°	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.7	1229.4	1229.0	1228.8
142.5°	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4	1275.3	1275.2	1275.2	1275.1
145°	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3	1344.0	1343.6	1343.4	1342.7
147.5°	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4	1406.2	1406.0	1405.7	1405.4
150°	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.3
152.5°	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6	1482.3	1483.0	1483.7	1483.7
155°	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2
157.5°	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3	1579.2	1580.1	1581.0	1580.9
160°	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3	1607.2	1608.1	1609.0	1608.6
162.5°	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7	1632.3	1633.9	1635.5	1635.6
165°	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7	1665.4	1667.2	1669.0	1669.4
167.5°	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7	1693.4	1695.2	1697.0	1697.0
170°	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6	1708.5	1710.3	1712.1	1711.9
172.5°	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7	1719.8	1721.7	1723.8	1723.8
175°	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2
177.5°	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0	1738.7	1740.3	1742.0	1741.9
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1460.4	1461.4	1458.0	1457.1	1458.0	1461.4	1460.4	1463.5	1463.9	1467.8	1466.4
5°	1355.0	1353.7	1350.6	1351.2	1350.6	1353.7	1355.0	1359.9	1362.4	1372.2	1371.0
7.5°	1264.7	1259.9	1261.2	1256.3	1261.2	1259.9	1264.7	1269.2	1276.7	1281.1	1291.6
10°	1209.4	1202.7	1197.1	1192.2	1197.1	1202.7	1209.4	1211.9	1222.4	1227.4	1237.8
12.5°	1134.0	1128.2	1120.7	1122.2	1120.7	1128.2	1134.0	1144.9	1158.3	1168.7	1185.1
15°	1027.0	1017.7	1003.0	1004.8	1003.0	1017.7	1027.0	1035.0	1048.6	1072.0	1083.1
17.5°	936.4	936.5	929.7	931.3	929.7	936.5	936.4	947.4	954.2	969.2	986.1
20°	889.6	885.2	885.8	884.0	885.8	885.2	889.6	902.5	909.9	920.3	938.9
22.5°	857.0	851.7	847.4	843.6	847.4	851.7	857.0	860.6	870.4	880.4	895.5
25°	802.0	798.3	792.7	791.5	792.7	798.3	802.0	807.5	812.4	825.5	834.6
27.5°	753.7	753.0	750.7	747.9	750.7	753.0	753.7	758.6	765.0	773.3	785.0
30°	725.6	724.3	723.1	721.2	723.1	724.3	725.6	730.5	735.4	742.2	751.4
32.5°	700.4	699.6	698.4	698.6	698.4	699.6	700.4	702.8	705.8	714.6	721.8
35°	664.5	663.9	662.7	662.1	662.7	663.9	664.5	667.0	668.9	671.3	677.4
37.5°	631.0	632.6	631.9	631.7	631.9	632.6	631.0	631.6	629.6	634.1	638.3
40°	607.8	608.4	609.7	609.0	609.7	608.4	607.8	608.4	608.4	608.4	612.2
42.5°	588.6	588.7	590.4	588.4	590.4	588.7	588.6	586.2	583.3	583.8	585.0
45°	554.2	557.9	557.2	557.2	557.2	557.9	554.2	549.8	549.3	546.8	546.8
47.5°	516.6	519.8	520.7	520.5	520.7	519.8	516.6	515.0	512.1	509.7	509.4
50°	492.0	490.7	492.6	492.0	492.6	490.7	492.0	488.8	484.6	484.6	483.3
52.5°	461.8	462.1	462.0	461.4	462.0	462.1	461.8	460.2	458.4	456.4	455.7
55°	415.4	416.1	414.8	415.4	414.8	416.1	415.4	414.8	414.8	413.7	414.8
57.5°	365.2	362.2	363.5	361.9	363.5	362.2	365.2	367.9	368.9	369.2	371.0
60°	329.2	324.2	323.0	320.6	323.0	324.2	329.2	335.4	337.8	339.0	340.9
62.5°	288.7	285.3	281.1	283.0	281.1	285.3	288.7	295.4	300.9	305.1	309.3
65°	234.9	232.4	230.5	233.0	230.5	232.4	234.9	239.8	244.7	254.6	263.9
67.5°	194.4	193.1	193.1	191.8	193.1	193.1	194.4	196.9	200.0	205.4	214.0
70°	173.3	171.4	171.4	170.1	171.4	171.4	173.3	173.3	176.3	178.8	184.9
72.5°	151.5	149.6	150.2	149.5	150.2	149.6	151.5	152.0	155.1	156.0	158.8
75°	112.2	109.1	109.1	109.8	109.1	109.1	112.2	115.9	119.0	124.5	125.7
77.5°	83.7	83.1	84.0	82.8	84.0	83.1	83.7	83.7	84.4	86.9	89.0
80°	68.4	67.8	67.2	69.0	67.2	67.8	68.4	68.4	69.0	69.6	70.3
82.5°	53.1	53.1	52.9	55.2	52.9	53.1	53.1	54.1	54.2	53.9	54.5
85°	32.0	30.9	32.0	30.9	32.0	30.9	32.0	31.5	32.0	31.5	32.0
87.5°	19.1	18.6	18.3	18.9	18.3	18.6	19.1	17.9	17.7	18.4	17.5
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2
92.5°	58.6	58.9	59.3	59.7	59.3	58.9	58.6	58.2	57.5	56.4	55.4
95°	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	105.8	104.9	104.0
97.5°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	165.9	164.9	163.8
100°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.1	207.5	206.9
102.5°	255.0	255.3	255.5	255.7	255.5	255.3	255.0	254.8	254.2	253.4	252.5
105°	325.4	326.3	327.2	328.1	327.2	326.3	325.4	324.5	323.6	322.7	321.8
107.5°	398.7	398.7	398.6	398.5	398.6	398.7	398.7	398.8	398.4	397.5	396.7
110°	446.4	447.3	448.2	449.1	448.2	447.3	446.4	445.5	445.3	445.9	446.6



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	500.2	500.3	500.5	500.7	500.5	500.3	500.2	500.0	500.0	500.1	500.2
115°	581.8	581.5	581.1	580.9	581.1	581.5	581.8	582.0	582.4	582.6	582.9
117.5°	659.0	658.4	657.8	657.2	657.8	658.4	659.0	659.6	660.4	661.5	662.5
120°	713.5	714.1	714.7	715.3	714.7	714.1	713.5	712.9	713.4	714.9	716.3
122.5°	767.0	765.9	764.8	763.8	764.8	765.9	767.0	768.0	769.1	770.1	771.1
125°	848.8	848.3	847.7	847.0	847.7	848.3	848.8	849.4	850.1	850.7	851.2
127.5°	925.7	925.2	924.7	924.3	924.7	925.2	925.7	926.1	926.7	927.3	927.9
130°	978.4	977.2	976.0	974.8	976.0	977.2	978.4	979.5	980.4	981.1	981.7
132.5°	1030.0	1029.6	1029.0	1028.6	1029.0	1029.6	1030.0	1030.5	1031.0	1031.6	1032.2
135°	1105.2	1104.3	1103.4	1102.5	1103.4	1104.3	1105.2	1106.1	1106.9	1107.5	1108.0
137.5°	1179.7	1179.9	1180.1	1180.3	1180.1	1179.9	1179.7	1179.6	1179.8	1180.6	1181.4
140°	1228.5	1228.2	1227.9	1227.6	1227.9	1228.2	1228.5	1228.8	1229.0	1229.4	1229.7
142.5°	1275.1	1275.1	1275.0	1274.9	1275.0	1275.1	1275.1	1275.1	1275.2	1275.2	1275.3
145°	1341.8	1341.0	1340.1	1339.2	1340.1	1341.0	1341.8	1342.7	1343.4	1343.6	1344.0
147.5°	1405.2	1404.9	1404.5	1404.3	1404.5	1404.9	1405.2	1405.4	1405.7	1406.0	1406.2
150°	1444.9	1444.7	1444.4	1444.0	1444.4	1444.7	1444.9	1445.3	1445.4	1445.4	1445.4
152.5°	1482.9	1482.2	1481.4	1480.6	1481.4	1482.2	1482.9	1483.7	1483.7	1483.0	1482.3
155°	1535.0	1533.8	1532.7	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8
157.5°	1579.9	1579.0	1577.9	1576.9	1577.9	1579.0	1579.9	1580.9	1581.0	1580.1	1579.2
160°	1607.2	1605.7	1604.2	1602.7	1604.2	1605.7	1607.2	1608.6	1609.0	1608.1	1607.2
162.5°	1634.1	1632.6	1631.1	1629.6	1631.1	1632.6	1634.1	1635.6	1635.5	1633.9	1632.3
165°	1668.1	1667.0	1665.7	1664.6	1665.7	1667.0	1668.1	1669.4	1669.0	1667.2	1665.4
167.5°	1695.1	1693.3	1691.4	1689.5	1691.4	1693.3	1695.1	1697.0	1697.0	1695.2	1693.4
170°	1709.9	1707.7	1705.7	1703.5	1705.7	1707.7	1709.9	1711.9	1712.1	1710.3	1708.5
172.5°	1721.6	1719.6	1717.4	1715.4	1717.4	1719.6	1721.6	1723.8	1723.8	1721.7	1719.8
175°	1734.0	1732.0	1729.8	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0
177.5°	1739.9	1738.0	1736.2	1734.2	1736.2	1738.0	1739.9	1741.9	1742.0	1740.3	1738.7
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1463.5	1466.9	1474.8	1483.6	1491.0	1497.4	1502.4	1509.3	1515.7	1524.6	1532.9
5°	1374.7	1383.3	1395.6	1410.4	1428.9	1441.3	1456.7	1470.3	1490.0	1509.7	1528.7
7.5°	1296.7	1306.3	1324.4	1344.8	1366.8	1387.0	1405.2	1429.1	1455.3	1484.0	1516.1
10°	1246.4	1257.0	1278.5	1301.9	1327.8	1347.6	1372.2	1400.5	1430.1	1465.3	1504.8
12.5°	1201.0	1211.0	1237.1	1261.0	1287.9	1309.6	1338.2	1367.0	1406.5	1444.6	1489.4
15°	1112.7	1139.2	1168.8	1197.1	1229.2	1255.7	1290.2	1319.8	1357.5	1411.0	1462.2
17.5°	1014.5	1042.8	1079.5	1123.3	1166.3	1199.1	1234.1	1270.9	1315.6	1370.4	1429.4
20°	957.3	980.2	1020.8	1069.5	1119.5	1165.1	1197.1	1237.8	1284.1	1343.3	1404.3
22.5°	914.4	933.8	965.6	1014.3	1068.2	1121.1	1162.1	1202.3	1253.5	1312.7	1379.1
25°	850.1	871.0	898.8	932.1	993.7	1049.8	1103.4	1149.7	1203.9	1263.1	1337.0
27.5°	796.6	814.8	840.2	874.9	916.3	978.2	1043.1	1095.9	1151.6	1215.0	1289.1
30°	765.0	779.8	800.8	835.9	875.4	930.9	996.8	1058.5	1114.5	1180.4	1257.6
32.5°	732.0	747.8	768.2	795.9	838.4	884.9	950.9	1018.5	1078.1	1145.5	1221.0
35°	688.0	700.3	718.8	747.2	785.3	826.0	884.6	954.2	1017.2	1089.2	1161.4
37.5°	643.5	658.0	672.5	697.9	729.2	772.9	820.8	892.0	961.6	1027.5	1097.9
40°	618.3	627.0	642.9	663.3	696.6	735.4	780.4	850.1	919.7	985.1	1056.0
42.5°	590.2	599.8	613.3	633.7	663.5	701.4	745.4	805.7	878.3	941.6	1006.1
45°	551.1	556.6	570.2	587.5	612.2	650.3	691.1	744.7	813.1	873.5	930.2
47.5°	511.7	516.5	525.0	540.7	568.4	599.1	637.1	685.3	745.3	805.7	853.6
50°	484.6	488.8	496.9	511.7	536.3	566.5	604.1	647.3	700.9	758.8	798.9
52.5°	457.4	459.8	467.3	484.0	504.7	534.5	568.1	607.8	658.0	706.1	746.6
55°	414.3	419.8	424.7	437.0	456.8	485.2	515.3	552.9	591.8	632.5	667.0
57.5°	369.3	375.3	382.5	393.3	408.9	435.3	462.4	492.9	526.1	559.8	588.8
60°	339.7	345.2	351.3	363.7	377.9	398.9	428.5	455.0	480.2	511.0	540.0
62.5°	310.6	316.1	323.2	333.1	346.8	366.8	391.5	414.5	440.8	467.6	489.2
65°	267.5	271.9	277.4	286.7	299.6	317.4	337.8	355.7	379.2	398.9	418.6
67.5°	220.3	228.5	235.9	243.3	254.3	271.0	285.7	302.8	318.7	333.4	351.3
70°	189.2	198.5	205.3	213.3	223.7	237.9	252.1	263.9	276.8	291.0	307.0
72.5°	163.1	170.4	175.7	184.2	193.7	206.9	220.1	229.8	240.3	250.0	265.6
75°	128.9	131.9	135.6	142.4	151.1	160.9	171.4	180.0	186.2	194.8	205.9
77.5°	92.6	98.5	100.9	105.8	111.9	118.2	125.0	132.3	138.2	141.2	149.8
80°	70.9	73.4	75.8	82.6	86.3	92.5	97.4	104.2	106.6	109.8	117.7
82.5°	55.1	56.6	58.1	59.9	62.2	68.3	73.2	77.6	80.0	81.1	87.2
85°	32.0	32.6	33.3	33.9	34.5	34.5	37.0	40.0	44.4	44.4	46.2
87.5°	17.1	17.3	16.8	15.8	16.3	15.9	15.8	15.1	16.0	16.8	17.6
90°	31.4	29.6	27.2	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0
92.5°	54.3	53.2	51.5	49.9	48.2	46.5	43.9	40.0	36.3	32.5	28.8
95°	103.1	102.2	100.1	98.0	95.9	93.8	91.4	88.7	86.1	83.4	80.7
97.5°	162.6	161.6	159.2	156.7	154.3	151.9	149.5	147.4	145.2	143.0	140.9
100°	206.3	205.7	203.0	200.4	197.7	194.9	193.1	191.8	190.6	189.4	188.2
102.5°	251.7	250.9	248.4	246.0	243.5	241.1	239.6	239.2	238.7	238.2	237.7
105°	320.9	320.0	318.8	317.6	316.4	315.2	314.5	314.1	313.9	313.6	313.3
107.5°	395.8	395.0	394.8	394.7	394.5	394.3	394.0	393.7	393.3	393.0	392.6
110°	447.1	447.7	448.0	448.4	448.6	449.0	448.8	448.2	447.5	447.0	446.4



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.3	500.4	501.0	501.5	502.0	502.6	502.8	502.7	502.6	502.5	502.3
115°	583.3	583.5	584.2	584.7	585.3	585.9	586.2	586.2	586.2	586.2	586.2
117.5°	663.4	664.5	664.9	665.3	665.8	666.2	666.3	666.0	665.8	665.5	665.3
120°	717.8	719.3	720.2	721.1	722.0	722.9	722.7	721.6	720.4	719.2	718.0
122.5°	772.1	773.1	773.6	773.9	774.4	774.8	774.7	774.3	773.8	773.3	772.8
125°	851.9	852.5	852.7	853.0	853.4	853.6	853.8	853.8	853.8	853.8	853.8
127.5°	928.4	929.1	929.6	930.1	930.5	931.0	930.8	929.9	929.0	928.1	927.2
130°	982.3	982.8	982.8	982.8	982.8	982.8	982.4	981.5	980.6	979.7	978.8
132.5°	1032.9	1033.4	1033.7	1033.9	1034.1	1034.4	1034.2	1033.5	1032.9	1032.2	1031.5
135°	1108.7	1109.3	1109.3	1109.3	1109.3	1109.3	1108.4	1106.6	1104.7	1103.0	1101.2
137.5°	1182.1	1182.9	1182.5	1182.0	1181.5	1181.1	1180.4	1179.6	1178.7	1177.9	1177.1
140°	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.4	1228.8	1228.2	1227.6
142.5°	1275.4	1275.4	1275.7	1275.9	1276.1	1276.4	1276.2	1275.6	1275.1	1274.4	1273.8
145°	1344.3	1344.5	1344.3	1344.0	1343.6	1343.4	1342.6	1341.4	1340.2	1339.0	1337.8
147.5°	1406.4	1406.7	1406.9	1407.1	1407.4	1407.7	1407.0	1405.6	1404.2	1402.8	1401.3
150°	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1444.8	1443.6	1442.4	1441.2	1440.0
152.5°	1481.6	1480.9	1480.7	1480.4	1480.2	1480.0	1479.4	1478.7	1478.0	1477.3	1476.6
155°	1532.7	1531.4	1531.8	1532.0	1532.3	1532.7	1532.8	1532.8	1532.8	1532.8	1532.8
157.5°	1578.3	1577.4	1577.5	1577.5	1577.6	1577.7	1578.0	1578.5	1579.0	1579.6	1580.1
160°	1606.3	1605.4	1605.7	1606.0	1606.3	1606.6	1606.9	1607.2	1607.5	1607.8	1608.1
162.5°	1630.7	1629.1	1629.3	1629.7	1630.0	1630.2	1630.8	1631.6	1632.4	1633.2	1633.9
165°	1663.7	1661.9	1662.5	1663.0	1663.7	1664.3	1665.0	1665.9	1666.8	1667.7	1668.6
167.5°	1691.7	1689.9	1689.8	1689.7	1689.7	1689.6	1690.2	1691.5	1692.7	1694.0	1695.2
170°	1706.6	1704.9	1704.6	1704.3	1704.0	1703.7	1704.3	1705.8	1707.3	1708.8	1710.3
172.5°	1717.7	1715.7	1715.6	1715.6	1715.5	1715.4	1716.0	1717.3	1718.5	1719.8	1721.0
175°	1729.8	1727.8	1728.0	1728.3	1728.7	1728.9	1729.8	1731.3	1732.9	1734.3	1735.8
177.5°	1737.0	1735.3	1735.3	1735.3	1735.3	1735.3	1735.9	1737.1	1738.3	1739.5	1740.6
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1539.4	1543.8	1548.7	1558.1	1566.0	1569.5	1576.4	1581.3	1579.8	1586.7	1598.6
5°	1545.4	1562.1	1581.2	1600.9	1623.1	1641.6	1656.4	1671.2	1682.9	1697.1	1718.1
7.5°	1544.4	1574.0	1606.2	1641.6	1677.9	1709.4	1738.5	1768.1	1794.3	1823.1	1860.6
10°	1540.5	1579.9	1620.0	1666.3	1712.4	1756.2	1795.7	1832.6	1867.9	1905.4	1952.9
12.5°	1536.1	1581.4	1629.9	1685.5	1743.0	1795.7	1842.1	1895.3	1939.3	1987.8	2042.6
15°	1516.4	1577.4	1643.4	1715.6	1784.6	1855.5	1919.0	1984.3	2045.3	2103.3	2172.4
17.5°	1494.0	1564.4	1642.2	1727.4	1810.4	1896.6	1971.8	2054.2	2116.7	2194.4	2258.5
20°	1475.8	1551.6	1634.8	1730.4	1824.7	1920.2	2003.4	2087.3	2157.6	2235.9	2317.2
22.5°	1453.6	1536.8	1626.9	1725.9	1824.7	1929.1	2021.2	2104.5	2191.6	2279.7	2363.6
25°	1417.8	1504.1	1599.6	1708.2	1821.6	1928.2	2026.9	2130.4	2224.1	2319.7	2394.9
27.5°	1373.9	1464.5	1565.3	1677.2	1793.6	1902.8	2019.0	2129.3	2223.7	2315.6	2381.2
30°	1338.9	1434.5	1531.2	1644.7	1765.5	1882.6	2007.2	2117.5	2216.7	2299.4	2336.3
32.5°	1302.9	1393.6	1493.3	1608.2	1732.0	1858.0	1981.5	2094.3	2186.1	2235.7	2236.7
35°	1240.3	1325.3	1428.9	1541.8	1668.7	1805.5	1930.7	2041.7	2097.7	2102.0	2041.7
37.5°	1172.0	1250.0	1347.8	1460.7	1599.8	1735.9	1863.8	1937.7	1956.5	1893.7	1782.0
40°	1123.2	1195.2	1289.6	1405.5	1543.6	1684.1	1800.6	1854.8	1835.1	1733.4	1608.9
42.5°	1071.8	1139.1	1229.9	1344.3	1482.9	1625.0	1724.2	1753.3	1701.0	1583.5	1437.8
45°	988.2	1049.8	1139.8	1255.1	1388.2	1521.3	1596.6	1581.8	1494.9	1355.6	1192.2
47.5°	901.0	960.6	1041.5	1148.2	1284.5	1399.5	1450.4	1405.8	1282.1	1128.8	996.0
50°	843.3	904.3	978.9	1080.7	1205.1	1316.1	1348.8	1280.9	1143.5	996.1	874.1
52.5°	786.6	838.7	911.9	1010.1	1129.2	1222.9	1240.3	1162.1	1020.2	888.1	779.9
55°	700.3	747.8	809.4	901.9	1004.8	1084.3	1075.0	974.6	845.8	733.0	647.9
57.5°	616.8	652.6	709.5	796.2	886.5	940.0	906.2	820.5	700.4	608.1	536.3
60°	561.6	594.9	647.9	723.7	803.3	833.4	805.0	712.0	617.1	532.6	472.2
62.5°	509.3	538.7	584.2	654.7	718.9	736.7	706.4	625.2	539.7	467.5	417.5
65°	433.4	460.5	499.4	549.3	593.6	602.3	582.6	499.4	434.6	374.2	339.7
67.5°	364.4	382.2	412.5	455.7	479.2	484.3	446.2	393.9	336.8	299.7	273.7
70°	318.1	330.4	358.7	382.2	401.3	401.9	366.8	324.9	281.1	250.9	231.8
72.5°	273.2	285.1	306.5	322.5	337.2	332.4	300.2	267.2	231.8	209.0	194.8
75°	210.8	221.3	232.4	239.8	239.8	233.6	210.2	185.6	165.2	151.7	147.3
77.5°	153.3	161.8	165.6	164.4	162.3	152.7	137.9	121.7	114.4	108.0	104.8
80°	120.2	123.9	125.1	122.1	118.3	107.3	97.4	90.6	83.8	81.4	80.2
82.5°	89.2	92.4	89.2	90.0	81.9	72.8	67.3	65.0	62.2	61.2	59.9
85°	47.4	46.8	45.7	42.5	37.0	35.8	35.1	34.5	33.3	33.9	32.6
87.5°	17.7	16.9	15.6	15.8	16.3	15.8	16.8	17.3	17.7	17.7	19.0
90°	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2
92.5°	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3	55.4
95°	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1	104.0
97.5°	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6	163.8
100°	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3	206.9
102.5°	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7	252.5
105°	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9	321.8
107.5°	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8	396.7
110°	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1	446.6





TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3	500.2
115°	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3	582.9
117.5°	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4	662.5
120°	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8	716.3
122.5°	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1	771.1
125°	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9	851.2
127.5°	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4	927.9
130°	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3	981.7
132.5°	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9	1032.2
135°	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7	1108.0
137.5°	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1	1181.4
140°	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.7
142.5°	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4	1275.3
145°	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3	1344.0
147.5°	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4	1406.2
150°	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6	1482.3
155°	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7	1533.8
157.5°	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3	1579.2
160°	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3	1607.2
162.5°	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7	1632.3
165°	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7	1665.4
167.5°	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7	1693.4
170°	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6	1708.5
172.5°	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7	1719.8
175°	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8	1732.0
177.5°	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0	1738.7
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1605.0	1607.0	1608.5	1613.4	1613.8	1618.3	1613.8
5°	1737.8	1746.4	1760.0	1773.5	1774.8	1783.3	1768.0
7.5°	1886.7	1906.7	1919.1	1941.1	1949.7	1955.1	1946.2
10°	1989.2	2007.8	2040.4	2056.5	2072.5	2074.9	2067.5
12.5°	2088.4	2117.7	2143.5	2173.8	2173.1	2194.8	2186.9
15°	2220.4	2250.7	2286.3	2320.3	2332.6	2332.6	2342.5
17.5°	2314.6	2370.0	2407.0	2433.6	2462.7	2467.7	2464.3
20°	2378.3	2438.0	2477.5	2512.0	2531.7	2537.3	2537.3
22.5°	2425.5	2476.5	2515.0	2546.0	2562.3	2568.8	2566.9
25°	2458.4	2502.1	2525.6	2534.8	2539.1	2537.9	2526.2
27.5°	2413.5	2411.5	2396.7	2368.4	2347.1	2334.1	2319.3
30°	2327.7	2295.6	2258.6	2218.0	2165.6	2125.5	2113.2
32.5°	2199.9	2128.0	2065.3	1997.5	1941.2	1901.1	1884.4
35°	1952.9	1838.9	1745.8	1664.4	1605.3	1568.3	1555.9
37.5°	1659.7	1549.3	1434.1	1355.2	1306.1	1268.7	1254.8
40°	1473.3	1353.1	1252.6	1178.7	1128.1	1091.7	1091.1
42.5°	1303.1	1188.4	1093.9	1040.5	986.1	962.0	961.9
45°	1067.0	975.2	895.1	853.2	820.5	800.8	795.2
47.5°	883.5	807.5	754.1	720.8	694.1	681.5	673.4
50°	780.4	713.8	671.3	642.3	627.5	611.5	610.3
52.5°	694.6	640.9	607.7	584.2	565.4	555.8	556.1
55°	583.8	541.3	517.8	499.9	485.2	477.8	474.7
57.5°	491.8	459.9	442.8	426.4	420.2	414.4	412.8
60°	434.6	413.0	397.0	384.1	374.8	372.9	372.3
62.5°	387.3	364.7	353.6	343.6	336.8	333.9	332.9
65°	319.3	302.6	292.8	284.8	282.3	278.0	277.4
67.5°	257.4	247.4	240.9	235.3	232.0	231.8	231.8
70°	219.5	213.9	208.4	205.3	203.4	202.2	202.2
72.5°	186.9	182.8	178.3	176.6	176.3	175.0	174.6
75°	142.4	138.1	138.7	135.6	133.1	130.1	128.2
77.5°	100.9	97.9	97.3	96.9	94.8	94.4	95.4
80°	78.3	75.2	74.5	75.2	74.5	72.8	72.8
82.5°	59.6	57.0	56.4	56.0	55.4	56.0	55.0
85°	32.0	30.9	30.9	30.9	32.0	31.5	30.9
87.5°	18.4	18.2	18.9	18.5	18.6	18.3	18.9
90°	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	445.9	445.3	445.5	446.4	447.3	448.2	449.1



TEST NUMBER: P333092-940

CATALOG NUMBER: S124RDIW-S1020D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)