

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333736-830

Luminaire Tested: **S125RDIW-S1270D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333736-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10518.7 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	45	44	44	38				
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	1.6
10°-20°	503.0	4.8
20°-30°	797.5	7.6
30°-40°	961.7	9.1
40°-50°	858.8	8.2
50°-60°	658.6	6.3
60°-70°	428.0	4.1
70°-80°	208.1	2.0
80°-90°	53.6	0.5
90°-100°	69.6	0.7
100°-110°	428.7	4.1
110°-120°	777.5	7.4
120°-130°	997.8	9.5
130°-140°	1073.2	10.2
140°-150°	1007.4	9.6
150°-160°	814.9	7.7
160°-170°	527.0	5.0
170°-180°	181.8	1.7
0°-30°	1472.1	14.0
0°-40°	2433.8	23.1
0°-60°	3951.3	37.6
0°-90°	4641.0	44.1
90°-120°	1275.7	12.1
90°-150°	4354.1	41.4
90°-180°	5878.0	55.9
0°-180°	10518.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	40
90°	34	1	34	1	34	16
95°	30	81	30	81	30	25
105°	421	417	421	417	421	381
115°	778	783	778	783	778	772
125°	1114	1114	1114	1114	1114	991
135°	1383	1389	1383	1389	1383	1068
145°	1606	1610	1606	1610	1606	1003
155°	1761	1774	1761	1774	1761	812
165°	1862	1872	1862	1872	1862	525
175°	1906	1914	1906	1914	1906	181
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	19.7	18.9	18.2	18.0	18.4	19.3	18.4	17.5	17.2	16.9	17.1
90°	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8	24.3	22.7	20.5
92.5°	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8	24.3	22.7	20.7
95°	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8	24.3	22.7	34.7
97.5°	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0	60.9	69.8	93.5
100°	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9	199.9	246.9	245.6
102.5°	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2	306.1	315.0	314.2
105°	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4	535.3	535.2	534.6
110°	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2	609.2	610.1	609.4



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3	681.6	682.8	682.4
115°	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2	790.4	791.7	791.5
117.5°	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3	895.9	897.6	896.4
120°	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1	962.8	963.4	962.4
122.5°	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8	1027.5	1028.1	1027.7
125°	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2	1122.5	1123.7	1123.7
127.5°	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5	1208.2	1208.9	1209.1
130°	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8	1264.7	1265.6	1265.3
132.5°	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4	1316.5	1316.7	1317.4
135°	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5	1394.1	1394.8	1395.3
137.5°	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4	1465.3	1465.1	1465.7
140°	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5	1508.9	1508.3	1508.5
142.5°	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7	1552.7	1552.6	1552.1
145°	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9	1613.5	1613.3	1613.3
147.5°	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2	1665.8	1665.5	1665.1
150°	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6	1699.0	1698.4	1697.7
152.5°	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2	1728.5	1727.9	1727.3
155°	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8	1768.9	1767.9	1767.3
157.5°	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4	1802.4	1801.4	1801.3
160°	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3	1823.1	1821.8	1821.5
162.5°	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5	1841.7	1839.9	1839.7
165°	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1	1866.2	1864.3	1864.1
167.5°	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8	1884.5	1882.3	1882.0
170°	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4	1893.9	1891.3	1891.0
172.5°	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8	1901.6	1899.3	1898.8
175°	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9	1909.5	1907.0	1906.7
177.5°	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3	1913.5	1911.8	1911.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	17.2	16.8	16.9	16.4	15.3	17.7	19.0	19.1	18.4	17.7	17.1
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9	20.1	18.3	16.6
95°	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9	79.9	79.0	78.0
97.5°	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8	170.5	172.2	174.0
100°	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0	237.9	238.8	239.8
102.5°	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2	307.4	308.6	309.8
105°	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2	418.4	419.7	420.9
107.5°	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
110°	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7	678.4	679.2	680.0
115°	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3	784.8	786.4	788.0
117.5°	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5	892.4	892.3	892.3
120°	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5	960.3	960.0	959.6
122.5°	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8	1021.9	1023.1	1024.4
125°	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8	1116.0	1118.2	1120.4
127.5°	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6	1204.2	1205.8	1207.4
130°	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1	1258.7	1260.3	1261.9
132.5°	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5	1313.4	1315.2	1317.1
135°	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0	1390.9	1392.9	1394.8
137.5°	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3	1461.9	1463.6	1465.2
140°	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8	1507.5	1508.1	1508.7
142.5°	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8	1549.2	1549.5	1549.9
145°	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4	1611.0	1611.7	1612.3
147.5°	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3	1664.2	1664.1	1664.0
150°	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1697.7	1697.1	1696.5
152.5°	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3	1729.9	1728.5	1727.1
155°	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6	1771.7	1769.8	1767.9
157.5°	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2	1805.1	1803.9	1802.8
160°	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9	1827.0	1825.1	1823.3
162.5°	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1	1845.2	1843.3	1841.4
165°	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5	1869.6	1867.6	1865.8
167.5°	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6	1887.7	1885.7	1883.8
170°	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9	1897.6	1895.5	1893.2
172.5°	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7	1904.5	1902.2	1900.1
175°	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0	1912.1	1910.3	1908.4
177.5°	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4	1915.9	1914.4	1912.9
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	17.0	17.4	17.3	18.9	17.6	18.7	18.9	18.7	19.0	19.3	18.9
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8	27.4	29.0	30.3
92.5°	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8	27.4	29.0	30.0
95°	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8	27.4	29.0	29.8
97.5°	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0	43.2	34.2	29.8
100°	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9	105.9	59.0	34.9
102.5°	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2	288.3	279.5	264.3
105°	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.6
107.5°	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4	535.4	535.5	535.0
110°	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2	607.3	606.3	606.1



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3	679.2	678.0	677.1
115°	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2	788.0	786.6	785.1
117.5°	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3	892.7	891.0	889.8
120°	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1	961.5	960.9	959.8
122.5°	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8	1026.2	1025.6	1024.4
125°	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2	1119.9	1118.7	1117.6
127.5°	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5	1206.8	1206.1	1204.6
130°	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8	1262.8	1261.9	1260.6
132.5°	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4	1316.2	1316.0	1315.0
135°	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5	1392.9	1392.2	1390.9
137.5°	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4	1465.5	1465.7	1464.9
140°	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5	1510.1	1510.8	1510.1
142.5°	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7	1552.9	1553.0	1552.2
145°	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9	1614.2	1614.5	1613.7
147.5°	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2	1666.6	1667.0	1666.0
150°	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6	1700.3	1700.9	1700.0
152.5°	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2	1729.8	1730.4	1729.6
155°	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8	1770.8	1771.7	1770.8
157.5°	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4	1804.4	1805.4	1804.7
160°	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3	1825.6	1826.8	1826.3
162.5°	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5	1845.3	1847.0	1846.5
165°	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1	1870.1	1872.0	1871.6
167.5°	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8	1889.0	1891.3	1891.0
170°	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4	1898.9	1901.4	1901.3
172.5°	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8	1906.1	1908.4	1908.1
175°	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9	1914.5	1917.0	1916.8
177.5°	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3	1917.0	1918.8	1918.7
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	19.8	19.3	19.5	19.7	19.5	19.3	19.8	18.9	19.3	19.0	18.7
90°	31.2	32.1	33.1	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8
92.5°	30.4	30.9	31.4	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8
95°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8
97.5°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0
100°	33.6	32.3	31.1	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9
102.5°	242.8	221.4	199.9	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2
105°	422.4	422.1	421.7	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8
107.5°	534.0	533.1	532.2	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4
110°	606.3	606.6	607.0	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	676.7	676.3	675.8	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3
115°	783.3	781.3	779.4	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2
117.5°	889.0	888.2	887.3	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3
120°	958.2	956.6	955.1	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1
122.5°	1022.6	1020.7	1018.9	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8
125°	1116.6	1115.7	1114.7	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2
127.5°	1202.2	1200.0	1197.6	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5
130°	1259.0	1257.4	1255.8	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8
132.5°	1313.5	1311.9	1310.3	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4
135°	1389.0	1387.1	1385.3	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5
137.5°	1463.2	1461.6	1459.9	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4
140°	1508.3	1506.4	1504.5	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5
142.5°	1550.2	1548.3	1546.4	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7
145°	1611.8	1610.0	1608.1	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9
147.5°	1663.8	1661.5	1659.3	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2
150°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6
152.5°	1727.3	1725.0	1722.8	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2
155°	1768.4	1765.9	1763.3	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8
157.5°	1802.1	1799.6	1797.1	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4
160°	1823.7	1821.2	1818.6	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3
162.5°	1843.8	1841.0	1838.2	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5
165°	1869.2	1866.6	1864.1	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1
167.5°	1888.2	1885.4	1882.5	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8
170°	1898.5	1895.6	1892.7	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4
172.5°	1905.3	1902.4	1899.6	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8
175°	1914.0	1911.2	1908.4	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9
177.5°	1916.7	1914.7	1912.6	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	18.9	18.7	17.6	18.9	17.3	17.4	17.0	17.1	17.7	18.4	19.1
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	24.3	22.7	20.7	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9
95°	24.3	22.7	34.7	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9
97.5°	60.9	69.8	93.5	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8
100°	199.9	246.9	245.6	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0
102.5°	306.1	315.0	314.2	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2
105°	422.8	422.8	422.8	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2
107.5°	535.3	535.2	534.6	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3
110°	609.2	610.1	609.4	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	681.6	682.8	682.4	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7
115°	790.4	791.7	791.5	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3
117.5°	895.9	897.6	896.4	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5
120°	962.8	963.4	962.4	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5
122.5°	1027.5	1028.1	1027.7	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8
125°	1122.5	1123.7	1123.7	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8
127.5°	1208.2	1208.9	1209.1	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6
130°	1264.7	1265.6	1265.3	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1
132.5°	1316.5	1316.7	1317.4	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5
135°	1394.1	1394.8	1395.3	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0
137.5°	1465.3	1465.1	1465.7	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3
140°	1508.9	1508.3	1508.5	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8
142.5°	1552.7	1552.6	1552.1	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8
145°	1613.5	1613.3	1613.3	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4
147.5°	1665.8	1665.5	1665.1	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3
150°	1699.0	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1695.8	1696.5	1697.1	1697.7
152.5°	1728.5	1727.9	1727.3	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3
155°	1768.9	1767.9	1767.3	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6
157.5°	1802.4	1801.4	1801.3	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2
160°	1823.1	1821.8	1821.5	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9
162.5°	1841.7	1839.9	1839.7	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1
165°	1866.2	1864.3	1864.1	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5
167.5°	1884.5	1882.3	1882.0	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6
170°	1893.9	1891.3	1891.0	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9
172.5°	1901.6	1899.3	1898.8	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7
175°	1909.5	1907.0	1906.7	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0
177.5°	1913.5	1911.8	1911.5	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	19.0	17.7	15.3	16.4	16.9	16.8	17.2	17.1	16.9	17.2	17.5
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8
92.5°	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8
95°	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8
97.5°	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0
100°	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9
102.5°	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2
105°	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4
110°	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3
115°	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2
117.5°	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3
120°	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1
122.5°	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8
125°	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2
127.5°	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5
130°	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8
132.5°	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4
135°	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5
137.5°	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4
140°	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5
142.5°	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7
145°	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9
147.5°	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2
150°	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6
152.5°	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2
155°	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8
157.5°	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4
160°	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3
162.5°	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5
165°	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1
167.5°	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8
170°	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4
172.5°	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8
175°	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9
177.5°	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	18.4	19.3	18.4	18.0	18.2	18.9	19.7
90°	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333736-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)