

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333651-830

Luminaire Tested: **S125RDIW-S375D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333651-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1050U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4789.7 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	77	68	61	56	69	61	56	51	49	44	41	37	34	32	25	24	22
4	71	60	53	47	63	54	48	43	43	39	35	33	29	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	36	30	49	39	33	28	31	26	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	16	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.1
10°-20°	151.6	3.2
20°-30°	219.8	4.6
30°-40°	250.5	5.2
40°-50°	244.1	5.1
50°-60°	205.5	4.3
60°-70°	144.1	3.0
70°-80°	74.1	1.5
80°-90°	21.4	0.4
90°-100°	82.2	1.7
100°-110°	242.7	5.1
110°-120°	411.1	8.6
120°-130°	541.1	11.3
130°-140°	606.3	12.7
140°-150°	594.2	12.4
150°-160°	499.1	10.4
160°-170°	331.7	6.9
170°-180°	116.1	2.4
0°-30°	425.6	8.9
0°-40°	676.0	14.1
0°-60°	1125.7	23.5
0°-90°	1365.2	28.5
90°-120°	736.0	15.4
90°-150°	2477.6	51.7
90°-180°	3424.0	71.5
0°-180°	4789.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	1	8	15	20	23	5
95°	62	64	74	80	82	66
105°	218	223	228	234	237	233
115°	412	415	417	416	416	407
125°	601	606	607	606	604	538
135°	781	787	788	788	784	602
145°	946	950	953	953	950	591
155°	1083	1083	1084	1087	1083	499
165°	1178	1176	1177	1180	1175	332
175°	1224	1221	1220	1226	1220	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.2	8.0	7.8	7.6	7.4	7.4	7.6	7.8	8.1	8.3	8.5
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	23.1	24.3	25.4	26.7	27.9	29.4	31.2	33.0	34.9	36.7	38.1
95°	62.1	62.5	63.0	63.3	63.8	65.0	67.2	69.3	71.4	73.5	75.0
97.5°	103.1	103.3	103.5	103.7	103.9	105.4	108.3	111.2	114.1	117.1	118.5
100°	133.7	133.7	133.7	133.7	133.7	135.1	137.8	140.6	143.4	146.1	148.1
102.5°	166.5	167.4	168.2	169.1	169.9	171.1	172.5	173.9	175.3	176.7	178.8
105°	217.7	218.8	219.9	220.9	222.0	223.2	224.4	225.7	227.0	228.3	229.5
107.5°	274.3	275.3	276.4	277.5	278.5	279.6	280.5	281.5	282.5	283.4	284.1
110°	313.2	314.3	315.4	316.4	317.5	318.4	319.0	319.6	320.3	320.9	321.5



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.0	353.5	354.1	354.7	355.2	355.9	356.7	357.5	358.3	359.1	359.4
115°	411.6	412.5	413.3	414.2	415.0	415.7	416.0	416.5	416.9	417.4	417.2
117.5°	470.4	470.8	471.2	471.6	472.0	472.4	472.8	473.2	473.5	473.9	474.1
120°	507.1	508.2	509.3	510.3	511.3	512.0	512.2	512.5	512.6	512.8	512.8
122.5°	546.9	547.2	547.6	548.0	548.4	548.8	549.4	550.0	550.5	551.1	550.9
125°	600.7	602.0	603.2	604.5	605.8	606.5	606.8	607.0	607.2	607.4	607.0
127.5°	658.0	658.7	659.5	660.2	660.9	661.4	661.7	661.9	662.1	662.4	662.2
130°	692.4	693.4	694.6	695.6	696.6	697.4	697.9	698.2	698.7	699.1	698.9
132.5°	726.8	728.5	730.3	732.0	733.8	734.6	734.5	734.4	734.3	734.2	734.1
135°	781.2	782.5	783.7	785.0	786.4	787.0	787.3	787.5	787.7	787.9	787.9
137.5°	832.5	833.7	834.9	836.1	837.4	838.2	838.7	839.1	839.6	840.1	840.3
140°	865.3	866.3	867.4	868.5	869.5	870.3	871.0	871.7	872.2	872.9	873.4
142.5°	898.1	899.0	899.9	900.8	901.7	902.6	903.3	904.2	904.9	905.8	906.0
145°	946.4	947.3	948.1	949.0	949.8	950.6	951.2	951.9	952.5	953.1	953.1
147.5°	991.2	991.6	992.1	992.5	993.0	993.5	994.0	994.5	995.0	995.5	996.1
150°	1021.0	1020.8	1020.5	1020.3	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8
152.5°	1045.4	1045.7	1045.9	1046.3	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8
155°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9
157.5°	1116.6	1116.2	1115.7	1115.2	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3
160°	1136.5	1135.9	1135.2	1134.6	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5
162.5°	1154.0	1153.6	1153.1	1152.6	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2
165°	1177.6	1177.1	1176.7	1176.3	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4
167.5°	1197.4	1196.6	1195.7	1194.9	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9
170°	1208.2	1207.3	1206.5	1205.6	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6
172.5°	1215.8	1214.9	1214.1	1213.2	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2
175°	1224.4	1223.5	1222.7	1221.8	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8
177.5°	1228.8	1228.0	1227.4	1226.7	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	8.7	9.0	9.1	9.2	9.3	9.3	9.4	9.4
90°	17.4	18.5	19.5	20.4	21.0	21.7	22.2	22.9
92.5°	39.5	40.9	42.3	43.2	43.6	44.1	44.6	45.1
95°	76.5	77.9	79.5	80.4	80.9	81.2	81.7	82.1
97.5°	119.9	121.3	122.7	123.5	123.8	124.0	124.3	124.5
100°	150.0	151.8	153.7	155.0	155.3	155.8	156.2	156.7
102.5°	180.9	182.9	185.0	186.3	186.9	187.6	188.1	188.7
105°	230.8	232.1	233.4	234.3	235.0	235.5	236.2	236.9
107.5°	284.7	285.4	286.0	286.3	286.3	286.3	286.2	286.2
110°	322.2	322.8	323.5	323.7	323.5	323.2	323.0	322.8



TEST NUMBER: P333651-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	359.7	360.0	360.2	360.2	359.9	359.5	359.1	358.7
115°	416.9	416.7	416.5	416.3	416.0	415.8	415.7	415.5
117.5°	474.2	474.4	474.6	474.2	473.3	472.5	471.6	470.8
120°	512.8	512.8	512.8	512.5	511.6	510.8	509.9	509.1
122.5°	550.7	550.5	550.4	550.0	549.3	548.6	547.9	547.2
125°	606.5	606.1	605.7	605.4	605.2	604.9	604.7	604.5
127.5°	661.9	661.8	661.6	661.3	660.8	660.4	660.0	659.6
130°	698.7	698.4	698.2	698.0	697.5	697.1	696.6	696.3
132.5°	733.8	733.6	733.4	733.0	732.4	731.8	731.2	730.6
135°	787.9	787.9	787.9	787.5	786.6	785.8	784.9	784.1
137.5°	840.6	840.8	841.0	840.7	839.6	838.6	837.4	836.4
140°	873.7	874.2	874.6	874.3	873.3	872.1	871.1	870.1
142.5°	906.3	906.5	906.8	906.3	905.3	904.3	903.2	902.1
145°	953.1	953.1	953.1	952.8	952.2	951.5	950.9	950.3
147.5°	996.6	997.0	997.6	997.1	995.7	994.2	992.8	991.4
150°	1023.8	1023.8	1023.8	1023.6	1023.1	1022.8	1022.3	1021.9
152.5°	1049.2	1049.8	1050.3	1050.2	1049.4	1048.7	1047.8	1047.1
155°	1085.7	1086.6	1087.4	1087.2	1086.2	1085.1	1084.1	1083.0
157.5°	1117.2	1118.0	1118.9	1118.6	1117.2	1115.8	1114.4	1113.0
160°	1136.3	1137.2	1138.0	1137.8	1136.8	1135.8	1134.7	1133.6
162.5°	1154.2	1155.2	1156.2	1156.1	1154.9	1153.7	1152.4	1151.2
165°	1178.3	1179.1	1180.0	1179.8	1178.6	1177.2	1176.0	1174.7
167.5°	1196.2	1197.4	1198.7	1198.7	1197.4	1196.1	1194.8	1193.4
170°	1206.8	1208.2	1209.4	1209.3	1207.8	1206.4	1204.9	1203.3
172.5°	1214.5	1215.8	1217.0	1217.0	1215.7	1214.4	1213.1	1211.7
175°	1223.0	1224.4	1225.7	1225.5	1224.1	1222.6	1221.1	1219.6
177.5°	1227.0	1228.0	1229.0	1228.9	1227.8	1226.5	1225.4	1224.2
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2

(END OF REPORT)