

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333647-830

Luminaire Tested: **S125RDIW-S375D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333647-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3873.4 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	46	41	37	36	32	30	27	24	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.4
10°-20°	151.6	3.9
20°-30°	219.8	5.7
30°-40°	250.5	6.5
40°-50°	244.1	6.3
50°-60°	205.5	5.3
60°-70°	144.1	3.7
70°-80°	74.1	1.9
80°-90°	20.7	0.5
90°-100°	60.2	1.6
100°-110°	177.8	4.6
110°-120°	301.2	7.8
120°-130°	396.4	10.2
130°-140°	444.2	11.5
140°-150°	435.3	11.2
150°-160°	365.6	9.4
160°-170°	243.1	6.3
170°-180°	85.1	2.2
0°-30°	425.6	11.0
0°-40°	676.0	17.5
0°-60°	1125.7	29.1
0°-90°	1364.5	35.2
90°-120°	539.3	13.9
90°-150°	1815.1	46.9
90°-180°	2509.0	64.8
0°-180°	3873.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	1	6	11	15	17	4
95°	46	47	54	59	60	49
105°	160	163	167	171	174	170
115°	302	304	306	305	304	298
125°	440	444	445	444	443	394
135°	572	576	577	577	574	441
145°	693	696	698	698	696	433
155°	793	793	794	797	793	365
165°	863	861	862	864	861	243
175°	897	894	894	898	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.2	7.8	7.5	7.3	7.0	6.9	7.1	7.2	7.4	7.4	7.6
90°	0.7	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0
92.5°	17.0	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9
95°	45.5	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0
97.5°	75.6	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8
100°	97.9	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5
102.5°	122.1	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0
105°	159.6	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1
107.5°	201.0	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1
110°	229.5	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.6	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3
115°	301.6	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6
117.5°	344.7	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3
120°	371.6	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7
122.5°	400.7	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6
125°	440.1	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7
127.5°	482.1	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1
130°	507.3	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0
132.5°	532.4	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8
135°	572.3	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2
137.5°	609.8	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7
140°	634.0	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8
142.5°	658.0	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7
145°	693.4	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3
147.5°	726.1	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7
150°	748.0	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1
152.5°	765.9	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4
155°	793.4	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8
157.5°	818.1	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8
160°	832.6	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9
162.5°	845.6	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9
165°	862.7	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6
167.5°	877.3	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4
170°	885.1	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3
172.5°	890.7	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8
175°	897.0	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1
177.5°	900.2	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	7.8	7.9	8.1	8.2	8.2	8.2	8.2	8.2
90°	12.7	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	28.9	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	56.1	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	87.8	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	109.8	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	132.5	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	169.1	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	208.6	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.0	236.5	237.0	237.1	237.0	236.8	236.7	236.5



TEST NUMBER: P333647-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	263.5	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.5	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.4	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.5	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.4	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	485.0	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.9	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.6	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	615.9	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.2	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	663.9	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.1	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	768.7	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	795.4	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	818.5	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	832.5	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	845.6	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.3	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	876.4	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	884.2	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	889.8	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	896.1	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	898.9	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)