

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333082-940

Luminaire Tested: **S124RDIW-S1020D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333082-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6096.8 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89		77	77	77		66	66	66	61
1	101	96	92	89	94	90	87	84	79	77	74		69	67	65		59	58	57	52
2	92	85	78	73	86	79	74	69	70	66	62		61	58	55		52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	53		54	50	47		47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45		48	44	40		42	39	36	33
5	71	59	51	45	66	56	49	43	49	44	39		43	39	35		38	34	31	29
6	65	53	45	39	61	50	43	38	45	39	34		39	35	31		35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30		36	31	28		32	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27		33	28	25		29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24		30	26	22		27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22		28	24	20		25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.5
10°-20°	421.8	6.9
20°-30°	609.1	10.0
30°-40°	690.4	11.3
40°-50°	666.7	10.9
50°-60°	554.4	9.1
60°-70°	382.8	6.3
70°-80°	194.0	3.2
80°-90°	52.3	0.9
90°-100°	56.4	0.9
100°-110°	167.2	2.7
110°-120°	283.8	4.7
120°-130°	374.2	6.1
130°-140°	420.2	6.9
140°-150°	413.0	6.8
150°-160°	347.3	5.7
160°-170°	231.1	3.8
170°-180°	80.9	1.3
0°-30°	1182.1	19.4
0°-40°	1872.5	30.7
0°-60°	3093.5	50.7
0°-90°	3722.7	61.1
90°-120°	507.4	8.3
90°-150°	1714.8	28.1
90°-180°	2374.0	38.9
0°-180°	6096.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	2	9	14	18	20	6
95°	40	46	50	52	52	44
105°	154	155	158	160	162	164
115°	289	288	287	287	286	284
125°	420	420	420	418	417	374
135°	542	546	546	545	543	419
145°	658	661	662	661	659	412
155°	754	754	754	756	754	347
165°	821	819	818	822	819	231
175°	854	851	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	23.1	21.7	20.2	18.8	17.4	16.7	16.7	16.7	16.7	16.8	16.7
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	14.2	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8
95°	39.7	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7
97.5°	69.4	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1
100°	92.6	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6
102.5°	117.0	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9
105°	154.2	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9
107.5°	193.2	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8
110°	219.7	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	247.3	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3
115°	288.6	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0
117.5°	327.4	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5
120°	353.4	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3
122.5°	380.4	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0
125°	420.3	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3
127.5°	456.4	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0
130°	481.8	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5
132.5°	507.7	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4
135°	542.1	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7
137.5°	579.3	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8
140°	604.2	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4
142.5°	627.0	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8
145°	658.5	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	689.7	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2
150°	708.8	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	726.8	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2
155°	754.5	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4
157.5°	777.8	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9
160°	791.6	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7
162.5°	804.2	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6
165°	821.4	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9
167.5°	834.4	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7
170°	841.9	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1
172.5°	847.1	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5
175°	854.4	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5
177.5°	856.8	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	16.7	16.6	16.6	16.7	16.9	17.2	17.5	17.7
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.3	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.2	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	80.6	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	101.8	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.3	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.4	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.3	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.8	219.5	219.2	219.3	219.7	220.2	220.6	221.1



TEST NUMBER: P333082-940

CATALOG NUMBER: S124RDIW-S1020D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.2	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	287.0	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	326.1	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	352.6	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.5	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	419.0	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.7	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	483.2	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	508.1	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.4	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.5	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.3	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.8	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.6	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.3	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.1	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	803.4	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	819.7	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	833.6	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.0	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	846.5	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	855.8	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)