

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333103-940

Luminaire Tested: **S124RDIW-S1195D1050U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333103-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8206.7 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	2.1
10°-20°	516.5	6.3
20°-30°	807.8	9.8
30°-40°	898.0	10.9
40°-50°	796.7	9.7
50°-60°	620.8	7.6
60°-70°	406.5	5.0
70°-80°	199.9	2.4
80°-90°	52.8	0.6
90°-100°	41.3	0.5
100°-110°	263.4	3.2
110°-120°	503.9	6.1
120°-130°	639.7	7.8
130°-140°	684.4	8.3
140°-150°	640.0	7.8
150°-160°	516.1	6.3
160°-170°	332.9	4.1
170°-180°	114.7	1.4
0°-30°	1495.5	18.2
0°-40°	2393.5	29.2
0°-60°	3811.0	46.4
0°-90°	4470.2	54.5
90°-120°	808.6	9.9
90°-150°	2772.8	33.8
90°-180°	3737.0	45.5
0°-180°	8206.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	27	3	27	3	27	13
95°	26	50	26	50	26	21
105°	258	272	258	272	258	225
115°	511	508	511	508	511	506
125°	719	714	719	714	719	640
135°	892	885	892	885	892	686
145°	1026	1021	1026	1021	1026	641
155°	1118	1119	1118	1119	1118	516
165°	1175	1181	1175	1181	1175	332
175°	1201	1208	1201	1208	1201	114
180°	1208	1208	1208	1208	1208	



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	17.9	17.3	17.8	17.7	18.2	17.5	17.8	18.7	17.3	17.7	17.3
90°	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3	21.0	19.9	18.3
92.5°	25.0	24.9	24.8	24.7	24.6	24.0	22.7	21.6	20.3	19.2	17.6
95°	26.2	26.0	25.8	25.6	25.4	24.7	23.5	22.3	21.0	19.9	19.7
97.5°	25.3	25.1	24.9	24.7	24.5	24.3	24.3	24.1	24.0	23.8	46.3
100°	25.3	25.1	24.9	24.7	24.5	26.1	29.5	32.9	36.4	39.8	67.5
102.5°	26.0	25.9	25.9	25.9	25.9	44.2	81.1	117.9	154.7	191.5	195.1
105°	257.5	264.7	272.0	279.2	286.4	289.1	287.3	285.5	283.7	281.9	280.9
107.5°	358.8	358.1	357.3	356.6	355.8	355.0	354.1	353.2	352.3	351.4	350.1
110°	403.0	402.3	401.7	401.2	400.6	400.0	399.7	399.2	398.9	398.4	397.3



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	447.0	446.3	445.5	444.8	444.0	443.6	443.7	443.8	443.9	444.0	443.4
115°	511.4	511.4	511.4	511.4	511.4	511.1	510.8	510.3	510.0	509.5	509.8
117.5°	576.8	576.8	576.9	577.0	577.1	577.2	577.3	577.3	577.4	577.5	577.0
120°	618.0	618.4	618.8	619.2	619.6	619.6	619.2	618.8	618.4	618.0	618.1
122.5°	658.4	658.9	659.2	659.7	660.0	660.1	659.9	659.7	659.4	659.2	658.9
125°	719.2	719.0	718.7	718.5	718.4	717.9	717.4	716.8	716.1	715.5	716.0
127.5°	772.5	772.6	772.8	772.9	773.1	773.2	773.4	773.5	773.6	773.7	772.8
130°	808.6	808.6	808.6	808.6	808.6	808.5	808.3	808.1	807.9	807.7	807.1
132.5°	841.9	842.0	842.1	842.3	842.5	842.5	842.3	842.0	841.9	841.7	840.9
135°	891.7	891.4	890.9	890.6	890.1	889.7	889.3	888.9	888.5	888.1	887.3
137.5°	934.3	934.5	934.6	934.7	934.9	934.7	934.2	933.8	933.4	932.9	932.0
140°	964.0	963.8	963.6	963.4	963.2	962.8	962.2	961.6	961.0	960.4	960.0
142.5°	988.6	988.6	988.5	988.5	988.4	988.2	987.7	987.3	986.9	986.4	986.1
145°	1026.4	1025.9	1025.6	1025.1	1024.8	1024.4	1024.2	1024.0	1023.9	1023.6	1023.6
147.5°	1057.6	1057.4	1057.2	1057.0	1056.8	1056.6	1056.4	1056.3	1056.1	1056.0	1056.1
150°	1077.8	1077.6	1077.5	1077.2	1077.0	1076.9	1076.9	1076.9	1076.9	1076.9	1077.1
152.5°	1095.2	1095.3	1095.4	1095.6	1095.6	1095.6	1095.2	1094.9	1094.6	1094.3	1094.7
155°	1118.5	1119.1	1119.7	1120.3	1120.9	1120.8	1120.0	1119.2	1118.4	1117.6	1118.2
157.5°	1138.0	1139.1	1140.1	1141.1	1142.2	1142.2	1141.1	1140.1	1139.1	1138.0	1138.7
160°	1151.0	1152.2	1153.4	1154.6	1155.8	1155.8	1154.6	1153.4	1152.2	1151.0	1151.2
162.5°	1161.1	1162.5	1163.9	1165.2	1166.6	1166.6	1165.5	1164.2	1163.1	1161.8	1162.1
165°	1175.4	1177.2	1179.0	1180.8	1182.6	1182.8	1181.2	1179.6	1177.9	1176.3	1176.3
167.5°	1186.1	1188.1	1190.1	1192.1	1194.1	1194.2	1192.5	1190.7	1188.9	1187.1	1187.3
170°	1192.6	1194.5	1196.6	1198.5	1200.6	1200.8	1199.2	1197.6	1196.0	1194.4	1194.2
172.5°	1196.1	1198.4	1200.5	1202.7	1204.9	1205.1	1203.5	1201.9	1200.3	1198.7	1198.5
175°	1200.7	1203.1	1205.5	1207.9	1210.3	1210.7	1208.8	1207.0	1205.2	1203.5	1203.2
177.5°	1203.6	1205.5	1207.5	1209.3	1211.3	1211.7	1210.3	1209.1	1207.7	1206.5	1206.1
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	17.0	16.1	16.9	16.6	16.7	18.5	19.8	19.9	18.6	17.4	16.1
90°	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7	4.9	7.1	9.4
92.5°	16.0	14.4	12.8	11.9	11.8	11.6	11.5	11.4	11.5	11.6	11.8
95°	19.4	19.3	19.1	22.4	29.2	36.0	42.9	49.7	42.9	36.0	29.2
97.5°	68.7	91.0	113.5	122.5	118.3	114.0	109.8	105.5	109.8	114.0	118.3
100°	95.1	122.9	150.6	162.6	159.0	155.4	151.8	148.2	151.8	155.4	159.0
102.5°	198.8	202.4	206.0	206.4	203.8	201.2	198.5	195.9	198.5	201.2	203.8
105°	279.9	278.8	277.9	276.8	275.5	274.4	273.1	272.0	273.1	274.4	275.5
107.5°	348.7	347.3	346.0	345.0	344.4	343.8	343.2	342.6	343.2	343.8	344.4
110°	396.0	394.8	393.6	392.7	392.1	391.5	390.9	390.3	390.9	391.5	392.1



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	442.8	442.3	441.8	440.9	439.8	438.7	437.7	436.6	437.7	438.7	439.8
115°	510.0	510.1	510.3	510.1	509.5	509.0	508.4	507.7	508.4	509.0	509.5
117.5°	576.6	576.1	575.7	575.1	574.3	573.5	572.7	571.9	572.7	573.5	574.3
120°	618.4	618.6	618.8	618.5	617.7	616.9	616.1	615.3	616.1	616.9	617.7
122.5°	658.6	658.4	658.1	657.6	657.2	656.7	656.2	655.8	656.2	656.7	657.2
125°	716.3	716.8	717.1	716.9	716.1	715.3	714.5	713.7	714.5	715.3	716.1
127.5°	771.9	771.0	770.0	769.5	769.3	769.1	768.8	768.7	768.8	769.1	769.3
130°	806.5	805.9	805.3	804.9	804.7	804.5	804.3	804.1	804.3	804.5	804.7
132.5°	840.2	839.4	838.7	838.0	837.7	837.3	837.0	836.6	837.0	837.3	837.7
135°	886.5	885.7	884.9	884.6	884.8	885.0	885.2	885.4	885.2	885.0	884.8
137.5°	931.1	930.2	929.3	928.9	928.8	928.7	928.6	928.5	928.6	928.7	928.8
140°	959.6	959.2	958.8	958.4	958.0	957.6	957.2	956.8	957.2	957.6	958.0
142.5°	985.9	985.7	985.4	985.0	984.3	983.5	982.8	982.0	982.8	983.5	984.3
145°	1023.6	1023.6	1023.6	1023.3	1022.7	1022.1	1021.5	1020.9	1021.5	1022.1	1022.7
147.5°	1056.4	1056.6	1056.8	1056.3	1055.2	1054.1	1052.9	1051.8	1052.9	1054.1	1055.2
150°	1077.4	1077.5	1077.7	1077.5	1076.7	1075.8	1075.0	1074.2	1075.0	1075.8	1076.7
152.5°	1095.0	1095.4	1095.7	1095.6	1094.9	1094.3	1093.7	1093.0	1093.7	1094.3	1094.9
155°	1118.8	1119.4	1120.0	1120.2	1120.0	1119.8	1119.6	1119.4	1119.6	1119.8	1120.0
157.5°	1139.3	1140.1	1140.8	1141.1	1141.2	1141.4	1141.5	1141.7	1141.5	1141.4	1141.2
160°	1151.4	1151.6	1151.8	1152.2	1152.8	1153.4	1154.1	1154.6	1154.1	1153.4	1152.8
162.5°	1162.3	1162.4	1162.6	1163.1	1163.9	1164.7	1165.5	1166.2	1165.5	1164.7	1163.9
165°	1176.3	1176.3	1176.3	1176.8	1177.8	1178.8	1179.8	1180.8	1179.8	1178.8	1177.8
167.5°	1187.4	1187.5	1187.7	1188.2	1189.3	1190.3	1191.3	1192.4	1191.3	1190.3	1189.3
170°	1194.0	1193.7	1193.6	1194.1	1195.2	1196.5	1197.7	1198.9	1197.7	1196.5	1195.2
172.5°	1198.3	1198.1	1197.9	1198.4	1199.6	1200.8	1202.0	1203.2	1202.0	1200.8	1199.6
175°	1203.0	1202.8	1202.7	1203.1	1204.3	1205.5	1206.8	1207.9	1206.8	1205.5	1204.3
177.5°	1205.9	1205.5	1205.2	1205.6	1206.8	1207.8	1209.0	1210.1	1209.0	1207.8	1206.8
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	16.6	16.3	16.7	15.9	16.8	17.0	16.8	17.0	17.8	16.9	17.0
90°	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3	23.5	24.7	25.5
92.5°	11.9	12.8	14.4	16.0	17.6	19.2	20.3	21.6	22.7	24.0	24.6
95°	22.4	19.1	19.3	19.4	19.7	19.9	21.0	22.3	23.5	24.7	25.4
97.5°	122.5	113.5	91.0	68.7	46.3	23.8	24.0	24.1	24.3	24.3	24.5
100°	162.6	150.6	122.9	95.1	67.5	39.8	36.4	32.9	29.5	26.1	24.5
102.5°	206.4	206.0	202.4	198.8	195.1	191.5	154.7	117.9	81.1	44.2	25.9
105°	276.8	277.9	278.8	279.9	280.9	281.9	283.7	285.5	287.3	289.1	286.4
107.5°	345.0	346.0	347.3	348.7	350.1	351.4	352.3	353.2	354.1	355.0	355.8
110°	392.7	393.6	394.8	396.0	397.3	398.4	398.9	399.2	399.7	400.0	400.6



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	440.9	441.8	442.3	442.8	443.4	444.0	443.9	443.8	443.7	443.6	444.0
115°	510.1	510.3	510.1	510.0	509.8	509.5	510.0	510.3	510.8	511.1	511.4
117.5°	575.1	575.7	576.1	576.6	577.0	577.5	577.4	577.3	577.3	577.2	577.1
120°	618.5	618.8	618.6	618.4	618.1	618.0	618.4	618.8	619.2	619.6	619.6
122.5°	657.6	658.1	658.4	658.6	658.9	659.2	659.4	659.7	659.9	660.1	660.0
125°	716.9	717.1	716.8	716.3	716.0	715.5	716.1	716.8	717.4	717.9	718.4
127.5°	769.5	770.0	771.0	771.9	772.8	773.7	773.6	773.5	773.4	773.2	773.1
130°	804.9	805.3	805.9	806.5	807.1	807.7	807.9	808.1	808.3	808.5	808.6
132.5°	838.0	838.7	839.4	840.2	840.9	841.7	841.9	842.0	842.3	842.5	842.5
135°	884.6	884.9	885.7	886.5	887.3	888.1	888.5	888.9	889.3	889.7	890.1
137.5°	928.9	929.3	930.2	931.1	932.0	932.9	933.4	933.8	934.2	934.7	934.9
140°	958.4	958.8	959.2	959.6	960.0	960.4	961.0	961.6	962.2	962.8	963.2
142.5°	985.0	985.4	985.7	985.9	986.1	986.4	986.9	987.3	987.7	988.2	988.4
145°	1023.3	1023.6	1023.6	1023.6	1023.6	1023.6	1023.9	1024.0	1024.2	1024.4	1024.8
147.5°	1056.3	1056.8	1056.6	1056.4	1056.1	1056.0	1056.1	1056.3	1056.4	1056.6	1056.8
150°	1077.5	1077.7	1077.5	1077.4	1077.1	1076.9	1076.9	1076.9	1076.9	1076.9	1077.0
152.5°	1095.6	1095.7	1095.4	1095.0	1094.7	1094.3	1094.6	1094.9	1095.2	1095.6	1095.6
155°	1120.2	1120.0	1119.4	1118.8	1118.2	1117.6	1118.4	1119.2	1120.0	1120.8	1120.9
157.5°	1141.1	1140.8	1140.1	1139.3	1138.7	1138.0	1139.1	1140.1	1141.1	1142.2	1142.2
160°	1152.2	1151.8	1151.6	1151.4	1151.2	1151.0	1152.2	1153.4	1154.6	1155.8	1155.8
162.5°	1163.1	1162.6	1162.4	1162.3	1162.1	1161.8	1163.1	1164.2	1165.5	1166.6	1166.6
165°	1176.8	1176.3	1176.3	1176.3	1176.3	1176.3	1177.9	1179.6	1181.2	1182.8	1182.6
167.5°	1188.2	1187.7	1187.5	1187.4	1187.3	1187.1	1188.9	1190.7	1192.5	1194.2	1194.1
170°	1194.1	1193.6	1193.7	1194.0	1194.2	1194.4	1196.0	1197.6	1199.2	1200.8	1200.6
172.5°	1198.4	1197.9	1198.1	1198.3	1198.5	1198.7	1200.3	1201.9	1203.5	1205.1	1204.9
175°	1203.1	1202.7	1202.8	1203.0	1203.2	1203.5	1205.2	1207.0	1208.8	1210.7	1210.3
177.5°	1205.6	1205.2	1205.5	1205.9	1206.1	1206.5	1207.7	1209.1	1210.3	1211.7	1211.3
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	18.3	17.8	17.3	17.9	17.3	17.8	18.3	17.0	16.9	17.8	17.0
90°	25.9	26.3	26.7	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3
92.5°	24.7	24.8	24.9	25.0	24.9	24.8	24.7	24.6	24.0	22.7	21.6
95°	25.6	25.8	26.0	26.2	26.0	25.8	25.6	25.4	24.7	23.5	22.3
97.5°	24.7	24.9	25.1	25.3	25.1	24.9	24.7	24.5	24.3	24.3	24.1
100°	24.7	24.9	25.1	25.3	25.1	24.9	24.7	24.5	26.1	29.5	32.9
102.5°	25.9	25.9	25.9	26.0	25.9	25.9	25.9	25.9	44.2	81.1	117.9
105°	279.2	272.0	264.7	257.5	264.7	272.0	279.2	286.4	289.1	287.3	285.5
107.5°	356.6	357.3	358.1	358.8	358.1	357.3	356.6	355.8	355.0	354.1	353.2
110°	401.2	401.7	402.3	403.0	402.3	401.7	401.2	400.6	400.0	399.7	399.2



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.8	445.5	446.3	447.0	446.3	445.5	444.8	444.0	443.6	443.7	443.8
115°	511.4	511.4	511.4	511.4	511.4	511.4	511.4	511.4	511.1	510.8	510.3
117.5°	577.0	576.9	576.8	576.8	576.8	576.9	577.0	577.1	577.2	577.3	577.3
120°	619.2	618.8	618.4	618.0	618.4	618.8	619.2	619.6	619.6	619.2	618.8
122.5°	659.7	659.2	658.9	658.4	658.9	659.2	659.7	660.0	660.1	659.9	659.7
125°	718.5	718.7	719.0	719.2	719.0	718.7	718.5	718.4	717.9	717.4	716.8
127.5°	772.9	772.8	772.6	772.5	772.6	772.8	772.9	773.1	773.2	773.4	773.5
130°	808.6	808.6	808.6	808.6	808.6	808.6	808.6	808.6	808.5	808.3	808.1
132.5°	842.3	842.1	842.0	841.9	842.0	842.1	842.3	842.5	842.5	842.3	842.0
135°	890.6	890.9	891.4	891.7	891.4	890.9	890.6	890.1	889.7	889.3	888.9
137.5°	934.7	934.6	934.5	934.3	934.5	934.6	934.7	934.9	934.7	934.2	933.8
140°	963.4	963.6	963.8	964.0	963.8	963.6	963.4	963.2	962.8	962.2	961.6
142.5°	988.5	988.5	988.6	988.6	988.6	988.5	988.5	988.4	988.2	987.7	987.3
145°	1025.1	1025.6	1025.9	1026.4	1025.9	1025.6	1025.1	1024.8	1024.4	1024.2	1024.0
147.5°	1057.0	1057.2	1057.4	1057.6	1057.4	1057.2	1057.0	1056.8	1056.6	1056.4	1056.3
150°	1077.2	1077.5	1077.6	1077.8	1077.6	1077.5	1077.2	1077.0	1076.9	1076.9	1076.9
152.5°	1095.6	1095.4	1095.3	1095.2	1095.3	1095.4	1095.6	1095.6	1095.6	1095.2	1094.9
155°	1120.3	1119.7	1119.1	1118.5	1119.1	1119.7	1120.3	1120.9	1120.8	1120.0	1119.2
157.5°	1141.1	1140.1	1139.1	1138.0	1139.1	1140.1	1141.1	1142.2	1142.2	1141.1	1140.1
160°	1154.6	1153.4	1152.2	1151.0	1152.2	1153.4	1154.6	1155.8	1155.8	1154.6	1153.4
162.5°	1165.2	1163.9	1162.5	1161.1	1162.5	1163.9	1165.2	1166.6	1166.6	1165.5	1164.2
165°	1180.8	1179.0	1177.2	1175.4	1177.2	1179.0	1180.8	1182.6	1182.8	1181.2	1179.6
167.5°	1192.1	1190.1	1188.1	1186.1	1188.1	1190.1	1192.1	1194.1	1194.2	1192.5	1190.7
170°	1198.5	1196.6	1194.5	1192.6	1194.5	1196.6	1198.5	1200.6	1200.8	1199.2	1197.6
172.5°	1202.7	1200.5	1198.4	1196.1	1198.4	1200.5	1202.7	1204.9	1205.1	1203.5	1201.9
175°	1207.9	1205.5	1203.1	1200.7	1203.1	1205.5	1207.9	1210.3	1210.7	1208.8	1207.0
177.5°	1209.3	1207.5	1205.5	1203.6	1205.5	1207.5	1209.3	1211.3	1211.7	1210.3	1209.1
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	16.8	17.0	16.8	15.9	16.7	16.3	16.6	16.1	17.4	18.6	19.9
90°	21.0	19.9	18.3	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7
92.5°	20.3	19.2	17.6	16.0	14.4	12.8	11.9	11.8	11.6	11.5	11.4
95°	21.0	19.9	19.7	19.4	19.3	19.1	22.4	29.2	36.0	42.9	49.7
97.5°	24.0	23.8	46.3	68.7	91.0	113.5	122.5	118.3	114.0	109.8	105.5
100°	36.4	39.8	67.5	95.1	122.9	150.6	162.6	159.0	155.4	151.8	148.2
102.5°	154.7	191.5	195.1	198.8	202.4	206.0	206.4	203.8	201.2	198.5	195.9
105°	283.7	281.9	280.9	279.9	278.8	277.9	276.8	275.5	274.4	273.1	272.0
107.5°	352.3	351.4	350.1	348.7	347.3	346.0	345.0	344.4	343.8	343.2	342.6
110°	398.9	398.4	397.3	396.0	394.8	393.6	392.7	392.1	391.5	390.9	390.3



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	443.9	444.0	443.4	442.8	442.3	441.8	440.9	439.8	438.7	437.7	436.6
115°	510.0	509.5	509.8	510.0	510.1	510.3	510.1	509.5	509.0	508.4	507.7
117.5°	577.4	577.5	577.0	576.6	576.1	575.7	575.1	574.3	573.5	572.7	571.9
120°	618.4	618.0	618.1	618.4	618.6	618.8	618.5	617.7	616.9	616.1	615.3
122.5°	659.4	659.2	658.9	658.6	658.4	658.1	657.6	657.2	656.7	656.2	655.8
125°	716.1	715.5	716.0	716.3	716.8	717.1	716.9	716.1	715.3	714.5	713.7
127.5°	773.6	773.7	772.8	771.9	771.0	770.0	769.5	769.3	769.1	768.8	768.7
130°	807.9	807.7	807.1	806.5	805.9	805.3	804.9	804.7	804.5	804.3	804.1
132.5°	841.9	841.7	840.9	840.2	839.4	838.7	838.0	837.7	837.3	837.0	836.6
135°	888.5	888.1	887.3	886.5	885.7	884.9	884.6	884.8	885.0	885.2	885.4
137.5°	933.4	932.9	932.0	931.1	930.2	929.3	928.9	928.8	928.7	928.6	928.5
140°	961.0	960.4	960.0	959.6	959.2	958.8	958.4	958.0	957.6	957.2	956.8
142.5°	986.9	986.4	986.1	985.9	985.7	985.4	985.0	984.3	983.5	982.8	982.0
145°	1023.9	1023.6	1023.6	1023.6	1023.6	1023.6	1023.3	1022.7	1022.1	1021.5	1020.9
147.5°	1056.1	1056.0	1056.1	1056.4	1056.6	1056.8	1056.3	1055.2	1054.1	1052.9	1051.8
150°	1076.9	1076.9	1077.1	1077.4	1077.5	1077.7	1077.5	1076.7	1075.8	1075.0	1074.2
152.5°	1094.6	1094.3	1094.7	1095.0	1095.4	1095.7	1095.6	1094.9	1094.3	1093.7	1093.0
155°	1118.4	1117.6	1118.2	1118.8	1119.4	1120.0	1120.2	1120.0	1119.8	1119.6	1119.4
157.5°	1139.1	1138.0	1138.7	1139.3	1140.1	1140.8	1141.1	1141.2	1141.4	1141.5	1141.7
160°	1152.2	1151.0	1151.2	1151.4	1151.6	1151.8	1152.2	1152.8	1153.4	1154.1	1154.6
162.5°	1163.1	1161.8	1162.1	1162.3	1162.4	1162.6	1163.1	1163.9	1164.7	1165.5	1166.2
165°	1177.9	1176.3	1176.3	1176.3	1176.3	1176.3	1176.8	1177.8	1178.8	1179.8	1180.8
167.5°	1188.9	1187.1	1187.3	1187.4	1187.5	1187.7	1188.2	1189.3	1190.3	1191.3	1192.4
170°	1196.0	1194.4	1194.2	1194.0	1193.7	1193.6	1194.1	1195.2	1196.5	1197.7	1198.9
172.5°	1200.3	1198.7	1198.5	1198.3	1198.1	1197.9	1198.4	1199.6	1200.8	1202.0	1203.2
175°	1205.2	1203.5	1203.2	1203.0	1202.8	1202.7	1203.1	1204.3	1205.5	1206.8	1207.9
177.5°	1207.7	1206.5	1206.1	1205.9	1205.5	1205.2	1205.6	1206.8	1207.8	1209.0	1210.1
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.8	18.5	16.7	16.6	16.9	16.1	17.0	17.3	17.7	17.3	18.7
90°	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3
92.5°	11.5	11.6	11.8	11.9	12.8	14.4	16.0	17.6	19.2	20.3	21.6
95°	42.9	36.0	29.2	22.4	19.1	19.3	19.4	19.7	19.9	21.0	22.3
97.5°	109.8	114.0	118.3	122.5	113.5	91.0	68.7	46.3	23.8	24.0	24.1
100°	151.8	155.4	159.0	162.6	150.6	122.9	95.1	67.5	39.8	36.4	32.9
102.5°	198.5	201.2	203.8	206.4	206.0	202.4	198.8	195.1	191.5	154.7	117.9
105°	273.1	274.4	275.5	276.8	277.9	278.8	279.9	280.9	281.9	283.7	285.5
107.5°	343.2	343.8	344.4	345.0	346.0	347.3	348.7	350.1	351.4	352.3	353.2
110°	390.9	391.5	392.1	392.7	393.6	394.8	396.0	397.3	398.4	398.9	399.2



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	437.7	438.7	439.8	440.9	441.8	442.3	442.8	443.4	444.0	443.9	443.8
115°	508.4	509.0	509.5	510.1	510.3	510.1	510.0	509.8	509.5	510.0	510.3
117.5°	572.7	573.5	574.3	575.1	575.7	576.1	576.6	577.0	577.5	577.4	577.3
120°	616.1	616.9	617.7	618.5	618.8	618.6	618.4	618.1	618.0	618.4	618.8
122.5°	656.2	656.7	657.2	657.6	658.1	658.4	658.6	658.9	659.2	659.4	659.7
125°	714.5	715.3	716.1	716.9	717.1	716.8	716.3	716.0	715.5	716.1	716.8
127.5°	768.8	769.1	769.3	769.5	770.0	771.0	771.9	772.8	773.7	773.6	773.5
130°	804.3	804.5	804.7	804.9	805.3	805.9	806.5	807.1	807.7	807.9	808.1
132.5°	837.0	837.3	837.7	838.0	838.7	839.4	840.2	840.9	841.7	841.9	842.0
135°	885.2	885.0	884.8	884.6	884.9	885.7	886.5	887.3	888.1	888.5	888.9
137.5°	928.6	928.7	928.8	928.9	929.3	930.2	931.1	932.0	932.9	933.4	933.8
140°	957.2	957.6	958.0	958.4	958.8	959.2	959.6	960.0	960.4	961.0	961.6
142.5°	982.8	983.5	984.3	985.0	985.4	985.7	985.9	986.1	986.4	986.9	987.3
145°	1021.5	1022.1	1022.7	1023.3	1023.6	1023.6	1023.6	1023.6	1023.6	1023.9	1024.0
147.5°	1052.9	1054.1	1055.2	1056.3	1056.8	1056.6	1056.4	1056.1	1056.0	1056.1	1056.3
150°	1075.0	1075.8	1076.7	1077.5	1077.7	1077.5	1077.4	1077.1	1076.9	1076.9	1076.9
152.5°	1093.7	1094.3	1094.9	1095.6	1095.7	1095.4	1095.0	1094.7	1094.3	1094.6	1094.9
155°	1119.6	1119.8	1120.0	1120.2	1120.0	1119.4	1118.8	1118.2	1117.6	1118.4	1119.2
157.5°	1141.5	1141.4	1141.2	1141.1	1140.8	1140.1	1139.3	1138.7	1138.0	1139.1	1140.1
160°	1154.1	1153.4	1152.8	1152.2	1151.8	1151.6	1151.4	1151.2	1151.0	1152.2	1153.4
162.5°	1165.5	1164.7	1163.9	1163.1	1162.6	1162.4	1162.3	1162.1	1161.8	1163.1	1164.2
165°	1179.8	1178.8	1177.8	1176.8	1176.3	1176.3	1176.3	1176.3	1176.3	1177.9	1179.6
167.5°	1191.3	1190.3	1189.3	1188.2	1187.7	1187.5	1187.4	1187.3	1187.1	1188.9	1190.7
170°	1197.7	1196.5	1195.2	1194.1	1193.6	1193.7	1194.0	1194.2	1194.4	1196.0	1197.6
172.5°	1202.0	1200.8	1199.6	1198.4	1197.9	1198.1	1198.3	1198.5	1198.7	1200.3	1201.9
175°	1206.8	1205.5	1204.3	1203.1	1202.7	1202.8	1203.0	1203.2	1203.5	1205.2	1207.0
177.5°	1209.0	1207.8	1206.8	1205.6	1205.2	1205.5	1205.9	1206.1	1206.5	1207.7	1209.1
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	17.8	17.5	18.2	17.7	17.8	17.3	17.9
90°	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	22.7	24.0	24.6	24.7	24.8	24.9	25.0
95°	23.5	24.7	25.4	25.6	25.8	26.0	26.2
97.5°	24.3	24.3	24.5	24.7	24.9	25.1	25.3
100°	29.5	26.1	24.5	24.7	24.9	25.1	25.3
102.5°	81.1	44.2	25.9	25.9	25.9	25.9	26.0
105°	287.3	289.1	286.4	279.2	272.0	264.7	257.5
107.5°	354.1	355.0	355.8	356.6	357.3	358.1	358.8
110°	399.7	400.0	400.6	401.2	401.7	402.3	403.0



TEST NUMBER: P333103-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	443.7	443.6	444.0	444.8	445.5	446.3	447.0
115°	510.8	511.1	511.4	511.4	511.4	511.4	511.4
117.5°	577.3	577.2	577.1	577.0	576.9	576.8	576.8
120°	619.2	619.6	619.6	619.2	618.8	618.4	618.0
122.5°	659.9	660.1	660.0	659.7	659.2	658.9	658.4
125°	717.4	717.9	718.4	718.5	718.7	719.0	719.2
127.5°	773.4	773.2	773.1	772.9	772.8	772.6	772.5
130°	808.3	808.5	808.6	808.6	808.6	808.6	808.6
132.5°	842.3	842.5	842.5	842.3	842.1	842.0	841.9
135°	889.3	889.7	890.1	890.6	890.9	891.4	891.7
137.5°	934.2	934.7	934.9	934.7	934.6	934.5	934.3
140°	962.2	962.8	963.2	963.4	963.6	963.8	964.0
142.5°	987.7	988.2	988.4	988.5	988.5	988.6	988.6
145°	1024.2	1024.4	1024.8	1025.1	1025.6	1025.9	1026.4
147.5°	1056.4	1056.6	1056.8	1057.0	1057.2	1057.4	1057.6
150°	1076.9	1076.9	1077.0	1077.2	1077.5	1077.6	1077.8
152.5°	1095.2	1095.6	1095.6	1095.6	1095.4	1095.3	1095.2
155°	1120.0	1120.8	1120.9	1120.3	1119.7	1119.1	1118.5
157.5°	1141.1	1142.2	1142.2	1141.1	1140.1	1139.1	1138.0
160°	1154.6	1155.8	1155.8	1154.6	1153.4	1152.2	1151.0
162.5°	1165.5	1166.6	1166.6	1165.2	1163.9	1162.5	1161.1
165°	1181.2	1182.8	1182.6	1180.8	1179.0	1177.2	1175.4
167.5°	1192.5	1194.2	1194.1	1192.1	1190.1	1188.1	1186.1
170°	1199.2	1200.8	1200.6	1198.5	1196.6	1194.5	1192.6
172.5°	1203.5	1205.1	1204.9	1202.7	1200.5	1198.4	1196.1
175°	1208.8	1210.7	1210.3	1207.9	1205.5	1203.1	1200.7
177.5°	1210.3	1211.7	1211.3	1209.3	1207.5	1205.5	1203.6
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9

(END OF REPORT)