

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333670-830

Luminaire Tested: **S125RDIW-S610D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333670-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1050U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6191.6 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31
3	79	70	63	57	71	63	57	53	52	47	44	41	38	35	30	28	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	1.4
10°-20°	249.2	4.0
20°-30°	361.3	5.8
30°-40°	411.8	6.7
40°-50°	401.4	6.5
50°-60°	337.9	5.5
60°-70°	236.8	3.8
70°-80°	121.7	2.0
80°-90°	33.4	0.5
90°-100°	46.7	0.8
100°-110°	288.0	4.7
110°-120°	522.3	8.4
120°-130°	670.4	10.8
130°-140°	721.0	11.6
140°-150°	676.8	10.9
150°-160°	547.5	8.8
160°-170°	354.1	5.7
170°-180°	122.1	2.0
0°-30°	699.6	11.3
0°-40°	1111.4	18.0
0°-60°	1850.7	29.9
0°-90°	2242.7	36.2
90°-120°	857.1	13.8
90°-150°	2925.3	47.2
90°-180°	3949.0	63.8
0°-180°	6191.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	8	15	20	23	4
95°	54	50	15	20	20	69
105°	280	284	284	284	283	297
115°	526	531	532	528	522	521
125°	748	755	755	751	748	668
135°	933	939	937	935	929	719
145°	1082	1084	1084	1084	1079	676
155°	1192	1186	1188	1190	1183	549
165°	1257	1252	1252	1258	1251	355
175°	1286	1281	1281	1288	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.4	12.8	12.3	11.7	11.1	10.9	11.1	11.3	11.5	11.7	11.9
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	14.7	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3
95°	54.3	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3
97.5°	113.5	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9
100°	159.2	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3
102.5°	205.8	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7
105°	280.2	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6
110°	408.0	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.2	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9
115°	526.2	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0
117.5°	599.6	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9
120°	645.4	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9
122.5°	685.8	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3
125°	748.3	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1
127.5°	807.9	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7
130°	844.6	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7
132.5°	881.2	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5
135°	933.2	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6
137.5°	981.1	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4
140°	1012.4	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7
142.5°	1040.6	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1
145°	1081.9	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1
147.5°	1118.1	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2
150°	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5
152.5°	1163.2	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3
155°	1191.6	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4
157.5°	1213.5	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0
160°	1228.8	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8
162.5°	1241.0	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4
165°	1257.4	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9
167.5°	1269.5	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1
170°	1276.4	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4
172.5°	1281.0	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5
175°	1285.9	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9
177.5°	1288.3	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	12.1	12.3	12.5	12.6	12.6	12.6	12.6	12.6
90°	17.3	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	17.3	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	17.3	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	35.0	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	102.7	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	199.6	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.6	408.0	407.4	407.2	407.4	407.6	407.7	408.0



TEST NUMBER: P333670-830

CATALOG NUMBER: S125RDIW-S610D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.1	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	530.2	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	600.9	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.4	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.8	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	753.3	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	811.2	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	849.0	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.4	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	936.2	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.5	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.2	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.2	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.3	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.5	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1141.9	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1161.7	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.0	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1211.6	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1225.7	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1238.6	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1255.1	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1267.6	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1274.1	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1279.1	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1284.6	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1286.8	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)