

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333104-940

Luminaire Tested: **S124RDIW-S1195D1050U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333104-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7710.8 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	92	84	78	73	85	79	74	69	69	65	62	59	57	54	51	49	47	43
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	43	40	37
4	77	66	59	53	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	48	41	35	56	46	39	34	40	35	31	36	31	28	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	40	33	28	49	38	31	27	34	28	25	30	26	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.2	2.2
10°-20°	516.5	6.7
20°-30°	807.8	10.5
30°-40°	898.0	11.6
40°-50°	796.7	10.3
50°-60°	620.8	8.1
60°-70°	406.5	5.3
70°-80°	199.9	2.6
80°-90°	52.8	0.7
90°-100°	77.0	1.0
100°-110°	228.2	3.0
110°-120°	387.4	5.0
120°-130°	510.8	6.6
130°-140°	573.6	7.4
140°-150°	563.7	7.3
150°-160°	474.1	6.1
160°-170°	315.4	4.1
170°-180°	110.5	1.4
0°-30°	1495.5	19.4
0°-40°	2393.5	31.0
0°-60°	3811.0	49.4
0°-90°	4470.2	58.0
90°-120°	692.6	9.0
90°-150°	2340.6	30.4
90°-180°	3241.0	42.0
0°-180°	7710.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	27	3	27	3	27	15
95°	71	54	71	54	71	74
105°	220	210	220	210	220	232
115°	390	394	390	394	390	386
125°	569	574	569	574	569	508
135°	741	740	741	740	741	572
145°	900	899	900	899	900	563
155°	1029	1030	1029	1030	1029	474
165°	1118	1121	1118	1121	1118	315
175°	1161	1166	1161	1166	1161	110
180°	1168	1168	1168	1168	1168	



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	17.9	17.3	17.8	17.7	18.2	17.5	17.8	18.7	17.3	17.7	17.3
90°	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3	21.0	19.9	18.3
92.5°	40.1	39.9	39.6	39.4	39.1	38.7	37.9	37.2	36.5	35.8	34.7
95°	71.3	71.3	71.3	71.3	71.3	71.1	70.4	69.8	69.3	68.7	67.2
97.5°	111.8	111.8	111.8	111.8	111.8	111.5	110.8	110.0	109.3	108.6	106.9
100°	140.0	140.0	140.0	140.0	140.0	139.8	139.4	139.0	138.6	138.2	136.4
102.5°	171.8	171.7	171.5	171.3	171.2	170.9	170.2	169.7	169.2	168.5	166.9
105°	220.4	219.8	219.2	218.6	218.0	217.4	216.8	216.2	215.6	215.0	214.2
107.5°	267.8	267.8	267.9	267.9	267.9	267.7	267.1	266.5	266.0	265.4	265.3
110°	301.8	301.1	300.5	299.9	299.3	299.2	299.6	300.0	300.4	300.8	301.0



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.4	336.3	336.2	336.1	335.9	335.9	336.0	336.1	336.2	336.3	336.6
115°	390.2	390.5	390.7	390.8	391.0	391.3	391.5	391.6	391.8	392.1	392.4
117.5°	441.6	441.9	442.4	442.7	443.2	443.7	444.3	445.1	445.8	446.4	446.7
120°	480.5	480.2	479.7	479.4	478.9	479.3	480.3	481.3	482.3	483.3	483.9
122.5°	513.1	513.8	514.5	515.2	515.9	516.7	517.4	518.1	518.7	519.4	519.7
125°	569.1	569.5	569.9	570.3	570.7	571.1	571.5	571.9	572.3	572.7	572.9
127.5°	621.0	621.3	621.6	621.9	622.2	622.6	623.0	623.4	623.8	624.2	624.6
130°	655.0	655.8	656.6	657.4	658.2	658.7	659.2	659.5	660.0	660.3	660.3
132.5°	691.1	691.3	691.7	692.1	692.3	692.7	693.1	693.5	693.9	694.3	694.5
135°	740.7	741.4	741.9	742.5	743.2	743.7	744.0	744.5	744.8	745.3	745.3
137.5°	792.9	792.8	792.7	792.6	792.5	792.6	793.2	793.7	794.2	794.8	794.4
140°	824.7	824.9	825.2	825.4	825.5	825.7	826.0	826.2	826.3	826.5	826.5
142.5°	856.6	856.6	856.7	856.7	856.7	856.8	856.8	856.8	856.8	856.9	857.1
145°	899.7	900.4	900.9	901.5	902.1	902.5	902.8	902.9	903.1	903.3	903.1
147.5°	943.4	943.6	943.9	944.1	944.2	944.4	944.6	944.8	944.9	945.0	945.2
150°	970.2	970.4	970.6	970.8	971.0	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	994.8	995.2	995.8	996.3	996.8	996.8	996.4	995.9	995.4	995.0	994.8
155°	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9	1029.1
157.5°	1059.4	1060.2	1060.8	1061.5	1062.2	1062.2	1061.6	1061.0	1060.4	1059.8	1059.8
160°	1076.7	1077.8	1078.8	1079.8	1080.8	1081.0	1080.4	1079.8	1079.1	1078.6	1078.8
162.5°	1094.8	1095.8	1096.9	1097.9	1098.9	1098.9	1097.7	1096.6	1095.6	1094.5	1094.7
165°	1118.3	1119.1	1119.9	1120.7	1121.5	1121.3	1120.2	1118.9	1117.8	1116.5	1117.0
167.5°	1135.1	1136.4	1137.6	1138.9	1140.1	1140.1	1138.9	1137.7	1136.5	1135.3	1135.2
170°	1144.5	1145.9	1147.4	1148.8	1150.1	1150.2	1149.1	1147.8	1146.7	1145.4	1145.2
172.5°	1152.4	1153.9	1155.3	1156.7	1158.1	1158.2	1156.7	1155.4	1154.1	1152.6	1152.6
175°	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8	1161.0
177.5°	1165.1	1166.4	1167.7	1168.9	1170.3	1170.4	1169.2	1168.1	1167.0	1165.8	1165.8
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	17.0	16.1	16.9	16.6	16.7	18.5	19.8	19.9	18.6	17.4	16.1
90°	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7	4.9	7.1	9.4
92.5°	33.5	32.4	31.3	29.4	26.9	24.4	21.8	19.4	21.8	24.4	26.9
95°	65.8	64.5	63.0	61.4	59.7	57.8	56.0	54.2	56.0	57.8	59.7
97.5°	105.3	103.6	102.0	100.5	99.0	97.6	96.1	94.7	96.1	97.6	99.0
100°	134.6	132.8	131.0	129.7	128.9	128.0	127.2	126.4	127.2	128.0	128.9
102.5°	165.2	163.6	161.9	161.0	160.7	160.3	160.1	159.7	160.1	160.3	160.7
105°	213.4	212.6	211.8	211.2	211.1	210.9	210.7	210.4	210.7	210.9	211.1
107.5°	265.2	265.0	264.9	264.7	264.5	264.2	264.0	263.8	264.0	264.2	264.5
110°	301.2	301.4	301.6	301.5	301.1	300.7	300.3	299.9	300.3	300.7	301.1





TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.0	337.3	337.7	337.8	337.7	337.7	337.6	337.5	337.6	337.7	337.7
115°	392.9	393.2	393.7	393.9	393.9	393.9	393.9	393.9	393.9	393.9	393.9
117.5°	447.0	447.3	447.5	447.6	447.5	447.3	447.1	447.0	447.1	447.3	447.5
120°	484.5	485.1	485.7	485.6	484.8	484.0	483.2	482.4	483.2	484.0	484.8
122.5°	520.0	520.2	520.6	520.5	520.2	519.9	519.6	519.2	519.6	519.9	520.2
125°	573.1	573.3	573.5	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6
127.5°	624.8	625.2	625.5	625.4	624.7	624.1	623.6	622.9	623.6	624.1	624.7
130°	660.3	660.3	660.3	660.0	659.4	658.8	658.3	657.6	658.3	658.8	659.4
132.5°	694.6	694.8	694.9	694.8	694.4	693.9	693.5	693.0	693.5	693.9	694.4
135°	745.3	745.3	745.3	744.7	743.4	742.3	741.0	739.9	741.0	742.3	743.4
137.5°	794.2	793.8	793.4	793.0	792.5	791.9	791.3	790.8	791.3	791.9	792.5
140°	826.5	826.5	826.5	826.3	826.0	825.5	825.2	824.7	825.2	825.5	826.0
142.5°	857.2	857.4	857.6	857.5	857.0	856.7	856.2	855.9	856.2	856.7	857.0
145°	902.9	902.8	902.5	902.1	901.3	900.4	899.6	898.8	899.6	900.4	901.3
147.5°	945.4	945.6	945.7	945.3	944.3	943.4	942.4	941.5	942.4	943.4	944.3
150°	971.1	971.1	971.1	970.7	969.9	969.1	968.3	967.5	968.3	969.1	969.9
152.5°	994.6	994.4	994.3	994.0	993.5	993.0	992.6	992.0	992.6	993.0	993.5
155°	1029.3	1029.5	1029.7	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8
157.5°	1059.9	1059.9	1060.0	1060.2	1060.5	1060.9	1061.2	1061.6	1061.2	1060.9	1060.5
160°	1079.0	1079.1	1079.4	1079.6	1079.8	1080.0	1080.2	1080.4	1080.2	1080.0	1079.8
162.5°	1094.9	1095.1	1095.3	1095.6	1096.2	1096.7	1097.3	1097.7	1097.3	1096.7	1096.2
165°	1117.3	1117.8	1118.1	1118.7	1119.3	1119.8	1120.4	1121.1	1120.4	1119.8	1119.3
167.5°	1135.2	1135.2	1135.1	1135.6	1136.4	1137.3	1138.1	1138.9	1138.1	1137.3	1136.4
170°	1145.0	1144.9	1144.6	1145.0	1146.0	1147.0	1148.1	1149.1	1148.1	1147.0	1146.0
172.5°	1152.6	1152.5	1152.5	1152.9	1153.8	1154.6	1155.4	1156.3	1155.4	1154.6	1153.8
175°	1161.2	1161.4	1161.6	1162.2	1163.2	1164.2	1165.2	1166.2	1165.2	1164.2	1163.2
177.5°	1165.8	1165.8	1165.8	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1167.9	1167.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	16.6	16.3	16.7	15.9	16.8	17.0	16.8	16.9	17.8	16.9	17.0
90°	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3	23.5	24.7	25.5
92.5°	29.4	31.3	32.4	33.5	34.7	35.8	36.5	37.2	37.9	38.7	39.1
95°	61.4	63.0	64.5	65.8	67.2	68.7	69.3	69.8	70.4	71.1	71.3
97.5°	100.5	102.0	103.6	105.3	106.9	108.6	109.3	110.0	110.8	111.5	111.8
100°	129.7	131.0	132.8	134.6	136.4	138.2	138.6	139.0	139.4	139.8	140.0
102.5°	161.0	161.9	163.6	165.2	166.9	168.5	169.2	169.7	170.2	170.9	171.2
105°	211.2	211.8	212.6	213.4	214.2	215.0	215.6	216.2	216.8	217.4	218.0
107.5°	264.7	264.9	265.0	265.2	265.3	265.4	266.0	266.5	267.1	267.7	267.9
110°	301.5	301.6	301.4	301.2	301.0	300.8	300.4	300.0	299.6	299.2	299.3



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	337.8	337.7	337.3	337.0	336.6	336.3	336.2	336.1	336.0	335.9	335.9
115°	393.9	393.7	393.2	392.9	392.4	392.1	391.8	391.6	391.5	391.3	391.0
117.5°	447.6	447.5	447.3	447.0	446.7	446.4	445.8	445.1	444.3	443.7	443.2
120°	485.6	485.7	485.1	484.5	483.9	483.3	482.3	481.3	480.3	479.3	478.9
122.5°	520.5	520.6	520.2	520.0	519.7	519.4	518.7	518.1	517.4	516.7	515.9
125°	573.6	573.5	573.3	573.1	572.9	572.7	572.3	571.9	571.5	571.1	570.7
127.5°	625.4	625.5	625.2	624.8	624.6	624.2	623.8	623.4	623.0	622.6	622.2
130°	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.5	659.2	658.7	658.2
132.5°	694.8	694.9	694.8	694.6	694.5	694.3	693.9	693.5	693.1	692.7	692.3
135°	744.7	745.3	745.3	745.3	745.3	745.3	744.8	744.5	744.0	743.7	743.2
137.5°	793.0	793.4	793.8	794.2	794.4	794.8	794.2	793.7	793.2	792.6	792.5
140°	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.2	826.0	825.7	825.5
142.5°	857.5	857.6	857.4	857.2	857.1	856.9	856.8	856.8	856.8	856.8	856.7
145°	902.1	902.5	902.8	902.9	903.1	903.3	903.1	902.9	902.8	902.5	902.1
147.5°	945.3	945.7	945.6	945.4	945.2	945.0	944.9	944.8	944.6	944.4	944.2
150°	970.7	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.0
152.5°	994.0	994.3	994.4	994.6	994.8	995.0	995.4	995.9	996.4	996.8	996.8
155°	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2
157.5°	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4	1061.0	1061.6	1062.2	1062.2
160°	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1	1079.8	1080.4	1081.0	1080.8
162.5°	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6	1096.6	1097.7	1098.9	1098.9
165°	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8	1118.9	1120.2	1121.3	1121.5
167.5°	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5	1137.7	1138.9	1140.1	1140.1
170°	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7	1147.8	1149.1	1150.2	1150.1
172.5°	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1	1155.4	1156.7	1158.2	1158.1
175°	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4
177.5°	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0	1168.1	1169.2	1170.4	1170.3
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	18.3	17.8	17.3	17.9	17.3	17.8	18.3	17.0	16.9	17.8	16.9
90°	25.9	26.3	26.7	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3
92.5°	39.4	39.6	39.9	40.1	39.9	39.6	39.4	39.1	38.7	37.9	37.2
95°	71.3	71.3	71.3	71.3	71.3	71.3	71.3	71.3	71.1	70.4	69.8
97.5°	111.8	111.8	111.8	111.8	111.8	111.8	111.8	111.8	111.5	110.8	110.0
100°	140.0	140.0	140.0	140.0	140.0	140.0	140.0	140.0	139.8	139.4	139.0
102.5°	171.3	171.5	171.7	171.8	171.7	171.5	171.3	171.2	170.9	170.2	169.7
105°	218.6	219.2	219.8	220.4	219.8	219.2	218.6	218.0	217.4	216.8	216.2
107.5°	267.9	267.9	267.8	267.8	267.8	267.9	267.9	267.9	267.7	267.1	266.5
110°	299.9	300.5	301.1	301.8	301.1	300.5	299.9	299.3	299.2	299.6	300.0



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	336.1	336.2	336.3	336.4	336.3	336.2	336.1	335.9	335.9	336.0	336.1
115°	390.8	390.7	390.5	390.2	390.5	390.7	390.8	391.0	391.3	391.5	391.6
117.5°	442.7	442.4	441.9	441.6	441.9	442.4	442.7	443.2	443.7	444.3	445.1
120°	479.4	479.7	480.2	480.5	480.2	479.7	479.4	478.9	479.3	480.3	481.3
122.5°	515.2	514.5	513.8	513.1	513.8	514.5	515.2	515.9	516.7	517.4	518.1
125°	570.3	569.9	569.5	569.1	569.5	569.9	570.3	570.7	571.1	571.5	571.9
127.5°	621.9	621.6	621.3	621.0	621.3	621.6	621.9	622.2	622.6	623.0	623.4
130°	657.4	656.6	655.8	655.0	655.8	656.6	657.4	658.2	658.7	659.2	659.5
132.5°	692.1	691.7	691.3	691.1	691.3	691.7	692.1	692.3	692.7	693.1	693.5
135°	742.5	741.9	741.4	740.7	741.4	741.9	742.5	743.2	743.7	744.0	744.5
137.5°	792.6	792.7	792.8	792.9	792.8	792.7	792.6	792.5	792.6	793.2	793.7
140°	825.4	825.2	824.9	824.7	824.9	825.2	825.4	825.5	825.7	826.0	826.2
142.5°	856.7	856.7	856.6	856.6	856.6	856.7	856.7	856.7	856.8	856.8	856.8
145°	901.5	900.9	900.4	899.7	900.4	900.9	901.5	902.1	902.5	902.8	902.9
147.5°	944.1	943.9	943.6	943.4	943.6	943.9	944.1	944.2	944.4	944.6	944.8
150°	970.8	970.6	970.4	970.2	970.4	970.6	970.8	971.0	971.1	971.1	971.1
152.5°	996.3	995.8	995.2	994.8	995.2	995.8	996.3	996.8	996.8	996.4	995.9
155°	1031.4	1030.6	1029.7	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6
157.5°	1061.5	1060.8	1060.2	1059.4	1060.2	1060.8	1061.5	1062.2	1062.2	1061.6	1061.0
160°	1079.8	1078.8	1077.8	1076.7	1077.8	1078.8	1079.8	1080.8	1081.0	1080.4	1079.8
162.5°	1097.9	1096.9	1095.8	1094.8	1095.8	1096.9	1097.9	1098.9	1098.9	1097.7	1096.6
165°	1120.7	1119.9	1119.1	1118.3	1119.1	1119.9	1120.7	1121.5	1121.3	1120.2	1118.9
167.5°	1138.9	1137.6	1136.4	1135.1	1136.4	1137.6	1138.9	1140.1	1140.1	1138.9	1137.7
170°	1148.8	1147.4	1145.9	1144.5	1145.9	1147.4	1148.8	1150.1	1150.2	1149.1	1147.8
172.5°	1156.7	1155.3	1153.9	1152.4	1153.9	1155.3	1156.7	1158.1	1158.2	1156.7	1155.4
175°	1165.0	1163.6	1162.2	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6
177.5°	1168.9	1167.7	1166.4	1165.1	1166.4	1167.7	1168.9	1170.3	1170.4	1169.2	1168.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	16.8	17.0	16.8	15.9	16.7	16.3	16.6	16.1	17.4	18.6	19.9
90°	21.0	19.9	18.3	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7
92.5°	36.5	35.8	34.7	33.5	32.4	31.3	29.4	26.9	24.4	21.8	19.4
95°	69.3	68.7	67.2	65.8	64.5	63.0	61.4	59.7	57.8	56.0	54.2
97.5°	109.3	108.6	106.9	105.3	103.6	102.0	100.5	99.0	97.6	96.1	94.7
100°	138.6	138.2	136.4	134.6	132.8	131.0	129.7	128.9	128.0	127.2	126.4
102.5°	169.2	168.5	166.9	165.2	163.6	161.9	161.0	160.7	160.3	160.1	159.7
105°	215.6	215.0	214.2	213.4	212.6	211.8	211.2	211.1	210.9	210.7	210.4
107.5°	266.0	265.4	265.3	265.2	265.0	264.9	264.7	264.5	264.2	264.0	263.8
110°	300.4	300.8	301.0	301.2	301.4	301.6	301.5	301.1	300.7	300.3	299.9



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	336.2	336.3	336.6	337.0	337.3	337.7	337.8	337.7	337.7	337.6	337.5
115°	391.8	392.1	392.4	392.9	393.2	393.7	393.9	393.9	393.9	393.9	393.9
117.5°	445.8	446.4	446.7	447.0	447.3	447.5	447.6	447.5	447.3	447.1	447.0
120°	482.3	483.3	483.9	484.5	485.1	485.7	485.6	484.8	484.0	483.2	482.4
122.5°	518.7	519.4	519.7	520.0	520.2	520.6	520.5	520.2	519.9	519.6	519.2
125°	572.3	572.7	572.9	573.1	573.3	573.5	573.6	573.6	573.6	573.6	573.6
127.5°	623.8	624.2	624.6	624.8	625.2	625.5	625.4	624.7	624.1	623.6	622.9
130°	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.4	658.8	658.3	657.6
132.5°	693.9	694.3	694.5	694.6	694.8	694.9	694.8	694.4	693.9	693.5	693.0
135°	744.8	745.3	745.3	745.3	745.3	745.3	744.7	743.4	742.3	741.0	739.9
137.5°	794.2	794.8	794.4	794.2	793.8	793.4	793.0	792.5	791.9	791.3	790.8
140°	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.0	825.5	825.2	824.7
142.5°	856.8	856.9	857.1	857.2	857.4	857.6	857.5	857.0	856.7	856.2	855.9
145°	903.1	903.3	903.1	902.9	902.8	902.5	902.1	901.3	900.4	899.6	898.8
147.5°	944.9	945.0	945.2	945.4	945.6	945.7	945.3	944.3	943.4	942.4	941.5
150°	971.1	971.1	971.1	971.1	971.1	971.1	970.7	969.9	969.1	968.3	967.5
152.5°	995.4	995.0	994.8	994.6	994.4	994.3	994.0	993.5	993.0	992.6	992.0
155°	1029.7	1028.9	1029.1	1029.3	1029.5	1029.7	1029.8	1029.8	1029.8	1029.8	1029.8
157.5°	1060.4	1059.8	1059.8	1059.9	1059.9	1060.0	1060.2	1060.5	1060.9	1061.2	1061.6
160°	1079.1	1078.6	1078.8	1079.0	1079.1	1079.4	1079.6	1079.8	1080.0	1080.2	1080.4
162.5°	1095.6	1094.5	1094.7	1094.9	1095.1	1095.3	1095.6	1096.2	1096.7	1097.3	1097.7
165°	1117.8	1116.5	1117.0	1117.3	1117.8	1118.1	1118.7	1119.3	1119.8	1120.4	1121.1
167.5°	1136.5	1135.3	1135.2	1135.2	1135.2	1135.1	1135.6	1136.4	1137.3	1138.1	1138.9
170°	1146.7	1145.4	1145.2	1145.0	1144.9	1144.6	1145.0	1146.0	1147.0	1148.1	1149.1
172.5°	1154.1	1152.6	1152.6	1152.6	1152.5	1152.5	1152.9	1153.8	1154.6	1155.4	1156.3
175°	1162.2	1160.8	1161.0	1161.2	1161.4	1161.6	1162.2	1163.2	1164.2	1165.2	1166.2
177.5°	1167.0	1165.8	1165.8	1165.8	1165.8	1165.8	1166.3	1167.1	1167.9	1168.7	1169.5
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.8	18.5	16.7	16.6	16.9	16.1	17.0	17.3	17.7	17.3	18.7
90°	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3
92.5°	21.8	24.4	26.9	29.4	31.3	32.4	33.5	34.7	35.8	36.5	37.2
95°	56.0	57.8	59.7	61.4	63.0	64.5	65.8	67.2	68.7	69.3	69.8
97.5°	96.1	97.6	99.0	100.5	102.0	103.6	105.3	106.9	108.6	109.3	110.0
100°	127.2	128.0	128.9	129.7	131.0	132.8	134.6	136.4	138.2	138.6	139.0
102.5°	160.1	160.3	160.7	161.0	161.9	163.6	165.2	166.9	168.5	169.2	169.7
105°	210.7	210.9	211.1	211.2	211.8	212.6	213.4	214.2	215.0	215.6	216.2
107.5°	264.0	264.2	264.5	264.7	264.9	265.0	265.2	265.3	265.4	266.0	266.5
110°	300.3	300.7	301.1	301.5	301.6	301.4	301.2	301.0	300.8	300.4	300.0





TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	337.6	337.7	337.7	337.8	337.7	337.3	337.0	336.6	336.3	336.2	336.1
115°	393.9	393.9	393.9	393.9	393.7	393.2	392.9	392.4	392.1	391.8	391.6
117.5°	447.1	447.3	447.5	447.6	447.5	447.3	447.0	446.7	446.4	445.8	445.1
120°	483.2	484.0	484.8	485.6	485.7	485.1	484.5	483.9	483.3	482.3	481.3
122.5°	519.6	519.9	520.2	520.5	520.6	520.2	520.0	519.7	519.4	518.7	518.1
125°	573.6	573.6	573.6	573.6	573.5	573.3	573.1	572.9	572.7	572.3	571.9
127.5°	623.6	624.1	624.7	625.4	625.5	625.2	624.8	624.6	624.2	623.8	623.4
130°	658.3	658.8	659.4	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.5
132.5°	693.5	693.9	694.4	694.8	694.9	694.8	694.6	694.5	694.3	693.9	693.5
135°	741.0	742.3	743.4	744.7	745.3	745.3	745.3	745.3	745.3	744.8	744.5
137.5°	791.3	791.9	792.5	793.0	793.4	793.8	794.2	794.4	794.8	794.2	793.7
140°	825.2	825.5	826.0	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.2
142.5°	856.2	856.7	857.0	857.5	857.6	857.4	857.2	857.1	856.9	856.8	856.8
145°	899.6	900.4	901.3	902.1	902.5	902.8	902.9	903.1	903.3	903.1	902.9
147.5°	942.4	943.4	944.3	945.3	945.7	945.6	945.4	945.2	945.0	944.9	944.8
150°	968.3	969.1	969.9	970.7	971.1	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	992.6	993.0	993.5	994.0	994.3	994.4	994.6	994.8	995.0	995.4	995.9
155°	1029.8	1029.8	1029.8	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7	1030.6
157.5°	1061.2	1060.9	1060.5	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4	1061.0
160°	1080.2	1080.0	1079.8	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1	1079.8
162.5°	1097.3	1096.7	1096.2	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6	1096.6
165°	1120.4	1119.8	1119.3	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8	1118.9
167.5°	1138.1	1137.3	1136.4	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5	1137.7
170°	1148.1	1147.0	1146.0	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7	1147.8
172.5°	1155.4	1154.6	1153.8	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1	1155.4
175°	1165.2	1164.2	1163.2	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2	1163.6
177.5°	1168.7	1167.9	1167.1	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0	1168.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	17.8	17.5	18.2	17.7	17.8	17.3	17.9
90°	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	37.9	38.7	39.1	39.4	39.6	39.9	40.1
95°	70.4	71.1	71.3	71.3	71.3	71.3	71.3
97.5°	110.8	111.5	111.8	111.8	111.8	111.8	111.8
100°	139.4	139.8	140.0	140.0	140.0	140.0	140.0
102.5°	170.2	170.9	171.2	171.3	171.5	171.7	171.8
105°	216.8	217.4	218.0	218.6	219.2	219.8	220.4
107.5°	267.1	267.7	267.9	267.9	267.9	267.8	267.8
110°	299.6	299.2	299.3	299.9	300.5	301.1	301.8



TEST NUMBER: P333104-940

CATALOG NUMBER: S124RDIW-S1195D1050U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	336.0	335.9	335.9	336.1	336.2	336.3	336.4
115°	391.5	391.3	391.0	390.8	390.7	390.5	390.2
117.5°	444.3	443.7	443.2	442.7	442.4	441.9	441.6
120°	480.3	479.3	478.9	479.4	479.7	480.2	480.5
122.5°	517.4	516.7	515.9	515.2	514.5	513.8	513.1
125°	571.5	571.1	570.7	570.3	569.9	569.5	569.1
127.5°	623.0	622.6	622.2	621.9	621.6	621.3	621.0
130°	659.2	658.7	658.2	657.4	656.6	655.8	655.0
132.5°	693.1	692.7	692.3	692.1	691.7	691.3	691.1
135°	744.0	743.7	743.2	742.5	741.9	741.4	740.7
137.5°	793.2	792.6	792.5	792.6	792.7	792.8	792.9
140°	826.0	825.7	825.5	825.4	825.2	824.9	824.7
142.5°	856.8	856.8	856.7	856.7	856.7	856.6	856.6
145°	902.8	902.5	902.1	901.5	900.9	900.4	899.7
147.5°	944.6	944.4	944.2	944.1	943.9	943.6	943.4
150°	971.1	971.1	971.0	970.8	970.6	970.4	970.2
152.5°	996.4	996.8	996.8	996.3	995.8	995.2	994.8
155°	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9
157.5°	1061.6	1062.2	1062.2	1061.5	1060.8	1060.2	1059.4
160°	1080.4	1081.0	1080.8	1079.8	1078.8	1077.8	1076.7
162.5°	1097.7	1098.9	1098.9	1097.9	1096.9	1095.8	1094.8
165°	1120.2	1121.3	1121.5	1120.7	1119.9	1119.1	1118.3
167.5°	1138.9	1140.1	1140.1	1138.9	1137.6	1136.4	1135.1
170°	1149.1	1150.2	1150.1	1148.8	1147.4	1145.9	1144.5
172.5°	1156.7	1158.2	1158.1	1156.7	1155.3	1153.9	1152.4
175°	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8
177.5°	1169.2	1170.4	1170.3	1168.9	1167.7	1166.4	1165.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1

(END OF REPORT)