

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333107-940

Luminaire Tested: **S124RDIW-S1195D1340U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333107-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9254.6 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42				42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36				36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31				31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27				27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23				23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21				21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17				17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	19	17	15				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	1.9
10°-20°	516.5	5.6
20°-30°	807.8	8.7
30°-40°	898.0	9.7
40°-50°	796.7	8.6
50°-60°	620.8	6.7
60°-70°	406.5	4.4
70°-80°	199.9	2.2
80°-90°	53.8	0.6
90°-100°	52.9	0.6
100°-110°	337.2	3.6
110°-120°	645.1	7.0
120°-130°	818.9	8.8
130°-140°	876.2	9.5
140°-150°	819.3	8.9
150°-160°	660.7	7.1
160°-170°	426.2	4.6
170°-180°	146.9	1.6
0°-30°	1495.5	16.2
0°-40°	2393.5	25.9
0°-60°	3811.0	41.2
0°-90°	4471.2	48.3
90°-120°	1035.2	11.2
90°-150°	3549.6	38.4
90°-180°	4783.0	51.7
0°-180°	9254.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	35	4	35	4	35	17
95°	34	64	34	64	34	27
105°	330	348	330	348	330	288
115°	655	650	655	650	655	648
125°	921	914	921	914	921	820
135°	1142	1134	1142	1134	1142	879
145°	1314	1307	1314	1307	1314	821
155°	1432	1433	1432	1433	1432	660
165°	1505	1512	1505	1512	1505	425
175°	1537	1546	1537	1546	1537	146
180°	1546	1546	1546	1546	1546	



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	19.4	18.8	19.3	19.2	19.6	18.8	19.1	20.0	18.5	18.7	18.4
90°	34.7	34.2	33.7	33.2	32.6	31.7	30.1	28.5	27.0	25.4	23.4
92.5°	31.9	31.8	31.7	31.7	31.5	30.7	29.2	27.6	26.0	24.5	22.5
95°	33.5	33.3	33.0	32.7	32.5	31.7	30.1	28.5	27.0	25.4	25.1
97.5°	32.4	32.1	31.8	31.7	31.4	31.1	31.0	30.9	30.7	30.5	29.2
100°	32.4	32.1	31.8	31.7	31.4	33.4	37.8	42.2	46.5	50.9	86.3
102.5°	33.3	33.3	33.2	33.2	33.1	56.6	103.8	151.0	198.0	245.2	249.9
105°	329.7	338.9	348.1	357.4	366.7	370.1	367.8	365.5	363.2	360.9	359.5
107.5°	459.4	458.4	457.4	456.5	455.5	454.4	453.3	452.2	451.0	450.0	448.2
110°	515.9	515.1	514.3	513.5	512.7	512.1	511.6	511.1	510.6	510.1	508.5



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.3	571.3	570.3	569.4	568.4	567.9	568.0	568.1	568.3	568.4	567.7
115°	654.6	654.6	654.6	654.6	654.6	654.3	653.9	653.4	652.8	652.3	652.6
117.5°	738.3	738.5	738.6	738.7	738.8	738.9	739.0	739.0	739.2	739.3	738.7
120°	791.1	791.7	792.1	792.6	793.2	793.2	792.6	792.1	791.7	791.1	791.4
122.5°	842.9	843.5	843.9	844.5	845.0	845.1	844.8	844.5	844.2	843.8	843.5
125°	920.7	920.4	920.2	919.9	919.6	919.1	918.4	917.6	916.8	916.1	916.5
127.5°	988.9	989.1	989.3	989.5	989.7	989.9	990.1	990.2	990.3	990.5	989.4
130°	1035.2	1035.2	1035.2	1035.2	1035.2	1035.0	1034.7	1034.5	1034.3	1034.0	1033.2
132.5°	1077.7	1077.9	1078.2	1078.3	1078.5	1078.5	1078.3	1078.0	1077.7	1077.5	1076.5
135°	1141.6	1141.0	1140.5	1140.1	1139.5	1139.0	1138.4	1138.0	1137.5	1136.9	1136.0
137.5°	1196.1	1196.3	1196.5	1196.6	1196.8	1196.6	1196.0	1195.4	1194.9	1194.3	1193.2
140°	1234.1	1233.9	1233.6	1233.3	1233.1	1232.5	1231.8	1231.0	1230.2	1229.5	1229.0
142.5°	1265.5	1265.5	1265.4	1265.4	1265.3	1265.1	1264.4	1263.9	1263.4	1262.8	1262.5
145°	1313.9	1313.4	1312.9	1312.3	1311.9	1311.4	1311.2	1310.9	1310.7	1310.5	1310.5
147.5°	1353.9	1353.6	1353.4	1353.2	1352.9	1352.6	1352.5	1352.3	1352.0	1351.8	1352.1
150°	1379.8	1379.6	1379.3	1379.0	1378.8	1378.7	1378.7	1378.7	1378.7	1378.7	1378.9
152.5°	1402.0	1402.2	1402.3	1402.5	1402.7	1402.5	1402.1	1401.7	1401.3	1400.9	1401.3
155°	1431.9	1432.6	1433.4	1434.2	1434.9	1434.9	1433.8	1432.8	1431.7	1430.7	1431.5
157.5°	1456.9	1458.2	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9	1457.8
160°	1473.6	1475.1	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6	1473.7
162.5°	1486.5	1488.2	1490.0	1491.7	1493.4	1493.5	1492.0	1490.5	1488.9	1487.4	1487.6
165°	1504.8	1507.1	1509.4	1511.7	1513.9	1514.1	1512.1	1510.0	1508.0	1505.9	1505.9
167.5°	1518.4	1521.0	1523.5	1526.1	1528.7	1528.8	1526.5	1524.3	1522.1	1519.7	1519.9
170°	1526.7	1529.3	1531.9	1534.5	1537.0	1537.2	1535.2	1533.1	1531.1	1529.0	1528.7
172.5°	1531.3	1534.1	1536.9	1539.6	1542.5	1542.8	1540.8	1538.6	1536.6	1534.5	1534.3
175°	1537.1	1540.2	1543.3	1546.4	1549.4	1549.9	1547.6	1545.2	1542.9	1540.6	1540.3
177.5°	1540.8	1543.3	1545.8	1548.2	1550.7	1551.1	1549.4	1547.8	1546.1	1544.5	1544.1
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	17.9	16.9	17.7	17.2	17.2	18.9	20.1	20.1	18.9	17.7	16.6
90°	21.3	19.3	17.2	14.8	11.9	9.1	6.3	3.5	6.3	9.1	11.9
92.5°	20.4	18.4	16.3	15.2	15.1	14.9	14.7	14.5	14.7	14.9	15.1
95°	25.0	24.7	24.4	28.6	37.4	46.1	54.8	63.6	54.8	46.1	37.4
97.5°	87.9	116.5	145.3	156.9	151.4	146.0	140.5	135.1	140.5	146.0	151.4
100°	121.8	157.3	192.8	208.2	203.6	198.9	194.3	189.7	194.3	198.9	203.6
102.5°	254.5	259.0	263.7	264.3	260.9	257.5	254.1	250.7	254.1	257.5	260.9
105°	358.3	357.0	355.7	354.3	352.8	351.2	349.6	348.1	349.6	351.2	352.8
107.5°	446.4	444.7	442.9	441.7	440.9	440.1	439.3	438.5	439.3	440.1	440.9
110°	506.9	505.4	503.9	502.7	501.9	501.2	500.4	499.6	500.4	501.2	501.9



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	566.9	566.2	565.4	564.5	563.0	561.7	560.3	558.8	560.3	561.7	563.0
115°	652.8	653.1	653.4	653.1	652.3	651.6	650.8	650.0	650.8	651.6	652.3
117.5°	738.2	737.6	737.0	736.2	735.2	734.1	733.2	732.1	733.2	734.1	735.2
120°	791.7	791.9	792.1	791.8	790.8	789.7	788.6	787.6	788.6	789.7	790.8
122.5°	843.1	842.8	842.4	842.0	841.3	840.7	840.1	839.5	840.1	840.7	841.3
125°	917.0	917.6	918.1	917.8	916.8	915.8	914.7	913.7	914.7	915.8	916.8
127.5°	988.1	986.9	985.8	985.1	984.8	984.5	984.3	984.0	984.3	984.5	984.8
130°	1032.4	1031.7	1030.9	1030.4	1030.1	1029.9	1029.7	1029.4	1029.7	1029.9	1030.1
132.5°	1075.5	1074.6	1073.6	1072.8	1072.4	1071.9	1071.5	1071.0	1071.5	1071.9	1072.4
135°	1134.9	1133.8	1132.8	1132.5	1132.7	1132.9	1133.2	1133.5	1133.2	1132.9	1132.7
137.5°	1192.0	1190.9	1189.8	1189.2	1189.1	1188.9	1188.8	1188.7	1188.8	1188.9	1189.1
140°	1228.4	1227.9	1227.4	1226.9	1226.4	1225.8	1225.4	1224.9	1225.4	1225.8	1226.4
142.5°	1262.1	1261.9	1261.5	1261.0	1260.0	1259.1	1258.1	1257.2	1258.1	1259.1	1260.0
145°	1310.5	1310.5	1310.5	1310.0	1309.3	1308.5	1307.7	1307.0	1307.7	1308.5	1309.3
147.5°	1352.4	1352.6	1352.9	1352.3	1350.9	1349.4	1347.9	1346.5	1347.9	1349.4	1350.9
150°	1379.2	1379.5	1379.7	1379.3	1378.3	1377.2	1376.3	1375.2	1376.3	1377.2	1378.3
152.5°	1401.8	1402.3	1402.8	1402.6	1401.7	1400.9	1400.1	1399.3	1400.1	1400.9	1401.7
155°	1432.3	1433.1	1433.8	1434.0	1433.8	1433.5	1433.2	1433.1	1433.2	1433.5	1433.8
157.5°	1458.6	1459.5	1460.4	1460.9	1461.0	1461.2	1461.3	1461.5	1461.3	1461.2	1461.0
160°	1474.0	1474.3	1474.5	1475.1	1475.8	1476.6	1477.4	1478.1	1477.4	1476.6	1475.8
162.5°	1487.9	1488.2	1488.4	1489.1	1490.0	1491.0	1491.9	1492.9	1491.9	1491.0	1490.0
165°	1505.9	1505.9	1505.9	1506.5	1507.8	1509.1	1510.4	1511.7	1510.4	1509.1	1507.8
167.5°	1520.1	1520.3	1520.4	1521.2	1522.5	1523.8	1525.2	1526.5	1525.2	1523.8	1522.5
170°	1528.5	1528.2	1528.0	1528.7	1530.2	1531.7	1533.3	1534.8	1533.3	1531.7	1530.2
172.5°	1534.1	1533.8	1533.6	1534.2	1535.7	1537.3	1538.8	1540.3	1538.8	1537.3	1535.7
175°	1540.1	1539.8	1539.5	1540.2	1541.8	1543.3	1544.8	1546.4	1544.8	1543.3	1541.8
177.5°	1543.7	1543.3	1542.8	1543.4	1544.8	1546.2	1547.7	1549.2	1547.7	1546.2	1544.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	17.2	17.1	17.6	16.8	17.7	18.2	17.9	18.3	19.1	18.3	18.5
90°	14.8	17.2	19.3	21.3	23.4	25.4	27.0	28.5	30.1	31.7	32.6
92.5°	15.2	16.3	18.4	20.4	22.5	24.5	26.0	27.6	29.2	30.7	31.5
95°	28.6	24.4	24.7	25.0	25.1	25.4	27.0	28.5	30.1	31.7	32.5
97.5°	156.9	145.3	116.5	87.9	59.2	30.5	30.7	30.9	31.0	31.1	31.4
100°	208.2	192.8	157.3	121.8	86.3	50.9	46.5	42.2	37.8	33.4	31.4
102.5°	264.3	263.7	259.0	254.5	249.9	245.2	198.0	151.0	103.8	56.6	33.1
105°	354.3	355.7	357.0	358.3	359.5	360.9	363.2	365.5	367.8	370.1	366.7
107.5°	441.7	442.9	444.7	446.4	448.2	450.0	451.0	452.2	453.3	454.4	455.5
110°	502.7	503.9	505.4	506.9	508.5	510.1	510.6	511.1	511.6	512.1	512.7



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	564.5	565.4	566.2	566.9	567.7	568.4	568.3	568.1	568.0	567.9	568.4
115°	653.1	653.4	653.1	652.8	652.6	652.3	652.8	653.4	653.9	654.3	654.6
117.5°	736.2	737.0	737.6	738.2	738.7	739.3	739.2	739.0	739.0	738.9	738.8
120°	791.8	792.1	791.9	791.7	791.4	791.1	791.7	792.1	792.6	793.2	793.2
122.5°	842.0	842.4	842.8	843.1	843.5	843.8	844.2	844.5	844.8	845.1	845.0
125°	917.8	918.1	917.6	917.0	916.5	916.1	916.8	917.6	918.4	919.1	919.6
127.5°	985.1	985.8	986.9	988.1	989.4	990.5	990.3	990.2	990.1	989.9	989.7
130°	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3	1034.5	1034.7	1035.0	1035.2
132.5°	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7	1078.0	1078.3	1078.5	1078.5
135°	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5	1138.0	1138.4	1139.0	1139.5
137.5°	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9	1195.4	1196.0	1196.6	1196.8
140°	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2	1231.0	1231.8	1232.5	1233.1
142.5°	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4	1263.9	1264.4	1265.1	1265.3
145°	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7	1310.9	1311.2	1311.4	1311.9
147.5°	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0	1352.3	1352.5	1352.6	1352.9
150°	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7	1378.7	1378.7	1378.7	1378.8
152.5°	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3	1401.7	1402.1	1402.5	1402.7
155°	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7	1432.8	1433.8	1434.9	1434.9
157.5°	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2	1459.6	1460.9	1462.2	1462.2
160°	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1	1476.6	1478.1	1479.7	1479.7
162.5°	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9	1490.5	1492.0	1493.5	1493.4
165°	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0	1510.0	1512.1	1514.1	1513.9
167.5°	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1	1524.3	1526.5	1528.8	1528.7
170°	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1	1533.1	1535.2	1537.2	1537.0
172.5°	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6	1538.6	1540.8	1542.8	1542.5
175°	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9	1545.2	1547.6	1549.9	1549.4
177.5°	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1	1547.8	1549.4	1551.1	1550.7
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	19.7	19.3	18.8	19.4	18.8	19.3	19.7	18.5	18.3	19.1	18.3
90°	33.2	33.7	34.2	34.7	34.2	33.7	33.2	32.6	31.7	30.1	28.5
92.5°	31.7	31.7	31.8	31.9	31.8	31.7	31.7	31.5	30.7	29.2	27.6
95°	32.7	33.0	33.3	33.5	33.3	33.0	32.7	32.5	31.7	30.1	28.5
97.5°	31.7	31.8	32.1	32.4	32.1	31.8	31.7	31.4	31.1	31.0	30.9
100°	31.7	31.8	32.1	32.4	32.1	31.8	31.7	31.4	33.4	37.8	42.2
102.5°	33.2	33.2	33.3	33.3	33.3	33.2	33.2	33.1	56.6	103.8	151.0
105°	357.4	348.1	338.9	329.7	338.9	348.1	357.4	366.7	370.1	367.8	365.5
107.5°	456.5	457.4	458.4	459.4	458.4	457.4	456.5	455.5	454.4	453.3	452.2
110°	513.5	514.3	515.1	515.9	515.1	514.3	513.5	512.7	512.1	511.6	511.1



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	569.4	570.3	571.3	572.3	571.3	570.3	569.4	568.4	567.9	568.0	568.1
115°	654.6	654.6	654.6	654.6	654.6	654.6	654.6	654.6	654.3	653.9	653.4
117.5°	738.7	738.6	738.5	738.3	738.5	738.6	738.7	738.8	738.9	739.0	739.0
120°	792.6	792.1	791.7	791.1	791.7	792.1	792.6	793.2	793.2	792.6	792.1
122.5°	844.5	843.9	843.5	842.9	843.5	843.9	844.5	845.0	845.1	844.8	844.5
125°	919.9	920.2	920.4	920.7	920.4	920.2	919.9	919.6	919.1	918.4	917.6
127.5°	989.5	989.3	989.1	988.9	989.1	989.3	989.5	989.7	989.9	990.1	990.2
130°	1035.2	1035.2	1035.2	1035.2	1035.2	1035.2	1035.2	1035.2	1035.0	1034.7	1034.5
132.5°	1078.3	1078.2	1077.9	1077.7	1077.9	1078.2	1078.3	1078.5	1078.5	1078.3	1078.0
135°	1140.1	1140.5	1141.0	1141.6	1141.0	1140.5	1140.1	1139.5	1139.0	1138.4	1138.0
137.5°	1196.6	1196.5	1196.3	1196.1	1196.3	1196.5	1196.6	1196.8	1196.6	1196.0	1195.4
140°	1233.3	1233.6	1233.9	1234.1	1233.9	1233.6	1233.3	1233.1	1232.5	1231.8	1231.0
142.5°	1265.4	1265.4	1265.5	1265.5	1265.5	1265.4	1265.4	1265.3	1265.1	1264.4	1263.9
145°	1312.3	1312.9	1313.4	1313.9	1313.4	1312.9	1312.3	1311.9	1311.4	1311.2	1310.9
147.5°	1353.2	1353.4	1353.6	1353.9	1353.6	1353.4	1353.2	1352.9	1352.6	1352.5	1352.3
150°	1379.0	1379.3	1379.6	1379.8	1379.6	1379.3	1379.0	1378.8	1378.7	1378.7	1378.7
152.5°	1402.5	1402.3	1402.2	1402.0	1402.2	1402.3	1402.5	1402.7	1402.5	1402.1	1401.7
155°	1434.2	1433.4	1432.6	1431.9	1432.6	1433.4	1434.2	1434.9	1434.9	1433.8	1432.8
157.5°	1460.9	1459.6	1458.2	1456.9	1458.2	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6
160°	1478.1	1476.6	1475.1	1473.6	1475.1	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6
162.5°	1491.7	1490.0	1488.2	1486.5	1488.2	1490.0	1491.7	1493.4	1493.5	1492.0	1490.5
165°	1511.7	1509.4	1507.1	1504.8	1507.1	1509.4	1511.7	1513.9	1514.1	1512.1	1510.0
167.5°	1526.1	1523.5	1521.0	1518.4	1521.0	1523.5	1526.1	1528.7	1528.8	1526.5	1524.3
170°	1534.5	1531.9	1529.3	1526.7	1529.3	1531.9	1534.5	1537.0	1537.2	1535.2	1533.1
172.5°	1539.6	1536.9	1534.1	1531.3	1534.1	1536.9	1539.6	1542.5	1542.8	1540.8	1538.6
175°	1546.4	1543.3	1540.2	1537.1	1540.2	1543.3	1546.4	1549.4	1549.9	1547.6	1545.2
177.5°	1548.2	1545.8	1543.3	1540.8	1543.3	1545.8	1548.2	1550.7	1551.1	1549.4	1547.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	17.9	18.2	17.7	16.8	17.6	17.1	17.2	16.6	17.7	18.9	20.1
90°	27.0	25.4	23.4	21.3	19.3	17.2	14.8	11.9	9.1	6.3	3.5
92.5°	26.0	24.5	22.5	20.4	18.4	16.3	15.2	15.1	14.9	14.7	14.5
95°	27.0	25.4	25.1	25.0	24.7	24.4	28.6	37.4	46.1	54.8	63.6
97.5°	30.7	30.5	59.2	87.9	116.5	145.3	156.9	151.4	146.0	140.5	135.1
100°	46.5	50.9	86.3	121.8	157.3	192.8	208.2	203.6	198.9	194.3	189.7
102.5°	198.0	245.2	249.9	254.5	259.0	263.7	264.3	260.9	257.5	254.1	250.7
105°	363.2	360.9	359.5	358.3	357.0	355.7	354.3	352.8	351.2	349.6	348.1
107.5°	451.0	450.0	448.2	446.4	444.7	442.9	441.7	440.9	440.1	439.3	438.5
110°	510.6	510.1	508.5	506.9	505.4	503.9	502.7	501.9	501.2	500.4	499.6



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	568.3	568.4	567.7	566.9	566.2	565.4	564.5	563.0	561.7	560.3	558.8
115°	652.8	652.3	652.6	652.8	653.1	653.4	653.1	652.3	651.6	650.8	650.0
117.5°	739.2	739.3	738.7	738.2	737.6	737.0	736.2	735.2	734.1	733.2	732.1
120°	791.7	791.1	791.4	791.7	791.9	792.1	791.8	790.8	789.7	788.6	787.6
122.5°	844.2	843.8	843.5	843.1	842.8	842.4	842.0	841.3	840.7	840.1	839.5
125°	916.8	916.1	916.5	917.0	917.6	918.1	917.8	916.8	915.8	914.7	913.7
127.5°	990.3	990.5	989.4	988.1	986.9	985.8	985.1	984.8	984.5	984.3	984.0
130°	1034.3	1034.0	1033.2	1032.4	1031.7	1030.9	1030.4	1030.1	1029.9	1029.7	1029.4
132.5°	1077.7	1077.5	1076.5	1075.5	1074.6	1073.6	1072.8	1072.4	1071.9	1071.5	1071.0
135°	1137.5	1136.9	1136.0	1134.9	1133.8	1132.8	1132.5	1132.7	1132.9	1133.2	1133.5
137.5°	1194.9	1194.3	1193.2	1192.0	1190.9	1189.8	1189.2	1189.1	1188.9	1188.8	1188.7
140°	1230.2	1229.5	1229.0	1228.4	1227.9	1227.4	1226.9	1226.4	1225.8	1225.4	1224.9
142.5°	1263.4	1262.8	1262.5	1262.1	1261.9	1261.5	1261.0	1260.0	1259.1	1258.1	1257.2
145°	1310.7	1310.5	1310.5	1310.5	1310.5	1310.5	1310.0	1309.3	1308.5	1307.7	1307.0
147.5°	1352.0	1351.8	1352.1	1352.4	1352.6	1352.9	1352.3	1350.9	1349.4	1347.9	1346.5
150°	1378.7	1378.7	1378.9	1379.2	1379.5	1379.7	1379.3	1378.3	1377.2	1376.3	1375.2
152.5°	1401.3	1400.9	1401.3	1401.8	1402.3	1402.8	1402.6	1401.7	1400.9	1400.1	1399.3
155°	1431.7	1430.7	1431.5	1432.3	1433.1	1433.8	1434.0	1433.8	1433.5	1433.2	1433.1
157.5°	1458.2	1456.9	1457.8	1458.6	1459.5	1460.4	1460.9	1461.0	1461.2	1461.3	1461.5
160°	1475.1	1473.6	1473.7	1474.0	1474.3	1474.5	1475.1	1475.8	1476.6	1477.4	1478.1
162.5°	1488.9	1487.4	1487.6	1487.9	1488.2	1488.4	1489.1	1490.0	1491.0	1491.9	1492.9
165°	1508.0	1505.9	1505.9	1505.9	1505.9	1505.9	1506.5	1507.8	1509.1	1510.4	1511.7
167.5°	1522.1	1519.7	1519.9	1520.1	1520.3	1520.4	1521.2	1522.5	1523.8	1525.2	1526.5
170°	1531.1	1529.0	1528.7	1528.5	1528.2	1528.0	1528.7	1530.2	1531.7	1533.3	1534.8
172.5°	1536.6	1534.5	1534.3	1534.1	1533.8	1533.6	1534.2	1535.7	1537.3	1538.8	1540.3
175°	1542.9	1540.6	1540.3	1540.1	1539.8	1539.5	1540.2	1541.8	1543.3	1544.8	1546.4
177.5°	1546.1	1544.5	1544.1	1543.7	1543.3	1542.8	1543.4	1544.8	1546.2	1547.7	1549.2
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	20.1	18.9	17.2	17.2	17.7	16.9	17.9	18.4	18.7	18.5	20.0
90°	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0	28.5
92.5°	14.7	14.9	15.1	15.2	16.3	18.4	20.4	22.5	24.5	26.0	27.6
95°	54.8	46.1	37.4	28.6	24.4	24.7	25.0	25.1	25.4	27.0	28.5
97.5°	140.5	146.0	151.4	156.9	145.3	116.5	87.9	59.2	30.5	30.7	30.9
100°	194.3	198.9	203.6	208.2	192.8	157.3	121.8	86.3	50.9	46.5	42.2
102.5°	254.1	257.5	260.9	264.3	263.7	259.0	254.5	249.9	245.2	198.0	151.0
105°	349.6	351.2	352.8	354.3	355.7	357.0	358.3	359.5	360.9	363.2	365.5
107.5°	439.3	440.1	440.9	441.7	442.9	444.7	446.4	448.2	450.0	451.0	452.2
110°	500.4	501.2	501.9	502.7	503.9	505.4	506.9	508.5	510.1	510.6	511.1



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	560.3	561.7	563.0	564.5	565.4	566.2	566.9	567.7	568.4	568.3	568.1
115°	650.8	651.6	652.3	653.1	653.4	653.1	652.8	652.6	652.3	652.8	653.4
117.5°	733.2	734.1	735.2	736.2	737.0	737.6	738.2	738.7	739.3	739.2	739.0
120°	788.6	789.7	790.8	791.8	792.1	791.9	791.7	791.4	791.1	791.7	792.1
122.5°	840.1	840.7	841.3	842.0	842.4	842.8	843.1	843.5	843.8	844.2	844.5
125°	914.7	915.8	916.8	917.8	918.1	917.6	917.0	916.5	916.1	916.8	917.6
127.5°	984.3	984.5	984.8	985.1	985.8	986.9	988.1	989.4	990.5	990.3	990.2
130°	1029.7	1029.9	1030.1	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3	1034.5
132.5°	1071.5	1071.9	1072.4	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7	1078.0
135°	1133.2	1132.9	1132.7	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5	1138.0
137.5°	1188.8	1188.9	1189.1	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9	1195.4
140°	1225.4	1225.8	1226.4	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2	1231.0
142.5°	1258.1	1259.1	1260.0	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4	1263.9
145°	1307.7	1308.5	1309.3	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7	1310.9
147.5°	1347.9	1349.4	1350.9	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0	1352.3
150°	1376.3	1377.2	1378.3	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7	1378.7
152.5°	1400.1	1400.9	1401.7	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3	1401.7
155°	1433.2	1433.5	1433.8	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7	1432.8
157.5°	1461.3	1461.2	1461.0	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2	1459.6
160°	1477.4	1476.6	1475.8	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1	1476.6
162.5°	1491.9	1491.0	1490.0	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9	1490.5
165°	1510.4	1509.1	1507.8	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0	1510.0
167.5°	1525.2	1523.8	1522.5	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1	1524.3
170°	1533.3	1531.7	1530.2	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1	1533.1
172.5°	1538.8	1537.3	1535.7	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6	1538.6
175°	1544.8	1543.3	1541.8	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9	1545.2
177.5°	1547.7	1546.2	1544.8	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1	1547.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	19.1	18.8	19.6	19.2	19.3	18.8	19.4
90°	30.1	31.7	32.6	33.2	33.7	34.2	34.7
92.5°	29.2	30.7	31.5	31.7	31.7	31.8	31.9
95°	30.1	31.7	32.5	32.7	33.0	33.3	33.5
97.5°	31.0	31.1	31.4	31.7	31.8	32.1	32.4
100°	37.8	33.4	31.4	31.7	31.8	32.1	32.4
102.5°	103.8	56.6	33.1	33.2	33.2	33.3	33.3
105°	367.8	370.1	366.7	357.4	348.1	338.9	329.7
107.5°	453.3	454.4	455.5	456.5	457.4	458.4	459.4
110°	511.6	512.1	512.7	513.5	514.3	515.1	515.9



TEST NUMBER: P333107-940

CATALOG NUMBER: S124RDIW-S1195D1340U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	568.0	567.9	568.4	569.4	570.3	571.3	572.3
115°	653.9	654.3	654.6	654.6	654.6	654.6	654.6
117.5°	739.0	738.9	738.8	738.7	738.6	738.5	738.3
120°	792.6	793.2	793.2	792.6	792.1	791.7	791.1
122.5°	844.8	845.1	845.0	844.5	843.9	843.5	842.9
125°	918.4	919.1	919.6	919.9	920.2	920.4	920.7
127.5°	990.1	989.9	989.7	989.5	989.3	989.1	988.9
130°	1034.7	1035.0	1035.2	1035.2	1035.2	1035.2	1035.2
132.5°	1078.3	1078.5	1078.5	1078.3	1078.2	1077.9	1077.7
135°	1138.4	1139.0	1139.5	1140.1	1140.5	1141.0	1141.6
137.5°	1196.0	1196.6	1196.8	1196.6	1196.5	1196.3	1196.1
140°	1231.8	1232.5	1233.1	1233.3	1233.6	1233.9	1234.1
142.5°	1264.4	1265.1	1265.3	1265.4	1265.4	1265.5	1265.5
145°	1311.2	1311.4	1311.9	1312.3	1312.9	1313.4	1313.9
147.5°	1352.5	1352.6	1352.9	1353.2	1353.4	1353.6	1353.9
150°	1378.7	1378.7	1378.8	1379.0	1379.3	1379.6	1379.8
152.5°	1402.1	1402.5	1402.7	1402.5	1402.3	1402.2	1402.0
155°	1433.8	1434.9	1434.9	1434.2	1433.4	1432.6	1431.9
157.5°	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9
160°	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6
162.5°	1492.0	1493.5	1493.4	1491.7	1490.0	1488.2	1486.5
165°	1512.1	1514.1	1513.9	1511.7	1509.4	1507.1	1504.8
167.5°	1526.5	1528.8	1528.7	1526.1	1523.5	1521.0	1518.4
170°	1535.2	1537.2	1537.0	1534.5	1531.9	1529.3	1526.7
172.5°	1540.8	1542.8	1542.5	1539.6	1536.9	1534.1	1531.3
175°	1547.6	1549.9	1549.4	1546.4	1543.3	1540.2	1537.1
177.5°	1549.4	1551.1	1550.7	1548.2	1545.8	1543.3	1540.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4

(END OF REPORT)