

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333667-830

Luminaire Tested: **S125RDIW-S610D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333667-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4750.8 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6124	6124	6124
5°	6137	6067	6105
10°	6091	6011	6011
15°	6019	5889	5841
20°	5926	5720	5650
25°	5818	5552	5430
30°	5683	5357	5186
35°	5544	5155	4912
40°	5415	4945	4643
45°	5259	4709	4350
50°	5101	4454	4044
55°	4919	4209	3718
60°	4735	3912	3367
65°	4520	3568	2966
70°	4273	3138	2555
75°	3933	2643	2126
80°	3463	2079	1785
85°	2920	1697	1593



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	1.9
10°-20°	249.2	5.2
20°-30°	361.3	7.6
30°-40°	411.8	8.7
40°-50°	401.4	8.4
50°-60°	337.9	7.1
60°-70°	236.8	5.0
70°-80°	121.7	2.6
80°-90°	32.7	0.7
90°-100°	60.2	1.3
100°-110°	177.8	3.7
110°-120°	301.2	6.3
120°-130°	396.4	8.3
130°-140°	444.2	9.3
140°-150°	435.3	9.2
150°-160°	365.6	7.7
160°-170°	243.1	5.1
170°-180°	85.1	1.8
0°-30°	699.6	14.7
0°-40°	1111.4	23.4
0°-60°	1850.7	39.0
0°-90°	2241.9	47.2
90°-120°	539.3	11.4
90°-150°	1815.1	38.2
90°-180°	2509.0	52.8
0°-180°	4750.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	944	936	943	942	90
15°	900	895	881	880	874	254
25°	816	805	779	770	762	375
35°	703	685	654	634	623	440
45°	576	554	516	488	476	444
55°	437	413	374	343	330	391
65°	296	271	234	206	194	293
75°	158	136	106	91	85	167
85°	39	27	23	22	22	44
90°	1	6	11	15	17	4
95°	46	47	54	59	60	49
105°	160	163	167	171	174	170
115°	302	304	306	305	304	298
125°	440	444	445	444	443	394
135°	572	576	577	577	574	441
145°	693	696	698	698	696	433
155°	793	793	794	797	793	365
165°	863	861	862	864	861	243
175°	897	894	894	898	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	949.9	949.5	949.1	948.8	948.4	947.5	946.2	945.0	943.7	942.4	943.7
5°	946.7	946.1	945.5	944.8	944.1	943.0	941.2	939.5	937.7	935.9	937.5
7.5°	937.5	936.8	936.2	935.6	935.0	933.7	931.5	929.4	927.4	925.2	926.3
10°	928.8	928.3	927.8	927.4	926.9	925.6	923.3	921.1	918.9	916.6	917.1
12.5°	919.1	918.5	917.8	917.3	916.6	914.8	911.9	908.9	905.9	902.9	903.2
15°	900.2	899.2	898.2	897.3	896.4	894.2	890.9	887.5	884.2	880.8	880.7
17.5°	878.8	877.4	875.9	874.5	873.0	870.2	865.9	861.8	857.5	853.4	852.5
20°	862.2	860.6	859.0	857.4	855.8	852.5	847.4	842.4	837.3	832.2	831.3
22.5°	843.9	842.3	840.7	839.1	837.5	834.1	828.7	823.4	818.0	812.7	811.2
25°	816.4	814.0	811.6	809.3	806.8	802.7	796.8	790.9	785.0	779.1	777.1
27.5°	784.9	782.0	779.1	776.2	773.3	768.7	762.4	756.1	749.8	743.5	740.6
30°	762.0	758.9	755.9	752.9	749.9	745.0	738.3	731.7	725.0	718.3	714.6
32.5°	739.6	736.1	732.5	729.1	725.5	720.3	713.5	706.7	699.8	693.1	689.0
35°	703.2	699.5	695.6	691.8	688.0	682.5	675.3	668.2	661.0	653.8	649.2
37.5°	667.6	662.9	658.3	653.7	649.0	643.0	635.6	628.2	620.9	613.4	607.9
40°	642.3	637.6	632.8	628.0	623.3	617.1	609.4	601.8	594.2	586.5	580.5
42.5°	616.0	611.1	606.2	601.3	596.4	590.0	582.1	574.2	566.4	558.5	552.6
45°	575.8	571.2	566.6	561.9	557.3	550.6	541.9	533.1	524.3	515.6	509.3
47.5°	534.1	529.2	524.3	519.5	514.6	507.7	499.0	490.1	481.4	472.5	466.0
50°	507.7	502.5	497.2	492.0	486.7	479.6	470.5	461.5	452.3	443.3	436.6
52.5°	479.1	473.7	468.3	463.0	457.6	450.6	442.1	433.5	424.9	416.3	409.2
55°	436.9	431.8	426.7	421.6	416.5	409.4	400.6	391.6	382.8	373.8	366.6
57.5°	394.2	388.7	383.2	377.9	372.4	365.3	356.8	348.2	339.6	331.0	324.0
60°	366.6	361.1	355.5	350.0	344.4	337.3	328.7	320.1	311.5	302.9	296.0
62.5°	337.4	332.2	326.8	321.5	316.2	309.2	300.5	291.7	283.0	274.3	267.8
65°	295.8	290.4	284.9	279.6	274.1	267.2	258.7	250.3	241.9	233.5	227.1
67.5°	254.4	248.9	243.6	238.2	232.7	226.0	217.9	209.8	201.7	193.6	187.8
70°	226.3	220.9	215.5	210.1	204.6	197.9	190.0	182.1	174.1	166.2	161.2
72.5°	198.8	193.5	188.2	182.9	177.7	171.3	163.8	156.4	148.9	141.5	137.0
75°	157.6	152.8	148.0	143.3	138.5	132.7	126.0	119.3	112.6	105.9	102.5
77.5°	116.6	112.7	109.0	105.1	101.3	96.7	91.3	86.1	80.7	75.3	72.9
80°	93.1	89.3	85.5	81.6	77.9	73.7	69.2	64.8	60.3	55.9	54.4
82.5°	70.2	66.7	63.3	59.9	56.5	53.2	50.1	47.0	44.0	41.0	40.3
85°	39.4	36.5	33.6	30.8	27.9	26.1	25.3	24.5	23.8	22.9	22.7
87.5°	13.3	12.6	12.1	11.4	10.7	10.5	10.6	10.7	10.7	10.8	11.0
90°	0.7	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0
92.5°	17.0	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9
95°	45.5	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0
97.5°	75.6	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8
100°	97.9	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5
102.5°	122.1	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0
105°	159.6	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1
107.5°	201.0	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1
110°	229.5	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.6	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3
115°	301.6	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6
117.5°	344.7	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3
120°	371.6	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7
122.5°	400.7	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6
125°	440.1	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7
127.5°	482.1	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1
130°	507.3	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0
132.5°	532.4	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8
135°	572.3	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2
137.5°	609.8	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7
140°	634.0	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8
142.5°	658.0	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7
145°	693.4	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3
147.5°	726.1	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7
150°	748.0	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1
152.5°	765.9	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4
155°	793.4	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8
157.5°	818.1	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8
160°	832.6	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9
162.5°	845.6	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9
165°	862.7	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6
167.5°	877.3	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4
170°	885.1	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3
172.5°	890.7	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8
175°	897.0	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1
177.5°	900.2	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	948.2	948.2	948.2	948.2	948.2	948.2	948.2	948.2
2.5°	945.0	946.2	947.5	948.1	948.0	947.8	947.7	947.6
5°	939.1	940.8	942.4	943.0	942.6	942.4	942.1	941.7
7.5°	927.5	928.6	929.7	930.1	929.7	929.3	929.1	928.7
10°	917.6	918.0	918.6	918.6	918.0	917.6	917.1	916.6
12.5°	903.6	904.0	904.3	904.1	903.3	902.7	901.9	901.2
15°	880.5	880.3	880.2	879.4	878.0	876.6	875.2	873.6
17.5°	851.8	850.9	850.2	849.1	848.0	846.8	845.6	844.4
20°	830.6	829.7	829.0	827.8	826.4	825.0	823.6	822.1
22.5°	809.5	807.9	806.4	805.0	803.9	802.7	801.5	800.3
25°	775.1	773.0	770.9	768.9	767.2	765.4	763.7	762.0
27.5°	737.7	734.8	731.9	729.6	727.9	726.2	724.5	722.8
30°	711.0	707.3	703.6	701.1	699.6	698.2	696.8	695.4
32.5°	684.9	681.0	676.9	674.0	672.1	670.3	668.5	666.8
35°	644.6	640.0	635.4	632.0	629.7	627.5	625.3	623.0
37.5°	602.4	596.8	591.3	587.4	585.2	583.2	581.0	578.8
40°	574.4	568.4	562.3	558.4	556.5	554.5	552.6	550.7
42.5°	546.9	541.0	535.3	530.9	528.2	525.4	522.5	519.8
45°	502.8	496.5	490.1	485.8	483.4	481.0	478.6	476.3
47.5°	459.4	452.8	446.3	441.7	439.0	436.4	433.8	431.1
50°	429.9	423.2	416.5	412.0	409.6	407.3	404.8	402.5
52.5°	402.0	394.7	387.6	382.8	380.4	378.1	375.6	373.2
55°	359.5	352.3	345.2	340.4	337.8	335.3	332.7	330.2
57.5°	317.0	310.0	303.0	298.3	296.1	293.8	291.6	289.4
60°	288.9	281.9	274.9	270.2	267.9	265.4	263.1	260.7
62.5°	261.3	254.8	248.3	243.8	241.5	239.1	236.7	234.3
65°	220.7	214.3	208.0	203.6	201.2	198.9	196.4	194.1
67.5°	182.0	176.2	170.3	166.5	164.6	162.7	160.7	158.8
70°	156.3	151.4	146.4	143.0	141.1	139.2	137.2	135.3
72.5°	132.4	127.8	123.3	120.4	119.1	117.8	116.6	115.3
75°	99.0	95.5	92.0	89.6	88.6	87.5	86.3	85.2
77.5°	70.4	68.0	65.5	63.9	63.1	62.2	61.5	60.6
80°	53.0	51.6	50.1	49.3	48.9	48.6	48.3	48.0
82.5°	39.6	38.9	38.3	37.9	37.7	37.5	37.3	37.1
85°	22.6	22.4	22.2	22.1	22.0	21.8	21.7	21.5
87.5°	11.1	11.3	11.5	11.5	11.5	11.4	11.4	11.4
90°	12.7	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	28.9	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	56.1	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	87.8	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	109.8	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	132.5	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	169.1	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	208.6	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.0	236.5	237.0	237.1	237.0	236.8	236.7	236.5



TEST NUMBER: P333667-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	263.5	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.5	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.4	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.5	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.4	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	485.0	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.9	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.6	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	615.9	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.2	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	663.9	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.1	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	768.7	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	795.4	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	818.5	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	832.5	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	845.6	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.3	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	876.4	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	884.2	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	889.8	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	896.1	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	898.9	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)