

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333691-830

Luminaire Tested: **S125RDIW-S850D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333691-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1050U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6489.0 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47						47														
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40						40														
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34						34														
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29						29														
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25						25														
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22						22														
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19						19														
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17						17														
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15						15														
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14						14														
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13						13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	1.9
10°-20°	340.6	5.2
20°-30°	493.9	7.6
30°-40°	562.9	8.7
40°-50°	548.6	8.5
50°-60°	461.8	7.1
60°-70°	323.7	5.0
70°-80°	166.4	2.6
80°-90°	44.7	0.7
90°-100°	82.2	1.3
100°-110°	242.7	3.7
110°-120°	411.1	6.3
120°-130°	541.1	8.3
130°-140°	606.3	9.3
140°-150°	594.2	9.2
150°-160°	499.1	7.7
160°-170°	331.7	5.1
170°-180°	116.1	1.8
0°-30°	956.3	14.7
0°-40°	1519.2	23.4
0°-60°	2529.7	39.0
0°-90°	3064.5	47.2
90°-120°	736.0	11.3
90°-150°	2477.6	38.2
90°-180°	3424.0	52.8
0°-180°	6489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	1	8	15	20	23	6
95°	62	64	74	80	82	66
105°	218	223	228	234	237	233
115°	412	415	417	416	416	407
125°	601	606	607	606	604	538
135°	781	787	788	788	784	602
145°	946	950	953	953	950	591
155°	1083	1083	1084	1087	1083	499
165°	1178	1176	1177	1180	1175	332
175°	1224	1221	1220	1226	1220	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.2	17.3	16.4	15.6	14.7	14.3	14.4	14.5	14.7	14.8	15.0
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	23.1	24.3	25.4	26.7	27.9	29.4	31.2	33.0	34.9	36.7	38.1
95°	62.1	62.5	63.0	63.3	63.8	65.0	67.2	69.3	71.4	73.5	75.0
97.5°	103.1	103.3	103.5	103.7	103.9	105.4	108.3	111.2	114.1	117.1	118.5
100°	133.7	133.7	133.7	133.7	133.7	135.1	137.8	140.6	143.4	146.1	148.1
102.5°	166.5	167.4	168.2	169.1	169.9	171.1	172.5	173.9	175.3	176.7	178.8
105°	217.7	218.8	219.9	220.9	222.0	223.2	224.4	225.7	227.0	228.3	229.5
107.5°	274.3	275.3	276.4	277.5	278.5	279.6	280.5	281.5	282.5	283.4	284.1
110°	313.2	314.3	315.4	316.4	317.5	318.4	319.0	319.6	320.3	320.9	321.5



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.0	353.5	354.1	354.7	355.2	355.9	356.7	357.5	358.3	359.1	359.4
115°	411.6	412.5	413.3	414.2	415.0	415.7	416.0	416.5	416.9	417.4	417.2
117.5°	470.4	470.8	471.2	471.6	472.0	472.4	472.8	473.2	473.5	473.9	474.1
120°	507.1	508.2	509.3	510.3	511.3	512.0	512.2	512.5	512.6	512.8	512.8
122.5°	546.9	547.2	547.6	548.0	548.4	548.8	549.4	550.0	550.5	551.1	550.9
125°	600.7	602.0	603.2	604.5	605.8	606.5	606.8	607.0	607.2	607.4	607.0
127.5°	658.0	658.7	659.5	660.2	660.9	661.4	661.7	661.9	662.1	662.4	662.2
130°	692.4	693.4	694.6	695.6	696.6	697.4	697.9	698.2	698.7	699.1	698.9
132.5°	726.8	728.5	730.3	732.0	733.8	734.6	734.5	734.4	734.3	734.2	734.1
135°	781.2	782.5	783.7	785.0	786.4	787.0	787.3	787.5	787.7	787.9	787.9
137.5°	832.5	833.7	834.9	836.1	837.4	838.2	838.7	839.1	839.6	840.1	840.3
140°	865.3	866.3	867.4	868.5	869.5	870.3	871.0	871.7	872.2	872.9	873.4
142.5°	898.1	899.0	899.9	900.8	901.7	902.6	903.3	904.2	904.9	905.8	906.0
145°	946.4	947.3	948.1	949.0	949.8	950.6	951.2	951.9	952.5	953.1	953.1
147.5°	991.2	991.6	992.1	992.5	993.0	993.5	994.0	994.5	995.0	995.5	996.1
150°	1021.0	1020.8	1020.5	1020.3	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8
152.5°	1045.4	1045.7	1045.9	1046.3	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8
155°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9
157.5°	1116.6	1116.2	1115.7	1115.2	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3
160°	1136.5	1135.9	1135.2	1134.6	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5
162.5°	1154.0	1153.6	1153.1	1152.6	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2
165°	1177.6	1177.1	1176.7	1176.3	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4
167.5°	1197.4	1196.6	1195.7	1194.9	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9
170°	1208.2	1207.3	1206.5	1205.6	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6
172.5°	1215.8	1214.9	1214.1	1213.2	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2
175°	1224.4	1223.5	1222.7	1221.8	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8
177.5°	1228.8	1228.0	1227.4	1226.7	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	15.3	15.5	15.6	15.7	15.6	15.6	15.6	15.6
90°	17.4	18.5	19.5	20.4	21.0	21.7	22.2	22.9
92.5°	39.5	40.9	42.3	43.2	43.6	44.1	44.6	45.1
95°	76.5	77.9	79.5	80.4	80.9	81.2	81.7	82.1
97.5°	119.9	121.3	122.7	123.5	123.8	124.0	124.3	124.5
100°	150.0	151.8	153.7	155.0	155.3	155.8	156.2	156.7
102.5°	180.9	182.9	185.0	186.3	186.9	187.6	188.1	188.7
105°	230.8	232.1	233.4	234.3	235.0	235.5	236.2	236.9
107.5°	284.7	285.4	286.0	286.3	286.3	286.3	286.2	286.2
110°	322.2	322.8	323.5	323.7	323.5	323.2	323.0	322.8



TEST NUMBER: P333691-830

CATALOG NUMBER: S125RDIW-S850D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	359.7	360.0	360.2	360.2	359.9	359.5	359.1	358.7
115°	416.9	416.7	416.5	416.3	416.0	415.8	415.7	415.5
117.5°	474.2	474.4	474.6	474.2	473.3	472.5	471.6	470.8
120°	512.8	512.8	512.8	512.5	511.6	510.8	509.9	509.1
122.5°	550.7	550.5	550.4	550.0	549.3	548.6	547.9	547.2
125°	606.5	606.1	605.7	605.4	605.2	604.9	604.7	604.5
127.5°	661.9	661.8	661.6	661.3	660.8	660.4	660.0	659.6
130°	698.7	698.4	698.2	698.0	697.5	697.1	696.6	696.3
132.5°	733.8	733.6	733.4	733.0	732.4	731.8	731.2	730.6
135°	787.9	787.9	787.9	787.5	786.6	785.8	784.9	784.1
137.5°	840.6	840.8	841.0	840.7	839.6	838.6	837.4	836.4
140°	873.7	874.2	874.6	874.3	873.3	872.1	871.1	870.1
142.5°	906.3	906.5	906.8	906.3	905.3	904.3	903.2	902.1
145°	953.1	953.1	953.1	952.8	952.2	951.5	950.9	950.3
147.5°	996.6	997.0	997.6	997.1	995.7	994.2	992.8	991.4
150°	1023.8	1023.8	1023.8	1023.6	1023.1	1022.8	1022.3	1021.9
152.5°	1049.2	1049.8	1050.3	1050.2	1049.4	1048.7	1047.8	1047.1
155°	1085.7	1086.6	1087.4	1087.2	1086.2	1085.1	1084.1	1083.0
157.5°	1117.2	1118.0	1118.9	1118.6	1117.2	1115.8	1114.4	1113.0
160°	1136.3	1137.2	1138.0	1137.8	1136.8	1135.8	1134.7	1133.6
162.5°	1154.2	1155.2	1156.2	1156.1	1154.9	1153.7	1152.4	1151.2
165°	1178.3	1179.1	1180.0	1179.8	1178.6	1177.2	1176.0	1174.7
167.5°	1196.2	1197.4	1198.7	1198.7	1197.4	1196.1	1194.8	1193.4
170°	1206.8	1208.2	1209.4	1209.3	1207.8	1206.4	1204.9	1203.3
172.5°	1214.5	1215.8	1217.0	1217.0	1215.7	1214.4	1213.1	1211.7
175°	1223.0	1224.4	1225.7	1225.5	1224.1	1222.6	1221.1	1219.6
177.5°	1227.0	1228.0	1229.0	1228.9	1227.8	1226.5	1225.4	1224.2
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2

(END OF REPORT)