

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333111-940

Luminaire Tested: **S124RDIW-S1195D1560U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333111-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10033.4 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28				
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25				
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	1.7
10°-20°	516.5	5.1
20°-30°	807.8	8.1
30°-40°	898.0	9.0
40°-50°	796.7	7.9
50°-60°	620.8	6.2
60°-70°	406.5	4.1
70°-80°	199.9	2.0
80°-90°	54.5	0.5
90°-100°	61.5	0.6
100°-110°	392.1	3.9
110°-120°	750.0	7.5
120°-130°	952.1	9.5
130°-140°	1018.7	10.2
140°-150°	952.6	9.5
150°-160°	768.2	7.7
160°-170°	495.5	4.9
170°-180°	170.8	1.7
0°-30°	1495.5	14.9
0°-40°	2393.5	23.9
0°-60°	3811.0	38.0
0°-90°	4471.9	44.6
90°-120°	1203.6	12.0
90°-150°	4127.0	41.1
90°-180°	5561.0	55.4
0°-180°	10033.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	40	4	40	4	40	19
95°	39	74	39	74	39	31
105°	383	405	383	405	383	334
115°	761	756	761	756	761	753
125°	1070	1062	1070	1062	1070	953
135°	1327	1318	1327	1318	1327	1022
145°	1528	1520	1528	1520	1528	955
155°	1665	1666	1665	1666	1665	768
165°	1750	1758	1750	1758	1750	494
175°	1787	1798	1787	1798	1787	170
180°	1798	1798	1798	1798	1798	



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	20.6	19.9	20.3	20.2	20.7	19.9	20.1	20.9	19.4	19.6	19.1
90°	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2	31.4	29.6	27.2
92.5°	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1	30.3	28.5	26.1
95°	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2	31.4	29.6	29.2
97.5°	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8	35.7	35.5	68.8
100°	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0	54.1	59.2	100.4
102.5°	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5	230.2	285.1	290.4
105°	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9	422.2	419.5	418.0
107.5°	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8	524.4	523.1	521.0
110°	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2	593.6	593.0	591.2



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6	660.7	660.8	660.0
115°	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6	759.0	758.4	758.8
117.5°	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3	859.4	859.5	858.9
120°	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0	920.4	919.8	920.1
122.5°	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9	981.5	981.1	980.7
125°	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8	1066.0	1065.1	1065.6
127.5°	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3	1151.5	1151.6	1150.2
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8	1202.5	1202.2	1201.3
132.5°	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4	1253.0	1252.8	1251.6
135°	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0	1322.5	1321.9	1320.7
137.5°	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9	1389.2	1388.6	1387.2
140°	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3	1430.4	1429.4	1428.9
142.5°	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5	1468.8	1468.2	1467.8
145°	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2	1523.8	1523.6	1523.6
147.5°	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2	1572.0	1571.7	1572.0
150°	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9	1602.9	1602.9	1603.2
152.5°	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7	1629.2	1628.7	1629.2
155°	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8	1664.6	1663.4	1664.4
157.5°	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8	1694.9
160°	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2	1713.5
162.5°	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0	1731.1	1729.3	1729.7
165°	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6	1753.2	1750.9	1750.9
167.5°	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3	1769.6	1767.0	1767.2
170°	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5	1780.1	1777.7	1777.4
172.5°	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0	1786.5	1784.2	1783.9
175°	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5	1793.9	1791.2	1790.9
177.5°	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6	1797.7	1795.7	1795.3
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	18.6	17.6	18.3	17.7	17.6	19.2	20.2	20.2	19.1	18.1	17.0
90°	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0	7.3	10.6	13.9
92.5°	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9	17.1	17.3	17.5
95°	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9	63.8	53.7	43.5
97.5°	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0	163.4	169.7	176.1
100°	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5	226.0	231.3	236.7
102.5°	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5	295.5	299.4	303.4
105°	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7	406.5	408.3	410.2
107.5°	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9	510.9	511.8	512.6
110°	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9	581.8	582.7	583.6



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8	651.4	653.0	654.6
115°	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7	756.6	757.5	758.4
117.5°	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2	852.4	853.6	854.8
120°	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8	916.9	918.2	919.4
122.5°	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0	976.7	977.4	978.1
125°	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4	1063.5	1064.7	1066.0
127.5°	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1	1144.4	1144.7	1145.0
130°	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9	1197.1	1197.4	1197.7
132.5°	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2	1245.7	1246.3	1246.9
135°	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9	1317.5	1317.2	1317.0
137.5°	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2	1382.2	1382.3	1382.5
140°	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1	1424.7	1425.3	1425.8
142.5°	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7	1462.8	1463.9	1465.0
145°	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6	1520.5	1521.3	1522.2
147.5°	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6	1567.2	1568.9	1570.6
150°	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9	1600.1	1601.2	1602.5
152.5°	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8	1627.8	1628.8	1629.7
155°	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2	1666.4	1666.7	1667.1
157.5°	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2	1699.1	1698.9	1698.7
160°	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6	1717.7	1716.8	1715.9
162.5°	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8	1734.6	1733.5	1732.4
165°	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6	1756.0	1754.6	1753.1
167.5°	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8	1773.3	1771.7	1770.1
170°	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5	1782.7	1780.8	1779.1
172.5°	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9	1789.1	1787.3	1785.6
175°	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9	1796.1	1794.3	1792.5
177.5°	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2	1799.5	1797.8	1796.1
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	17.7	17.7	18.2	17.5	18.5	19.0	18.8	19.2	20.1	19.4	19.5
90°	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2	35.0	36.7	38.0
92.5°	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1	33.9	35.7	36.6
95°	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2	35.0	36.7	37.8
97.5°	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8	36.0	36.2	36.5
100°	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0	44.0	38.9	36.5
102.5°	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5	120.6	65.9	38.5
105°	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9	427.7	430.3	426.2
107.5°	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8	527.1	528.3	529.6
110°	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2	594.9	595.4	596.2



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6	660.4	660.3	660.8
115°	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6	760.2	760.8	761.2
117.5°	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3	859.2	859.1	859.0
120°	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0	921.6	922.2	922.2
122.5°	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9	982.2	982.6	982.4
125°	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8	1067.7	1068.6	1069.3
127.5°	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3	1151.1	1150.9	1150.7
130°	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8	1203.1	1203.4	1203.5
132.5°	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4	1253.7	1253.9	1254.0
135°	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0	1323.7	1324.3	1324.9
137.5°	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9	1390.5	1391.2	1391.4
140°	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3	1432.2	1433.1	1433.6
142.5°	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5	1470.2	1470.8	1471.1
145°	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2	1524.5	1524.7	1525.3
147.5°	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2	1572.4	1572.7	1573.0
150°	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9	1602.9	1602.9	1603.1
152.5°	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7	1630.1	1630.7	1630.8
155°	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8	1667.1	1668.2	1668.4
157.5°	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0
160°	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4
162.5°	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0	1734.7	1736.5	1736.3
165°	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6	1758.0	1760.4	1760.2
167.5°	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3	1774.9	1777.5	1777.4
170°	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5	1784.9	1787.3	1787.0
172.5°	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0	1791.4	1793.8	1793.3
175°	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5	1799.3	1802.0	1801.5
177.5°	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6	1801.5	1803.4	1803.0
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	20.8	20.3	19.9	20.6	19.9	20.3	20.8	19.5	19.4	20.1	19.2
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2
92.5°	36.7	36.9	37.0	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1
95°	38.1	38.4	38.7	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2
97.5°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8
100°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0
102.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5
105°	415.5	404.7	394.0	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9
107.5°	530.7	531.8	533.0	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8
110°	597.1	598.0	598.9	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	662.0	663.1	664.2	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6
115°	761.2	761.2	761.2	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6
117.5°	858.8	858.7	858.6	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3
120°	921.6	921.0	920.4	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0
122.5°	981.9	981.2	980.6	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9
125°	1069.5	1069.8	1070.1	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8
127.5°	1150.5	1150.2	1150.0	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8
132.5°	1253.7	1253.5	1253.3	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4
135°	1325.4	1326.1	1326.7	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0
137.5°	1391.2	1391.1	1390.9	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9
140°	1434.0	1434.2	1434.5	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3
142.5°	1471.2	1471.3	1471.3	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5
145°	1525.8	1526.4	1527.1	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2
147.5°	1573.2	1573.5	1573.9	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2
150°	1603.4	1603.7	1604.0	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9
152.5°	1630.6	1630.4	1630.2	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7
155°	1667.5	1666.6	1665.7	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8
157.5°	1698.5	1696.9	1695.4	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9
160°	1718.6	1716.8	1715.0	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8
162.5°	1734.4	1732.3	1730.3	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0
165°	1757.6	1754.9	1752.2	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6
167.5°	1774.3	1771.4	1768.4	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3
170°	1784.0	1781.0	1778.1	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5
172.5°	1790.1	1786.9	1783.7	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0
175°	1797.9	1794.3	1790.7	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5
177.5°	1800.1	1797.2	1794.3	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	18.8	19.0	18.5	17.5	18.2	17.7	17.7	17.0	18.1	19.1	20.2
90°	31.4	29.6	27.2	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0
92.5°	30.3	28.5	26.1	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9
95°	31.4	29.6	29.2	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9
97.5°	35.7	35.5	68.8	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0
100°	54.1	59.2	100.4	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5
102.5°	230.2	285.1	290.4	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5
105°	422.2	419.5	418.0	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7
107.5°	524.4	523.1	521.0	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9
110°	593.6	593.0	591.2	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	660.7	660.8	660.0	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8
115°	759.0	758.4	758.8	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7
117.5°	859.4	859.5	858.9	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2
120°	920.4	919.8	920.1	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8
122.5°	981.5	981.1	980.7	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0
125°	1066.0	1065.1	1065.6	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4
127.5°	1151.5	1151.6	1150.2	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1
130°	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9
132.5°	1253.0	1252.8	1251.6	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2
135°	1322.5	1321.9	1320.7	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9
137.5°	1389.2	1388.6	1387.2	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2
140°	1430.4	1429.4	1428.9	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1
142.5°	1468.8	1468.2	1467.8	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7
145°	1523.8	1523.6	1523.6	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6
147.5°	1572.0	1571.7	1572.0	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6
150°	1602.9	1602.9	1603.2	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9
152.5°	1629.2	1628.7	1629.2	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8
155°	1664.6	1663.4	1664.4	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2
157.5°	1695.4	1693.8	1694.9	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2
160°	1715.0	1713.2	1713.5	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6
162.5°	1731.1	1729.3	1729.7	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8
165°	1753.2	1750.9	1750.9	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6
167.5°	1769.6	1767.0	1767.2	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8
170°	1780.1	1777.7	1777.4	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5
172.5°	1786.5	1784.2	1783.9	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9
175°	1793.9	1791.2	1790.9	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9
177.5°	1797.7	1795.7	1795.3	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	20.2	19.2	17.6	17.7	18.3	17.6	18.6	19.1	19.6	19.4	20.9
90°	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2
92.5°	17.1	17.3	17.5	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1
95°	63.8	53.7	43.5	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2
97.5°	163.4	169.7	176.1	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8
100°	226.0	231.3	236.7	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0
102.5°	295.5	299.4	303.4	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5
105°	406.5	408.3	410.2	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9
107.5°	510.9	511.8	512.6	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8
110°	581.8	582.7	583.6	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	651.4	653.0	654.6	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6
115°	756.6	757.5	758.4	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6
117.5°	852.4	853.6	854.8	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3
120°	916.9	918.2	919.4	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0
122.5°	976.7	977.4	978.1	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9
125°	1063.5	1064.7	1066.0	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8
127.5°	1144.4	1144.7	1145.0	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3
130°	1197.1	1197.4	1197.7	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8
132.5°	1245.7	1246.3	1246.9	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4
135°	1317.5	1317.2	1317.0	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0
137.5°	1382.2	1382.3	1382.5	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9
140°	1424.7	1425.3	1425.8	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3
142.5°	1462.8	1463.9	1465.0	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5
145°	1520.5	1521.3	1522.2	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2
147.5°	1567.2	1568.9	1570.6	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2
150°	1600.1	1601.2	1602.5	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9
152.5°	1627.8	1628.8	1629.7	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7
155°	1666.4	1666.7	1667.1	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8
157.5°	1699.1	1698.9	1698.7	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9
160°	1717.7	1716.8	1715.9	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8
162.5°	1734.6	1733.5	1732.4	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0
165°	1756.0	1754.6	1753.1	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6
167.5°	1773.3	1771.7	1770.1	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3
170°	1782.7	1780.8	1779.1	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5
172.5°	1789.1	1787.3	1785.6	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0
175°	1796.1	1794.3	1792.5	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5
177.5°	1799.5	1797.8	1796.1	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	20.1	19.9	20.7	20.2	20.3	19.9	20.6
90°	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	33.9	35.7	36.6	36.7	36.9	37.0	37.1
95°	35.0	36.7	37.8	38.1	38.4	38.7	39.0
97.5°	36.0	36.2	36.5	36.7	37.1	37.4	37.6
100°	44.0	38.9	36.5	36.7	37.1	37.4	37.6
102.5°	120.6	65.9	38.5	38.5	38.6	38.7	38.7
105°	427.7	430.3	426.2	415.5	404.7	394.0	383.3
107.5°	527.1	528.3	529.6	530.7	531.8	533.0	534.1
110°	594.9	595.4	596.2	597.1	598.0	598.9	599.8



TEST NUMBER: P333111-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	660.4	660.3	660.8	662.0	663.1	664.2	665.4
115°	760.2	760.8	761.2	761.2	761.2	761.2	761.2
117.5°	859.2	859.1	859.0	858.8	858.7	858.6	858.4
120°	921.6	922.2	922.2	921.6	921.0	920.4	919.8
122.5°	982.2	982.6	982.4	981.9	981.2	980.6	980.1
125°	1067.7	1068.6	1069.3	1069.5	1069.8	1070.1	1070.4
127.5°	1151.1	1150.9	1150.7	1150.5	1150.2	1150.0	1149.8
130°	1203.1	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5
132.5°	1253.7	1253.9	1254.0	1253.7	1253.5	1253.3	1253.0
135°	1323.7	1324.3	1324.9	1325.4	1326.1	1326.7	1327.2
137.5°	1390.5	1391.2	1391.4	1391.2	1391.1	1390.9	1390.7
140°	1432.2	1433.1	1433.6	1434.0	1434.2	1434.5	1434.9
142.5°	1470.2	1470.8	1471.1	1471.2	1471.3	1471.3	1471.4
145°	1524.5	1524.7	1525.3	1525.8	1526.4	1527.1	1527.6
147.5°	1572.4	1572.7	1573.0	1573.2	1573.5	1573.9	1574.1
150°	1602.9	1602.9	1603.1	1603.4	1603.7	1604.0	1604.3
152.5°	1630.1	1630.7	1630.8	1630.6	1630.4	1630.2	1630.0
155°	1667.1	1668.2	1668.4	1667.5	1666.6	1665.7	1664.8
157.5°	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8
160°	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2
162.5°	1734.7	1736.5	1736.3	1734.4	1732.3	1730.3	1728.2
165°	1758.0	1760.4	1760.2	1757.6	1754.9	1752.2	1749.5
167.5°	1774.9	1777.5	1777.4	1774.3	1771.4	1768.4	1765.4
170°	1784.9	1787.3	1787.0	1784.0	1781.0	1778.1	1775.0
172.5°	1791.4	1793.8	1793.3	1790.1	1786.9	1783.7	1780.4
175°	1799.3	1802.0	1801.5	1797.9	1794.3	1790.7	1787.2
177.5°	1801.5	1803.4	1803.0	1800.1	1797.2	1794.3	1791.4
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9

(END OF REPORT)