

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333097-940

Luminaire Tested: **S124RDIW-S1195D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333097-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5969.4 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	52
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	22
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.9
10°-20°	487.1	8.2
20°-30°	703.4	11.8
30°-40°	797.3	13.4
40°-50°	770.0	12.9
50°-60°	640.3	10.7
60°-70°	442.1	7.4
70°-80°	224.1	3.8
80°-90°	59.1	1.0
90°-100°	18.5	0.3
100°-110°	117.8	2.0
110°-120°	225.4	3.8
120°-130°	286.1	4.8
130°-140°	306.1	5.1
140°-150°	286.3	4.8
150°-160°	230.9	3.9
160°-170°	148.9	2.5
170°-180°	51.3	0.9
0°-30°	1365.2	22.9
0°-40°	2162.6	36.2
0°-60°	3572.8	59.9
0°-90°	4298.0	72.0
90°-120°	361.7	6.1
90°-150°	1240.3	20.8
90°-180°	1671.0	28.0
0°-180°	5969.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	1	6	9	11	12	5
95°	22	9	9	11	12	29
105°	122	124	126	129	115	127
115°	227	228	228	229	229	223
125°	319	321	320	321	322	285
135°	396	396	397	398	399	305
145°	457	458	458	458	459	285
155°	501	501	500	501	500	231
165°	528	526	526	529	526	149
175°	540	538	538	541	537	51
180°	540	540	540	540	540	



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.5	24.6	22.8	21.0	19.2	18.2	18.0	17.9	17.8	17.7	17.6
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	5.1	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1
95°	22.2	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5
97.5°	47.2	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7
100°	66.3	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2
102.5°	87.7	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2
105°	121.6	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9
107.5°	153.3	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6
110°	174.6	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.3	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6
115°	227.1	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1
117.5°	255.8	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2
120°	275.2	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6
122.5°	293.3	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0
125°	319.2	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3
127.5°	343.8	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1
130°	359.6	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4
132.5°	374.3	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6
135°	396.0	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4
137.5°	415.4	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5
140°	427.9	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9
142.5°	439.3	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4
145°	456.6	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0
147.5°	470.5	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4
150°	480.5	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7
152.5°	488.9	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6
155°	500.7	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2
157.5°	510.7	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5
160°	516.5	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4
162.5°	521.7	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2
165°	528.2	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9
167.5°	533.3	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8
170°	536.3	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9
172.5°	538.2	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9
175°	540.3	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1
177.5°	541.3	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	17.5	17.3	17.1	17.2	17.5	17.8	18.1	18.4
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	9.6	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.0	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	14.7	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	52.7	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	127.7	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.0	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.6	178.8	179.0	179.1	179.4	179.7	179.9	180.2



TEST NUMBER: P333097-940

CATALOG NUMBER: S124RDIW-S1195D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.5	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.3	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.1	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.6	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	346.0	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.5	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.6	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.7	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.2	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.6	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.1	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.7	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	500.6	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	520.8	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	527.6	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	532.6	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	535.7	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	537.6	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	539.9	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	540.8	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)