

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333696-830

Luminaire Tested: **S125RDIW-S850D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333696-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1560U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8970.5 lumens  
Efficiency: N/A  
Efficacy: 131.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	37	36	30
2	86	79	73	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	26	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7700	7700	7700	7700
5°	8858	7710	6809	7710
10°	10161	7671	6008	7671
15°	10975	7592	5340	7592
20°	12103	7501	4931	7501
25°	14006	7380	4576	7380
30°	15242	7252	4343	7252
35°	12857	7104	4129	7104
40°	8979	6837	3945	6837
45°	6660	6477	3764	6477
50°	5311	6103	3609	6103
55°	4507	5638	3471	5638
60°	3894	5222	3250	5222
65°	3470	4772	2797	4772
70°	3051	4371	2551	4371
75°	2640	3785	2395	3785
80°	2001	3187	2001	3187
85°	1667	2497	1882	2497



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.3	1.3
10°-20°	335.0	3.7
20°-30°	531.2	5.9
30°-40°	640.6	7.1
40°-50°	572.1	6.4
50°-60°	438.7	4.9
60°-70°	285.1	3.2
70°-80°	138.6	1.5
80°-90°	37.1	0.4
90°-100°	69.6	0.8
100°-110°	428.7	4.8
110°-120°	777.5	8.7
120°-130°	997.8	11.1
130°-140°	1073.2	12.0
140°-150°	1007.4	11.2
150°-160°	814.9	9.1
160°-170°	527.0	5.9
170°-180°	181.8	2.0
0°-30°	980.6	10.9
0°-40°	1621.2	18.1
0°-60°	2632.0	29.3
0°-90°	3092.8	34.5
90°-120°	1275.7	14.2
90°-150°	4354.1	48.5
90°-180°	5878.0	65.5
0°-180°	8970.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1192	1192	1192	1192	1192	
5°	1366	1189	1050	1189	1366	137
15°	1642	1136	799	1136	1642	470
25°	1966	1036	642	1036	1966	902
35°	1631	901	524	901	1631	985
45°	729	709	412	709	729	582
55°	400	501	308	501	400	363
65°	227	312	183	312	227	226
75°	106	152	96	152	106	113
85°	22	34	25	34	22	27
90°	34	1	34	1	34	16
95°	30	81	30	81	30	25
105°	421	417	421	417	421	381
115°	778	783	778	783	778	772
125°	1114	1114	1114	1114	1114	991
135°	1383	1389	1383	1389	1383	1068
145°	1606	1610	1606	1610	1606	1003
155°	1761	1774	1761	1774	1761	812
165°	1862	1872	1862	1872	1862	525
175°	1906	1914	1906	1914	1906	181
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1254.1	1253.3	1254.9	1250.6	1250.9	1244.3	1244.3	1239.2	1232.6	1227.5	1225.1
5°	1366.4	1367.4	1365.5	1358.1	1353.2	1345.9	1337.6	1322.9	1310.6	1298.9	1289.6
7.5°	1482.1	1482.8	1476.4	1474.1	1461.8	1452.7	1434.3	1414.3	1396.6	1374.0	1356.9
10°	1549.4	1549.0	1542.2	1536.7	1526.0	1512.3	1494.2	1470.6	1448.7	1424.2	1400.7
12.5°	1588.7	1587.3	1585.2	1578.7	1568.7	1556.5	1541.2	1518.1	1490.9	1464.1	1436.7
15°	1641.5	1638.0	1631.7	1623.3	1609.2	1595.0	1577.9	1557.4	1531.3	1501.0	1475.6
17.5°	1706.9	1706.9	1697.2	1685.6	1666.3	1641.3	1614.9	1581.7	1546.4	1513.1	1485.9
20°	1761.0	1759.4	1749.6	1727.1	1705.2	1673.8	1643.4	1602.8	1559.7	1516.2	1482.4
22.5°	1838.4	1834.7	1824.5	1794.9	1760.8	1720.4	1674.0	1624.4	1572.3	1522.9	1478.6
25°	1965.5	1962.6	1942.5	1908.3	1860.3	1798.1	1737.4	1669.4	1594.5	1529.5	1475.6
27.5°	2052.4	2049.2	2034.3	2005.8	1961.6	1896.2	1814.0	1723.2	1629.7	1540.1	1462.4
30°	2043.8	2051.2	2049.2	2036.0	2002.7	1944.0	1868.1	1765.9	1654.7	1549.4	1457.0
32.5°	1920.8	1927.4	1944.7	1970.6	1972.6	1949.1	1892.3	1797.9	1682.9	1563.2	1452.6
35°	1630.7	1639.6	1672.8	1725.2	1793.7	1851.0	1862.7	1811.8	1708.5	1579.8	1446.2
37.5°	1253.7	1301.8	1329.8	1385.0	1488.5	1593.8	1695.2	1732.4	1688.5	1573.0	1435.8
40°	1065.0	1076.7	1126.6	1188.8	1275.9	1385.5	1529.9	1634.2	1637.6	1557.4	1419.3
42.5°	911.4	926.3	960.6	1010.2	1084.9	1194.5	1343.5	1481.1	1544.8	1514.3	1397.8
45°	729.2	740.5	765.4	803.6	860.9	951.4	1079.7	1238.7	1365.0	1414.4	1340.0
47.5°	599.1	605.1	626.9	655.9	698.3	764.3	863.6	1001.6	1153.1	1259.2	1248.8
50°	528.6	535.5	552.0	574.1	609.8	665.6	744.9	859.9	1016.1	1145.8	1171.7
52.5°	473.7	479.5	489.8	510.7	540.1	583.0	647.0	751.0	891.6	1029.4	1089.4
55°	400.3	404.3	412.6	424.3	447.8	478.6	534.0	605.9	719.4	858.5	946.5
57.5°	339.9	341.8	347.1	358.0	374.2	396.7	436.7	497.7	579.1	704.3	801.4
60°	301.5	303.4	310.3	317.6	330.4	350.9	382.2	424.8	503.1	606.3	704.7
62.5°	271.0	272.1	275.0	282.4	293.5	309.4	334.0	368.8	431.1	521.8	614.7
65°	227.1	227.6	228.6	234.4	241.3	253.1	269.2	293.6	340.6	409.2	491.3
67.5°	185.0	185.7	189.1	191.1	198.3	204.4	214.0	232.7	265.8	312.0	375.9
70°	161.6	161.0	164.5	166.9	169.4	176.6	183.0	198.2	218.8	254.0	307.4
72.5°	139.6	138.3	139.8	140.6	143.9	148.9	155.2	164.6	180.4	204.6	245.5
75°	105.8	106.2	106.2	107.2	109.6	111.6	113.6	118.5	127.2	143.4	165.4
77.5°	74.2	73.4	75.5	75.8	77.2	79.4	81.1	83.0	86.6	93.3	104.6
80°	53.8	53.8	54.3	55.8	55.3	56.3	58.7	60.7	65.1	69.0	73.0
82.5°	41.3	40.9	41.4	41.7	41.6	42.6	43.5	43.8	45.5	47.5	50.2
85°	22.5	22.5	23.0	23.0	23.5	23.5	23.9	23.9	23.9	24.5	25.0
87.5°	15.5	14.8	14.2	14.0	14.2	14.8	14.1	13.4	13.1	12.7	12.7
90°	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8	24.3	22.7	20.5
92.5°	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8	24.3	22.7	20.7
95°	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8	24.3	22.7	34.7
97.5°	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0	60.9	69.8	93.5
100°	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9	199.9	246.9	245.6
102.5°	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2	306.1	315.0	314.2
105°	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4	535.3	535.2	534.6
110°	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2	609.2	610.1	609.4



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3	681.6	682.8	682.4
115°	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2	790.4	791.7	791.5
117.5°	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3	895.9	897.6	896.4
120°	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1	962.8	963.4	962.4
122.5°	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8	1027.5	1028.1	1027.7
125°	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2	1122.5	1123.7	1123.7
127.5°	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5	1208.2	1208.9	1209.1
130°	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8	1264.7	1265.6	1265.3
132.5°	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4	1316.5	1316.7	1317.4
135°	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5	1394.1	1394.8	1395.3
137.5°	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4	1465.3	1465.1	1465.7
140°	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5	1508.9	1508.3	1508.5
142.5°	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7	1552.7	1552.6	1552.1
145°	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9	1613.5	1613.3	1613.3
147.5°	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2	1665.8	1665.5	1665.1
150°	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6	1699.0	1698.4	1697.7
152.5°	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2	1728.5	1727.9	1727.3
155°	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8	1768.9	1767.9	1767.3
157.5°	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4	1802.4	1801.4	1801.3
160°	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3	1823.1	1821.8	1821.5
162.5°	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5	1841.7	1839.9	1839.7
165°	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1	1866.2	1864.3	1864.1
167.5°	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8	1884.5	1882.3	1882.0
170°	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4	1893.9	1891.3	1891.0
172.5°	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8	1901.6	1899.3	1898.8
175°	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9	1909.5	1907.0	1906.7
177.5°	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3	1913.5	1911.8	1911.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1225.1	1222.4	1217.3	1212.6	1206.7	1201.6	1198.1	1193.8	1188.3	1181.7	1176.2
5°	1279.3	1268.6	1254.3	1242.2	1226.4	1214.3	1201.6	1189.3	1177.0	1161.4	1147.6
7.5°	1339.4	1317.2	1295.6	1268.4	1243.7	1221.6	1200.5	1179.1	1158.2	1136.0	1114.5
10°	1376.2	1349.3	1319.5	1285.2	1253.9	1224.0	1196.7	1169.7	1141.3	1116.3	1089.4
12.5°	1410.7	1375.9	1341.8	1298.5	1260.9	1224.5	1189.6	1156.0	1125.7	1093.3	1064.4
15°	1441.8	1407.6	1369.4	1316.5	1264.1	1220.1	1179.0	1135.5	1097.8	1061.6	1029.3
17.5°	1453.9	1418.0	1373.6	1322.8	1265.6	1210.1	1157.2	1109.4	1065.1	1022.8	986.6
20°	1449.2	1414.4	1368.9	1320.4	1259.2	1201.6	1144.2	1091.4	1042.0	997.4	958.8
22.5°	1437.8	1401.8	1357.9	1306.7	1248.7	1187.4	1126.2	1069.9	1018.0	971.9	929.8
25°	1420.8	1371.9	1326.8	1276.9	1221.5	1160.9	1097.8	1035.6	980.3	933.3	887.3
27.5°	1403.1	1342.0	1284.7	1235.1	1176.7	1122.5	1061.7	997.9	939.8	891.9	844.7
30°	1387.0	1318.5	1255.4	1199.1	1143.8	1092.4	1034.6	972.4	912.8	863.4	815.4
32.5°	1367.1	1294.2	1224.8	1159.9	1106.5	1055.6	1003.3	943.9	885.7	834.7	786.0
35°	1342.0	1249.0	1173.7	1104.6	1045.4	996.0	949.0	901.0	842.7	789.9	742.4
37.5°	1309.1	1203.5	1116.3	1041.2	978.7	929.1	892.0	848.2	795.0	744.4	700.3
40°	1289.1	1170.6	1075.3	1000.9	935.3	882.9	848.2	811.0	762.5	715.0	671.0
42.5°	1262.5	1140.6	1033.8	956.2	890.2	839.8	804.6	772.2	731.6	686.8	639.7
45°	1210.3	1082.1	970.1	886.8	820.3	770.8	738.0	709.2	678.3	637.3	596.1
47.5°	1142.4	1021.2	903.8	813.0	747.8	701.9	670.1	647.3	625.3	590.3	550.4
50°	1088.0	971.0	856.5	768.4	698.9	655.3	625.5	607.4	587.3	555.4	522.2
52.5°	1023.8	919.4	807.1	717.1	651.5	610.7	582.0	563.9	547.3	521.4	489.7
55°	922.6	831.0	728.2	646.5	586.4	545.2	517.8	500.7	490.9	468.8	443.9
57.5°	805.8	740.2	649.5	570.7	517.6	476.9	456.9	442.2	431.2	415.6	398.0
60°	724.3	678.3	597.1	522.2	473.3	434.6	416.5	404.3	394.0	380.8	367.0
62.5°	641.7	608.2	537.5	473.3	428.2	395.9	378.9	367.9	356.0	347.1	333.8
65°	531.0	501.1	452.2	401.8	360.2	334.2	322.1	312.3	304.9	295.1	285.8
67.5°	413.0	401.0	367.1	332.4	302.6	279.5	268.9	262.0	253.3	247.3	241.0
70°	340.6	334.8	310.8	287.8	259.9	244.2	234.4	231.5	220.7	214.9	210.5
72.5°	276.4	273.7	259.9	243.9	224.2	210.6	201.5	198.2	191.3	186.6	183.8
75°	189.4	190.4	187.9	177.7	170.3	161.6	153.6	151.7	146.8	142.9	140.4
77.5°	119.8	124.8	125.0	124.5	121.6	116.2	112.9	111.5	106.7	105.2	104.6
80°	82.2	87.6	92.5	92.0	91.0	89.5	87.1	85.7	83.2	81.7	80.8
82.5°	54.9	59.9	63.9	66.5	66.4	64.9	63.2	62.6	62.0	61.0	60.8
85°	25.9	27.0	28.4	31.9	34.2	34.8	34.2	33.7	32.3	32.8	33.3
87.5°	12.6	12.3	12.2	11.7	10.8	12.3	12.9	12.8	12.5	12.3	12.0
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9	20.1	18.3	16.6
95°	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9	79.9	79.0	78.0
97.5°	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8	170.5	172.2	174.0
100°	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0	237.9	238.8	239.8
102.5°	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2	307.4	308.6	309.8
105°	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2	418.4	419.7	420.9
107.5°	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
110°	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3	607.3	607.3	607.3





TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7	678.4	679.2	680.0
115°	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3	784.8	786.4	788.0
117.5°	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5	892.4	892.3	892.3
120°	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5	960.3	960.0	959.6
122.5°	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8	1021.9	1023.1	1024.4
125°	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8	1116.0	1118.2	1120.4
127.5°	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6	1204.2	1205.8	1207.4
130°	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1	1258.7	1260.3	1261.9
132.5°	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5	1313.4	1315.2	1317.1
135°	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0	1390.9	1392.9	1394.8
137.5°	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3	1461.9	1463.6	1465.2
140°	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8	1507.5	1508.1	1508.7
142.5°	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8	1549.2	1549.5	1549.9
145°	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4	1611.0	1611.7	1612.3
147.5°	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3	1664.2	1664.1	1664.0
150°	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1697.7	1697.1	1696.5
152.5°	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3	1729.9	1728.5	1727.1
155°	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6	1771.7	1769.8	1767.9
157.5°	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2	1805.1	1803.9	1802.8
160°	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9	1827.0	1825.1	1823.3
162.5°	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1	1845.2	1843.3	1841.4
165°	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5	1869.6	1867.6	1865.8
167.5°	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6	1887.7	1885.7	1883.8
170°	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9	1897.6	1895.5	1893.2
172.5°	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7	1904.5	1902.2	1900.1
175°	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0	1912.1	1910.3	1908.4
177.5°	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4	1915.9	1914.4	1912.9
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1172.2	1166.8	1162.8	1155.0	1149.5	1147.2	1142.9	1141.7	1146.0	1142.9	1142.5
5°	1137.4	1123.2	1111.9	1100.7	1088.4	1080.6	1068.8	1067.0	1063.9	1059.6	1058.6
7.5°	1095.6	1077.1	1062.6	1044.1	1027.8	1014.8	1000.1	993.3	989.4	983.7	976.1
10°	1067.4	1045.4	1025.8	1007.2	987.1	971.0	956.3	945.1	937.7	930.9	927.9
12.5°	1039.6	1017.2	992.1	969.6	947.3	929.1	912.9	905.5	897.4	889.4	882.5
15°	996.5	966.6	939.1	913.2	894.2	874.6	858.9	848.2	835.9	832.5	819.3
17.5°	950.6	921.3	889.3	862.0	839.8	818.3	801.1	788.8	779.7	767.0	760.9
20°	922.1	887.3	856.0	831.0	806.5	781.1	763.5	753.2	744.4	734.1	729.2
22.5°	891.6	857.5	825.5	796.2	771.3	746.3	733.8	723.0	713.0	703.6	697.1
25°	846.7	812.5	778.6	748.3	722.4	704.3	689.6	677.3	671.9	662.7	655.8
27.5°	802.4	765.9	730.8	700.7	680.3	662.4	650.4	640.6	630.9	622.8	616.9
30°	773.7	736.6	698.4	674.4	652.9	635.7	622.5	613.2	605.9	598.5	594.2
32.5°	745.2	706.8	673.0	647.0	626.6	611.9	598.2	589.4	581.6	573.5	568.4
35°	699.4	660.3	632.8	607.4	587.3	573.6	564.3	551.6	545.2	539.3	534.0
37.5°	656.8	620.4	590.7	568.4	551.0	537.3	525.4	518.5	510.7	505.4	500.9
40°	625.5	592.2	565.2	541.8	529.0	513.9	502.7	493.8	488.0	481.1	476.2
42.5°	597.3	566.4	540.2	519.1	503.2	490.4	479.6	470.7	463.3	458.4	454.3
45°	557.4	526.6	501.1	481.5	466.9	454.7	443.4	439.0	429.2	423.4	421.4
47.5°	516.2	488.6	464.1	446.0	431.0	419.4	408.9	399.8	394.5	388.7	385.6
50°	488.4	462.0	439.0	421.4	406.7	394.0	384.2	378.3	371.0	365.6	361.7
52.5°	460.6	436.2	413.2	396.3	383.6	370.9	360.0	354.0	347.1	343.7	340.9
55°	420.9	394.9	375.4	358.7	345.5	333.8	323.5	317.6	313.2	309.8	308.8
57.5°	375.9	355.3	337.1	322.2	308.4	297.4	288.3	282.8	278.9	278.3	275.4
60°	346.5	327.9	311.2	295.1	283.3	273.1	265.2	258.9	255.0	254.5	253.5
62.5°	317.2	299.4	283.9	269.7	259.1	249.2	241.8	234.6	232.2	229.8	227.7
65°	273.6	257.4	244.7	233.5	222.2	213.9	206.5	202.1	196.7	193.8	188.4
67.5°	230.8	218.3	206.0	196.5	187.8	179.8	173.7	167.2	163.5	161.2	157.3
70°	202.6	192.8	180.6	170.3	163.4	157.1	152.2	144.9	142.4	140.4	138.5
72.5°	176.0	167.4	157.1	148.8	141.9	135.9	130.3	126.9	124.4	122.4	121.3
75°	138.5	130.2	121.4	115.5	110.7	105.8	102.7	100.3	99.3	98.9	96.9
77.5°	101.7	97.3	90.2	85.6	82.3	80.4	77.8	76.4	76.3	74.2	73.5
80°	77.9	75.4	69.5	67.6	65.1	63.2	61.6	59.2	56.7	55.8	54.3
82.5°	57.9	55.4	53.1	50.0	47.9	46.7	45.2	44.3	44.7	43.3	42.6
85°	30.8	28.4	27.4	27.0	25.9	27.0	26.4	25.9	25.4	25.0	25.4
87.5°	12.1	12.5	12.6	13.9	13.1	13.9	14.2	14.1	14.5	14.8	14.7
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8	27.4	29.0	30.3
92.5°	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8	27.4	29.0	30.0
95°	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8	27.4	29.0	29.8
97.5°	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0	43.2	34.2	29.8
100°	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9	105.9	59.0	34.9
102.5°	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2	288.3	279.5	264.3
105°	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.6
107.5°	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4	535.4	535.5	535.0
110°	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2	607.3	606.3	606.1



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3	679.2	678.0	677.1
115°	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2	788.0	786.6	785.1
117.5°	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3	892.7	891.0	889.8
120°	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1	961.5	960.9	959.8
122.5°	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8	1026.2	1025.6	1024.4
125°	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2	1119.9	1118.7	1117.6
127.5°	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5	1206.8	1206.1	1204.6
130°	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8	1262.8	1261.9	1260.6
132.5°	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4	1316.2	1316.0	1315.0
135°	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5	1392.9	1392.2	1390.9
137.5°	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4	1465.5	1465.7	1464.9
140°	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5	1510.1	1510.8	1510.1
142.5°	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7	1552.9	1553.0	1552.2
145°	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9	1614.2	1614.5	1613.7
147.5°	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2	1666.6	1667.0	1666.0
150°	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6	1700.3	1700.9	1700.0
152.5°	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2	1729.8	1730.4	1729.6
155°	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8	1770.8	1771.7	1770.8
157.5°	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4	1804.4	1805.4	1804.7
160°	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3	1825.6	1826.8	1826.3
162.5°	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5	1845.3	1847.0	1846.5
165°	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1	1870.1	1872.0	1871.6
167.5°	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8	1889.0	1891.3	1891.0
170°	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4	1898.9	1901.4	1901.3
172.5°	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8	1906.1	1908.4	1908.1
175°	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9	1914.5	1917.0	1916.8
177.5°	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3	1917.0	1918.8	1918.7
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1142.1	1137.8	1136.6	1138.2	1136.6	1137.8	1142.1	1142.5	1142.9	1146.0	1141.7
5°	1053.7	1048.9	1051.2	1050.3	1051.2	1048.9	1053.7	1058.6	1059.6	1063.9	1067.0
7.5°	976.0	969.9	963.5	965.5	963.5	969.9	976.0	976.1	983.7	989.4	993.3
10°	921.5	916.7	913.7	916.2	913.7	916.7	921.5	927.9	930.9	937.7	945.1
12.5°	875.7	872.8	870.2	869.2	870.2	872.8	875.7	882.5	889.4	897.4	905.5
15°	813.4	807.6	805.1	798.7	805.1	807.6	813.4	819.3	832.5	835.9	848.2
17.5°	755.9	754.0	747.6	744.9	747.6	754.0	755.9	760.9	767.0	779.7	788.8
20°	721.9	719.9	713.6	717.5	713.6	719.9	721.9	729.2	734.1	744.4	753.2
22.5°	693.7	689.4	687.3	686.2	687.3	689.4	693.7	697.1	703.6	713.0	723.0
25°	653.8	647.5	645.1	642.2	645.1	647.5	653.8	655.8	662.7	671.9	677.3
27.5°	614.2	610.7	607.5	606.7	607.5	610.7	614.2	616.9	622.8	630.9	640.6
30°	588.2	584.8	582.4	582.4	582.4	584.8	588.2	594.2	598.5	605.9	613.2
32.5°	565.1	562.5	560.1	559.7	560.1	562.5	565.1	568.4	573.5	581.6	589.4
35°	531.5	527.6	526.6	523.7	526.6	527.6	531.5	534.0	539.3	545.2	551.6
37.5°	496.5	493.3	493.2	492.9	493.2	493.3	496.5	500.9	505.4	510.7	518.5
40°	474.3	471.8	471.3	467.9	471.3	471.8	474.3	476.2	481.1	488.0	493.8
42.5°	450.3	449.1	447.4	445.9	447.4	449.1	450.3	454.3	458.4	463.3	470.7
45°	417.9	414.5	414.5	412.1	414.5	414.5	417.9	421.4	423.4	429.2	439.0
47.5°	384.5	381.8	382.1	379.6	382.1	381.8	384.5	385.6	388.7	394.5	399.8
50°	362.1	360.7	360.2	359.2	360.2	360.7	362.1	361.7	365.6	371.0	378.3
52.5°	339.9	339.1	341.0	338.8	341.0	339.1	339.9	340.9	343.7	347.1	354.0
55°	309.8	308.3	311.2	308.3	311.2	308.3	309.8	308.8	309.8	313.2	317.6
57.5°	275.2	273.9	276.5	275.0	276.5	273.9	275.2	275.4	278.3	278.9	282.8
60°	252.5	249.6	251.1	251.6	251.1	249.6	252.5	253.5	254.5	255.0	258.9
62.5°	225.6	223.8	224.8	222.6	224.8	223.8	225.6	227.7	229.8	232.2	234.6
65°	187.5	186.0	184.0	183.0	184.0	186.0	187.5	188.4	193.8	196.7	202.1
67.5°	157.5	154.0	153.9	154.7	153.9	154.0	157.5	157.3	161.2	163.5	167.2
70°	135.5	135.5	135.1	135.1	135.1	135.5	135.5	138.5	140.4	142.4	144.9
72.5°	120.3	119.9	119.0	118.7	119.0	119.9	120.3	121.3	122.4	124.4	126.9
75°	96.9	97.4	96.4	96.0	96.4	97.4	96.9	96.9	98.9	99.3	100.3
77.5°	71.5	69.5	70.6	69.5	70.6	69.5	71.5	73.5	74.2	76.3	76.4
80°	54.3	53.8	55.3	53.8	55.3	53.8	54.3	54.3	55.8	56.7	59.2
82.5°	43.0	42.5	43.2	42.1	43.2	42.5	43.0	42.6	43.3	44.7	44.3
85°	25.9	25.4	25.0	25.4	25.0	25.4	25.9	25.4	25.0	25.4	25.9
87.5°	15.3	15.1	15.3	15.5	15.3	15.1	15.3	14.7	14.8	14.5	14.1
90°	31.2	32.1	33.1	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8
92.5°	30.4	30.9	31.4	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8
95°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8
97.5°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0
100°	33.6	32.3	31.1	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9
102.5°	242.8	221.4	199.9	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2
105°	422.4	422.1	421.7	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8
107.5°	534.0	533.1	532.2	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4
110°	606.3	606.6	607.0	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	676.7	676.3	675.8	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3
115°	783.3	781.3	779.4	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2
117.5°	889.0	888.2	887.3	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3
120°	958.2	956.6	955.1	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1
122.5°	1022.6	1020.7	1018.9	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8
125°	1116.6	1115.7	1114.7	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2
127.5°	1202.2	1200.0	1197.6	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5
130°	1259.0	1257.4	1255.8	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8
132.5°	1313.5	1311.9	1310.3	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4
135°	1389.0	1387.1	1385.3	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5
137.5°	1463.2	1461.6	1459.9	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4
140°	1508.3	1506.4	1504.5	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5
142.5°	1550.2	1548.3	1546.4	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7
145°	1611.8	1610.0	1608.1	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9
147.5°	1663.8	1661.5	1659.3	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2
150°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6
152.5°	1727.3	1725.0	1722.8	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2
155°	1768.4	1765.9	1763.3	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8
157.5°	1802.1	1799.6	1797.1	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4
160°	1823.7	1821.2	1818.6	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3
162.5°	1843.8	1841.0	1838.2	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5
165°	1869.2	1866.6	1864.1	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1
167.5°	1888.2	1885.4	1882.5	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8
170°	1898.5	1895.6	1892.7	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4
172.5°	1905.3	1902.4	1899.6	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8
175°	1914.0	1911.2	1908.4	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9
177.5°	1916.7	1914.7	1912.6	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1142.9	1147.2	1149.5	1155.0	1162.8	1166.8	1172.2	1176.2	1181.7	1188.3	1193.8
5°	1068.8	1080.6	1088.4	1100.7	1111.9	1123.2	1137.4	1147.6	1161.4	1177.0	1189.3
7.5°	1000.1	1014.8	1027.8	1044.1	1062.6	1077.1	1095.6	1114.5	1136.0	1158.2	1179.1
10°	956.3	971.0	987.1	1007.2	1025.8	1045.4	1067.4	1089.4	1116.3	1141.3	1169.7
12.5°	912.9	929.1	947.3	969.6	992.1	1017.2	1039.6	1064.4	1093.3	1125.7	1156.0
15°	858.9	874.6	894.2	913.2	939.1	966.6	996.5	1029.3	1061.6	1097.8	1135.5
17.5°	801.1	818.3	839.8	862.0	889.3	921.3	950.6	986.6	1022.8	1065.1	1109.4
20°	763.5	781.1	806.5	831.0	856.0	887.3	922.1	958.8	997.4	1042.0	1091.4
22.5°	733.8	746.3	771.3	796.2	825.5	857.5	891.6	929.8	971.9	1018.0	1069.9
25°	689.6	704.3	722.4	748.3	778.6	812.5	846.7	887.3	933.3	980.3	1035.6
27.5°	650.4	662.4	680.3	700.7	730.8	765.9	802.4	844.7	891.9	939.8	997.9
30°	622.5	635.7	652.9	674.4	698.4	736.6	773.7	815.4	863.4	912.8	972.4
32.5°	598.2	611.9	626.6	647.0	673.0	706.8	745.2	786.0	834.7	885.7	943.9
35°	564.3	573.6	587.3	607.4	632.8	660.3	699.4	742.4	789.9	842.7	901.0
37.5°	525.4	537.3	551.0	568.4	590.7	620.4	656.8	700.3	744.4	795.0	848.2
40°	502.7	513.9	529.0	541.8	565.2	592.2	625.5	671.0	715.0	762.5	811.0
42.5°	479.6	490.4	503.2	519.1	540.2	566.4	597.3	639.7	686.8	731.6	772.2
45°	443.4	454.7	466.9	481.5	501.1	526.6	557.4	596.1	637.3	678.3	709.2
47.5°	408.9	419.4	431.0	446.0	464.1	488.6	516.2	550.4	590.3	625.3	647.3
50°	384.2	394.0	406.7	421.4	439.0	462.0	488.4	522.2	555.4	587.3	607.4
52.5°	360.0	370.9	383.6	396.3	413.2	436.2	460.6	489.7	521.4	547.3	563.9
55°	323.5	333.8	345.5	358.7	375.4	394.9	420.9	443.9	468.8	490.9	500.7
57.5°	288.3	297.4	308.4	322.2	337.1	355.3	375.9	398.0	415.6	431.2	442.2
60°	265.2	273.1	283.3	295.1	311.2	327.9	346.5	367.0	380.8	394.0	404.3
62.5°	241.8	249.2	259.1	269.7	283.9	299.4	317.2	333.8	347.1	356.0	367.9
65°	206.5	213.9	222.2	233.5	244.7	257.4	273.6	285.8	295.1	304.9	312.3
67.5°	173.7	179.8	187.8	196.5	206.0	218.3	230.8	241.0	247.3	253.3	262.0
70°	152.2	157.1	163.4	170.3	180.6	192.8	202.6	210.5	214.9	220.7	231.5
72.5°	130.3	135.9	141.9	148.8	157.1	167.4	176.0	183.8	186.6	191.3	198.2
75°	102.7	105.8	110.7	115.5	121.4	130.2	138.5	140.4	142.9	146.8	151.7
77.5°	77.8	80.4	82.3	85.6	90.2	97.3	101.7	104.6	105.2	106.7	111.5
80°	61.6	63.2	65.1	67.6	69.5	75.4	77.9	80.8	81.7	83.2	85.7
82.5°	45.2	46.7	47.9	50.0	53.1	55.4	57.9	60.8	61.0	62.0	62.6
85°	26.4	27.0	25.9	27.0	27.4	28.4	30.8	33.3	32.8	32.3	33.7
87.5°	14.2	13.9	13.1	13.9	12.6	12.5	12.1	12.0	12.3	12.5	12.8
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	24.3	22.7	20.7	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9
95°	24.3	22.7	34.7	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9
97.5°	60.9	69.8	93.5	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8
100°	199.9	246.9	245.6	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0
102.5°	306.1	315.0	314.2	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2
105°	422.8	422.8	422.8	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2
107.5°	535.3	535.2	534.6	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3
110°	609.2	610.1	609.4	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	681.6	682.8	682.4	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7
115°	790.4	791.7	791.5	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3
117.5°	895.9	897.6	896.4	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5
120°	962.8	963.4	962.4	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5
122.5°	1027.5	1028.1	1027.7	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8
125°	1122.5	1123.7	1123.7	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8
127.5°	1208.2	1208.9	1209.1	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6
130°	1264.7	1265.6	1265.3	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1
132.5°	1316.5	1316.7	1317.4	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5
135°	1394.1	1394.8	1395.3	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0
137.5°	1465.3	1465.1	1465.7	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3
140°	1508.9	1508.3	1508.5	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8
142.5°	1552.7	1552.6	1552.1	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8
145°	1613.5	1613.3	1613.3	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4
147.5°	1665.8	1665.5	1665.1	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3
150°	1699.0	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1695.8	1696.5	1697.1	1697.7
152.5°	1728.5	1727.9	1727.3	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3
155°	1768.9	1767.9	1767.3	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6
157.5°	1802.4	1801.4	1801.3	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2
160°	1823.1	1821.8	1821.5	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9
162.5°	1841.7	1839.9	1839.7	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1
165°	1866.2	1864.3	1864.1	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5
167.5°	1884.5	1882.3	1882.0	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6
170°	1893.9	1891.3	1891.0	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9
172.5°	1901.6	1899.3	1898.8	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7
175°	1909.5	1907.0	1906.7	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0
177.5°	1913.5	1911.8	1911.5	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1198.1	1201.6	1206.7	1212.6	1217.3	1222.4	1225.1	1225.1	1227.5	1232.6	1239.2
5°	1201.6	1214.3	1226.4	1242.2	1254.3	1268.6	1279.3	1289.6	1298.9	1310.6	1322.9
7.5°	1200.5	1221.6	1243.7	1268.4	1295.6	1317.2	1339.4	1356.9	1374.0	1396.6	1414.3
10°	1196.7	1224.0	1253.9	1285.2	1319.5	1349.3	1376.2	1400.7	1424.2	1448.7	1470.6
12.5°	1189.6	1224.5	1260.9	1298.5	1341.8	1375.9	1410.7	1436.7	1464.1	1490.9	1518.1
15°	1179.0	1220.1	1264.1	1316.5	1369.4	1407.6	1441.8	1475.6	1501.0	1531.3	1557.4
17.5°	1157.2	1210.1	1265.6	1322.8	1373.6	1418.0	1453.9	1485.9	1513.1	1546.4	1581.7
20°	1144.2	1201.6	1259.2	1320.4	1368.9	1414.4	1449.2	1482.4	1516.2	1559.7	1602.8
22.5°	1126.2	1187.4	1248.7	1306.7	1357.9	1401.8	1437.8	1478.6	1522.9	1572.3	1624.4
25°	1097.8	1160.9	1221.5	1276.9	1326.8	1371.9	1420.8	1475.6	1529.5	1594.5	1669.4
27.5°	1061.7	1122.5	1176.7	1235.1	1284.7	1342.0	1403.1	1462.4	1540.1	1629.7	1723.2
30°	1034.6	1092.4	1143.8	1199.1	1255.4	1318.5	1387.0	1457.0	1549.4	1654.7	1765.9
32.5°	1003.3	1055.6	1106.5	1159.9	1224.8	1294.2	1367.1	1452.6	1563.2	1682.9	1797.9
35°	949.0	996.0	1045.4	1104.6	1173.7	1249.0	1342.0	1446.2	1579.8	1708.5	1811.8
37.5°	892.0	929.1	978.7	1041.2	1116.3	1203.5	1309.1	1435.8	1573.0	1688.5	1732.4
40°	848.2	882.9	935.3	1000.9	1075.3	1170.6	1289.1	1419.3	1557.4	1637.6	1634.2
42.5°	804.6	839.8	890.2	956.2	1033.8	1140.6	1262.5	1397.8	1514.3	1544.8	1481.1
45°	738.0	770.8	820.3	886.8	970.1	1082.1	1210.3	1340.0	1414.4	1365.0	1238.7
47.5°	670.1	701.9	747.8	813.0	903.8	1021.2	1142.4	1248.8	1259.2	1153.1	1001.6
50°	625.5	655.3	698.9	768.4	856.5	971.0	1088.0	1171.7	1145.8	1016.1	859.9
52.5°	582.0	610.7	651.5	717.1	807.1	919.4	1023.8	1089.4	1029.4	891.6	751.0
55°	517.8	545.2	586.4	646.5	728.2	831.0	922.6	946.5	858.5	719.4	605.9
57.5°	456.9	476.9	517.6	570.7	649.5	740.2	805.8	801.4	704.3	579.1	497.7
60°	416.5	434.6	473.3	522.2	597.1	678.3	724.3	704.7	606.3	503.1	424.8
62.5°	378.9	395.9	428.2	473.3	537.5	608.2	641.7	614.7	521.8	431.1	368.8
65°	322.1	334.2	360.2	401.8	452.2	501.1	531.0	491.3	409.2	340.6	293.6
67.5°	268.9	279.5	302.6	332.4	367.1	401.0	413.0	375.9	312.0	265.8	232.7
70°	234.4	244.2	259.9	287.8	310.8	334.8	340.6	307.4	254.0	218.8	198.2
72.5°	201.5	210.6	224.2	243.9	259.9	273.7	276.4	245.5	204.6	180.4	164.6
75°	153.6	161.6	170.3	177.7	187.9	190.4	189.4	165.4	143.4	127.2	118.5
77.5°	112.9	116.2	121.6	124.5	125.0	124.8	119.8	104.6	93.3	86.6	83.0
80°	87.1	89.5	91.0	92.0	92.5	87.6	82.2	73.0	69.0	65.1	60.7
82.5°	63.2	64.9	66.4	66.5	63.9	59.9	54.9	50.2	47.5	45.5	43.8
85°	34.2	34.8	34.2	31.9	28.4	27.0	25.9	25.0	24.5	23.9	23.9
87.5°	12.9	12.3	10.8	11.7	12.2	12.3	12.6	12.7	12.7	13.1	13.4
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8
92.5°	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8
95°	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8
97.5°	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0
100°	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9
102.5°	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2
105°	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4
110°	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2





TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3
115°	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2
117.5°	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3
120°	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1
122.5°	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8
125°	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2
127.5°	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5
130°	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8
132.5°	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4
135°	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5
137.5°	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4
140°	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5
142.5°	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7
145°	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9
147.5°	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2
150°	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6
152.5°	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2
155°	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8
157.5°	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4
160°	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3
162.5°	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5
165°	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1
167.5°	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8
170°	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4
172.5°	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8
175°	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9
177.5°	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2	1192.2
2.5°	1244.3	1244.3	1250.9	1250.6	1254.9	1253.3	1254.1
5°	1337.6	1345.9	1353.2	1358.1	1365.5	1367.4	1366.4
7.5°	1434.3	1452.7	1461.8	1474.1	1476.4	1482.8	1482.1
10°	1494.2	1512.3	1526.0	1536.7	1542.2	1549.0	1549.4
12.5°	1541.2	1556.5	1568.7	1578.7	1585.2	1587.3	1588.7
15°	1577.9	1595.0	1609.2	1623.3	1631.7	1638.0	1641.5
17.5°	1614.9	1641.3	1666.3	1685.6	1697.2	1706.9	1706.9
20°	1643.4	1673.8	1705.2	1727.1	1749.6	1759.4	1761.0
22.5°	1674.0	1720.4	1760.8	1794.9	1824.5	1834.7	1838.4
25°	1737.4	1798.1	1860.3	1908.3	1942.5	1962.6	1965.5
27.5°	1814.0	1896.2	1961.6	2005.8	2034.3	2049.2	2052.4
30°	1868.1	1944.0	2002.7	2036.0	2049.2	2051.2	2043.8
32.5°	1892.3	1949.1	1972.6	1970.6	1944.7	1927.4	1920.8
35°	1862.7	1851.0	1793.7	1725.2	1672.8	1639.6	1630.7
37.5°	1695.2	1593.8	1488.5	1385.0	1329.8	1301.8	1253.7
40°	1529.9	1385.5	1275.9	1188.8	1126.6	1076.7	1065.0
42.5°	1343.5	1194.5	1084.9	1010.2	960.6	926.3	911.4
45°	1079.7	951.4	860.9	803.6	765.4	740.5	729.2
47.5°	863.6	764.3	698.3	655.9	626.9	605.1	599.1
50°	744.9	665.6	609.8	574.1	552.0	535.5	528.6
52.5°	647.0	583.0	540.1	510.7	489.8	479.5	473.7
55°	534.0	478.6	447.8	424.3	412.6	404.3	400.3
57.5°	436.7	396.7	374.2	358.0	347.1	341.8	339.9
60°	382.2	350.9	330.4	317.6	310.3	303.4	301.5
62.5°	334.0	309.4	293.5	282.4	275.0	272.1	271.0
65°	269.2	253.1	241.3	234.4	228.6	227.6	227.1
67.5°	214.0	204.4	198.3	191.1	189.1	185.7	185.0
70°	183.0	176.6	169.4	166.9	164.5	161.0	161.6
72.5°	155.2	148.9	143.9	140.6	139.8	138.3	139.6
75°	113.6	111.6	109.6	107.2	106.2	106.2	105.8
77.5°	81.1	79.4	77.2	75.8	75.5	73.4	74.2
80°	58.7	56.3	55.3	55.8	54.3	53.8	53.8
82.5°	43.5	42.6	41.6	41.7	41.4	40.9	41.3
85°	23.9	23.5	23.5	23.0	23.0	22.5	22.5
87.5°	14.1	14.8	14.2	14.0	14.2	14.8	15.5
90°	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333696-830

CATALOG NUMBER: S125RDIW-S850D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)