

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333687-830

Luminaire Tested: **S125RDIW-S850D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333687-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D770U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5572.7 lumens  
Efficiency: N/A  
Efficacy: 123.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	65	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	2.2
10°-20°	340.6	6.1
20°-30°	493.9	8.9
30°-40°	562.9	10.1
40°-50°	548.6	9.8
50°-60°	461.8	8.3
60°-70°	323.7	5.8
70°-80°	166.4	3.0
80°-90°	44.0	0.8
90°-100°	60.2	1.1
100°-110°	177.8	3.2
110°-120°	301.2	5.4
120°-130°	396.4	7.1
130°-140°	444.2	8.0
140°-150°	435.3	7.8
150°-160°	365.6	6.6
160°-170°	243.1	4.4
170°-180°	85.1	1.5
0°-30°	956.3	17.2
0°-40°	1519.2	27.3
0°-60°	2529.7	45.4
0°-90°	3063.8	55.0
90°-120°	539.3	9.7
90°-150°	1815.1	32.6
90°-180°	2509.0	45.0
0°-180°	5572.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	1	6	11	15	17	5
95°	46	47	54	59	60	49
105°	160	163	167	171	174	170
115°	302	304	306	305	304	298
125°	440	444	445	444	443	394
135°	572	576	577	577	574	441
145°	693	696	698	698	696	433
155°	793	793	794	797	793	365
165°	863	861	862	864	861	243
175°	897	894	894	898	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.2	17.2	16.2	15.3	14.2	13.9	13.9	13.9	13.9	13.9	14.1
90°	0.7	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0
92.5°	17.0	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9
95°	45.5	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0
97.5°	75.6	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8
100°	97.9	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5
102.5°	122.1	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0
105°	159.6	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1
107.5°	201.0	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1
110°	229.5	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5



TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.6	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3
115°	301.6	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6
117.5°	344.7	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3
120°	371.6	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7
122.5°	400.7	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6
125°	440.1	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7
127.5°	482.1	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1
130°	507.3	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0
132.5°	532.4	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8
135°	572.3	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2
137.5°	609.8	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7
140°	634.0	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8
142.5°	658.0	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7
145°	693.4	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3
147.5°	726.1	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7
150°	748.0	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1
152.5°	765.9	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4
155°	793.4	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8
157.5°	818.1	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8
160°	832.6	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9
162.5°	845.6	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9
165°	862.7	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6
167.5°	877.3	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4
170°	885.1	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3
172.5°	890.7	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8
175°	897.0	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1
177.5°	900.2	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	14.3	14.4	14.6	14.6	14.6	14.5	14.4	14.3
90°	12.7	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	28.9	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	56.1	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	87.8	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	109.8	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	132.5	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	169.1	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	208.6	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.0	236.5	237.0	237.1	237.0	236.8	236.7	236.5





TEST NUMBER: P333687-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	263.5	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.5	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.4	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.5	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.4	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	485.0	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.9	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.6	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	615.9	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.2	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	663.9	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.1	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	768.7	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	795.4	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	818.5	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	832.5	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	845.6	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.3	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	876.4	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	884.2	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	889.8	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	896.1	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	898.9	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)