

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333102-940

Luminaire Tested: **S124RDIW-S1195D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333102-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D770U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6673.2 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	71	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.6
10°-20°	487.1	7.3
20°-30°	703.4	10.5
30°-40°	797.3	11.9
40°-50°	770.0	11.5
50°-60°	640.3	9.6
60°-70°	442.1	6.6
70°-80°	224.1	3.4
80°-90°	60.0	0.9
90°-100°	56.4	0.8
100°-110°	167.2	2.5
110°-120°	283.8	4.3
120°-130°	374.2	5.6
130°-140°	420.2	6.3
140°-150°	413.0	6.2
150°-160°	347.3	5.2
160°-170°	231.1	3.5
170°-180°	80.9	1.2
0°-30°	1365.2	20.5
0°-40°	2162.6	32.4
0°-60°	3572.8	53.5
0°-90°	4299.0	64.4
90°-120°	507.4	7.6
90°-150°	1714.8	25.7
90°-180°	2374.0	35.6
0°-180°	6673.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	2	9	14	18	20	6
95°	40	46	50	52	52	44
105°	154	155	158	160	162	164
115°	289	288	287	287	286	284
125°	420	420	420	418	417	374
135°	542	546	546	545	543	419
145°	658	661	662	661	659	412
155°	754	754	754	756	754	347
165°	821	819	818	822	819	231
175°	854	851	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.6	24.9	23.2	21.5	19.8	18.9	18.9	18.9	18.9	18.8	18.8
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	14.2	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8
95°	39.7	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7
97.5°	69.4	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1
100°	92.6	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6
102.5°	117.0	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9
105°	154.2	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9
107.5°	193.2	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8
110°	219.7	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	247.3	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3
115°	288.6	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0
117.5°	327.4	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5
120°	353.4	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3
122.5°	380.4	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0
125°	420.3	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3
127.5°	456.4	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0
130°	481.8	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5
132.5°	507.7	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4
135°	542.1	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7
137.5°	579.3	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8
140°	604.2	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4
142.5°	627.0	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8
145°	658.5	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	689.7	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2
150°	708.8	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	726.8	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2
155°	754.5	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4
157.5°	777.8	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9
160°	791.6	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7
162.5°	804.2	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6
165°	821.4	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9
167.5°	834.4	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7
170°	841.9	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1
172.5°	847.1	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5
175°	854.4	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5
177.5°	856.8	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.7	18.6	18.5	18.6	19.0	19.3	19.6	19.9
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.3	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.2	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	80.6	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	101.8	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.3	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.4	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.3	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.8	219.5	219.2	219.3	219.7	220.2	220.6	221.1



TEST NUMBER: P333102-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.2	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	287.0	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	326.1	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	352.6	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.5	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	419.0	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.7	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	483.2	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	508.1	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.4	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.5	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.3	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.8	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.6	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.3	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.1	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	803.4	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	819.7	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	833.6	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.0	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	846.5	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	855.8	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)