

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333454-930

Luminaire Tested: **S125DIW-S1090D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333454-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8746.1 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	80	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8373	8373	8373	8373
5°	9697	8401	7356	8401
10°	11281	8358	6445	8358
15°	12488	8297	5945	8297
20°	13978	8199	5544	8199
25°	16376	8089	5349	8089
30°	17687	7982	5179	7982
35°	14542	7779	5067	7779
40°	10336	7497	4945	7497
45°	7941	7117	4875	7117
50°	6779	6646	4866	6646
55°	6035	6184	4908	6184
60°	5444	5679	5032	5679
65°	5029	5171	5164	5171
70°	4572	4645	5238	4645
75°	4037	4092	5190	4092
80°	3396	3336	4749	3336
85°	2690	2401	3831	2401



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	1.4
10°-20°	371.6	4.2
20°-30°	603.4	6.9
30°-40°	736.0	8.4
40°-50°	669.6	7.7
50°-60°	533.4	6.1
60°-70°	371.5	4.2
70°-80°	198.1	2.3
80°-90°	53.4	0.6
90°-100°	60.2	0.7
100°-110°	370.8	4.2
110°-120°	672.5	7.7
120°-130°	863.1	9.9
130°-140°	928.3	10.6
140°-150°	871.4	10.0
150°-160°	704.9	8.1
160°-170°	455.9	5.2
170°-180°	157.2	1.8
0°-30°	1099.8	12.6
0°-40°	1835.9	21.0
0°-60°	3038.8	34.7
0°-90°	3661.9	41.9
90°-120°	1103.5	12.6
90°-150°	3766.2	43.1
90°-180°	5084.0	58.1
0°-180°	8746.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1496	1296	1135	1296	1496	151
15°	1868	1241	889	1241	1868	535
25°	2298	1135	751	1135	2298	1050
35°	1844	987	643	987	1844	1129
45°	869	779	534	779	869	696
55°	536	549	436	549	536	483
65°	329	338	338	338	329	327
75°	162	164	208	164	162	174
85°	36	32	52	32	36	43
90°	29	1	29	1	29	14
95°	26	70	26	70	26	21
105°	364	361	364	361	364	330
115°	672	678	672	678	672	668
125°	963	963	963	963	963	857
135°	1197	1202	1197	1202	1197	923
145°	1389	1393	1389	1393	1389	868
155°	1523	1534	1523	1534	1523	702
165°	1610	1619	1610	1619	1610	454
175°	1648	1656	1648	1656	1648	157
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1371.3	1369.5	1367.8	1364.2	1366.9	1359.4	1355.9	1349.7	1342.2	1339.6	1336.5
5°	1495.7	1498.4	1501.2	1489.6	1490.7	1483.0	1465.4	1451.1	1439.6	1424.7	1414.2
7.5°	1645.4	1638.8	1638.3	1630.8	1618.0	1607.6	1589.1	1565.5	1542.8	1516.8	1495.3
10°	1720.2	1720.8	1715.8	1707.0	1693.2	1683.3	1659.1	1636.0	1607.9	1574.9	1551.3
12.5°	1776.5	1778.8	1772.6	1760.7	1754.0	1731.8	1712.9	1685.3	1652.0	1625.5	1589.6
15°	1867.7	1861.7	1857.3	1842.3	1830.8	1807.7	1777.4	1748.8	1712.5	1678.9	1645.4
17.5°	1955.5	1960.3	1952.1	1938.5	1902.7	1875.7	1835.1	1795.9	1750.7	1705.7	1665.6
20°	2033.8	2038.2	2025.6	2002.0	1959.0	1932.1	1878.7	1828.1	1775.8	1718.0	1674.0
22.5°	2131.6	2128.1	2111.0	2075.0	2037.8	1987.9	1930.2	1868.6	1803.0	1737.8	1679.3
25°	2298.0	2274.8	2264.4	2219.9	2170.9	2097.7	2018.4	1928.2	1846.7	1760.4	1685.5
27.5°	2390.2	2383.0	2371.3	2340.2	2288.8	2210.5	2117.1	2007.1	1892.2	1783.1	1685.2
30°	2371.7	2372.8	2373.9	2364.0	2331.0	2272.2	2179.1	2060.8	1924.4	1801.6	1688.2
32.5°	2208.0	2228.0	2247.1	2269.8	2279.1	2267.8	2209.5	2102.7	1962.2	1822.8	1686.5
35°	1844.5	1850.6	1912.8	1974.4	2058.1	2123.0	2166.5	2119.1	2000.8	1840.7	1684.4
37.5°	1438.3	1467.9	1511.0	1580.6	1701.4	1809.5	1948.5	2012.4	1974.2	1846.6	1680.6
40°	1226.0	1253.5	1281.7	1352.6	1454.4	1585.3	1743.3	1878.1	1909.5	1828.1	1667.4
42.5°	1062.3	1084.1	1115.2	1168.6	1253.7	1369.7	1520.5	1696.7	1805.2	1774.3	1639.6
45°	869.4	883.2	907.4	949.8	1011.5	1102.2	1235.4	1428.0	1595.9	1651.4	1573.9
47.5°	744.2	744.1	763.0	792.2	836.7	913.8	1012.3	1163.2	1342.5	1475.1	1468.9
50°	674.7	671.9	686.7	712.1	747.3	798.5	892.6	1013.1	1185.3	1335.5	1377.4
52.5°	614.8	615.1	624.3	642.9	672.5	716.2	786.4	895.1	1042.3	1196.5	1275.2
55°	536.0	533.8	544.2	556.9	578.4	607.0	657.6	740.7	860.1	1011.9	1114.4
57.5°	463.7	469.9	474.0	482.8	500.7	519.8	562.5	623.5	718.2	848.6	956.8
60°	421.5	427.5	430.9	439.7	454.0	470.5	503.5	553.0	632.8	745.1	852.4
62.5°	383.7	388.4	389.5	397.4	409.1	425.2	451.1	492.8	555.8	654.0	759.0
65°	329.1	329.1	331.3	339.5	345.0	359.3	379.1	409.4	460.1	536.5	626.2
67.5°	276.5	279.1	278.6	282.2	287.2	298.4	312.6	337.5	375.0	430.9	502.6
70°	242.1	244.3	243.8	246.5	252.0	259.2	270.8	294.4	321.4	369.2	430.9
72.5°	211.3	212.2	210.8	214.4	217.7	224.0	236.8	249.5	274.7	315.1	365.7
75°	161.8	162.9	164.0	166.2	169.5	172.8	179.4	192.1	208.6	238.8	271.3
77.5°	121.3	119.2	121.8	121.5	123.4	125.9	131.8	138.4	152.0	171.1	196.2
80°	91.3	91.9	91.9	92.5	95.2	96.9	101.8	106.7	117.2	131.5	149.1
82.5°	66.7	68.2	67.3	68.2	70.5	71.7	74.5	78.6	84.6	95.9	108.6
85°	36.3	33.6	34.7	35.8	35.8	36.3	38.5	40.2	43.5	47.9	52.8
87.5°	16.5	17.2	17.4	17.3	17.5	17.4	18.8	18.6	19.6	20.6	22.0
90°	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3	21.0	19.6	17.7
92.5°	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3	21.0	19.6	17.9
95°	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3	21.0	19.6	30.0
97.5°	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0	52.7	60.4	80.9
100°	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2	172.9	213.5	212.5
102.5°	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1	264.8	272.5	271.8
105°	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1	463.0	462.9	462.4
110°	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1	526.9	527.7	527.2



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5	589.5	590.6	590.3
115°	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7	683.7	684.9	684.6
117.5°	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6	774.9	776.4	775.3
120°	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3	832.8	833.3	832.5
122.5°	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2	888.8	889.3	888.9
125°	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9	970.9	972.0	972.0
127.5°	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5	1045.1	1045.7	1045.9
130°	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2	1094.0	1094.8	1094.5
132.5°	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6	1138.8	1139.0	1139.5
135°	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3	1205.9	1206.5	1207.0
137.5°	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5	1267.5	1267.3	1267.8
140°	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7	1305.2	1304.6	1304.9
142.5°	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1	1343.0	1343.0	1342.6
145°	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0	1395.7	1395.5	1395.5
147.5°	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3	1441.0	1440.6	1440.3
150°	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1	1469.7	1469.1	1468.5
152.5°	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7	1495.2	1494.6	1494.1
155°	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9	1530.1	1529.3	1528.7
157.5°	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9	1559.1	1558.2	1558.1
160°	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0	1577.0	1575.9	1575.6
162.5°	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6	1593.1	1591.5	1591.3
165°	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9	1614.3	1612.7	1612.4
167.5°	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1	1630.1	1628.2	1627.9
170°	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4	1638.2	1636.0	1635.7
172.5°	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8	1644.9	1642.9	1642.4
175°	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8	1651.7	1649.5	1649.3
177.5°	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8	1655.2	1653.7	1653.4
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1333.9	1330.8	1327.3	1321.1	1313.6	1309.7	1303.5	1299.6	1291.6	1285.0	1278.0
5°	1401.6	1387.3	1374.1	1357.0	1338.3	1326.2	1311.9	1295.9	1279.4	1262.3	1243.7
7.5°	1471.7	1446.3	1418.9	1389.3	1360.3	1333.7	1308.2	1283.3	1260.0	1231.8	1207.9
10°	1518.8	1486.9	1452.8	1412.6	1373.5	1339.4	1304.7	1274.5	1243.7	1210.6	1181.5
12.5°	1565.9	1523.4	1475.2	1431.1	1384.1	1342.9	1302.1	1263.5	1224.7	1188.2	1154.1
15°	1599.1	1561.7	1517.1	1454.4	1401.6	1344.9	1290.9	1240.9	1194.1	1153.4	1110.5
17.5°	1621.1	1572.8	1524.9	1464.8	1395.5	1332.1	1271.1	1213.7	1161.0	1109.4	1068.0
20°	1625.0	1575.5	1525.4	1466.5	1395.5	1322.9	1261.8	1193.0	1136.4	1083.0	1032.3
22.5°	1623.7	1567.6	1513.0	1452.5	1383.2	1316.3	1242.4	1172.3	1110.8	1058.3	1005.5
25°	1611.3	1551.3	1483.0	1422.0	1353.7	1282.7	1207.9	1135.2	1072.5	1012.5	960.3
27.5°	1600.9	1523.1	1445.9	1374.6	1308.7	1243.7	1172.0	1097.6	1028.0	967.3	918.0
30°	1588.1	1502.8	1415.8	1341.6	1273.9	1210.6	1143.0	1070.3	997.7	938.2	885.4
32.5°	1576.7	1477.3	1385.5	1304.6	1233.0	1171.4	1109.1	1039.9	968.6	908.3	855.5
35°	1554.5	1439.6	1334.5	1243.1	1166.6	1103.3	1051.1	986.7	921.2	862.8	812.2
37.5°	1526.5	1390.0	1277.2	1181.5	1097.6	1030.9	982.3	932.9	870.0	813.8	768.0
40°	1504.5	1354.8	1235.4	1137.4	1050.5	981.1	936.0	889.2	837.0	784.7	736.3
42.5°	1476.8	1323.1	1193.1	1087.7	1001.6	934.1	886.7	847.0	800.9	752.1	707.2
45°	1425.8	1265.7	1124.8	1011.5	924.5	857.9	808.9	779.2	744.5	698.3	660.3
47.5°	1350.9	1196.6	1050.9	933.9	844.2	782.5	736.6	708.1	683.7	649.3	614.9
50°	1284.3	1145.2	997.7	881.6	791.9	729.7	687.3	661.5	640.5	614.1	585.0
52.5°	1210.0	1080.4	945.3	830.5	741.7	680.4	638.9	616.1	598.7	579.8	551.1
55°	1091.8	981.7	856.2	747.3	665.3	605.3	569.0	549.2	534.9	520.6	503.0
57.5°	961.6	875.5	764.3	664.7	589.2	534.7	500.8	481.5	470.3	463.0	452.7
60°	870.0	796.3	700.5	609.7	536.0	487.5	454.5	439.7	430.3	424.3	416.5
62.5°	785.1	724.5	635.8	552.9	488.4	442.6	413.2	398.8	389.8	386.9	380.5
65°	659.8	613.0	539.8	471.1	416.0	376.9	352.2	338.4	332.9	329.6	330.2
67.5°	536.4	507.9	449.1	390.4	346.6	313.8	294.0	283.4	280.6	276.2	276.1
70°	461.1	439.7	390.1	339.0	299.9	274.6	257.0	246.0	243.2	241.0	240.5
72.5°	394.7	375.9	332.9	291.9	256.7	234.6	220.0	213.4	208.9	207.6	207.5
75°	296.6	286.2	252.0	219.6	195.3	179.9	170.1	164.0	160.7	160.1	160.7
77.5°	210.8	201.7	180.0	157.0	141.8	130.1	121.7	119.6	115.9	116.0	115.4
80°	158.5	152.5	138.7	120.5	107.9	97.9	93.5	89.7	88.6	86.9	88.6
82.5°	114.9	108.4	99.1	87.5	77.0	71.1	66.7	65.5	64.8	64.1	64.4
85°	56.7	57.2	51.7	42.9	38.5	35.2	32.4	32.4	31.9	31.4	31.9
87.5°	22.5	21.3	19.2	17.4	14.8	13.0	12.1	12.1	11.3	11.3	12.1
90°	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9	17.4	15.8	14.3
95°	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0	69.1	68.3	67.5
97.5°	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0	147.5	149.0	150.5
100°	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0	205.8	206.6	207.4
102.5°	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9	265.9	266.9	268.0
105°	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9	361.9	363.1	364.1
107.5°	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5	460.5	460.5	460.5
110°	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2	586.9	587.5	588.2
115°	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5	678.8	680.2	681.6
117.5°	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0	771.9	771.8	771.8
120°	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9	830.6	830.4	830.1
122.5°	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0	883.9	885.0	886.1
125°	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4	965.3	967.3	969.1
127.5°	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2	1041.6	1043.0	1044.4
130°	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4	1088.8	1090.1	1091.5
132.5°	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5	1136.1	1137.7	1139.3
135°	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5	1203.1	1204.8	1206.5
137.5°	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1	1264.5	1266.0	1267.4
140°	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4	1304.0	1304.5	1305.0
142.5°	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7	1340.0	1340.4	1340.7
145°	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0	1393.5	1394.1	1394.7
147.5°	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7	1439.5	1439.4	1439.3
150°	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1468.5	1468.0	1467.5
152.5°	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5	1496.4	1495.2	1494.0
155°	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1	1532.5	1530.9	1529.3
157.5°	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4	1561.4	1560.4	1559.4
160°	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0	1580.4	1578.7	1577.1
162.5°	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7	1596.1	1594.5	1592.8
165°	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9	1617.2	1615.5	1613.9
167.5°	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5	1632.9	1631.2	1629.5
170°	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4	1641.4	1639.6	1637.6
172.5°	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3	1647.4	1645.4	1643.6
175°	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6	1654.0	1652.4	1650.7
177.5°	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6	1657.3	1656.0	1654.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1274.0	1269.2	1265.2	1256.4	1251.6	1245.0	1239.7	1245.4	1239.3	1241.9	1238.0
5°	1234.3	1218.9	1207.9	1191.9	1178.2	1165.5	1156.2	1154.5	1150.1	1147.9	1141.3
7.5°	1186.5	1167.3	1148.3	1127.4	1109.8	1091.8	1080.4	1071.0	1064.7	1056.5	1050.8
10°	1158.4	1132.5	1110.5	1085.2	1063.2	1043.9	1028.5	1020.8	1013.7	1003.1	999.3
12.5°	1123.6	1096.8	1070.0	1042.9	1021.7	1000.3	987.1	975.4	970.5	958.7	957.5
15°	1081.9	1041.7	1015.3	987.7	958.6	941.0	930.0	917.3	911.8	903.6	897.5
17.5°	1032.1	996.2	963.2	934.7	909.7	894.9	881.3	872.5	863.1	857.7	847.7
20°	996.1	961.9	928.9	898.6	879.4	862.3	851.3	843.0	833.2	830.4	820.5
22.5°	965.6	928.0	896.3	870.9	849.9	830.6	818.7	813.1	806.2	797.8	795.8
25°	916.2	877.2	850.2	824.9	806.2	788.6	780.3	773.1	766.5	760.5	758.3
27.5°	873.5	838.6	806.6	783.7	767.4	751.4	744.1	735.4	730.6	725.7	719.7
30°	843.6	807.8	779.8	757.7	740.1	725.9	718.1	712.1	707.7	703.3	699.9
32.5°	812.8	779.7	752.4	730.9	713.3	702.5	695.7	691.4	686.6	681.3	677.1
35°	772.1	735.7	709.3	690.6	676.9	668.6	660.9	657.0	651.5	651.5	647.1
37.5°	726.2	694.8	671.5	654.4	642.0	634.7	626.3	623.7	620.2	617.8	616.3
40°	698.9	669.7	647.7	630.6	617.4	611.4	604.8	600.4	598.2	595.4	594.3
42.5°	670.7	642.9	621.7	606.0	594.5	589.4	583.2	580.1	575.7	572.1	571.4
45°	627.9	600.9	581.6	569.0	559.1	553.0	549.2	542.6	540.4	536.0	535.4
47.5°	587.3	561.4	542.5	532.1	523.4	518.4	512.4	505.8	503.3	501.1	500.8
50°	556.9	533.2	515.6	505.7	497.5	490.3	484.3	479.9	478.2	478.2	479.3
52.5°	526.1	505.9	491.0	478.8	471.1	463.4	457.9	455.2	452.7	455.3	457.3
55°	480.9	460.6	449.6	438.1	430.3	421.5	418.7	417.7	416.0	420.4	422.7
57.5°	433.2	418.9	406.0	394.5	387.6	382.5	378.8	378.1	381.2	383.4	390.4
60°	402.8	386.3	374.7	365.9	357.7	354.4	353.3	352.2	354.4	360.4	369.8
62.5°	369.3	356.0	343.5	336.9	330.8	325.3	325.1	325.8	330.2	337.1	346.4
65°	320.2	308.7	300.4	292.8	287.8	284.5	285.6	287.8	292.8	302.1	312.6
67.5°	270.4	262.5	255.1	248.8	244.1	244.1	245.2	248.5	254.4	265.1	274.7
70°	238.3	229.5	223.4	220.7	216.8	214.6	217.9	223.4	228.4	238.3	246.5
72.5°	206.1	198.7	194.0	192.1	190.4	188.7	189.7	195.7	202.4	212.3	221.8
75°	158.5	155.7	152.5	150.3	148.5	149.7	150.7	156.3	161.8	172.3	183.3
77.5°	115.7	112.8	110.8	110.3	109.4	110.0	113.0	117.1	122.5	130.1	138.4
80°	87.5	86.4	85.3	84.7	84.7	85.3	89.7	92.5	97.4	104.5	111.1
82.5°	63.8	63.0	62.9	62.7	63.2	63.3	66.0	69.5	73.6	79.0	84.7
85°	33.6	32.4	34.1	34.7	33.6	35.2	36.3	38.5	40.2	42.9	45.7
87.5°	13.0	14.3	14.3	15.1	15.4	16.7	16.6	18.6	19.7	20.9	20.6
90°	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3	23.7	25.1	26.2
92.5°	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3	23.7	25.1	25.9
95°	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3	23.7	25.1	25.8
97.5°	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0	37.3	29.6	25.8
100°	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2	91.6	51.0	30.2
102.5°	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1	249.4	241.7	228.6
105°	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.6
107.5°	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1	463.1	463.2	462.8
110°	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1	525.3	524.5	524.2



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5	587.5	586.4	585.7
115°	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7	681.6	680.4	679.1
117.5°	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6	772.2	770.7	769.6
120°	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3	831.7	831.2	830.2
122.5°	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2	887.7	887.1	886.1
125°	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9	968.7	967.7	966.7
127.5°	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5	1043.9	1043.3	1042.0
130°	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2	1092.3	1091.5	1090.4
132.5°	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6	1138.5	1138.3	1137.5
135°	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3	1204.8	1204.3	1203.1
137.5°	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5	1267.6	1267.8	1267.1
140°	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7	1306.3	1306.8	1306.3
142.5°	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1	1343.3	1343.4	1342.6
145°	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0	1396.3	1396.5	1395.9
147.5°	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3	1441.6	1441.9	1441.1
150°	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1	1470.7	1471.3	1470.5
152.5°	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7	1496.2	1496.8	1496.1
155°	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9	1531.7	1532.5	1531.8
157.5°	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9	1560.8	1561.7	1561.1
160°	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0	1579.2	1580.2	1579.7
162.5°	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6	1596.2	1597.7	1597.3
165°	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9	1617.6	1619.3	1618.9
167.5°	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1	1634.0	1636.0	1635.7
170°	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4	1642.6	1644.7	1644.6
172.5°	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8	1648.8	1650.7	1650.5
175°	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8	1656.0	1658.2	1658.1
177.5°	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8	1658.2	1659.8	1659.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1235.3	1238.4	1235.7	1239.3	1235.7	1238.4	1235.3	1238.0	1241.9	1239.3	1245.4
5°	1138.6	1133.6	1136.9	1134.7	1136.9	1133.6	1138.6	1141.3	1147.9	1150.1	1154.5
7.5°	1049.2	1044.5	1039.0	1036.5	1039.0	1044.5	1049.2	1050.8	1056.5	1064.7	1071.0
10°	993.3	987.2	986.7	982.8	986.7	987.2	993.3	999.3	1003.1	1013.7	1020.8
12.5°	952.4	946.7	940.4	938.8	940.4	946.7	952.4	957.5	958.7	970.5	975.4
15°	894.2	889.8	886.0	889.2	886.0	889.8	894.2	897.5	903.6	911.8	917.3
17.5°	845.9	842.3	841.6	837.6	841.6	842.3	845.9	847.7	857.7	863.1	872.5
20°	815.5	812.8	813.9	806.7	813.9	812.8	815.5	820.5	830.4	833.2	843.0
22.5°	791.3	785.9	785.3	783.8	785.3	785.9	791.3	795.8	797.8	806.2	813.1
25°	753.3	750.6	747.9	750.6	747.9	750.6	753.3	758.3	760.5	766.5	773.1
27.5°	720.2	716.9	716.2	716.5	716.2	716.9	720.2	719.7	725.7	730.6	735.4
30°	699.9	694.5	695.0	694.5	695.0	694.5	699.9	699.9	703.3	707.7	712.1
32.5°	677.9	674.2	673.4	672.5	673.4	674.2	677.9	677.1	681.3	686.6	691.4
35°	645.5	645.5	642.7	642.7	642.7	645.5	645.5	647.1	651.5	651.5	657.0
37.5°	615.0	614.4	612.8	613.0	612.8	614.4	615.0	616.3	617.8	620.2	623.7
40°	592.1	591.6	589.9	586.6	589.9	591.6	592.1	594.3	595.4	598.2	600.4
42.5°	570.1	568.3	567.4	566.4	567.4	568.3	570.1	571.4	572.1	575.7	580.1
45°	535.4	535.4	534.3	533.8	534.3	535.4	535.4	535.4	536.0	540.4	542.6
47.5°	501.7	502.7	504.8	504.5	504.8	502.7	501.7	500.8	501.1	503.3	505.8
50°	481.5	482.1	483.7	484.3	483.7	482.1	481.5	479.3	478.2	478.2	479.9
52.5°	459.0	462.3	464.3	464.0	464.3	462.3	459.0	457.3	455.3	452.7	455.2
55°	427.5	431.5	435.3	435.9	435.3	431.5	427.5	422.7	420.4	416.0	417.7
57.5°	396.4	401.8	405.9	407.2	405.9	401.8	396.4	390.4	383.4	381.2	378.1
60°	375.3	382.5	387.4	389.6	387.4	382.5	375.3	369.8	360.4	354.4	352.2
62.5°	355.1	363.1	368.0	368.4	368.0	363.1	355.1	346.4	337.1	330.2	325.8
65°	321.9	330.2	334.6	337.9	334.6	330.2	321.9	312.6	302.1	292.8	287.8
67.5°	286.3	294.5	299.4	302.0	299.4	294.5	286.3	274.7	265.1	254.4	248.5
70°	260.3	268.6	275.2	277.4	275.2	268.6	260.3	246.5	238.3	228.4	223.4
72.5°	234.7	242.1	247.4	250.1	247.4	242.1	234.7	221.8	212.3	202.4	195.7
75°	190.4	200.3	205.3	208.0	205.3	200.3	190.4	183.3	172.3	161.8	156.3
77.5°	146.8	155.8	158.8	160.2	158.8	155.8	146.8	138.4	130.1	122.5	117.1
80°	117.7	123.3	127.1	127.7	127.1	123.3	117.7	111.1	104.5	97.4	92.5
82.5°	90.5	95.1	96.3	97.8	96.3	95.1	90.5	84.7	79.0	73.6	69.5
85°	49.5	51.7	52.3	51.7	52.3	51.7	49.5	45.7	42.9	40.2	38.5
87.5°	21.7	21.4	21.6	22.6	21.6	21.4	21.7	20.6	20.9	19.7	18.6
90°	27.0	27.8	28.6	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3
92.5°	26.3	26.7	27.1	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3
95°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3
97.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0
100°	29.0	28.0	26.9	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2
102.5°	210.0	191.5	172.9	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1
105°	365.3	365.1	364.8	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7
107.5°	461.9	461.1	460.3	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1
110°	524.5	524.7	525.1	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	585.4	585.0	584.6	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5
115°	677.5	675.8	674.2	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7
117.5°	769.0	768.3	767.5	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6
120°	828.8	827.4	826.1	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3
122.5°	884.5	882.9	881.3	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2
125°	965.9	965.1	964.3	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9
127.5°	1039.9	1038.0	1035.9	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5
130°	1089.1	1087.7	1086.3	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2
132.5°	1136.2	1134.8	1133.4	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6
135°	1201.5	1199.9	1198.2	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3
137.5°	1265.7	1264.3	1262.8	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5
140°	1304.6	1303.0	1301.4	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7
142.5°	1340.9	1339.3	1337.7	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1
145°	1394.2	1392.6	1391.0	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0
147.5°	1439.2	1437.2	1435.3	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3
150°	1468.3	1466.1	1464.0	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1
152.5°	1494.1	1492.2	1490.2	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7
155°	1529.7	1527.5	1525.3	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9
157.5°	1558.9	1556.7	1554.4	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9
160°	1577.5	1575.3	1573.1	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0
162.5°	1594.9	1592.4	1590.1	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6
165°	1616.8	1614.6	1612.4	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9
167.5°	1633.3	1630.8	1628.4	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1
170°	1642.2	1639.7	1637.2	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4
172.5°	1648.0	1645.6	1643.2	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8
175°	1655.6	1653.2	1650.7	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8
177.5°	1657.9	1656.2	1654.4	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1239.7	1245.0	1251.6	1256.4	1265.2	1269.2	1274.0	1278.0	1285.0	1291.6	1299.6
5°	1156.2	1165.5	1178.2	1191.9	1207.9	1218.9	1234.3	1243.7	1262.3	1279.4	1295.9
7.5°	1080.4	1091.8	1109.8	1127.4	1148.3	1167.3	1186.5	1207.9	1231.8	1260.0	1283.3
10°	1028.5	1043.9	1063.2	1085.2	1110.5	1132.5	1158.4	1181.5	1210.6	1243.7	1274.5
12.5°	987.1	1000.3	1021.7	1042.9	1070.0	1096.8	1123.6	1154.1	1188.2	1224.7	1263.5
15°	930.0	941.0	958.6	987.7	1015.3	1041.7	1081.9	1110.5	1153.4	1194.1	1240.9
17.5°	881.3	894.9	909.7	934.7	963.2	996.2	1032.1	1068.0	1109.4	1161.0	1213.7
20°	851.3	862.3	879.4	898.6	928.9	961.9	996.1	1032.3	1083.0	1136.4	1193.0
22.5°	818.7	830.6	849.9	870.9	896.3	928.0	965.6	1005.5	1058.3	1110.8	1172.3
25°	780.3	788.6	806.2	824.9	850.2	877.2	916.2	960.3	1012.5	1072.5	1135.2
27.5°	744.1	751.4	767.4	783.7	806.6	838.6	873.5	918.0	967.3	1028.0	1097.6
30°	718.1	725.9	740.1	757.7	779.8	807.8	843.6	885.4	938.2	997.7	1070.3
32.5°	695.7	702.5	713.3	730.9	752.4	779.7	812.8	855.5	908.3	968.6	1039.9
35°	660.9	668.6	676.9	690.6	709.3	735.7	772.1	812.2	862.8	921.2	986.7
37.5°	626.3	634.7	642.0	654.4	671.5	694.8	726.2	768.0	813.8	870.0	932.9
40°	604.8	611.4	617.4	630.6	647.7	669.7	698.9	736.3	784.7	837.0	889.2
42.5°	583.2	589.4	594.5	606.0	621.7	642.9	670.7	707.2	752.1	800.9	847.0
45°	549.2	553.0	559.1	569.0	581.6	600.9	627.9	660.3	698.3	744.5	779.2
47.5°	512.4	518.4	523.4	532.1	542.5	561.4	587.3	614.9	649.3	683.7	708.1
50°	484.3	490.3	497.5	505.7	515.6	533.2	556.9	585.0	614.1	640.5	661.5
52.5°	457.9	463.4	471.1	478.8	491.0	505.9	526.1	551.1	579.8	598.7	616.1
55°	418.7	421.5	430.3	438.1	449.6	460.6	480.9	503.0	520.6	534.9	549.2
57.5°	378.8	382.5	387.6	394.5	406.0	418.9	433.2	452.7	463.0	470.3	481.5
60°	353.3	354.4	357.7	365.9	374.7	386.3	402.8	416.5	424.3	430.3	439.7
62.5°	325.1	325.3	330.8	336.9	343.5	356.0	369.3	380.5	386.9	389.8	398.8
65°	285.6	284.5	287.8	292.8	300.4	308.7	320.2	330.2	329.6	332.9	338.4
67.5°	245.2	244.1	244.1	248.8	255.1	262.5	270.4	276.1	276.2	280.6	283.4
70°	217.9	214.6	216.8	220.7	223.4	229.5	238.3	240.5	241.0	243.2	246.0
72.5°	189.7	188.7	190.4	192.1	194.0	198.7	206.1	207.5	207.6	208.9	213.4
75°	150.7	149.7	148.5	150.3	152.5	155.7	158.5	160.7	160.1	160.7	164.0
77.5°	113.0	110.0	109.4	110.3	110.8	112.8	115.7	115.4	116.0	115.9	119.6
80°	89.7	85.3	84.7	84.7	85.3	86.4	87.5	88.6	86.9	88.6	89.7
82.5°	66.0	63.3	63.2	62.7	62.9	63.0	63.8	64.4	64.1	64.8	65.5
85°	36.3	35.2	33.6	34.7	34.1	32.4	33.6	31.9	31.4	31.9	32.4
87.5°	16.6	16.7	15.4	15.1	14.3	14.3	13.0	12.1	11.3	11.3	12.1
90°	21.0	19.6	17.7	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	21.0	19.6	17.9	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9
95°	21.0	19.6	30.0	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0
97.5°	52.7	60.4	80.9	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0
100°	172.9	213.5	212.5	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0
102.5°	264.8	272.5	271.8	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9
105°	365.7	365.7	365.7	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9
107.5°	463.0	462.9	462.4	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5
110°	526.9	527.7	527.2	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	589.5	590.6	590.3	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2
115°	683.7	684.9	684.6	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5
117.5°	774.9	776.4	775.3	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0
120°	832.8	833.3	832.5	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9
122.5°	888.8	889.3	888.9	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0
125°	970.9	972.0	972.0	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4
127.5°	1045.1	1045.7	1045.9	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2
130°	1094.0	1094.8	1094.5	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4
132.5°	1138.8	1139.0	1139.5	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5
135°	1205.9	1206.5	1207.0	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5
137.5°	1267.5	1267.3	1267.8	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1
140°	1305.2	1304.6	1304.9	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4
142.5°	1343.0	1343.0	1342.6	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7
145°	1395.7	1395.5	1395.5	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0
147.5°	1441.0	1440.6	1440.3	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7
150°	1469.7	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1
152.5°	1495.2	1494.6	1494.1	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5
155°	1530.1	1529.3	1528.7	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1
157.5°	1559.1	1558.2	1558.1	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4
160°	1577.0	1575.9	1575.6	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0
162.5°	1593.1	1591.5	1591.3	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7
165°	1614.3	1612.7	1612.4	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9
167.5°	1630.1	1628.2	1627.9	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5
170°	1638.2	1636.0	1635.7	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4
172.5°	1644.9	1642.9	1642.4	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3
175°	1651.7	1649.5	1649.3	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6
177.5°	1655.2	1653.7	1653.4	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1303.5	1309.7	1313.6	1321.1	1327.3	1330.8	1333.9	1336.5	1339.6	1342.2	1349.7
5°	1311.9	1326.2	1338.3	1357.0	1374.1	1387.3	1401.6	1414.2	1424.7	1439.6	1451.1
7.5°	1308.2	1333.7	1360.3	1389.3	1418.9	1446.3	1471.7	1495.3	1516.8	1542.8	1565.5
10°	1304.7	1339.4	1373.5	1412.6	1452.8	1486.9	1518.8	1551.3	1574.9	1607.9	1636.0
12.5°	1302.1	1342.9	1384.1	1431.1	1475.2	1523.4	1565.9	1589.6	1625.5	1652.0	1685.3
15°	1290.9	1344.9	1401.6	1454.4	1517.1	1561.7	1599.1	1645.4	1678.9	1712.5	1748.8
17.5°	1271.1	1332.1	1395.5	1464.8	1524.9	1572.8	1621.1	1665.6	1705.7	1750.7	1795.9
20°	1261.8	1322.9	1395.5	1466.5	1525.4	1575.5	1625.0	1674.0	1718.0	1775.8	1828.1
22.5°	1242.4	1316.3	1383.2	1452.5	1513.0	1567.6	1623.7	1679.3	1737.8	1803.0	1868.6
25°	1207.9	1282.7	1353.7	1422.0	1483.0	1551.3	1611.3	1685.5	1760.4	1846.7	1928.2
27.5°	1172.0	1243.7	1308.7	1374.6	1445.9	1523.1	1600.9	1685.2	1783.1	1892.2	2007.1
30°	1143.0	1210.6	1273.9	1341.6	1415.8	1502.8	1588.1	1688.2	1801.6	1924.4	2060.8
32.5°	1109.1	1171.4	1233.0	1304.6	1385.5	1477.3	1576.7	1686.5	1822.8	1962.2	2102.7
35°	1051.1	1103.3	1166.6	1243.1	1334.5	1439.6	1554.5	1684.4	1840.7	2000.8	2119.1
37.5°	982.3	1030.9	1097.6	1181.5	1277.2	1390.0	1526.5	1680.6	1846.6	1974.2	2012.4
40°	936.0	981.1	1050.5	1137.4	1235.4	1354.8	1504.5	1667.4	1828.1	1909.5	1878.1
42.5°	886.7	934.1	1001.6	1087.7	1193.1	1323.1	1476.8	1639.6	1774.3	1805.2	1696.7
45°	808.9	857.9	924.5	1011.5	1124.8	1265.7	1425.8	1573.9	1651.4	1595.9	1428.0
47.5°	736.6	782.5	844.2	933.9	1050.9	1196.6	1350.9	1468.9	1475.1	1342.5	1163.2
50°	687.3	729.7	791.9	881.6	997.7	1145.2	1284.3	1377.4	1335.5	1185.3	1013.1
52.5°	638.9	680.4	741.7	830.5	945.3	1080.4	1210.0	1275.2	1196.5	1042.3	895.1
55°	569.0	605.3	665.3	747.3	856.2	981.7	1091.8	1114.4	1011.9	860.1	740.7
57.5°	500.8	534.7	589.2	664.7	764.3	875.5	961.6	956.8	848.6	718.2	623.5
60°	454.5	487.5	536.0	609.7	700.5	796.3	870.0	852.4	745.1	632.8	553.0
62.5°	413.2	442.6	488.4	552.9	635.8	724.5	785.1	759.0	654.0	555.8	492.8
65°	352.2	376.9	416.0	471.1	539.8	613.0	659.8	626.2	536.5	460.1	409.4
67.5°	294.0	313.8	346.6	390.4	449.1	507.9	536.4	502.6	430.9	375.0	337.5
70°	257.0	274.6	299.9	339.0	390.1	439.7	461.1	430.9	369.2	321.4	294.4
72.5°	220.0	234.6	256.7	291.9	332.9	375.9	394.7	365.7	315.1	274.7	249.5
75°	170.1	179.9	195.3	219.6	252.0	286.2	296.6	271.3	238.8	208.6	192.1
77.5°	121.7	130.1	141.8	157.0	180.0	201.7	210.8	196.2	171.1	152.0	138.4
80°	93.5	97.9	107.9	120.5	138.7	152.5	158.5	149.1	131.5	117.2	106.7
82.5°	66.7	71.1	77.0	87.5	99.1	108.4	114.9	108.6	95.9	84.6	78.6
85°	32.4	35.2	38.5	42.9	51.7	57.2	56.7	52.8	47.9	43.5	40.2
87.5°	12.1	13.0	14.8	17.4	19.2	21.3	22.5	22.0	20.6	19.6	18.6
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3
92.5°	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3
95°	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3
97.5°	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0
100°	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2
102.5°	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1
105°	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1
110°	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5
115°	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7
117.5°	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6
120°	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3
122.5°	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2
125°	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9
127.5°	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5
130°	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2
132.5°	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6
135°	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3
137.5°	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5
140°	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7
142.5°	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1
145°	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0
147.5°	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3
150°	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1
152.5°	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7
155°	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9
157.5°	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9
160°	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0
162.5°	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6
165°	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9
167.5°	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1
170°	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4
172.5°	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8
175°	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8
177.5°	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1355.9	1359.4	1366.9	1364.2	1367.8	1369.5	1371.3
5°	1465.4	1483.0	1490.7	1489.6	1501.2	1498.4	1495.7
7.5°	1589.1	1607.6	1618.0	1630.8	1638.3	1638.8	1645.4
10°	1659.1	1683.3	1693.2	1707.0	1715.8	1720.8	1720.2
12.5°	1712.9	1731.8	1754.0	1760.7	1772.6	1778.8	1776.5
15°	1777.4	1807.7	1830.8	1842.3	1857.3	1861.7	1867.7
17.5°	1835.1	1875.7	1902.7	1938.5	1952.1	1960.3	1955.5
20°	1878.7	1932.1	1959.0	2002.0	2025.6	2038.2	2033.8
22.5°	1930.2	1987.9	2037.8	2075.0	2111.0	2128.1	2131.6
25°	2018.4	2097.7	2170.9	2219.9	2264.4	2274.8	2298.0
27.5°	2117.1	2210.5	2288.8	2340.2	2371.3	2383.0	2390.2
30°	2179.1	2272.2	2331.0	2364.0	2373.9	2372.8	2371.7
32.5°	2209.5	2267.8	2279.1	2269.8	2247.1	2228.0	2208.0
35°	2166.5	2123.0	2058.1	1974.4	1912.8	1850.6	1844.5
37.5°	1948.5	1809.5	1701.4	1580.6	1511.0	1467.9	1438.3
40°	1743.3	1585.3	1454.4	1352.6	1281.7	1253.5	1226.0
42.5°	1520.5	1369.7	1253.7	1168.6	1115.2	1084.1	1062.3
45°	1235.4	1102.2	1011.5	949.8	907.4	883.2	869.4
47.5°	1012.3	913.8	836.7	792.2	763.0	744.1	744.2
50°	892.6	798.5	747.3	712.1	686.7	671.9	674.7
52.5°	786.4	716.2	672.5	642.9	624.3	615.1	614.8
55°	657.6	607.0	578.4	556.9	544.2	533.8	536.0
57.5°	562.5	519.8	500.7	482.8	474.0	469.9	463.7
60°	503.5	470.5	454.0	439.7	430.9	427.5	421.5
62.5°	451.1	425.2	409.1	397.4	389.5	388.4	383.7
65°	379.1	359.3	345.0	339.5	331.3	329.1	329.1
67.5°	312.6	298.4	287.2	282.2	278.6	279.1	276.5
70°	270.8	259.2	252.0	246.5	243.8	244.3	242.1
72.5°	236.8	224.0	217.7	214.4	210.8	212.2	211.3
75°	179.4	172.8	169.5	166.2	164.0	162.9	161.8
77.5°	131.8	125.9	123.4	121.5	121.8	119.2	121.3
80°	101.8	96.9	95.2	92.5	91.9	91.9	91.3
82.5°	74.5	71.7	70.5	68.2	67.3	68.2	66.7
85°	38.5	36.3	35.8	35.8	34.7	33.6	36.3
87.5°	18.8	17.4	17.5	17.3	17.4	17.2	16.5
90°	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333454-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)