

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333434-930

Luminaire Tested: **S125DIW-S1090D470U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333434-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D470U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5149.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	32	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	35	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	2.5
10°-20°	370.5	7.2
20°-30°	547.1	10.6
30°-40°	638.4	12.4
40°-50°	641.2	12.5
50°-60°	562.8	10.9
60°-70°	419.4	8.1
70°-80°	239.8	4.7
80°-90°	70.8	1.4
90°-100°	18.1	0.4
100°-110°	111.4	2.2
110°-120°	202.1	3.9
120°-130°	259.4	5.0
130°-140°	279.0	5.4
140°-150°	261.9	5.1
150°-160°	211.8	4.1
160°-170°	137.0	2.7
170°-180°	47.3	0.9
0°-30°	1048.8	20.4
0°-40°	1687.2	32.8
0°-60°	2891.2	56.2
0°-90°	3621.1	70.3
90°-120°	331.6	6.4
90°-150°	1131.8	22.0
90°-180°	1528.0	29.7
0°-180°	5149.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	0	3	6	8	9	4
95°	21	19	6	8	8	27
105°	108	110	110	110	110	115
115°	204	205	206	204	202	202
125°	290	292	292	291	290	259
135°	361	363	363	362	360	278
145°	419	419	419	420	418	262
155°	461	459	460	460	458	212
165°	486	484	485	487	484	137
175°	498	496	496	498	495	47
180°	498	498	498	498	498	



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	23.8	24.0	24.1	24.2	24.4	24.4	24.3	24.2	24.1	24.1	24.1
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	5.9	6.3
92.5°	5.7	5.2	4.7	4.3	3.8	3.8	4.4	4.9	5.4	5.9	6.3
95°	21.0	20.8	20.5	20.3	20.1	18.3	15.2	12.1	9.0	5.9	6.3
97.5°	43.9	44.4	44.8	45.2	45.7	42.8	36.6	30.5	24.3	18.2	15.8
100°	61.6	61.9	62.1	62.4	62.6	62.9	63.2	63.5	63.8	64.2	51.9
102.5°	79.6	79.9	80.2	80.6	80.9	81.1	81.3	81.4	81.7	81.9	79.6
105°	108.4	108.8	109.1	109.4	109.7	109.9	109.9	109.9	109.9	109.9	109.9
107.5°	138.4	138.4	138.4	138.4	138.4	138.4	138.6	138.8	138.9	139.1	139.2
110°	157.8	157.8	157.8	157.8	157.8	157.9	158.1	158.2	158.4	158.6	158.3



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.2	176.3	176.5	176.8	176.9	177.1	177.2	177.3	177.4	177.5	177.2
115°	203.6	204.0	204.4	204.8	205.2	205.5	205.5	205.6	205.7	205.8	205.5
117.5°	232.0	232.0	232.0	232.0	232.0	232.1	232.4	232.7	233.0	233.3	232.9
120°	249.7	249.6	249.6	249.5	249.4	249.5	249.7	250.0	250.2	250.5	250.3
122.5°	265.4	265.6	266.0	266.3	266.6	266.8	266.9	267.0	267.2	267.3	267.1
125°	289.5	290.1	290.7	291.2	291.8	292.1	292.1	292.1	292.1	292.1	291.8
127.5°	312.6	313.1	313.5	313.9	314.3	314.5	314.4	314.4	314.3	314.2	314.1
130°	326.8	327.2	327.6	328.0	328.4	328.6	328.7	328.8	328.9	329.0	328.7
132.5°	341.0	341.4	341.9	342.3	342.8	343.0	342.8	342.7	342.4	342.3	342.3
135°	361.1	361.6	362.1	362.6	363.1	363.2	363.1	362.9	362.7	362.6	362.4
137.5°	379.6	380.0	380.4	380.9	381.3	381.5	381.3	381.2	381.0	380.8	380.9
140°	391.7	391.8	392.0	392.2	392.3	392.4	392.3	392.2	392.2	392.1	392.2
142.5°	402.6	402.8	402.8	402.9	403.0	403.1	403.2	403.3	403.5	403.6	403.6
145°	418.7	418.8	419.0	419.1	419.3	419.4	419.4	419.4	419.4	419.4	419.5
147.5°	432.7	432.6	432.6	432.5	432.5	432.5	432.7	432.8	432.8	432.9	433.0
150°	441.5	441.3	441.2	441.0	440.8	440.8	441.0	441.2	441.3	441.5	441.6
152.5°	450.0	449.7	449.3	449.0	448.6	448.5	448.7	448.8	449.0	449.1	449.3
155°	461.1	460.6	460.1	459.6	459.1	458.9	459.1	459.3	459.4	459.6	459.8
157.5°	469.5	469.2	469.0	468.6	468.3	468.2	468.2	468.2	468.2	468.3	468.6
160°	475.4	474.9	474.4	473.9	473.4	473.3	473.4	473.4	473.5	473.6	473.9
162.5°	480.1	479.6	479.2	478.7	478.2	478.0	478.1	478.2	478.3	478.3	478.7
165°	486.5	486.0	485.5	485.0	484.5	484.3	484.4	484.5	484.5	484.6	485.1
167.5°	491.2	490.7	490.2	489.7	489.2	488.9	489.0	489.1	489.2	489.3	489.9
170°	493.9	493.3	492.7	492.1	491.5	491.3	491.4	491.5	491.5	491.6	492.3
172.5°	495.6	495.0	494.5	493.9	493.3	493.2	493.3	493.4	493.6	493.7	494.3
175°	497.6	497.1	496.6	496.1	495.6	495.4	495.5	495.5	495.6	495.7	496.4
177.5°	498.5	498.1	497.7	497.3	496.8	496.7	496.8	496.8	496.9	497.0	497.4
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	24.2	24.3	24.4	24.3	23.9	23.6	23.2	22.9
90°	6.7	7.1	7.5	7.9	8.2	8.4	8.6	8.9
92.5°	6.7	7.1	7.5	7.8	7.9	8.1	8.2	8.2
95°	6.7	7.1	7.5	7.7	7.7	7.7	7.7	7.7
97.5°	13.5	11.3	8.9	7.7	7.7	7.7	7.7	7.7
100°	39.8	27.6	15.3	9.0	8.7	8.4	8.1	7.7
102.5°	77.3	74.9	72.6	68.7	63.1	57.6	51.9	46.4
105°	109.9	109.9	109.9	109.9	109.8	109.7	109.7	109.6
107.5°	139.2	139.2	139.2	139.1	138.8	138.6	138.4	138.1
110°	158.1	157.8	157.6	157.5	157.6	157.7	157.8	157.8



TEST NUMBER: P333434-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.8	176.5	176.3	176.0	175.9	175.8	175.7	175.5
115°	205.1	204.8	204.5	204.1	203.6	203.1	202.6	202.1
117.5°	232.4	232.0	231.6	231.3	231.1	230.9	230.6	230.5
120°	250.1	250.0	249.8	249.5	249.1	248.7	248.3	247.9
122.5°	266.9	266.8	266.6	266.3	265.8	265.3	264.9	264.4
125°	291.5	291.1	290.8	290.5	290.2	290.0	289.8	289.5
127.5°	313.9	313.7	313.6	313.2	312.5	311.9	311.3	310.7
130°	328.5	328.2	328.0	327.7	327.3	326.9	326.4	326.0
132.5°	342.2	342.1	342.1	341.9	341.4	341.0	340.6	340.2
135°	362.2	362.1	361.9	361.6	361.1	360.6	360.1	359.6
137.5°	380.9	381.0	381.0	380.8	380.3	379.9	379.5	379.1
140°	392.4	392.6	392.7	392.6	392.1	391.6	391.1	390.6
142.5°	403.7	403.7	403.7	403.5	403.0	402.5	402.0	401.5
145°	419.6	419.6	419.7	419.5	419.0	418.5	418.0	417.5
147.5°	433.2	433.3	433.3	433.1	432.5	431.9	431.3	430.7
150°	441.8	442.0	442.1	441.9	441.2	440.6	439.9	439.3
152.5°	449.5	449.6	449.8	449.6	449.0	448.4	447.8	447.3
155°	460.1	460.3	460.6	460.3	459.7	459.0	458.4	457.7
157.5°	468.8	469.0	469.3	469.1	468.5	467.8	467.2	466.5
160°	474.3	474.6	474.9	474.7	474.1	473.4	472.8	472.1
162.5°	479.2	479.7	480.1	480.0	479.3	478.6	477.8	477.1
165°	485.7	486.2	486.7	486.6	485.9	485.2	484.5	483.9
167.5°	490.5	491.1	491.6	491.6	490.8	490.1	489.3	488.6
170°	492.9	493.7	494.3	494.2	493.5	492.8	492.0	491.3
172.5°	494.9	495.5	496.1	496.0	495.3	494.6	493.8	493.1
175°	497.0	497.7	498.3	498.3	497.6	496.8	496.1	495.4
177.5°	497.9	498.3	498.8	498.8	498.2	497.7	497.2	496.7
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6

(END OF REPORT)