

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333030-940

Luminaire Tested: **S124RDIW-S350D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333030-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5426.6 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	1.0
10°-20°	144.4	2.7
20°-30°	208.5	3.8
30°-40°	236.4	4.4
40°-50°	228.2	4.2
50°-60°	189.8	3.5
60°-70°	131.1	2.4
70°-80°	66.4	1.2
80°-90°	21.5	0.4
90°-100°	98.6	1.8
100°-110°	292.2	5.4
110°-120°	495.9	9.1
120°-130°	653.9	12.0
130°-140°	734.3	13.5
140°-150°	721.6	13.3
150°-160°	606.9	11.2
160°-170°	403.8	7.4
170°-180°	141.4	2.6
0°-30°	404.7	7.5
0°-40°	641.0	11.8
0°-60°	1059.1	19.5
0°-90°	1278.0	23.6
90°-120°	886.7	16.3
90°-150°	2996.4	55.2
90°-180°	4149.0	76.5
0°-180°	5426.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	4	16	25	32	35	6
95°	69	80	88	91	91	77
105°	270	271	275	279	282	286
115°	504	504	502	501	500	497
125°	734	734	733	731	728	654
135°	947	954	954	952	948	732
145°	1151	1155	1156	1155	1152	720
155°	1318	1318	1317	1321	1317	606
165°	1435	1432	1429	1436	1432	404
175°	1493	1487	1486	1493	1486	142
180°	1495	1495	1495	1495	1495	



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	8.5	8.4	8.4	8.4	8.3	8.5	8.8	9.2	9.5	9.8	10.1
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	24.8	28.0	31.2	34.4	37.7	40.0	41.5	42.9	44.3	45.8	46.7
95°	69.4	71.7	74.0	76.3	78.6	80.7	82.5	84.3	86.1	87.9	88.6
97.5°	121.2	123.1	124.9	126.7	128.6	130.5	132.7	134.8	136.9	139.0	139.9
100°	161.9	162.9	164.0	165.0	166.0	167.6	170.0	172.3	174.6	176.9	177.5
102.5°	204.5	204.9	205.3	205.7	206.1	207.3	209.5	211.6	213.7	215.8	216.5
105°	269.5	269.7	270.0	270.2	270.5	271.1	272.2	273.2	274.2	275.3	276.0
107.5°	337.7	338.0	338.3	338.6	338.9	339.1	339.3	339.5	339.7	339.7	340.5
110°	384.0	384.4	385.0	385.5	386.0	386.1	385.8	385.6	385.4	385.1	384.6



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.0	432.1	432.2	432.4	432.5	432.3	431.9	431.3	430.9	430.4	430.3
115°	504.2	504.2	504.2	504.2	504.2	504.0	503.5	502.9	502.4	501.9	501.7
117.5°	572.2	572.4	572.7	572.8	573.0	572.9	572.6	572.2	571.9	571.5	570.6
120°	617.5	618.6	619.6	620.6	621.6	621.8	621.0	620.3	619.5	618.7	617.4
122.5°	664.7	665.1	665.6	665.9	666.4	666.4	666.0	665.7	665.3	664.9	664.1
125°	734.3	734.3	734.3	734.3	734.3	734.2	734.0	733.7	733.4	733.2	732.6
127.5°	797.5	798.3	799.1	799.8	800.6	800.8	800.3	800.0	799.5	799.1	798.6
130°	841.9	842.7	843.5	844.2	845.0	845.3	845.3	845.3	845.3	845.3	844.8
132.5°	887.3	887.8	888.3	888.9	889.5	889.7	889.5	889.2	889.0	888.9	888.3
135°	947.1	948.7	950.2	951.7	953.3	954.0	954.0	954.0	954.0	954.0	953.6
137.5°	1012.4	1013.1	1013.8	1014.5	1015.2	1015.8	1016.2	1016.6	1017.0	1017.4	1016.7
140°	1055.9	1056.3	1056.9	1057.4	1057.9	1058.1	1058.1	1058.1	1058.1	1058.1	1057.9
142.5°	1095.6	1096.1	1096.6	1097.2	1097.7	1097.8	1097.6	1097.4	1097.3	1097.0	1097.0
145°	1150.7	1151.7	1152.7	1153.8	1154.8	1155.4	1155.7	1155.9	1156.2	1156.5	1156.2
147.5°	1205.2	1206.5	1207.7	1209.0	1210.1	1210.7	1210.5	1210.3	1210.1	1209.9	1209.7
150°	1238.6	1239.6	1240.6	1241.6	1242.7	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1
152.5°	1270.0	1270.6	1271.2	1271.8	1272.5	1272.9	1273.1	1273.3	1273.5	1273.7	1274.3
155°	1318.3	1318.3	1318.3	1318.3	1318.3	1318.2	1317.9	1317.7	1317.4	1317.2	1318.2
157.5°	1359.1	1358.6	1358.2	1357.6	1357.2	1356.9	1356.9	1356.8	1356.8	1356.7	1357.5
160°	1383.1	1382.9	1382.6	1382.3	1382.1	1381.8	1381.5	1381.3	1381.1	1380.8	1381.5
162.5°	1405.3	1404.6	1404.0	1403.3	1402.7	1402.2	1401.9	1401.7	1401.4	1401.1	1402.6
165°	1435.1	1434.4	1433.6	1432.8	1432.1	1431.5	1430.9	1430.4	1429.9	1429.3	1430.9
167.5°	1458.0	1457.0	1455.9	1454.8	1453.8	1453.2	1453.3	1453.3	1453.4	1453.4	1455.0
170°	1471.0	1469.7	1468.5	1467.1	1465.9	1465.3	1465.6	1465.9	1466.2	1466.3	1467.9
172.5°	1480.2	1479.2	1478.1	1477.0	1476.0	1475.4	1475.5	1475.5	1475.6	1475.6	1477.4
175°	1493.0	1491.7	1490.4	1489.2	1487.8	1487.0	1486.8	1486.6	1486.3	1486.0	1487.8
177.5°	1497.1	1496.1	1495.0	1494.1	1493.0	1492.5	1492.5	1492.5	1492.5	1492.5	1494.0
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	10.3	10.5	10.8	11.0	11.1	11.3	11.5	11.7
90°	28.5	30.1	31.6	32.6	33.2	33.7	34.2	34.7
92.5°	47.6	48.6	49.5	50.1	50.4	50.7	51.0	51.4
95°	89.4	90.2	91.0	91.4	91.4	91.4	91.4	91.4
97.5°	140.9	141.8	142.7	143.2	143.2	143.2	143.2	143.2
100°	178.0	178.5	179.0	179.2	179.2	179.2	179.2	179.2
102.5°	217.2	217.9	218.6	219.1	219.4	219.5	219.7	220.0
105°	276.8	277.6	278.3	279.1	279.8	280.6	281.4	282.1
107.5°	341.2	341.9	342.7	343.0	343.0	342.9	342.9	342.8
110°	384.1	383.5	383.1	383.2	384.0	384.7	385.5	386.3



TEST NUMBER: P333030-940

CATALOG NUMBER: S124RDIW-S350D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	430.3	430.2	430.0	430.1	430.2	430.3	430.5	430.7
115°	501.4	501.1	500.9	500.6	500.3	500.1	499.8	499.6
117.5°	569.8	568.9	568.0	567.3	566.8	566.3	565.8	565.3
120°	616.2	614.8	613.6	613.1	613.7	614.2	614.7	615.2
122.5°	663.2	662.4	661.5	660.6	659.6	658.7	657.8	656.8
125°	732.2	731.6	731.1	730.6	730.1	729.6	729.1	728.5
127.5°	798.1	797.5	797.0	796.6	796.2	795.8	795.3	795.0
130°	844.4	843.8	843.3	842.6	841.5	840.4	839.5	838.4
132.5°	887.8	887.3	886.8	886.4	885.9	885.5	885.1	884.7
135°	953.1	952.5	952.0	951.4	950.6	949.9	949.0	948.2
137.5°	1016.1	1015.5	1014.8	1014.5	1014.7	1014.9	1014.9	1015.1
140°	1057.7	1057.4	1057.1	1056.9	1056.6	1056.3	1056.1	1055.9
142.5°	1096.9	1096.9	1096.8	1096.7	1096.7	1096.6	1096.6	1096.5
145°	1155.9	1155.7	1155.4	1154.9	1154.1	1153.3	1152.6	1151.8
147.5°	1209.4	1209.2	1209.1	1208.8	1208.5	1208.3	1208.1	1207.8
150°	1243.1	1243.1	1243.1	1243.0	1242.8	1242.5	1242.2	1242.1
152.5°	1275.0	1275.6	1276.2	1276.1	1275.5	1274.8	1274.2	1273.5
155°	1319.3	1320.3	1321.3	1321.3	1320.3	1319.3	1318.2	1317.2
157.5°	1358.3	1359.1	1359.9	1359.8	1358.9	1358.0	1357.2	1356.3
160°	1382.3	1383.1	1383.8	1383.6	1382.3	1381.1	1379.7	1378.5
162.5°	1403.9	1405.3	1406.7	1406.8	1405.4	1404.2	1402.9	1401.6
165°	1432.4	1434.0	1435.6	1435.8	1434.8	1433.7	1432.7	1431.6
167.5°	1456.5	1458.0	1459.6	1459.6	1457.9	1456.3	1454.8	1453.2
170°	1469.5	1471.0	1472.6	1472.4	1470.6	1468.8	1467.0	1465.3
172.5°	1479.1	1480.9	1482.6	1482.6	1480.8	1479.0	1477.2	1475.4
175°	1489.6	1491.4	1493.3	1493.3	1491.4	1489.6	1487.8	1486.0
177.5°	1495.4	1496.8	1498.3	1498.2	1496.6	1494.9	1493.3	1491.6
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3

(END OF REPORT)